

# Coaxial Directional Coupler

## ZEDC-15-2B

50Ω

1 to 1000 MHz



CASE STYLE: V37

Connectors	Model	Price	Qty.
SMA	ZEDC-15-2B	\$64.95 ea.	(1-9)

### Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

### Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

### Features

- wideband, 1 to 1000 MHz
- excellent mainline loss, 0.8 dB typ.
- excellent directivity, 30 dB typ.
- rugged shielded case

### Applications

- VHF/UHF
- instrumentation
- communication receivers & transmitters
- cellular


### Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS <sup>1</sup> (dB)				DIRECTIVITY (dB)			VSWR (:1)	POWER INPUT (W)					
	Nom.	Flatness	L		M		U		L		M	U	L	MU		
f <sub>L</sub> -f <sub>U</sub>			Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Max.	
1-1000	15±0.5	±0.5	0.5	1.4	0.8	1.2	1.0	1.4	35	30	30	20	25	15	1.5	3.0

L = low range [f<sub>L</sub> to 10 f<sub>L</sub>] M = mid range [10 f<sub>L</sub> to f<sub>U</sub>/2] U = upper range [f<sub>U</sub>/2 to f<sub>U</sub>]

1. Mainline loss includes theoretical power loss at coupled port.

### Outline Drawing




### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.83	.83	.75	.37	.42	1.25	.10
21.08	21.08	19.05	9.40	10.67	31.75	2.54
H	J	K	L	M	N	wt
1.050	.10	.640	.21	.106	.06	grams
26.67	2.54	16.26	5.33	2.69	1.52	22.0


### Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		Cpl
				In	Out	
1.00	0.89	14.88	79.23	20.86	18.52	18.59
5.00	0.62	14.60	77.98	28.31	22.92	22.83
9.00	0.60	14.58	75.18	30.07	23.46	23.42
96.00	0.68	14.64	47.38	28.75	22.70	22.81
248.00	0.72	14.68	36.05	27.13	22.32	22.74
420.00	0.79	14.71	29.08	25.36	21.07	22.68
520.00	0.84	14.73	26.18	24.45	19.92	22.58
640.00	0.91	14.73	23.49	23.56	18.30	22.45
840.00	1.06	14.76	20.21	22.53	15.42	22.17
1000.00	1.15	14.70	18.59	22.05	13.20	21.93


ZEDC-15-2B MAINLINE LOSS




ZEDC-15-2B COUPLING & DIRECTIVITY



ZEDC-15-2B RETURN LOSS



### Electrical Schematic



\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

For detailed performance specs & shipping online see web site

**Mini-Circuits**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at [minicircuits.com](http://minicircuits.com)  
IF/RF MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp).

REV. A  
M119986  
ZEDC-15-2B  
WZ/TD/CP/AM  
090915