

Coaxial Directional Coupler

50Ω

0.1 to 250 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

INPUT	3
OUTPUT	2
COUPLED	1


Features

- excellent mainline loss, 0.5 dB typ.
- rugged shielded case

Applications

- HF/VHF
- amateur radio
- instrumentation

ZMDC-30-1+



Generic photo used for illustration purposes only
CASE STYLE: M21


Connectors Model

SMA ZMDC-30-1+
BRACKET (OPTION "B")
BRACKET (OPTION "BR")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.50	1.13	1.00	.50	.155	2.345	.138	.987
38.10	28.70	25.40	12.70	3.94	59.56	3.51	25.07
J	K	L	M	N	P	S	wt
2.50	.10	.31	.75	1.19	.66	.150	grams
63.50	2.54	7.87	19.05	30.23	16.76	3.81	40.0

Directional Coupler Electrical Specifications




FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)	
			L		M		U		L		M		U				
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.
0.1-250	30±0.5	±0.5	0.4	0.9	0.5	0.8	0.55	0.85	23	18	20	15	17	10	1.5	1.0	3.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
0.10	0.74	30.77	40.14	12.25	12.19	31.41
0.50	0.38	30.66	40.18	23.93	23.16	43.69
0.90	0.34	30.68	40.64	26.86	25.57	46.63
24.00	0.20	30.67	37.39	37.30	29.40	21.95
52.00	0.22	30.68	35.22	31.72	28.95	21.94
89.00	0.24	30.72	33.59	27.65	27.78	21.97
132.00	0.27	30.80	30.45	24.51	26.44	22.01
169.00	0.29	30.87	29.99	22.53	24.92	22.09
214.00	0.32	30.97	28.18	20.61	23.40	22.22
250.00	0.35	31.09	28.60	19.35	22.21	22.35



Electrical Schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
ECO-025937
ZMDC-30-1+
MCL NY
250707
Page 1 of 1