# Coaxial **Wideband Amplifier**

**50**Ω **20 to 6000 MHz** 

## **The Big Deal**

- Ultra wideband
- High dynamic range: +19dBm P1dB compression +35dBm Output IP3



ZX60-V82+

CASE STYLE: GC957

## **Product Overview**

The ZX60-V82+ (RoHS compliant) is a very compact wideband amplifier covering 20 to 6000MHz with 13.5dB gain (at 2GHz). Housed in a rugged, cost effective unibody chassis, this amplifier supports a wide variety of applications requiring moderate power output, low distortion and 50 ohm matched input/output ports.

## **Key Features**

Feature	Advantages					
Ultra Wide band high dynamic range	The ZX60-V82+ covers a wide spectrum of application frequencies from VHF through 'C' band. When combined with the output power and IP3, this amplifier supports a broad array of systems and test applications.					
Well Matched input / output ports	With typical input VSWR of 1.3:1 and output VSWR of 1.5:1 at 2GHz, the ZX60-V82+ can be used in cascade with many components and maintain minimal interaction or reflections.					
Very small size, 0.75" x 0.75'	The unique unibody construction enables the ZX60-V82+ to be used in compact designs.					
Unconditionally stable	No adverse effects due to loading of the input and output ports.					

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and termedies thereunder, please wist Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.js



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# Coaxial Wideband Amplifier

20 to 6000 MHz

#### 50Ω

#### Features

- · Wideband, 20 to 6000 MHz
- Output power at 1dB compression, +19 dBm typ.
- · Good output IP3, 35 dBm typ.
- Good VSWR
- · Unconditionally stable
- Protected by US patents 6,790,049 & 6,943,629

## **Applications**

- Base station infrastructure
- · CATV & DBS MMDS & wireless LAN
- LTE Buffer amplifier
- PCS
- Test equipment

### Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units	
Frequency Range		20		6000	MHz	
	100	13.5	15.2	16.8		
	1000		14.7			
Gain	2000	12.0	13.5	15.2	dB	
Gain	3000		12.3		UD UD	
	4000	9.5	11.4	13.0		
	6000		9.1			
	100	17.0	19.0			
	1000	17.5	19.5		dBm	
Output Dower at 1dP compression	2000	18.0	20.0			
Output Power at 1dB compression	3000		19.7		u Dini	
	4000		19.4			
	6000		17.5			
	100		6.5	8.0		
	1000		6.7			
Noise Figure	2000		6.8	8.4	dB	
Noise Figure	3000		6.9			
	4000		7.0			
	6000		7.7			
	100		38.5			
	1000		36.5		dBm	
Output third and an intersect a sint	2000	33.0	35.0			
Output third order intercept point	3000		34.0			
	4000		33.5			
	6000		31.0			
	100		1.10			
	1000		1.15			
Instant VOWD	2000		1.30	1.5	:1	
Input VSWR	3000		1.30		:1	
	4000		1.30			
	6000		1.70			
	100		1.30			
	1000		1.40			
Output VOMP	2000		1.50	1.9		
Output VSWR	3000		1.70		:1	
	4000		1.70			
	6000		2.30			
Active Directivity	20-6000		11		dB	
DC Supply Voltage		4.8	5.0	5.2	V	
DC Supply Current			100	120	mA	

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the exclusive rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and memodies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. B M152326 RTB-88/1 ZX60-V82+ RAV 150818 Page 2 of 4

## **Mini-Circuits**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com





Case Style: GC957 Connectors Model ZX60-V82-S+ SMA

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Maximum Ratings**

Parameter	Ratings					
Operating Temperature	-40°C to 85°C Case					
Storage Temperature	-55°C to 100°C					
DC Voltage	5.5 V					
Input RF Power (no damage)	20 dBm					
Power Consumption	840 mW					
Dermanant demoge may easur if any of these limits are exceeded						

Permanent damage may occur if any of these limits are exceeded.

#### **Outline Drawing**



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note  $\underline{AN-40-10}$ .

### Outline Dimensions (inch )


А	В	С	D	Е	F	G	н	J	к	L	М	Ν	Р	Q	R	wt.
0.74	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.18	1.00	.37	.18	.106	grams
18.80	19.05	11.68	29.97	1.02	4.32	11.43	14.99	8.38	5.33	5.59	4.57	25.40	9.40	4.57	2.69	23.0

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

# Typical Performance Data/Curves

## **ZX60-V82+**

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR IN (:1)	VSWR OUT (:1)	POWER OUT @ 1dB COMPRESSION (dBm)	OUTPUT IP3 (dBm)	NF (dB)
			(.1)	(.1)	(uBill)	(ubiii)	
20	14.83	9.70	1.19	1.48	18.46	38.01	6.26
100	15.15	9.03	1.07	1.27	19.23	38.50	6.51
420	15.06	9.18	1.08	1.27	19.50	37.95	6.65
1000	14.66	9.33	1.15	1.35	19.51	36.39	6.73
1220	14.43	9.46	1.18	1.39	19.57	36.12	6.74
1420	14.21	9.61	1.20	1.42	19.67	35.86	6.74
1620	13.96	9.79	1.22	1.46	19.55	35.71	6.75
2000	13.49	10.09	1.26	1.53	19.81	35.12	6.77
2220	13.21	10.23	1.28	1.58	19.80	34.93	6.80
2420	12.97	10.44	1.29	1.61	19.70	34.67	6.83
2620	12.72	10.61	1.29	1.64	19.87	34.48	6.84
3000	12.30	10.92	1.30	1.69	19.71	34.27	6.88
3420	11.88	11.15	1.29	1.72	19.47	33.61	6.91
4000	11.36	11.48	1.25	1.71	19.40	33.64	7.00
4420	11.03	11.69	1.20	1.72	19.14	33.14	7.08
5000	10.48	12.18	1.20	1.83	18.72	32.41	7.27
5420	9.94	12.78	1.34	2.05	18.36	31.90	7.38
6000	8.96	14.10	1.68	2.44	17.34	31.22	7.65
6620	7.66	15.87	2.11	2.81	16.55	30.43	7.90
7000	6.73	17.14	2.38	2.92	16.35	30.15	8.19



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document of Mini-Circuit's applicable established test performance and quality attributes and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document of Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## **Mini-Circuits**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com