

Non-Catalog Model

Frequency Mixer

Level 7 (LO Power +7 dBm)

LMX-149

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BB48

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	10		1500	MHz
	RF (fL to fU)	10		1500	MHz
	IF	0		1500	MHz
Conversion Loss	mid band			7.0	dB
	Total Range			9.0	dB
LO-RF Isolation	Low Range	40	55		dB
	Mid Range	35	45		dB
	Upper Range	20	30		dB
LO-IF Isolation	Low Range	40	50		dB
	Mid Range	25	40		dB
	Upper Range	12	20		dB
1 dB Comp. Input Power			+1		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]


Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	5
IF	4
GROUND	1, 2, 3, 6, 7

Electrical Schematics



Frequency Mixer

LMX-149

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+7	+10	+13		+7	+10	+13	+7	+10	+13
10.0	40.0	5.89	5.55	5.41	10.0	64.0	67.0	65.3	64.0	67.0	63.8
20.0	50.0	5.95	5.61	5.44	20.0	64.0	61.1	59.6	64.0	60.0	58.0
145.5	115.5	5.91	5.65	5.54	145.5	46.3	45.2	44.1	44.0	43.2	42.6
190.6	160.6	5.96	5.73	5.59	190.6	44.5	43.1	42.0	41.8	41.3	40.6
235.8	205.8	6.02	5.77	5.60	235.8	43.2	41.7	40.6	40.4	40.0	39.3
326.1	296.1	5.90	5.68	5.53	326.1	41.0	39.5	38.6	38.2	37.9	37.2
416.4	386.4	6.16	5.87	5.68	416.4	39.2	38.1	37.2	36.2	35.9	35.4
500.0	470.0	6.08	5.77	5.56	500.0	38.1	37.3	36.7	34.5	34.6	34.6
551.8	521.8	6.07	5.79	5.59	551.8	37.4	36.7	36.2	33.5	33.6	33.3
642.1	612.1	6.19	5.89	5.65	642.1	36.8	36.5	36.1	31.9	32.2	32.2
732.4	702.8	6.45	6.08	5.81	732.4	36.8	37.0	36.7	30.5	31.3	31.4
822.7	792.7	6.68	6.26	5.93	822.7	36.8	37.1	37.3	29.1	30.1	31.1
913.0	883.3	7.15	6.56	6.16	913.0	37.0	37.2	37.5	28.5	29.3	29.7
1000.0	970.3	7.56	6.94	6.51	1000.0	37.5	37.6	37.9	28.4	29.1	29.9
1048.5	1018.6	7.69	7.22	6.77	1048.5	37.8	38.0	38.2	28.4	29.3	30.0
1138.8	1109.1	7.70	7.23	6.81	1138.8	38.3	38.8	38.9	28.1	29.1	29.8
1229.1	1199.1	7.74	7.24	6.82	1229.1	38.5	39.0	40.1	28.0	29.0	29.7
1319.4	1289.5	7.85	7.39	7.02	1319.4	38.5	38.9	39.0	28.2	28.9	29.7
1409.7	1380.0	7.99	7.38	7.05	1409.7	38.5	38.9	40.0	27.6	28.9	30.2
1500.0	1469.9	8.14	7.40	7.15	1500.0	39.6	40.1	40.3	28.9	29.6	31.0

REV. X1

LMX-149

060612

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

LMX-149

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)			LO/RF (MHz)	max. DC output (mV)	DC Offset (mV)
	@LO (dBm)			@LO (dBm)				@LO (dBm)			@LO (dBm)		
	+7	+10	+13	+7	+10	+13		+7	+10	+13	+10		
10.0	1.25	1.16	1.11	1.83	2.77	3.83	10.0	1.81	1.54	1.38	10.0	230.0	-0.08
50.0	1.20	1.10	1.03	1.89	2.94	4.19	50.0	1.78	1.53	1.38	20.0	229.4	-0.08
100.0	1.20	1.10	1.04	1.75	2.68	3.70	100.0	1.76	1.52	1.37	48.0	225.0	-0.09
145.5	1.20	1.10	1.06	1.77	2.62	3.52	145.5	1.73	1.52	1.37	50.0	224.9	-0.09
200.0	1.21	1.13	1.09	1.76	2.59	3.54	200.0	1.72	1.53	1.38	100.0	226.5	-0.09
280.9	1.23	1.17	1.14	1.83	2.54	3.50	280.9	1.69	1.52	1.40	162.2	228.7	-0.12
371.2	1.27	1.22	1.20	1.88	2.63	3.45	371.2	1.67	1.54	1.45	200.2	226.3	-0.16
461.5	1.31	1.30	1.28	2.00	2.83	3.56	461.5	1.65	1.55	1.50	276.3	234.0	-0.27
506.7	1.33	1.34	1.32	2.05	2.74	3.58	506.7	1.66	1.58	1.54	390.4	206.6	-0.53
597.0	1.39	1.41	1.40	2.21	2.80	3.67	597.0	1.65	1.62	1.60	466.5	210.3	-0.51
687.3	1.49	1.53	1.52	2.36	3.19	3.98	687.3	1.71	1.69	1.70	504.5	213.0	-0.58
777.6	1.62	1.66	1.66	2.55	3.30	4.11	777.6	1.76	1.76	1.75	580.6	217.2	-0.89
867.9	1.77	1.83	1.79	2.76	3.65	4.32	867.9	1.82	1.84	1.80	656.7	205.9	-1.08
958.2	1.97	2.03	2.00	3.03	3.80	4.46	958.2	1.88	1.92	1.87	770.8	189.7	-1.47
1003.3	2.08	2.17	2.12	3.11	3.93	4.39	1003.3	1.91	1.96	1.92	808.8	188.1	-1.63
1093.6	2.36	2.41	2.38	3.42	4.20	4.79	1093.6	1.92	1.98	1.94	884.9	193.9	-2.09
1183.9	2.52	2.63	2.58	3.55	4.18	4.72	1183.9	1.88	1.95	1.92	961.0	181.6	-2.31
1274.2	2.68	2.95	2.81	3.65	4.32	4.73	1274.2	1.82	1.90	1.86	1000.0	177.7	-2.13
1364.5	2.84	3.22	2.92	3.90	3.99	4.54	1364.5	1.76	1.82	1.76	1250.0	156.9	-2.29
1500.0	3.05	3.43	3.09	4.28	3.48	4.32	1500.0	1.69	1.72	1.64	1500.0	152.4	-2.17

REV. X1

LMX-149

060612

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR




LO VSWR



IF VSWR



Max. DC Output



REV. X1

LMX-149

060612

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

