



CERAMIC

# Low Pass Filter


## LFCN-630+

Mini-Circuits

50Ω DC<sup>1</sup> to 630 MHz

### FEATURES

- Excellent power handling, 8.5 W
- Small size
- 7 sections
- Temperature stable
- LTCC construction
- Protected by U.S. Patent 6,943,646



Generic photo used for illustration purposes only

CASE STYLE: FV1206

### APPLICATIONS

- Harmonic rejection
- VHF/UHF transmitters/receivers

**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance.  
 See our website for methodologies and qualifications

### ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT 25°C

| Parameter | F#             | Frequency (MHz) | Min.      | Typ. | Max. | Units |    |
|-----------|----------------|-----------------|-----------|------|------|-------|----|
| Passband  | Insertion Loss | DC-F1           | DC-630    | —    | —    | 1.2   | dB |
|           | Freq. Cut-Off  | F2              | 830       | —    | 3.0  | —     | dB |
|           | VSWR           | DC-F1           | DC-630    | —    | 1.2  | —     | :1 |
| Stopband  | Rejection Loss | F3              | 1000      | 20   | —    | —     | dB |
|           |                | F4-F5           | 1050-3500 | —    | 40   | —     |    |
|           | VSWR           | F6              | 6000      | —    | 20   | —     | :1 |
|           |                | F3-F6           | 1000-6000 | —    | 20   | —     |    |


1. In Applications where DC isolation to ground is required, coupling capacitors are recommended to avoid DC leakage. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide >100 MOhm isolation to ground.
2. Measured on Mini-Circuits Characterization Test Board TB-LFCN-630+.

### ABSOLUTE MAXIMUM RATINGS


| Parameter                   | Ratings             |
|-----------------------------|---------------------|
| Operating Temperature       | -55°C to +100°C     |
| Storage Temperature         | -55°C to +100°C     |
| RF Power Input <sup>3</sup> | 8.5 W max. at +25°C |

3. Passband rating, derate linearly to 3.5 W at +100°C ambient. Permanent damage may occur if any of these limits are exceeded.

### TYPICAL FREQUENCY RESPONSE



### FUNCTIONAL SCHEMATIC





CERAMIC

# Low Pass Filter

# LFCN-630+

Mini-Circuits


50Ω DC<sup>1</sup> to 630 MHz

### PIN CONNECTIONS

|        |     |
|--------|-----|
| RF IN  | 1   |
| RF OUT | 3   |
| GROUND | 2,4 |

PRODUCT MARKING: R4


DEMO BOARD MCL P/N: TB-LFCN-630+  
SUGGESTED PCB LAYOUT (PL-137)




- NOTES:**
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### OUTLINE DRAWING



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

### OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F    | G    |       |
|------|------|------|------|------|------|------|-------|
| .126 | .063 | .037 | .020 | .032 | .009 | .169 |       |
| 3.20 | 1.60 | 0.94 | 0.51 | 0.81 | 0.23 | 4.29 |       |
| H    | J    | K    | L    | M    | N    | P    | wt    |
| .087 | .024 | .122 | .024 | .087 | .012 | .071 | grams |
| 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020  |

TAPE & REEL INFORMATION: F71



CERAMIC

# Low Pass Filter



## LFCN-630+

Mini-Circuits

50Ω DC<sup>1</sup> to 630 MHz

### TYPICAL PERFORMANCE DATA AT +25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 1               | 0.05                | 1.01      |
| 100             | 0.18                | 1.06      |
| 630             | 0.75                | 1.13      |
| 700             | 0.95                | 1.20      |
| 830             | 2.02                | 1.39      |
| 900             | 7.06                | 4.64      |
| 955             | 16.49               | 11.38     |
| 1000            | 25.84               | 15.96     |
| 1040            | 35.54               | 18.50     |
| 1130            | 66.95               | 22.29     |
| 2015            | 74.70               | 43.44     |
| 3000            | 51.23               | 49.64     |
| 3500            | 45.12               | 45.72     |
| 5000            | 30.26               | 35.46     |
| 6000            | 23.74               | 25.94     |



#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# Ceramic Low Pass Filter

# LFCN-630+

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS<br>(dB) |          |           | INPUT RETURN LOSS<br>(dB) |          |           | OUTPUT RETURNLOSS<br>(dB) |          |           |
|----------------|------------------------|----------|-----------|---------------------------|----------|-----------|---------------------------|----------|-----------|
|                | @ -55° C               | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C |
| 1              | 0.02                   | 0.05     | 0.07      | 47.63                     | 46.06    | 45.03     | 47.60                     | 46.06    | 45.00     |
| 50             | 0.11                   | 0.14     | 0.16      | 34.19                     | 32.62    | 31.86     | 34.16                     | 32.65    | 31.83     |
| 100            | 0.15                   | 0.18     | 0.21      | 32.09                     | 31.11    | 30.56     | 33.08                     | 31.97    | 31.36     |
| 630            | 0.60                   | 0.75     | 0.87      | 24.85                     | 24.48    | 23.91     | 25.48                     | 25.28    | 24.83     |
| 700            | 0.77                   | 0.95     | 1.12      | 21.69                     | 21.02    | 20.31     | 23.20                     | 22.64    | 22.00     |
| 830            | 1.62                   | 2.02     | 2.40      | 16.41                     | 15.67    | 14.80     | 20.51                     | 19.65    | 18.39     |
| 840            | 1.84                   | 2.29     | 2.74      | 14.16                     | 13.40    | 12.56     | 16.79                     | 15.97    | 14.93     |
| 865            | 2.82                   | 3.49     | 4.18      | 8.88                      | 8.28     | 7.68      | 10.10                     | 9.53     | 8.91      |
| 900            | 5.97                   | 7.06     | 8.12      | 3.98                      | 3.80     | 3.63      | 4.69                      | 4.57     | 4.42      |
| 935            | 11.37                  | 12.72    | 13.99     | 1.90                      | 1.97     | 2.01      | 2.43                      | 2.57     | 2.65      |
| 955            | 15.07                  | 16.49    | 17.81     | 1.41                      | 1.53     | 1.61      | 1.88                      | 2.07     | 2.20      |
| 970            | 18.01                  | 19.47    | 20.83     | 1.18                      | 1.32     | 1.42      | 1.64                      | 1.84     | 1.98      |
| 1000           | 24.29                  | 25.84    | 27.29     | 0.95                      | 1.09     | 1.20      | 1.34                      | 1.54     | 1.70      |
| 1020           | 28.82                  | 30.47    | 32.01     | 0.87                      | 1.01     | 1.12      | 1.21                      | 1.42     | 1.57      |
| 1040           | 33.74                  | 35.54    | 37.24     | 0.81                      | 0.94     | 1.05      | 1.12                      | 1.33     | 1.48      |
| 1050           | 36.43                  | 38.34    | 40.15     | 0.78                      | 0.91     | 1.02      | 1.09                      | 1.29     | 1.44      |
| 1065           | 40.84                  | 42.95    | 44.98     | 0.74                      | 0.88     | 0.98      | 1.04                      | 1.23     | 1.38      |
| 1130           | 70.27                  | 66.95    | 64.94     | 0.65                      | 0.78     | 0.88      | 0.87                      | 1.05     | 1.19      |
| 1250           | 52.87                  | 52.91    | 52.91     | 0.54                      | 0.67     | 0.78      | 0.67                      | 0.84     | 0.96      |
| 1360           | 48.09                  | 48.49    | 48.88     | 0.48                      | 0.61     | 0.71      | 0.55                      | 0.69     | 0.81      |
| 1625           | 54.79                  | 55.33    | 55.76     | 0.36                      | 0.49     | 0.60      | 0.37                      | 0.50     | 0.59      |
| 2015           | 71.76                  | 74.70    | 79.60     | 0.26                      | 0.40     | 0.52      | 0.25                      | 0.36     | 0.44      |
| 2500           | 54.64                  | 54.20    | 54.19     | 0.23                      | 0.36     | 0.46      | 0.17                      | 0.28     | 0.35      |
| 3000           | 47.67                  | 51.23    | 51.12     | 0.25                      | 0.35     | 0.44      | 0.21                      | 0.29     | 0.35      |
| 3500           | 44.31                  | 45.12    | 46.33     | 0.26                      | 0.38     | 0.47      | 0.17                      | 0.29     | 0.36      |
| 4000           | 43.70                  | 42.34    | 42.46     | 0.24                      | 0.39     | 0.48      | 0.15                      | 0.29     | 0.39      |
| 4500           | 34.74                  | 35.87    | 36.82     | 0.26                      | 0.39     | 0.53      | 0.22                      | 0.35     | 0.47      |
| 5000           | 29.02                  | 30.26    | 31.04     | 0.37                      | 0.49     | 0.65      | 0.33                      | 0.45     | 0.60      |
| 5400           | 24.78                  | 22.43    | 23.85     | 1.49                      | 1.92     | 1.38      | 0.34                      | 0.56     | 0.65      |
| 6000           | 23.85                  | 23.74    | 24.70     | 0.50                      | 0.67     | 0.92      | 0.39                      | 0.55     | 0.72      |
| 6500           | 23.55                  | 23.95    | 24.28     | 0.43                      | 0.66     | 0.89      | 0.25                      | 0.45     | 0.62      |
| 7000           | 22.24                  | 22.42    | 22.45     | 0.47                      | 0.68     | 0.90      | 0.31                      | 0.49     | 0.66      |
| 7500           | 21.49                  | 21.62    | 21.97     | 0.58                      | 0.84     | 1.06      | 0.25                      | 0.44     | 0.60      |
| 8000           | 20.48                  | 20.87    | 20.92     | 0.59                      | 0.79     | 1.07      | 0.21                      | 0.37     | 0.54      |
| 9000           | 17.84                  | 18.13    | 18.05     | 0.85                      | 1.06     | 1.22      | 0.26                      | 0.52     | 0.75      |
| 10000          | 16.42                  | 16.41    | 16.32     | 0.86                      | 1.09     | 1.31      | 0.44                      | 0.77     | 1.05      |
| 11000          | 16.72                  | 17.28    | 17.81     | 0.79                      | 1.14     | 1.50      | 0.93                      | 1.37     | 1.78      |
| 12000          | 28.13                  | 29.41    | 31.11     | 3.20                      | 2.71     | 2.75      | 1.76                      | 2.26     | 2.61      |
| 14000          | 14.76                  | 15.59    | 16.48     | 1.77                      | 2.16     | 2.40      | 2.47                      | 2.87     | 3.41      |
| 16000          | 16.34                  | 16.48    | 17.40     | 4.05                      | 4.15     | 4.68      | 3.64                      | 3.73     | 3.95      |
| 18000          | 18.32                  | 17.01    | 17.60     | 9.63                      | 8.70     | 7.58      | 7.01                      | 11.23    | 16.94     |
| 20000          | 8.59                   | 9.08     | 9.82      | 6.52                      | 7.10     | 7.66      | 1.66                      | 2.20     | 2.75      |

REV. X1  
LFCN-630+  
080722  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE




### INPUT RETURN LOSS vs. TEMPERATURE




### OUTPUT RETURN LOSS vs. TEMPERATURE



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | M              | N              | P              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| FV1206 | .126<br>(3.20) | .063<br>(1.60) | .037<br>(0.94) | .020<br>(0.51) | .032<br>(0.81) | .009<br>(0.23) | .169<br>(4.29) | .087<br>(2.21) | .024<br>(0.61) | .122<br>(3.10) | .024<br>(0.61) | .087<br>(2.21) | .012<br>(0.30) | .071<br>(1.80) | .020     |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

1. Open style, ceramic base.
2. Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F71




ILLUSTRATION 1

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION           | DATE     | DR  | AUTH |
|-----|---------|-----------------------|----------|-----|------|
| OR  | M88634  | NEW RELEASE           | 08/28/03 | GF  | ABD  |
| A   | M102713 | ADDED "...WITH SMOBC" | 01/17/06 | MMG | IL   |
|     |         |                       |          |     |      |

SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION



- NOTES:**
- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" ± .0015".  
 COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

08/27/03

TOLERANCES ON:

CHECKED

AV

08/28/03

2 PL DECIMALS ±

APPROVED


ABD

08/28/03

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95




**Mini-Circuits®**

13 Neptune Avenue  
 Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

|                  |                     |                          |           |
|------------------|---------------------|--------------------------|-----------|
| SIZE<br>A        | CODE IDENT<br>15542 | DRAWING NO:<br>98-PL-137 | REV:<br>A |
| FILE:<br>98PL137 | SCALE:<br>10:1      | SHEET:<br>1 OF 1         |           |


# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition   | Reference/Spec   |
|----------------------------|---|--|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment  | Individual Model Data Sheet  |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability              | 10X Magnification   | J-STD-002, Para 4.2.5, Test S, 95% Coverage  |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A   |