

Plug-In

# Voltage Controlled Oscillator

POS-1060+


Linear Tuning 750 to 1060 MHz

## Features

- wide tuning range
- 3 dB modulation bandwidth 1 MHz, typ.
- low phase noise
- hermetically sealed

## Applications

- cellular up & down converters
- CATV distribution set top converters
- agile communications systems
- test instruments



CASE STYLE: A06

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications

| FREQUENCY (MHz) |      | POWER OUTPUT (dBm) | TUNING VOLTAGE (V) |      | PHASE NOISE (dBc/Hz)<br>SSB at offset frequencies:<br>Typ. |        |         |       | PULLING pk-pk @ 12 dB (MHz) | PUSHING (MHz/V) | TUNING SENSITIVITY (MHz/V) | HARMONICS (dBc) |      | 3 dB MODULATION BANDWIDTH (MHz) | DC OPERATING POWER      |                   |
|-----------------|------|--------------------|--------------------|------|------------------------------------------------------------|--------|---------|-------|-----------------------------|-----------------|----------------------------|-----------------|------|---------------------------------|-------------------------|-------------------|
| Min.            | Max. | Typ.               | Min.               | Max. | 1 kHz                                                      | 10 kHz | 100 kHz | 1 MHz | Typ.                        | Typ.            | Typ.                       | Typ.            | Max. | Typ.                            | V <sub>CC</sub> (volts) | Current (mA) Max. |
| 750             | 1060 | +12.0              | 1                  | 20   | -65                                                        | -90    | -112    | -132  | 50                          | 3.0             | 18-32                      | -11             | —    | 1.0                             | 8                       | 30                |

## Pin Connections


|             |           |
|-------------|-----------|
| RF OUT      | 2         |
| VCC         | 1         |
| V-TUNE      | 8         |
| GROUND      | 3,4,5,6,7 |
| CASE GROUND | 3,4,5,6,7 |

## Maximum Ratings

|                                                   |                |
|---------------------------------------------------|----------------|
| Operating Temperature                             | -55°C to 85°C  |
| Storage Temperature                               | -55°C to 100°C |
| Absolute Max. Supply Voltage (V <sub>CC</sub> )   | +10V           |
| Absolute Max. Tuning Voltage (V <sub>tune</sub> ) | +22V           |

all specifications: 50 ohm system  
Permanent damage may occur if any of these limits are exceeded.

## Outline Drawing



## Outline Dimensions (inch/mm)

| A      | B     | C     | D     | E     | F     | G    | H    | J     | K      | wt    |
|--------|-------|-------|-------|-------|-------|------|------|-------|--------|-------|
| .770   | .800  | .285  | .310  | .370  | .400  | .200 | .20  | .14   | .031   | grams |
| 19.558 | 20.32 | 7.239 | 7.874 | 9.398 | 10.16 | 5.08 | 5.08 | 3.556 | 0.7874 | 5.2   |


### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





# Performance Data & Curves


# POS-1060+



| V<br>TUNE | TUNING<br>SENS.<br>(MHz/V) | FREQUENCY (MHz) |         |         | POWER OUTPUT (dBm) |       |       |
|-----------|----------------------------|-----------------|---------|---------|--------------------|-------|-------|
|           |                            | -55°C           | +25°C   | +85°C   | -55°C              | +25°C | +85°C |
| 0.00      | 23.35                      | 667.98          | 660.15  | 652.46  | 11.14              | 10.85 | 10.25 |
| 2.00      | 19.99                      | 705.71          | 697.66  | 690.63  | 10.98              | 10.98 | 10.90 |
| 4.00      | 20.73                      | 749.19          | 741.35  | 732.14  | 12.00              | 11.56 | 11.00 |
| 6.00      | 24.32                      | 786.40          | 777.56  | 770.01  | 11.90              | 12.04 | 12.05 |
| 8.00      | 25.69                      | 841.58          | 833.68  | 826.97  | 12.52              | 12.45 | 12.15 |
| 10.00     | 26.61                      | 901.15          | 893.70  | 884.16  | 12.85              | 12.52 | 12.11 |
| 12.00     | 27.64                      | 959.47          | 949.31  | 938.49  | 12.63              | 12.33 | 12.14 |
| 14.00     | 27.49                      | 1002.41         | 994.54  | 986.85  | 12.48              | 12.54 | 12.51 |
| 16.00     | 23.00                      | 1052.01         | 1046.38 | 1037.38 | 12.20              | 12.00 | 11.60 |
| 18.00     | 25.88                      | 1092.75         | 1083.05 | 1067.83 | 11.49              | 11.64 | 11.86 |
| 20.00     | 14.94                      | 1138.66         | 1124.15 | 1108.01 | 12.03              | 11.92 | 11.49 |



| V<br>TUNE | HARMONICS (dBc) |        |        | FREQ. PUSHING<br>(MHz/V) |
|-----------|-----------------|--------|--------|--------------------------|
|           | F2              | F3     | F4     |                          |
| 0.00      | -26.45          | -28.96 | -36.75 | 1.45                     |
| 2.00      | -21.14          | -34.52 | -28.82 | 1.60                     |
| 4.00      | -17.10          | -35.34 | -27.13 | 1.73                     |
| 6.00      | -13.96          | -27.35 | -26.30 | 1.97                     |
| 8.00      | -12.30          | -23.93 | -26.93 | 2.04                     |
| 10.00     | -10.84          | -24.58 | -22.23 | 2.21                     |
| 12.00     | -9.60           | -19.71 | -20.91 | 2.46                     |
| 14.00     | -10.84          | -17.99 | -19.54 | 2.69                     |
| 16.00     | -10.78          | -14.74 | -19.27 | 2.79                     |
| 18.00     | -14.89          | -15.81 | -22.11 | 4.59                     |
| 20.00     | -20.96          | -14.73 | -18.43 | 3.52                     |



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Voltage Controlled Oscillator

POS-1060+

## Typical Performance Data

| V<br>TUNE | TUNE<br>SENS<br>(MHz/V) | FREQUENCY<br>(MHz) |        |        | POWER OUTPUT<br>(dBm) |       |       | HARMONICS<br>(dBc) |       |       | FREQ.<br>PUSH<br>(MHz/V) | FREQ<br>OFFSET<br>(KHz) | PHASE<br>NOISE<br>(dBc/Hz) |
|-----------|-------------------------|--------------------|--------|--------|-----------------------|-------|-------|--------------------|-------|-------|--------------------------|-------------------------|----------------------------|
|           |                         | -55°C              | +25°C  | +85°C  | -55°C                 | +25°C | +85°C | F2                 | F3    | F4    |                          |                         |                            |
| 2.0       | 19.99                   | 705.7              | 697.7  | 690.6  | 10.98                 | 10.98 | 10.90 | -21.1              | -34.5 | -28.8 | 1.60                     | 1                       | -65                        |
| 4.0       | 20.73                   | 749.2              | 741.4  | 732.1  | 12.00                 | 11.56 | 11.00 | -17.1              | -35.3 | -27.1 | 1.73                     | 10                      | -90                        |
| 6.0       | 24.32                   | 786.4              | 777.6  | 770.0  | 11.90                 | 12.04 | 12.05 | -14.0              | -27.4 | -26.3 | 1.97                     | 100                     | -112                       |
| 8.0       | 25.69                   | 841.6              | 833.7  | 827.0  | 12.52                 | 12.45 | 12.15 | -12.3              | -23.9 | -26.9 | 2.04                     | 1000                    | -132                       |
| 10.0      | 26.61                   | 901.2              | 893.7  | 884.2  | 12.85                 | 12.52 | 12.11 | -10.8              | -24.6 | -22.2 | 2.21                     |                         |                            |
| 12.0      | 27.64                   | 959.5              | 949.3  | 938.5  | 12.63                 | 12.33 | 12.14 | -9.6               | -19.7 | -20.9 | 2.46                     |                         |                            |
| 14.0      | 27.49                   | 1002.4             | 994.5  | 986.9  | 12.48                 | 12.54 | 12.51 | -10.8              | -18.0 | -19.5 | 2.69                     |                         |                            |
| 16.0      | 23.00                   | 1052.0             | 1046.4 | 1037.4 | 12.20                 | 12.00 | 11.60 | -10.8              | -14.7 | -19.3 | 2.79                     |                         |                            |
| 18.0      | 25.88                   | 1092.8             | 1083.1 | 1067.8 | 11.49                 | 11.64 | 11.86 | -14.9              | -15.8 | -22.1 | 4.59                     |                         |                            |
| 20.0      | 14.94                   | 1138.7             | 1124.2 | 1108.0 | 12.03                 | 11.92 | 11.49 | -21.0              | -14.7 | -18.4 | 3.52                     |                         |                            |

REV. X1  
POS-1060+  
070205  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Voltage Controlled Oscillator


POS-1060+

## Typical Performance Data



A01  
A04  
A05  
A06

## Outline Dimensions



| CASE# | A               | B               | C              | D               | E              | F               | G              | H             | J             | K             | WT,<br>GRAM |
|-------|-----------------|-----------------|----------------|-----------------|----------------|-----------------|----------------|---------------|---------------|---------------|-------------|
| A01   | .770<br>(19.56) | .800<br>(20.32) | .385<br>(9.78) | .400<br>(10.16) | .370<br>(9.40) | .400<br>(10.16) | .200<br>(5.08) | .20<br>(5.08) | .14<br>(3.56) | .031<br>(.79) | 5.2         |
| A04   |                 |                 | .200<br>(5.08) | .210<br>(5.33)  |                |                 |                |               |               |               | 3.7         |
| A05   |                 |                 | .240<br>(6.10) | .250<br>(6.35)  |                |                 |                |               |               |               | 3.7         |
| A06   |                 |                 | .285<br>(7.24) | .310<br>(7.87)  |                |                 |                |               |               |               | 5.2         |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Header material: C.R.S.  
Pin material: #52 alloy.  
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter  $\pm .005$  inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Moisture Resistance            | 10 cycles, 24 hours per cycle                                                                                                                                   | MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Resistance to Solder Heat      | 260°C for 10 seconds                                                                                                                                            | MIL-STD-202, Method 210, Condition B                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |
| Terminal Strength              | 4 1/2 Pound Pull                                                                                                                                                | MIL-STD-202, Method 211, Condition A                                                                 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification       | Test/Inspection Condition | Reference/Spec                       |
|---------------------|---------------------------|--------------------------------------|
| Gross Leak          | 125°C Bubble Test         | MIL-STD-202, Method 112, Condition D |
| Barometric Pressure | 100,000 Feet              | MIL-STD-202, Method 105, Condition D |