

Plug-In Frequency Mixer

Level 13 (LO Power +13 dBm) 0.025 to 200 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA


Permanent damage may occur if any of these limits are exceeded.

Pin Connections

LO	8
RF	1
IF	3,4 [^]
GROUND	2,5,6,7
CASE GROUND	2

[^] pins must be connected together externally

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K		
.200	.20	.14	.031		
5.08	5.08	3.56	0.79		

				wt	
				grams	
				5.2	

Features

- excellent conversion loss, 4.77 dB typ.
- high L-R isolation, 45 dB typ. L-I isolation, 40 dB typ.
- rugged welded construction
- hermetic

Applications

- VHF
- defense & federal communications
- FM broadcast radio

SRA-3MH+



Generic photo used for illustration purposes only

CASE STYLE: A01

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)					
LO/RF f_L - f_U	IF	Mid-Band m		Total Range Max.		L		M		U		L		M		U	
		$\bar{X}$	σ	Max.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
.025-200	DC-200	4.77	.07	7.5	8.5	60	50	45	35	35	25	45	35	40	30	30	20


1 dB COMP.: +9 dBm typ.

L = low range [f_L to 10 f_L]
m = mid band [$2f_L$ to $f_U/2$]
M = mid range [10 f_L to $f_U/2$]
U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
0.025	30.025	7.47	73.00	68.27	1.27	2.12
5.00	35.00	4.97	68.46	58.54	1.25	2.13
20.00	50.00	5.12	61.10	56.96	1.24	2.18
28.59	58.59	5.10	58.49	56.16	1.23	2.14
35.74	65.74	5.10	55.30	54.57	1.22	2.11
42.88	72.88	5.07	53.39	53.33	1.21	2.12
50.00	80.00	5.05	51.26	51.58	1.20	2.09
64.30	94.30	5.00	48.21	48.64	1.18	2.06
121.44	91.44	4.95	40.55	41.10	1.17	2.03
128.58	98.58	5.04	39.34	40.10	1.16	2.03
135.72	105.72	5.04	39.85	40.26	1.14	1.99
142.87	112.87	4.99	40.78	40.74	1.13	2.02
150.01	120.01	5.06	40.53	40.11	1.12	2.01
157.15	127.15	5.11	39.65	39.23	1.09	2.03
164.29	134.29	5.14	38.33	38.13	1.07	2.10
171.43	141.43	5.21	36.83	37.20	1.04	2.10
178.58	148.58	5.29	35.77	36.86	1.03	2.07
185.72	155.72	5.36	35.84	37.45	1.02	2.05
192.86	162.86	5.42	36.35	38.14	1.02	2.07
200.00	170.00	5.45	36.17	38.15	1.12	2.19

Electrical Schematic









Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
SRA-3MH
DJ/TD/CP/AM
200402
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

SRA-3MH+

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+10	+13	+16		+10	+13	+16	+10	+13	+16
0.03	30.0	7.66	7.47	7.24	0.03	70.00	73.00	71.40	70.00	68.27	65.79
5.0	35.0	5.25	4.97	4.89	5.0	70.00	68.46	66.56	59.18	58.54	57.93
20.0	50.0	5.35	5.12	5.01	20.0	61.88	61.10	59.95	57.74	56.96	56.24
28.6	58.6	5.33	5.10	5.00	28.6	59.36	58.49	57.19	56.88	56.16	55.40
35.7	65.7	5.30	5.10	5.02	35.7	56.32	55.30	53.21	54.86	54.57	52.46
42.9	72.9	5.28	5.07	5.00	42.9	55.01	53.39	51.43	54.32	53.33	51.21
50.0	80.0	5.24	5.05	4.98	50.0	52.83	51.26	49.70	52.92	51.58	49.80
64.3	94.3	5.16	5.00	4.96	64.3	49.34	48.21	46.87	49.57	48.64	47.17
121.4	91.4	5.08	4.95	4.94	121.4	39.62	40.55	41.49	39.89	41.10	42.02
128.6	98.6	5.14	5.04	5.02	128.6	39.12	39.34	39.90	39.33	40.10	40.89
135.7	105.7	5.12	5.04	5.05	135.7	39.51	39.85	40.17	39.32	40.26	40.71
142.9	112.9	5.07	4.99	5.03	142.9	39.76	40.78	41.83	39.11	40.74	42.00
150.0	120.0	5.16	5.06	5.06	150.0	39.05	40.53	42.04	38.26	40.11	42.01
157.2	127.2	5.19	5.11	5.10	157.2	37.95	39.65	41.17	37.38	39.23	40.80
164.3	134.3	5.22	5.14	5.13	164.3	36.71	38.33	39.63	36.71	38.13	39.47
171.4	141.4	5.29	5.21	5.20	171.4	35.60	36.83	37.79	36.39	37.20	38.17
178.6	148.6	5.36	5.29	5.27	178.6	34.99	35.77	36.61	36.34	36.86	37.65
185.7	155.7	5.43	5.36	5.31	185.7	35.16	35.84	36.47	36.83	37.45	38.03
192.9	162.9	5.51	5.42	5.34	192.9	35.21	36.35	37.02	37.09	38.14	38.78
200.0	170.0	5.59	5.45	5.38	200.0	34.68	36.17	37.04	36.75	38.15	38.89

REV. X1
SRA-3MH+
070509
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

SRA-3MH+

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)			LO/RF (MHz)	max. DC output (mV)	DC Offset (mV)
	@LO (dBm)			@LO (dBm)				@LO (dBm)			@LO (dBm)		
	+10	+13	+16	+10	+13	+16		+10	+13	+16	+13		
5.0	1.42	1.27	1.15	1.29	2.12	3.35	5.0	1.58	1.50	1.44	0.03	-505.3	-0.02
32.9	1.39	1.25	1.14	1.32	2.13	3.22	32.9	1.59	1.52	1.47	5.00	-541.5	-0.08
38.4	1.39	1.24	1.13	1.34	2.18	3.24	38.4	1.59	1.53	1.47	20.00	-543.8	-0.06
50.0	1.37	1.23	1.12	1.33	2.14	3.24	50.0	1.61	1.54	1.49	28.59	-544.0	-0.06
60.7	1.36	1.22	1.11	1.29	2.11	3.20	60.7	1.64	1.57	1.52	35.74	-541.6	-0.06
66.3	1.35	1.21	1.11	1.31	2.12	3.25	66.3	1.66	1.59	1.53	42.88	-542.5	0.05
71.9	1.34	1.20	1.10	1.27	2.09	3.17	71.9	1.68	1.60	1.54	50.00	-542.8	-0.03
83.0	1.31	1.18	1.09	1.26	2.06	2.97	83.0	1.71	1.63	1.57	64.30	-555.4	-0.02
88.6	1.30	1.17	1.08	1.27	2.03	2.94	88.6	1.72	1.64	1.58	121.44	-549.9	0.17
94.1	1.28	1.16	1.06	1.27	2.03	2.91	94.1	1.73	1.65	1.59	128.58	-541.9	0.03
99.7	1.26	1.14	1.05	1.29	1.99	2.89	99.7	1.74	1.67	1.61	135.72	-542.8	0.00
105.3	1.25	1.13	1.04	1.28	2.02	2.90	105.3	1.77	1.69	1.63	142.87	-541.9	0.02
110.9	1.23	1.12	1.03	1.31	2.01	2.94	110.9	1.75	1.67	1.61	150.01	-546.6	0.05
122.0	1.21	1.09	1.01	1.32	2.03	2.91	122.0	1.84	1.75	1.69	157.15	-551.6	0.27
133.1	1.19	1.07	1.02	1.37	2.10	3.07	133.1	1.92	1.82	1.76	164.29	-558.1	0.39
144.3	1.16	1.04	1.04	1.36	2.10	3.06	144.3	1.98	1.88	1.82	171.43	-557.2	0.54
149.9	1.14	1.03	1.06	1.37	2.07	2.99	149.9	2.02	1.92	1.86	178.58	-552.2	0.63
155.4	1.12	1.02	1.08	1.42	2.05	2.99	155.4	2.04	1.95	1.88	185.72	-547.4	0.54
161.0	1.11	1.02	1.09	1.42	2.07	2.94	161.0	2.07	1.97	1.91	192.86	-543.3	0.44
200.0	1.05	1.12	1.22	1.47	2.19	3.07	200.0	2.37	2.22	2.15	200.00	-541.0	0.27

REV. X1
SRA-3MH+
070509
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR




LO VSWR



IF VSWR



Max. DC Output



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D