



Mini-Circuits®

ULTRA-SMALL CERAMIC

## Power Splitter/Combiner

QCN-27D+


2 Way-90° 50Ω 1700 to 2700 MHz

## FEATURES

- Low insertion loss, 0.4 dB typ.
- High isolation, 30 dB typ.
- Wrap-around terminal for excellent solderability
- Ultra small, 0.12"X0.06"X0.035"
- Patent pending

## APPLICATIONS

- Balanced amplifiers
- Modulators
- PCS/DCS
- MMDS
- ISM



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

## +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT +25°C

| Parameter                            | Frequency (MHz) | Min. | Typ. | Max. | Unit   |
|--------------------------------------|-----------------|------|------|------|--------|
| Frequency Range                      |                 | 1700 |      | 2700 | MHz    |
| Average Insertion Loss, above 3.0 dB | 1700 - 1800     |      | 0.4  | 0.7  | dB     |
|                                      | 1800 - 2000     |      | 0.4  | 0.7  |        |
|                                      | 2000 - 2400     |      | 0.4  | 0.7  |        |
|                                      | 2400 - 2700     |      | 0.5  | 0.9  |        |
| Isolation                            | 1700 - 1800     | 18   | 21   |      | dB     |
|                                      | 1800 - 2000     | 18   | 22   |      |        |
|                                      | 2000 - 2400     | 20   | 30   |      |        |
|                                      | 2400 - 2700     | 20   | 30   |      |        |
| Phase Unbalance                      | 1700 - 1800     |      | 3    | 6    | Degree |
|                                      | 1800 - 2000     |      | 2    | 6    |        |
|                                      | 2000 - 2400     |      | 3    | 6    |        |
|                                      | 2400 - 2700     |      | 3    | 6    |        |
| Amplitude Unbalance                  | 1700 - 1800     |      | 0.5  | 1.0  | dB     |
|                                      | 1800 - 2000     |      | 0.3  | 0.8  |        |
|                                      | 2000 - 2400     |      | 0.2  | 0.8  |        |
|                                      | 2400 - 2700     |      | 0.6  | 1.0  |        |
| VSWR                                 | 1700 - 1800     |      | 1.2  |      | :1     |
|                                      | 1800 - 2000     |      | 1.2  |      |        |
|                                      | 2000 - 2400     |      | 1.2  |      |        |
|                                      | 2400 - 2700     |      | 1.2  |      |        |


1. For applications requiring DC voltage to be applied to the RF ports. DC resistance to ground is 100 Mohms min.

## MAXIMUM RATINGS

| Parameter                   | Ratings         |
|-----------------------------|-----------------|
| Operating Temperature       | -55°C to +100°C |
| Storage Temperature         | -55°C to +100°C |
| Power Input (as a splitter) | 15 W* max.      |

\* Derate linearly to 7 W at +100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## ELECTRICAL SCHEMATIC (NOTE 1)



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. N  
ECO-023420  
QCN-27D+  
ED-10849/5  
MCL NY  
250718  
PAGE 1 OF 3



Mini-Circuits

ULTRA-SMALL CERAMIC

## Power Splitter/Combiner

QCN-27D+


2 Way-90° 50Ω 1700 to 2700 MHz

## PIN CONNECTIONS

|                      |     |
|----------------------|-----|
| SUM PORT             | 1   |
| PORT 1 (0°)          | 4   |
| PORT 2 (+90°)        | 6   |
| GROUND               | 2,5 |
| 50 OHM TERM EXTERNAL | 3   |

PRODUCT MARKING: P4

DEMO BOARD MCL P/N: TB-QCN-27D+  
SUGGESTED PCB LAYOUT (PL-131)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS  $0.020" \pm 0.0015"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm 0.002$

## OUTLINE DIMENSIONS (Inches/mm)

| A    | B    | C    | D    | E    | F     |
|------|------|------|------|------|-------|
| .126 | .063 | .035 | .024 | .022 | .011  |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28  |
| G    | H    | J    | K    |      | wt    |
| .039 | .024 | .042 | .123 |      | grams |
| 0.99 | 0.61 | 1.07 | 3.12 |      | .020  |

## TAPE &amp; REEL INFORMATION: F75





Mini-Circuits

ULTRA-SMALL CERAMIC

## Power Splitter/Combiner




QCN-27D+

2 Way-90° 50Ω 1700 to 2700 MHz

## TYPICAL PERFORMANCE DATA

| Frequency<br>(MHz) | Total Loss <sup>2</sup><br>(dB) |      | Amplitude<br>Unbalance<br>(dB) | Isolation<br>(dB) | Phase<br>Unbalance<br>(deg.) | VSWR<br>(:1) |      |      |
|--------------------|---------------------------------|------|--------------------------------|-------------------|------------------------------|--------------|------|------|
|                    | S-1                             | S-2  |                                |                   |                              | S            | 1    | 2    |
| 1700.00            | 3.12                            | 3.68 | 0.56                           | 21.52             | 88.45                        | 1.23         | 1.26 | 1.19 |
| 1800.00            | 3.24                            | 3.55 | 0.31                           | 22.55             | 88.66                        | 1.21         | 1.24 | 1.17 |
| 1900.00            | 3.33                            | 3.44 | 0.12                           | 23.84             | 88.92                        | 1.18         | 1.23 | 1.14 |
| 2000.00            | 3.40                            | 3.37 | 0.03                           | 25.33             | 88.93                        | 1.16         | 1.21 | 1.12 |
| 2100.00            | 3.45                            | 3.33 | 0.12                           | 26.85             | 88.95                        | 1.14         | 1.20 | 1.10 |
| 2200.00            | 3.48                            | 3.32 | 0.16                           | 28.90             | 89.07                        | 1.12         | 1.19 | 1.09 |
| 2300.00            | 3.48                            | 3.33 | 0.15                           | 31.22             | 89.25                        | 1.10         | 1.18 | 1.09 |
| 2400.00            | 3.45                            | 3.37 | 0.08                           | 34.26             | 89.24                        | 1.08         | 1.17 | 1.10 |
| 2500.00            | 3.40                            | 3.44 | 0.04                           | 38.56             | 89.27                        | 1.06         | 1.17 | 1.11 |
| 2600.00            | 3.33                            | 3.54 | 0.22                           | 45.07             | 89.20                        | 1.04         | 1.16 | 1.12 |
| 2650.00            | 3.28                            | 3.61 | 0.33                           | 52.09             | 89.34                        | 1.03         | 1.16 | 1.13 |
| 2700.00            | 3.23                            | 3.68 | 0.45                           | 57.17             | 89.32                        | 1.01         | 1.16 | 1.14 |

2. Total Loss = Insertion Loss + 3 dB splitter loss.



## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# 2 Way-90° Power Splitter/Combiner

QCN-27D+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB) | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|------------------------------------|-------------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                                    |                   | S            | 1    | 2    |
| 900            | 1.61                            | 6.19 | 4.58                   | 3.15                               | 18.98             | 1.27         | 1.26 | 1.27 |
| 950            | 1.72                            | 5.91 | 4.19                   | 3.15                               | 18.95             | 1.27         | 1.27 | 1.27 |
| 1000           | 1.82                            | 5.66 | 3.83                   | 3.12                               | 19.00             | 1.27         | 1.27 | 1.27 |
| 1100           | 2.03                            | 5.21 | 3.18                   | 3.04                               | 19.16             | 1.27         | 1.26 | 1.26 |
| 1150           | 2.13                            | 5.01 | 2.88                   | 2.97                               | 19.31             | 1.26         | 1.26 | 1.26 |
| 1200           | 2.23                            | 4.82 | 2.60                   | 2.90                               | 19.48             | 1.26         | 1.26 | 1.25 |
| 1250           | 2.32                            | 4.66 | 2.34                   | 2.82                               | 19.67             | 1.25         | 1.25 | 1.24 |
| 1300           | 2.41                            | 4.50 | 2.09                   | 2.74                               | 19.92             | 1.24         | 1.25 | 1.24 |
| 1350           | 2.50                            | 4.36 | 1.86                   | 2.68                               | 20.15             | 1.23         | 1.24 | 1.23 |
| 1400           | 2.58                            | 4.23 | 1.65                   | 2.60                               | 20.45             | 1.23         | 1.23 | 1.22 |
| 1450           | 2.66                            | 4.11 | 1.44                   | 2.53                               | 20.76             | 1.22         | 1.22 | 1.21 |
| 1500           | 2.74                            | 4.00 | 1.26                   | 2.46                               | 21.04             | 1.21         | 1.22 | 1.20 |
| 1600           | 2.89                            | 3.80 | 0.91                   | 2.31                               | 21.79             | 1.19         | 1.20 | 1.18 |
| 1650           | 2.95                            | 3.71 | 0.76                   | 2.30                               | 22.22             | 1.18         | 1.19 | 1.17 |
| 1700           | 3.02                            | 3.64 | 0.62                   | 2.22                               | 22.68             | 1.17         | 1.18 | 1.16 |
| 1750           | 3.08                            | 3.57 | 0.49                   | 2.17                               | 23.14             | 1.16         | 1.17 | 1.15 |
| 1800           | 3.13                            | 3.50 | 0.37                   | 2.14                               | 23.66             | 1.16         | 1.16 | 1.13 |
| 1850           | 3.18                            | 3.45 | 0.27                   | 2.09                               | 24.23             | 1.15         | 1.15 | 1.12 |
| 1900           | 3.22                            | 3.40 | 0.17                   | 2.05                               | 24.83             | 1.14         | 1.14 | 1.11 |
| 1950           | 3.26                            | 3.36 | 0.09                   | 2.01                               | 25.54             | 1.13         | 1.13 | 1.11 |
| 2000           | 3.30                            | 3.32 | 0.03                   | 1.99                               | 26.30             | 1.12         | 1.12 | 1.10 |
| 2050           | 3.33                            | 3.29 | 0.03                   | 1.96                               | 27.01             | 1.11         | 1.11 | 1.09 |
| 2100           | 3.36                            | 3.27 | 0.08                   | 1.95                               | 28.02             | 1.10         | 1.10 | 1.08 |
| 2150           | 3.38                            | 3.26 | 0.12                   | 1.94                               | 28.99             | 1.09         | 1.10 | 1.07 |
| 2200           | 3.39                            | 3.25 | 0.15                   | 1.92                               | 30.19             | 1.08         | 1.09 | 1.07 |
| 2300           | 3.41                            | 3.25 | 0.16                   | 1.88                               | 33.06             | 1.07         | 1.07 | 1.06 |
| 2350           | 3.41                            | 3.26 | 0.15                   | 1.86                               | 34.91             | 1.06         | 1.06 | 1.06 |
| 2400           | 3.40                            | 3.27 | 0.13                   | 1.84                               | 37.08             | 1.05         | 1.06 | 1.06 |
| 2450           | 3.39                            | 3.29 | 0.09                   | 1.84                               | 39.58             | 1.05         | 1.05 | 1.07 |
| 2500           | 3.37                            | 3.32 | 0.05                   | 1.83                               | 41.74             | 1.04         | 1.04 | 1.07 |
| 2550           | 3.35                            | 3.36 | 0.01                   | 1.81                               | 41.44             | 1.04         | 1.03 | 1.08 |
| 2600           | 3.32                            | 3.40 | 0.09                   | 1.81                               | 39.51             | 1.04         | 1.03 | 1.08 |
| 2650           | 3.28                            | 3.46 | 0.17                   | 1.74                               | 36.98             | 1.04         | 1.03 | 1.09 |
| 2700           | 3.24                            | 3.52 | 0.27                   | 1.69                               | 35.03             | 1.04         | 1.03 | 1.10 |
| 2750           | 3.20                            | 3.58 | 0.38                   | 1.65                               | 33.34             | 1.04         | 1.03 | 1.11 |
| 2800           | 3.15                            | 3.66 | 0.51                   | 1.60                               | 31.80             | 1.05         | 1.04 | 1.12 |
| 2850           | 3.09                            | 3.74 | 0.65                   | 1.56                               | 30.83             | 1.06         | 1.05 | 1.13 |
| 2900           | 3.03                            | 3.84 | 0.81                   | 1.46                               | 29.72             | 1.07         | 1.06 | 1.14 |
| 3000           | 2.89                            | 4.06 | 1.17                   | 1.26                               | 28.19             | 1.10         | 1.08 | 1.17 |
| 3050           | 2.82                            | 4.19 | 1.37                   | 1.11                               | 27.45             | 1.11         | 1.09 | 1.17 |
| 3100           | 2.74                            | 4.34 | 1.59                   | 0.99                               | 26.70             | 1.12         | 1.10 | 1.19 |
| 3150           | 2.66                            | 4.50 | 1.84                   | 0.83                               | 26.11             | 1.14         | 1.12 | 1.20 |
| 3200           | 2.58                            | 4.67 | 2.09                   | 0.66                               | 25.49             | 1.15         | 1.13 | 1.22 |
| 3250           | 2.49                            | 4.86 | 2.37                   | 0.45                               | 24.93             | 1.17         | 1.15 | 1.23 |
| 3300           | 2.40                            | 5.07 | 2.67                   | 0.20                               | 24.43             | 1.18         | 1.16 | 1.24 |
| 3350           | 2.31                            | 5.30 | 2.99                   | 0.06                               | 23.93             | 1.20         | 1.18 | 1.26 |
| 3400           | 2.22                            | 5.56 | 3.34                   | 0.34                               | 23.53             | 1.22         | 1.19 | 1.27 |
| 3450           | 2.12                            | 5.84 | 3.71                   | 0.67                               | 23.11             | 1.23         | 1.21 | 1.29 |
| 3500           | 2.03                            | 6.15 | 4.11                   | 1.01                               | 22.70             | 1.25         | 1.23 | 1.30 |
| 3550           | 1.94                            | 6.49 | 4.55                   | 1.42                               | 22.38             | 1.27         | 1.25 | 1.32 |
| 3600           | 1.85                            | 6.86 | 5.01                   | 1.91                               | 22.03             | 1.29         | 1.27 | 1.33 |
| 3700           | 1.67                            | 7.73 | 6.06                   | 3.09                               | 21.45             | 1.32         | 1.30 | 1.37 |
| 3750           | 1.59                            | 8.23 | 6.65                   | 3.79                               | 21.19             | 1.34         | 1.32 | 1.38 |
| 3800           | 1.50                            | 8.80 | 7.29                   | 4.59                               | 20.90             | 1.36         | 1.34 | 1.39 |

<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss



# 2 Way-90° Power Splitter/Combiner

QCN-27D+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -55°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB) | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|------------------------------------|-------------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                                    |                   | S            | 1    | 2    |
| 900            | 1.46                            | 6.06 | 4.60                   | 3.38                               | 18.71             | 1.27         | 1.27 | 1.28 |
| 950            | 1.57                            | 5.78 | 4.21                   | 3.42                               | 18.65             | 1.28         | 1.28 | 1.28 |
| 1000           | 1.67                            | 5.53 | 3.85                   | 3.47                               | 18.57             | 1.28         | 1.28 | 1.29 |
| 1100           | 1.87                            | 5.07 | 3.20                   | 3.54                               | 18.69             | 1.28         | 1.29 | 1.29 |
| 1150           | 1.97                            | 4.88 | 2.91                   | 3.48                               | 18.72             | 1.28         | 1.29 | 1.29 |
| 1200           | 2.06                            | 4.69 | 2.63                   | 3.50                               | 18.72             | 1.29         | 1.29 | 1.29 |
| 1250           | 2.15                            | 4.53 | 2.38                   | 3.48                               | 18.80             | 1.28         | 1.29 | 1.29 |
| 1300           | 2.23                            | 4.38 | 2.14                   | 3.36                               | 19.01             | 1.28         | 1.28 | 1.28 |
| 1350           | 2.31                            | 4.23 | 1.92                   | 3.31                               | 19.32             | 1.27         | 1.28 | 1.28 |
| 1400           | 2.39                            | 4.10 | 1.71                   | 3.19                               | 19.52             | 1.26         | 1.26 | 1.27 |
| 1450           | 2.46                            | 3.97 | 1.51                   | 3.11                               | 19.77             | 1.25         | 1.26 | 1.26 |
| 1500           | 2.53                            | 3.86 | 1.33                   | 3.02                               | 20.04             | 1.24         | 1.25 | 1.25 |
| 1600           | 2.66                            | 3.65 | 0.99                   | 2.79                               | 20.78             | 1.21         | 1.23 | 1.22 |
| 1650           | 2.72                            | 3.55 | 0.83                   | 2.74                               | 21.27             | 1.20         | 1.21 | 1.20 |
| 1700           | 2.78                            | 3.46 | 0.68                   | 2.66                               | 21.70             | 1.19         | 1.21 | 1.19 |
| 1750           | 2.83                            | 3.38 | 0.55                   | 2.56                               | 22.20             | 1.18         | 1.19 | 1.16 |
| 1800           | 2.88                            | 3.31 | 0.42                   | 2.52                               | 22.74             | 1.17         | 1.17 | 1.14 |
| 1850           | 2.93                            | 3.24 | 0.31                   | 2.45                               | 23.47             | 1.15         | 1.15 | 1.12 |
| 1900           | 2.97                            | 3.18 | 0.21                   | 2.43                               | 24.13             | 1.14         | 1.13 | 1.10 |
| 1950           | 3.01                            | 3.12 | 0.11                   | 2.43                               | 24.89             | 1.13         | 1.12 | 1.08 |
| 2000           | 3.05                            | 3.08 | 0.04                   | 2.47                               | 26.02             | 1.12         | 1.11 | 1.06 |
| 2050           | 3.08                            | 3.04 | 0.04                   | 2.48                               | 26.72             | 1.12         | 1.10 | 1.04 |
| 2100           | 3.10                            | 3.01 | 0.09                   | 2.53                               | 27.76             | 1.11         | 1.08 | 1.02 |
| 2150           | 3.12                            | 2.99 | 0.14                   | 2.62                               | 29.30             | 1.10         | 1.07 | 1.02 |
| 2200           | 3.14                            | 2.97 | 0.17                   | 2.69                               | 30.60             | 1.10         | 1.06 | 1.04 |
| 2300           | 3.15                            | 2.96 | 0.19                   | 2.78                               | 32.50             | 1.08         | 1.03 | 1.08 |
| 2350           | 3.15                            | 2.97 | 0.17                   | 2.84                               | 32.97             | 1.08         | 1.02 | 1.10 |
| 2400           | 3.13                            | 2.99 | 0.14                   | 2.93                               | 32.79             | 1.07         | 1.01 | 1.13 |
| 2450           | 3.11                            | 3.01 | 0.10                   | 2.91                               | 32.10             | 1.06         | 1.02 | 1.15 |
| 2500           | 3.09                            | 3.04 | 0.05                   | 2.91                               | 30.91             | 1.05         | 1.04 | 1.17 |
| 2550           | 3.07                            | 3.08 | 0.01                   | 2.91                               | 29.31             | 1.05         | 1.05 | 1.19 |
| 2600           | 3.03                            | 3.13 | 0.10                   | 2.90                               | 27.79             | 1.04         | 1.06 | 1.21 |
| 2650           | 2.99                            | 3.19 | 0.19                   | 2.77                               | 27.00             | 1.04         | 1.08 | 1.24 |
| 2700           | 2.96                            | 3.24 | 0.28                   | 2.64                               | 26.31             | 1.04         | 1.09 | 1.26 |
| 2750           | 2.92                            | 3.32 | 0.40                   | 2.53                               | 25.24             | 1.07         | 1.11 | 1.28 |
| 2800           | 2.87                            | 3.39 | 0.52                   | 2.34                               | 24.49             | 1.08         | 1.13 | 1.31 |
| 2850           | 2.82                            | 3.47 | 0.64                   | 2.20                               | 23.99             | 1.10         | 1.14 | 1.33 |
| 2900           | 2.78                            | 3.55 | 0.77                   | 2.00                               | 23.63             | 1.11         | 1.16 | 1.34 |
| 3000           | 2.66                            | 3.73 | 1.07                   | 1.77                               | 23.10             | 1.14         | 1.18 | 1.35 |
| 3050           | 2.60                            | 3.83 | 1.23                   | 1.63                               | 23.03             | 1.14         | 1.18 | 1.36 |
| 3100           | 2.53                            | 3.94 | 1.41                   | 1.55                               | 22.86             | 1.14         | 1.19 | 1.35 |
| 3150           | 2.46                            | 4.06 | 1.61                   | 1.53                               | 22.83             | 1.14         | 1.19 | 1.35 |
| 3200           | 2.36                            | 4.20 | 1.84                   | 1.63                               | 23.20             | 1.13         | 1.17 | 1.34 |
| 3250           | 2.27                            | 4.37 | 2.10                   | 1.62                               | 23.15             | 1.14         | 1.17 | 1.34 |
| 3300           | 2.18                            | 4.54 | 2.36                   | 1.63                               | 23.27             | 1.12         | 1.17 | 1.33 |
| 3350           | 2.07                            | 4.72 | 2.65                   | 1.65                               | 23.82             | 1.10         | 1.17 | 1.29 |
| 3400           | 1.95                            | 4.94 | 2.99                   | 1.67                               | 24.30             | 1.09         | 1.16 | 1.27 |
| 3450           | 1.83                            | 5.19 | 3.36                   | 1.64                               | 24.78             | 1.08         | 1.14 | 1.25 |
| 3500           | 1.71                            | 5.46 | 3.75                   | 1.54                               | 25.20             | 1.07         | 1.13 | 1.22 |
| 3550           | 1.60                            | 5.77 | 4.18                   | 1.41                               | 25.87             | 1.07         | 1.13 | 1.19 |
| 3600           | 1.47                            | 6.12 | 4.65                   | 1.23                               | 26.32             | 1.09         | 1.13 | 1.16 |
| 3700           | 1.25                            | 6.94 | 5.69                   | 0.62                               | 26.76             | 1.12         | 1.12 | 1.10 |
| 3750           | 1.14                            | 7.42 | 6.28                   | 0.29                               | 26.48             | 1.15         | 1.12 | 1.06 |
| 3800           | 1.04                            | 7.96 | 6.92                   | 0.17                               | 25.69             | 1.18         | 1.13 | 1.06 |

<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss

# 2 Way-90° Power Splitter/Combiner

QCN-27D+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +100°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |       | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB) | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|-------|------------------------|------------------------------------|-------------------|--------------|------|------|
|                | S-1                             | S-2   |                        |                                    |                   | S            | 1    | 2    |
| 900            | 1.67                            | 6.23  | 4.56                   | 2.83                               | 19.52             | 1.27         | 1.26 | 1.26 |
| 950            | 1.78                            | 5.95  | 4.17                   | 2.76                               | 19.55             | 1.26         | 1.26 | 1.26 |
| 1000           | 1.89                            | 5.69  | 3.80                   | 2.69                               | 19.70             | 1.26         | 1.25 | 1.25 |
| 1100           | 2.10                            | 5.23  | 3.13                   | 2.57                               | 20.02             | 1.24         | 1.24 | 1.22 |
| 1150           | 2.20                            | 5.03  | 2.83                   | 2.45                               | 20.28             | 1.23         | 1.23 | 1.21 |
| 1200           | 2.30                            | 4.84  | 2.55                   | 2.36                               | 20.59             | 1.22         | 1.22 | 1.20 |
| 1250           | 2.40                            | 4.67  | 2.28                   | 2.25                               | 20.87             | 1.21         | 1.21 | 1.19 |
| 1300           | 2.49                            | 4.52  | 2.02                   | 2.18                               | 21.18             | 1.20         | 1.20 | 1.17 |
| 1350           | 2.58                            | 4.37  | 1.79                   | 2.13                               | 21.45             | 1.19         | 1.19 | 1.16 |
| 1400           | 2.67                            | 4.25  | 1.57                   | 2.05                               | 21.84             | 1.18         | 1.18 | 1.15 |
| 1450           | 2.76                            | 4.13  | 1.36                   | 2.01                               | 22.24             | 1.17         | 1.17 | 1.14 |
| 1500           | 2.84                            | 4.02  | 1.17                   | 1.96                               | 22.56             | 1.16         | 1.16 | 1.13 |
| 1600           | 3.01                            | 3.83  | 0.82                   | 1.85                               | 23.46             | 1.15         | 1.15 | 1.12 |
| 1650           | 3.08                            | 3.75  | 0.67                   | 1.82                               | 23.93             | 1.14         | 1.14 | 1.12 |
| 1700           | 3.15                            | 3.68  | 0.53                   | 1.79                               | 24.32             | 1.13         | 1.13 | 1.12 |
| 1750           | 3.22                            | 3.62  | 0.40                   | 1.74                               | 24.62             | 1.13         | 1.13 | 1.13 |
| 1800           | 3.28                            | 3.57  | 0.29                   | 1.74                               | 24.98             | 1.13         | 1.13 | 1.13 |
| 1850           | 3.33                            | 3.52  | 0.19                   | 1.73                               | 25.37             | 1.12         | 1.13 | 1.14 |
| 1900           | 3.38                            | 3.49  | 0.11                   | 1.71                               | 25.66             | 1.12         | 1.13 | 1.15 |
| 1950           | 3.42                            | 3.45  | 0.03                   | 1.69                               | 25.97             | 1.12         | 1.13 | 1.16 |
| 2000           | 3.46                            | 3.43  | 0.03                   | 1.70                               | 26.17             | 1.12         | 1.13 | 1.17 |
| 2050           | 3.50                            | 3.41  | 0.08                   | 1.69                               | 26.28             | 1.12         | 1.13 | 1.17 |
| 2100           | 3.53                            | 3.40  | 0.12                   | 1.67                               | 26.52             | 1.12         | 1.13 | 1.18 |
| 2150           | 3.55                            | 3.40  | 0.15                   | 1.65                               | 26.65             | 1.11         | 1.13 | 1.19 |
| 2200           | 3.57                            | 3.40  | 0.17                   | 1.60                               | 26.87             | 1.11         | 1.13 | 1.19 |
| 2300           | 3.58                            | 3.42  | 0.16                   | 1.55                               | 27.32             | 1.10         | 1.14 | 1.20 |
| 2350           | 3.58                            | 3.44  | 0.14                   | 1.49                               | 27.60             | 1.10         | 1.13 | 1.20 |
| 2400           | 3.57                            | 3.46  | 0.11                   | 1.44                               | 27.97             | 1.10         | 1.13 | 1.20 |
| 2450           | 3.55                            | 3.49  | 0.06                   | 1.38                               | 28.43             | 1.09         | 1.13 | 1.20 |
| 2500           | 3.53                            | 3.53  | 0.01                   | 1.30                               | 28.93             | 1.08         | 1.12 | 1.19 |
| 2550           | 3.51                            | 3.57  | 0.06                   | 1.22                               | 29.31             | 1.08         | 1.12 | 1.18 |
| 2600           | 3.47                            | 3.62  | 0.14                   | 1.14                               | 29.58             | 1.07         | 1.12 | 1.17 |
| 2650           | 3.43                            | 3.67  | 0.24                   | 1.02                               | 30.12             | 1.06         | 1.11 | 1.17 |
| 2700           | 3.39                            | 3.73  | 0.34                   | 0.90                               | 30.73             | 1.05         | 1.11 | 1.16 |
| 2750           | 3.35                            | 3.80  | 0.46                   | 0.80                               | 31.15             | 1.05         | 1.11 | 1.14 |
| 2800           | 3.30                            | 3.89  | 0.59                   | 0.65                               | 31.28             | 1.05         | 1.10 | 1.13 |
| 2850           | 3.24                            | 3.97  | 0.73                   | 0.55                               | 31.21             | 1.06         | 1.10 | 1.11 |
| 2900           | 3.18                            | 4.07  | 0.89                   | 0.42                               | 31.05             | 1.07         | 1.09 | 1.09 |
| 3000           | 3.04                            | 4.29  | 1.25                   | 0.22                               | 29.99             | 1.09         | 1.07 | 1.05 |
| 3050           | 2.97                            | 4.42  | 1.45                   | 0.12                               | 29.25             | 1.11         | 1.05 | 1.04 |
| 3100           | 2.90                            | 4.57  | 1.67                   | 0.08                               | 28.21             | 1.13         | 1.04 | 1.03 |
| 3150           | 2.82                            | 4.74  | 1.92                   | 0.00                               | 27.16             | 1.16         | 1.02 | 1.05 |
| 3200           | 2.75                            | 4.94  | 2.19                   | 0.04                               | 26.10             | 1.19         | 1.01 | 1.09 |
| 3250           | 2.67                            | 5.16  | 2.49                   | 0.14                               | 25.19             | 1.21         | 1.04 | 1.13 |
| 3300           | 2.58                            | 5.40  | 2.82                   | 0.20                               | 24.36             | 1.24         | 1.07 | 1.17 |
| 3350           | 2.49                            | 5.68  | 3.19                   | 0.31                               | 23.49             | 1.27         | 1.12 | 1.22 |
| 3400           | 2.41                            | 6.00  | 3.59                   | 0.53                               | 22.81             | 1.31         | 1.17 | 1.28 |
| 3450           | 2.32                            | 6.35  | 4.03                   | 0.84                               | 22.14             | 1.35         | 1.22 | 1.35 |
| 3500           | 2.25                            | 6.76  | 4.51                   | 1.24                               | 21.49             | 1.40         | 1.28 | 1.42 |
| 3550           | 2.18                            | 7.20  | 5.01                   | 1.79                               | 20.98             | 1.46         | 1.35 | 1.50 |
| 3600           | 2.11                            | 7.70  | 5.59                   | 2.58                               | 20.51             | 1.51         | 1.41 | 1.59 |
| 3700           | 2.02                            | 8.81  | 6.79                   | 4.76                               | 19.97             | 1.64         | 1.56 | 1.77 |
| 3750           | 1.98                            | 9.45  | 7.47                   | 6.19                               | 19.70             | 1.70         | 1.64 | 1.86 |
| 3800           | 1.95                            | 10.12 | 8.18                   | 7.76                               | 19.48             | 1.76         | 1.71 | 1.94 |






<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss



# 2 Way-90° Power Splitter/Combiner

QCN-27D+

## Typical Performance Curves



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see







REV. X2  
QCN-27D+  
100627  
Page 1 of 2

# 2 Way-90° Power Splitter/Combiner

QCN-27D+

## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L  | M  | N  | P  | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126<br>(3.20) | .063<br>(1.60) | .035<br>(0.89) | .024<br>(0.61) | .022<br>(0.56) | .011<br>(0.28) | .039<br>(0.99) | .024<br>(0.61) | .042<br>(1.07) | .123<br>(3.12) | -- | -- | -- | -- | .020     |

Dimensions are in inches (mm). Tolerances: 2 PL.  $\pm .01$ ; 3 PL.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

### Applicable Case Styles

FV1206-1  
FV1206-3

### Applicable Case Styles

FV1206-4  
FV1206-5  
FV1206-6  
FV1206-7  
FV1206-9

### Applicable Case Styles

FV1206-11  
FV1206-12  
GE0805C-18  
NL1008C-6  
NL1008C-7  
NL1008C-9  
NL1008C-10

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers NORTH AMERICA** 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION               | DATE     | DR  | AUTH |
|-----|---------|---------------------------|----------|-----|------|
| OR  | M87001  | NEW RELEASE               | 05/20/03 | MMG | ABD  |
| A   | M87231  | CORRECTED DWG.            | 05/28/03 | MMG | ABD  |
| B   | M91636  | ADDED "pn" PIN CONNECTION | 04/07/04 | AV  | ABD  |
| C   | M102713 | ADDED "...WITH SMOBC"     | 01/16/06 | GF  | IL   |

SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-1 CASE STYLE, "pb/pn" PIN CONNECTIONS




NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020"  $\pm$  0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, pb/pn, FV1206-1, QCN/BDCN, TB-255

SIZE  
ACODE IDENT  
15542DRAWING NO:  
98-PL-131REV:  
C


FILE: 98PL131

SCALE: 10:1

SHEET: 1 OF 1

# Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |