



THIN FILM SURFACE MOUNT

Bandpass Filter

ABF-15R75G+

Mini-Circuits

50Ω


14.2 to 17.4 GHz

KEY FEATURES

- Low Passband Insertion Loss of 1.5 dB Typ.
- High Rejection of 50 dB Typ.
- 20 dB rejection up to 35000 MHz
- Small Size, 5.59 x 8.13 x 2.03 mm

APPLICATIONS

- Receivers
- Satellite




Generic photo used for illustration purposes only

PRODUCT OVERVIEW

Mini-Circuits' Surface Mount Thin-Film filters offer low insertion loss and high rejection realized via Thin-Film on Alumina substrate, using a sputtering process that can guarantee an enhanced Q and repeatable performance. Low pass, high pass, and bandpass surface mount thin-film designs can be realized with this technology up to 40GHz in a small form factor helping customers achieve their SWaP objectives. Using our high quality thin-film manufacturing process we can guarantee repeatability on large batches of filters.

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

| Parameter | F# | Frequency (GHz) | Min. | Typ. | Max. | Units |
|-------------------------------|-------|-----------------|------|------|------|-------|
| Passband | | | | | | |
| Center Frequency ⁴ | — | — | — | 15.8 | — | GHz |
| Insertion Loss | F1-F2 | 14.2 - 17.4 | — | 1.5 | 3.0 | dB |
| Return Loss | F1-F2 | 14.2 - 17.4 | — | 10 | — | dB |
| Stopband, Lower | | | | | | |
| Rejection | DC-F3 | DC - 7 | 40 | 50 | — | dB |
| | F3-F4 | 7 - 11.2 | 20 | 30 | — | dB |
| Stopband, Upper | | | | | | |
| Rejection | F5-F6 | 20.5 - 35 | — | 20 | — | dB |

1. Tested on Evaluation Board P/N TB-ABF-15R75G+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line.

2. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

3. This component is not intended for use as a DC-blocking circuit element. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

4. Typical variation ±3%.


ABSOLUTE MAXIMUM RATINGS⁵

| Parameter | Ratings |
|--------------------------|-------------------|
| Operating Temperature | -55 °C to +125 °C |
| Storage Temperature | -55 °C to +125 °C |
| Input Power ⁶ | 1W Max. at 25°C |

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE AT +25°C





THIN FILM SURFACE MOUNT

Bandpass Filter





ABF-15R75G+

50Ω

50Ω

14.2 to 17.4 GHz

TYPICAL PERFORMANCE GRAPHS AT +25°C





FUNCTIONAL DIAGRAM





Figure 1. ABF-15R75G+ Functional Diagram


PAD DESCRIPTION

| Function | Pad Number | Description |
|------------------|------------|--|
| RF1 ² | 1 | Connects to RF Input Port |
| RF2 ² | 2 | Connects to RF Output Port |
| GROUND | 3 | Connects to Ground on PCB, (See drawing PL-652) |
| NC | — | No connection, not used internally. See drawing PL-652 for connection to PCB |

CASE STYLE DRAWING



SUGGESTED PCB LAYOUT (PL-652)



NOTES:

- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .010±.0010. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 ■ DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK


Figure 2. Suggested PCB Layout PL-652

PRODUCT MARKING*: ABF-15R75G

*Marking may contain other features or characters for internal lot control.





RECOMMENDED PCB LAYOUT PATTERN FOR FILTER



PCB Pattern Recommendations

Filter RF I/O Detail (Filter Back Side)




- 1) Customer PCB's ground pattern length (dimension A) can be similar to filter length.
- 2) Customer PCB's ground pattern width (dimension B) can be similar to filter width.
- 3) Dimensions C and D on Filter RF I/O detail and Customer PCB pattern can be closely match. The dimensions of C and D on the Customer PCB pattern can be slightly larger to account for component alignment tolerance (ground metal can be pulled back from RF I/O trace).
- 4) Recommend to use Solder mask at Customer PCB at outer area of filter pattern/ footprint with a clearance of about 1.25mil at each side. (Tighter registration tolerance required for solder mask)
- 5) Recommended to use Solder mask at I/O of Customer PCB as per above diagram (refer detail B).




COMMENTS ON COMPONENT HANDLING AND SOLDER ATTACH

- 1) Avoid using soldering iron directly to the ceramic filter. This would lead to development of crack in the component due to thermal shock.
- 2) Vacuum pick-up tool or plastic tweezers are recommended for handling the components. Extra care should be taken not to scratch the filter or metal area.
- 3) Use 2-3 mil thickness stencil plate and screen print the solder. Refer below picture for recommended stencil pattern to get the best solder attachment.

Stencil opening drawing



Solder location after screen print



- 4) Plugged ground vias in the PWB will improve attachment consistency.
- 5) Recommended to have a similar or closer test board material and thickness (refer Mini-Circuits evaluation board for details) to minimize the CTE over the temperature range.



THIN FILM SURFACE MOUNT

Bandpass Filter

ABF-15R75G+

Mini-Circuits

50Ω

14.2 to 17.4 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD.

[CLICK HERE](#)

| | |
|---------------------------------|---|
| Performance Data and Graphs | Data |
| | Graphs |
| | S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads |
| Case Style | UC2731 Lead Finish: Gold over Nickel Plate |
| RoHS Status | Compliant |
| Tape and Reel | TR-F003 |
| Suggested Layout for PCB Design | PL-652 |
| Evaluation Board | TB-ABF-15R75G+ |
| | Gerber File |
| Environmental Rating | ENV120 |

NOTES




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data


| FREQ. | Insertion Loss | Input Return Loss | Output Return Loss | FREQ. | Group Delay |
|-------|----------------|-------------------|--------------------|-------|-------------|
| (MHz) | (dB) | (dB) | (dB) | (MHz) | (ns) |
| 10 | 105.30 | 0.05 | 0.08 | 14200 | 0.40 |
| 50 | 89.69 | 0.04 | 0.05 | 14250 | 0.40 |
| 100 | 86.13 | 0.03 | 0.01 | 14300 | 0.40 |
| 500 | 72.19 | 0.08 | 0.10 | 14350 | 0.40 |
| 1000 | 66.10 | 0.07 | 0.10 | 14400 | 0.39 |
| 1500 | 62.33 | 0.02 | 0.03 | 14450 | 0.39 |
| 2000 | 59.73 | 0.02 | 0.02 | 14500 | 0.39 |
| 2500 | 57.81 | 0.07 | 0.06 | 14550 | 0.38 |
| 3000 | 56.09 | 0.18 | 0.21 | 14600 | 0.38 |
| 4000 | 54.12 | 0.13 | 0.13 | 14650 | 0.38 |
| 5000 | 52.96 | 0.01 | 0.04 | 14700 | 0.37 |
| 6000 | 52.40 | 0.04 | 0.02 | 14750 | 0.37 |
| 7000 | 51.59 | 0.04 | 0.00 | 14800 | 0.37 |
| 7500 | 50.85 | 0.07 | 0.11 | 14850 | 0.37 |
| 8000 | 49.97 | 0.10 | 0.10 | 14900 | 0.36 |
| 8500 | 49.09 | 0.09 | 0.14 | 14950 | 0.37 |
| 9000 | 47.07 | 0.08 | 0.15 | 15000 | 0.37 |
| 9500 | 44.73 | 0.03 | 0.10 | 15050 | 0.36 |
| 10000 | 41.41 | 0.02 | 0.03 | 15100 | 0.36 |
| 11000 | 32.79 | 0.15 | 0.23 | 15150 | 0.36 |
| 11200 | 30.68 | 0.17 | 0.30 | 15200 | 0.36 |
| 12000 | 20.03 | 0.34 | 0.38 | 15250 | 0.36 |
| 12500 | 10.13 | 1.06 | 0.87 | 15300 | 0.37 |
| 12830 | 3.03 | 5.01 | 4.58 | 15350 | 0.36 |
| 14200 | 0.67 | 26.56 | 26.28 | 15400 | 0.36 |
| 14700 | 0.84 | 13.45 | 13.05 | 15450 | 0.37 |
| 15000 | 0.94 | 11.53 | 11.94 | 15500 | 0.36 |
| 15500 | 0.85 | 12.83 | 13.26 | 15550 | 0.36 |
| 15750 | 0.78 | 16.28 | 16.42 | 15600 | 0.37 |
| 16000 | 0.78 | 23.88 | 26.29 | 15650 | 0.37 |
| 16300 | 0.92 | 18.62 | 19.59 | 15700 | 0.36 |
| 16700 | 1.17 | 12.25 | 11.82 | 15750 | 0.37 |
| 17000 | 1.17 | 12.68 | 12.04 | 15800 | 0.37 |
| 17400 | 1.24 | 27.13 | 22.78 | 15850 | 0.37 |
| 17990 | 3.00 | 20.60 | 20.87 | 15900 | 0.37 |
| 18310 | 10.30 | 5.05 | 4.06 | 15950 | 0.37 |
| 18610 | 20.15 | 2.57 | 1.80 | 16000 | 0.37 |
| 18920 | 30.04 | 1.87 | 1.22 | 16050 | 0.37 |
| 19000 | 33.56 | 1.79 | 1.15 | 16100 | 0.37 |
| 19500 | 37.33 | 1.39 | 0.84 | 16150 | 0.37 |
| 20000 | 29.40 | 1.26 | 0.76 | 16200 | 0.37 |
| 20500 | 25.52 | 1.43 | 0.89 | 16250 | 0.37 |
| 21000 | 22.90 | 1.61 | 1.07 | 16300 | 0.37 |
| 21500 | 21.73 | 1.49 | 1.22 | 16350 | 0.37 |
| 22000 | 21.03 | 1.30 | 1.52 | 16400 | 0.37 |
| 22500 | 20.97 | 1.16 | 1.83 | 16450 | 0.37 |
| 23000 | 22.21 | 0.88 | 1.61 | 16500 | 0.37 |
| 23500 | 25.31 | 0.53 | 0.94 | 16550 | 0.37 |
| 24000 | 28.77 | 0.30 | 0.49 | 16600 | 0.37 |
| 25000 | 33.33 | 0.28 | 0.24 | 16650 | 0.38 |
| 26000 | 35.27 | 0.53 | 0.24 | 16700 | 0.38 |
| 27000 | 37.13 | 0.65 | 0.46 | 16750 | 0.38 |
| 28000 | 44.37 | 0.42 | 0.71 | 16800 | 0.38 |
| 29000 | 48.67 | 0.32 | 0.70 | 16850 | 0.38 |
| 30000 | 38.75 | 0.32 | 0.40 | 16900 | 0.39 |
| 31000 | 33.14 | 0.44 | 0.15 | 17000 | 0.40 |
| 32000 | 29.16 | 0.61 | 0.14 | 17100 | 0.43 |
| 33000 | 28.77 | 0.66 | 0.33 | 17200 | 0.44 |
| 34000 | 29.15 | 0.75 | 0.67 | 17300 | 0.46 |
| 35000 | 28.98 | 1.14 | 1.39 | 17400 | 0.48 |

Typical Performance Curves



Outline Dimensions

UC2731



Notes:

1. Case material: Gold over Nickel over Annealed Stainless Steel.
2. Base: Ceramic
3. Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Gold over Nickel plate. All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F003



| Tape Width, mm | Device Cavity Pitch, mm | Real Size, inches | Devices per Reel See note |
|-------------------|----------------------------|----------------------|------------------------------|
| 16 | 12 | 7 | 10 |
| | | | 20 |
| | | | 50 |
| | | | 100 |
| | | | 200 |
| | | 13 | 500 |

Note: Please consult individual model data sheet/dashboard to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|------------|-----------------------------------|--------|-----|------|
| OR | ECO-007104 | NEW RELEASE | MAR 21 | DDR | VC |
| A | ECO-010633 | UPDATED AS PER CURRENT TEST BOARD | NOV 21 | DDR | VC |
| B | ECO-019739 | UPDATED TRACE AND SPACE WIDTH | OCT 23 | LK | VC |
| | | TOLERANCE ONLY NO OTHER CHANGES | | | |

SUGGESTED MOUNTING CONFIGURATION FOR UC2731 CASE STYLE



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS $.010 \pm .0010$. COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|--------------|-----------|
| DIMENSIONS ARE IN INCHES | DRAWN: DDR | 29 MAR 21 |
| TOLERANCES ON: | CHECKED: RR | 29 MAR 21 |
| 2 PL DECIMALS ± | APPROVED: NN | 29 MAR 21 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |

Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235


PL DWG, UC2731 C.S, 50 OHM, ABF

| | | | |
|-----------------|-------------------|-----------------------|--------|
| SIZE: A | CODE IDENT: 15542 | DRAWING NO: 98-PL-652 | REV: B |
| FILE: 98-PL-652 | SCALE: 10:1 | SHEET: 1 OF 1 | |


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit

TB-ABF-15R75G+




Schematic diagram



Notes:

1. PCB Material: ROGERS (R04350B) OR Equivalent, Dielectric Constant=3.48±.05
Dielectric Thickness: .010±.001
2. 50 Ohm 2.92mm Female Connectors.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-----------------------|---------------------------------------|---|
| Operating Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Thermal Shock | -55° to 125°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, Except +125°C |