

Engineering Development Model

Power Splitter/Combiner

AD3PS-ED11087/1

3 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CJ725

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.5		380 MHz
Isolation	0.5 - 5 MHz		33	dB
	5 - 190 MHz		28	dB
	190 - 380 MHz		19	dB
Insertion Loss Above 4.8 dB	0.5 - 5 MHz		0.60	dB
	5 - 190 MHz		0.50	dB
	190 - 380 MHz		0.80	dB
Phase Unbalance	0.5 - 5 MHz		0.036	deg.
	5 - 190 MHz		0.281	deg.
	190 - 380 MHz		1.343	deg.
Amplitude Unbalance	0.5 - 5 MHz		0.009	dB
	5 - 190 MHz		0.017	dB
	190 - 380 MHz		0.208	dB
VSWR	SUM Port		1.10	(:1)
	OUT Ports		1.10	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	8
PORT 2	5
PORT 3	4
GND EXT	2, 3, 6, 7

Functional Diagram



3 Way-0° Power Splitter/Combiner

AD3PS-ED11087/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	1-3	2-3			S	1	2	3
0.5	5.78	5.78	5.77	0.01	32.88	31.11	32.72	0.02	0.5	1.38	1.34	1.36	1.34
0.9	5.59	5.59	5.59	0.01	33.63	32.34	33.57	0.03	0.9	1.25	1.25	1.26	1.25
1.0	5.57	5.56	5.56	0.01	33.75	32.53	33.70	0.04	1.0	1.23	1.23	1.24	1.23
2.0	5.39	5.39	5.39	0.00	34.59	33.65	34.57	0.02	2.0	1.14	1.17	1.17	1.17
3.0	5.31	5.31	5.31	0.01	35.11	34.37	35.13	0.04	3.0	1.11	1.14	1.14	1.14
4.0	5.27	5.27	5.27	0.01	35.46	34.83	35.52	0.06	4.0	1.09	1.13	1.13	1.13
5.0	5.24	5.25	5.25	0.01	35.64	35.08	35.70	0.04	5.0	1.07	1.12	1.12	1.12
10.0	5.22	5.22	5.21	0.01	35.90	35.47	35.91	0.05	10.0	1.05	1.10	1.10	1.10
15.0	5.21	5.21	5.21	0.01	35.71	35.38	35.66	0.06	15.0	1.04	1.10	1.10	1.10
20.0	5.21	5.21	5.21	0.00	35.34	35.08	35.18	0.12	20.0	1.04	1.10	1.10	1.10
25.0	5.21	5.21	5.21	0.00	34.79	34.66	34.63	0.13	25.0	1.04	1.10	1.10	1.09
30.0	5.22	5.22	5.22	0.00	34.26	34.20	34.02	0.12	30.0	1.05	1.10	1.10	1.09
35.0	5.23	5.22	5.22	0.00	33.66	33.66	33.34	0.17	35.0	1.05	1.10	1.10	1.09
40.0	5.23	5.23	5.23	0.00	33.05	33.13	32.70	0.19	40.0	1.05	1.10	1.10	1.09
45.0	5.24	5.23	5.23	0.01	32.51	32.60	32.10	0.18	45.0	1.06	1.10	1.10	1.09
50.0	5.24	5.24	5.24	0.00	31.91	32.10	31.47	0.23	50.0	1.06	1.10	1.10	1.09
55.0	5.25	5.24	5.24	0.01	31.35	31.59	30.91	0.19	55.0	1.06	1.10	1.10	1.09
60.0	5.26	5.25	5.25	0.01	30.82	31.06	30.34	0.22	60.0	1.07	1.10	1.10	1.09
65.0	5.26	5.25	5.26	0.00	30.31	30.58	29.80	0.29	65.0	1.07	1.10	1.10	1.10
80.0	5.28	5.27	5.26	0.01	28.88	29.24	28.36	0.36	80.0	1.09	1.11	1.11	1.11
100.0	5.30	5.28	5.28	0.02	27.25	27.66	26.68	0.42	100.0	1.11	1.12	1.12	1.13
120.0	5.32	5.29	5.29	0.03	25.87	26.31	25.27	0.50	120.0	1.12	1.12	1.12	1.13
140.0	5.35	5.31	5.30	0.05	24.66	25.10	24.06	0.59	140.0	1.14	1.12	1.12	1.13
160.0	5.38	5.33	5.32	0.07	23.60	24.05	22.99	0.68	160.0	1.15	1.12	1.12	1.13
180.0	5.41	5.35	5.33	0.08	22.65	23.11	22.02	0.79	180.0	1.16	1.13	1.13	1.14
200.0	5.44	5.37	5.34	0.10	21.80	22.26	21.17	0.86	200.0	1.18	1.15	1.15	1.15
220.0	5.48	5.38	5.36	0.11	21.04	21.50	20.40	0.93	220.0	1.20	1.15	1.15	1.15
240.0	5.52	5.41	5.38	0.14	20.32	20.78	19.68	1.06	240.0	1.22	1.15	1.14	1.15
260.0	5.56	5.43	5.40	0.16	19.66	20.12	19.01	1.18	260.0	1.24	1.14	1.14	1.15
280.0	5.61	5.46	5.42	0.18	19.06	19.51	18.40	1.30	280.0	1.25	1.16	1.15	1.17
300.0	5.66	5.48	5.44	0.22	18.49	18.93	17.82	1.38	300.0	1.27	1.19	1.18	1.19
320.0	5.70	5.50	5.46	0.24	17.95	18.38	17.27	1.47	320.0	1.28	1.21	1.20	1.21
340.0	5.75	5.52	5.48	0.27	17.43	17.87	16.75	1.62	340.0	1.30	1.21	1.19	1.21
360.0	5.81	5.57	5.50	0.31	16.95	17.38	16.25	1.78	360.0	1.32	1.20	1.18	1.20
380.0	5.87	5.59	5.52	0.35	16.49	16.91	15.79	1.85	380.0	1.33	1.21	1.19	1.20

¹ Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2

AD3PS-ED11087/1

100707

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




3 Way-0° Power Splitter/Combiner


AD3PS-ED11087/1

Typical Performance Curves





PCB Land Pattern



METALLIZATION

Weight: .40 gram

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.01; 3 Pl. ±.005 Inch

Notes:

1. Case material: Plastic.
2. Termination finish:
Tin plate over Nickel plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR CJ725 CASE STYLE, "ma", "nf" PIN CONNECTIONS



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $0.020'' \pm 0.0015''$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/18/02

TOLERANCES ON:

CHECKED

HY

08/01/02

2 PL DECIMALS $\pm$

APPROVED

DJ

08/06/02

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VEEDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, ma/nf, CJ725, AD3PS/ADQ, TB-83


SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-063REV:
A

FILE: 98PL063


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-188



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215