

High IP3 Frequency Mixer

ADE-10H+

Level 17 (LO Power +17 dBm) 400 to 1000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	4
RF	6
IF	3
GROUND	1,2,5

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54
H	J	K	L	wt		
.030	.026	.065	.300	grams		
0.76	0.66	1.65	7.62	0.20		

Demo Board MCL P/N: TB-02
Suggested PCB Layout (PL-051)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low conversion loss, 7.0 dB typ.
- good L-R isolation, 39 dB typ.
- high IP3, 30 dBm typ.
- excellent solderability
- aqueous washable
- protected by U.S. Patent 6,133,525

Applications

- cellular
- UHF



Generic photo used for illustration purposes only
CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications


FREQUENCY (MHz)		CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF	IF	\bar{X}	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
400-1000	DC-500	7.0	0.10	8.5	39	29	25	17	30







1 dB COMP.: +14 dBm typ.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
400.00	430.00	6.43	39.60	29.90	2.25	2.68
442.86	472.86	6.26	39.50	28.80	2.68	2.25
485.71	515.71	6.23	38.80	28.70	2.32	2.01
500.00	530.00	6.33	39.00	28.70	2.01	2.32
528.57	558.57	6.44	38.90	28.20	2.37	2.35
571.43	601.43	6.60	37.50	26.60	2.35	2.37
600.00	630.00	6.77	37.30	26.10	2.08	2.35
614.29	644.29	6.66	37.30	25.80	2.35	2.08
657.14	687.14	6.62	36.70	25.20	1.80	2.37
700.00	730.00	6.81	38.00	25.50	2.37	1.80
742.86	772.86	6.52	37.70	25.00	2.27	2.55
750.00	780.00	6.59	37.90	25.10	2.55	2.27
785.71	815.71	6.45	37.70	25.70	1.87	2.65
800.00	830.00	6.52	37.70	25.80	2.65	1.87
828.57	858.57	6.47	36.70	25.50	2.65	1.78
871.43	901.43	6.91	36.70	25.20	1.78	2.65
900.00	930.00	7.26	35.60	24.30	2.55	2.27
914.29	944.29	7.17	35.50	24.10	2.27	2.55
957.14	987.14	7.74	35.20	23.50	2.65	1.82
1000.00	1030.00	7.66	34.20	22.90	1.82	2.65

Electrical Schematic





Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

ADE-10H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+14	+17	+20			+14	+17	+20			+14	+17	+20
160.1	190.1	25.06	11.14	7.61	160.1	190.1	3.93	16.84	22.73	160.1	190.1	-12.20	-1.45	0.13
220.1	250.1	12.76	7.92	6.91	220.1	250.1	13.86	21.35	30.50	220.1	250.1	-2.46	0.09	0.08
280.1	310.1	8.88	7.07	6.74	280.1	310.1	20.09	27.00	30.60	280.1	310.1	0.08	0.21	0.07
340.1	370.1	8.01	6.93	6.65	340.1	370.1	21.94	28.10	31.19	340.1	370.1	0.61	0.19	0.07
400.1	430.1	7.34	6.78	6.54	400.1	430.1	25.19	28.33	30.03	400.1	430.1	0.59	0.19	0.08
460.1	490.1	7.19	6.75	6.54	460.1	490.1	30.46	30.61	31.74	460.1	490.1	0.57	0.16	0.10
520.1	550.1	7.21	6.74	6.50	520.1	550.1	28.61	30.31	30.37	520.1	550.1	0.58	0.22	0.11
580.1	610.1	7.22	6.72	6.41	580.1	610.1	26.23	25.79	28.03	580.1	610.1	0.44	0.24	0.17
640.1	670.1	7.17	6.82	6.50	640.1	670.1	26.79	26.45	30.85	640.1	670.1	0.56	0.20	0.18
700.1	730.1	7.10	6.77	6.50	700.1	730.1	26.66	27.33	26.22	700.1	730.1	0.74	0.30	0.23
740.1	770.1	7.12	6.78	6.50	740.1	770.1	23.90	28.75	29.16	740.1	770.1	0.84	0.35	0.27
800.1	830.1	7.17	6.70	6.34	800.1	830.1	22.12	37.50	29.46	800.1	830.1	1.15	0.69	0.52
840.1	870.1	7.29	6.65	6.31	840.1	870.1	21.04	28.76	32.94	840.1	870.1	1.13	0.83	0.63
900.1	930.1	7.80	6.87	6.41	900.1	930.1	23.86	23.87	26.12	900.1	930.1	0.90	0.89	0.75
940.1	970.1	8.17	7.15	6.54	940.1	970.1	19.06	24.65	24.48	940.1	970.1	0.74	0.93	0.89
1000.1	1030.1	8.53	7.51	6.75	1000.1	1030.1	16.82	24.13	24.47	1000.1	1030.1	0.65	0.87	0.99
1040.1	1070.1	8.69	7.70	6.85	1040.1	1070.1	16.22	19.57	25.28	1040.1	1070.1	0.58	0.76	1.04
1100.1	1130.1	8.91	8.04	7.06	1100.1	1130.1	16.14	17.45	22.81	1100.1	1130.1	0.47	0.64	1.05
1140.1	1170.1	8.88	8.05	7.10	1140.1	1170.1	16.50	17.57	21.36	1140.1	1170.1	0.55	0.67	1.06
1200.1	1230.1	8.75	7.95	7.12	1200.1	1230.1	17.17	18.45	20.43	1200.1	1230.1	0.78	0.88	1.16
1240.1	1270.1	8.66	7.87	7.03	1240.1	1270.1	16.78	17.60	19.42	1240.1	1270.1	0.88	0.90	1.25
1300.1	1330.1	8.45	7.65	6.74	1300.1	1330.1	15.71	16.44	18.89	1300.1	1330.1	1.27	1.17	1.51
1340.1	1370.1	8.12	7.29	6.37	1340.1	1370.1	15.63	17.47	19.82	1340.1	1370.1	1.50	1.42	1.69
1400.1	1430.1	7.81	6.88	6.23	1400.1	1430.1	16.91	21.08	21.15	1400.1	1430.1	1.95	1.85	1.74
1440.1	1470.1	7.68	6.74	6.26	1440.1	1470.1	19.82	20.66	22.23	1440.1	1470.1	2.03	1.83	1.58
1500.1	1530.1	7.45	6.74	6.43	1500.1	1530.1	21.08	21.64	23.27	1500.1	1530.1	2.08	1.65	1.36
1540.1	1570.1	7.38	6.82	6.59	1540.1	1570.1	20.78	22.43	23.62	1540.1	1570.1	2.14	1.51	1.20
1600.1	1630.1	7.48	7.01	6.88	1600.1	1630.1	22.03	23.42	23.77	1600.1	1630.1	2.04	1.25	0.96
1640.1	1670.1	7.56	7.15	7.01	1640.1	1670.1	22.15	23.94	24.12	1640.1	1670.1	1.95	1.08	0.81
1700.1	1730.1	7.75	7.37	7.26	1700.1	1730.1	20.20	24.13	25.28	1700.1	1730.1	2.06	0.99	0.73
1740.1	1770.1	7.86	7.45	7.38	1740.1	1770.1	19.34	24.35	25.40	1740.1	1770.1	2.21	1.04	0.71
1800.1	1830.1	7.96	7.57	7.53	1800.1	1830.1	18.45	24.09	25.79	1800.1	1830.1	2.40	1.11	0.72
1840.1	1870.1	8.13	7.68	7.57	1840.1	1870.1	17.95	23.82	26.22	1840.1	1870.1	2.62	1.31	0.85
1900.1	1930.1	8.34	7.81	7.68	1900.1	1930.1	17.35	23.71	25.67	1900.1	1930.1	2.92	1.55	0.98
1940.1	1970.1	8.62	7.96	7.79	1940.1	1970.1	16.85	22.36	25.72	1940.1	1970.1	3.13	1.77	1.12
2000.1	2030.1	8.96	8.29	8.13	2000.1	2030.1	16.51	22.23	25.38	2000.1	2030.1	3.25	1.83	1.22
2040.1	2070.1	9.48	8.70	8.42	2040.1	2070.1	16.23	21.41	26.03	2040.1	2070.1	3.34	1.90	1.25
2100.1	2130.1	9.87	9.15	8.93	2100.1	2130.1	16.07	21.23	26.26	2100.1	2130.1	3.27	1.73	1.19
2140.1	2170.1	10.40	9.55	9.28	2140.1	2170.1	16.40	19.79	25.08	2140.1	2170.1	3.34	1.74	1.17
2200.1	2230.1	10.80	10.05	9.80	2200.1	2230.1	16.82	20.08	23.90	2200.1	2230.1	3.25	1.50	0.98



Frequency Mixer

ADE-10H+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=700.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=400.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
300.0	400.1	5.91	10.0	410.1	6.73	500.0	500.1	5.44
284.7	415.4	6.01	22.6	422.7	6.72	487.4	512.7	5.51
269.5	430.6	6.05	35.1	435.2	6.74	474.9	525.2	5.72
254.2	445.9	6.14	47.7	447.8	6.76	462.3	537.8	5.85
238.9	461.2	6.17	60.3	460.4	6.86	449.7	550.4	5.93
223.7	476.4	6.24	72.8	472.9	6.86	437.2	562.9	5.99
208.4	491.7	6.22	85.4	485.5	6.86	424.6	575.5	6.02
193.2	506.9	6.29	97.9	498.0	6.88	412.1	588.0	6.06
177.9	522.2	6.31	110.5	510.6	6.84	399.5	600.6	6.07
162.6	537.5	6.36	123.1	523.2	6.90	386.9	613.2	6.10
147.4	552.7	6.39	135.6	535.7	6.96	374.4	625.7	6.16
132.1	568.0	6.38	148.2	548.3	6.96	361.8	638.3	6.14
116.8	583.3	6.39	160.8	560.9	7.04	349.2	650.9	6.19
101.6	598.5	6.41	173.3	573.4	7.06	336.7	663.4	6.29
86.3	613.8	6.46	185.9	586.0	7.07	324.1	676.0	6.29
71.1	629.0	6.43	198.5	598.6	7.17	311.5	688.6	6.30
55.8	644.3	6.56	211.0	611.1	7.17	299.0	701.1	6.32
40.5	659.6	6.63	223.6	623.7	7.19	286.4	713.7	6.36
25.3	674.8	6.69	236.2	636.3	7.30	273.8	726.3	6.42
10.0	690.1	6.75	248.7	648.8	7.33	261.3	738.8	6.43
10.0	710.1	6.77	261.3	661.4	7.43	248.7	751.4	6.46
24.5	724.6	6.77	273.8	673.9	7.49	236.2	763.9	6.53
39.0	739.1	6.79	286.4	686.5	7.43	223.6	776.5	6.51
53.5	753.6	6.82	299.0	699.1	7.48	211.0	789.1	6.52
68.0	768.1	6.77	311.5	711.6	7.49	198.5	801.6	6.56
82.5	782.6	6.85	324.1	724.2	7.46	185.9	814.2	6.52
97.0	797.1	6.78	336.7	736.8	7.53	173.3	826.8	6.54
111.5	811.6	6.74	349.2	749.3	7.47	160.8	839.3	6.60
126.0	826.1	6.78	361.8	761.9	7.49	148.2	851.9	6.57
140.5	840.6	6.79	374.4	774.5	7.55	135.6	864.5	6.56
155.0	855.1	6.80	386.9	787.0	7.44	123.1	877.0	6.56
169.5	869.6	6.77	399.5	799.6	7.40	110.5	889.6	6.55
184.0	884.1	6.84	412.1	812.2	7.41	97.9	902.2	6.64
198.5	898.6	6.93	424.6	824.7	7.35	85.4	914.7	6.60
213.0	913.1	7.04	437.2	837.3	7.43	72.8	927.3	6.67
227.5	927.6	7.18	449.7	849.8	7.42	60.3	939.8	6.81
242.0	942.1	7.29	462.3	862.4	7.39	47.7	952.4	6.82
256.5	956.6	7.55	474.9	875.0	7.47	35.1	965.0	6.97
285.5	985.6	7.71	487.4	887.5	7.50	22.6	977.5	7.08
300.0	1000.1	7.82	500.0	900.1	7.59	10.0	990.1	7.16



Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
160.1	45.18	44.42	43.34	34.72	35.10	36.81
220.1	44.81	42.46	41.26	30.11	32.39	36.93
280.1	42.54	40.33	39.68	27.03	31.18	34.96
340.1	38.73	38.39	38.69	26.37	30.46	33.64
400.1	36.36	36.73	37.44	25.92	29.36	32.26
460.1	35.07	35.96	36.74	24.70	27.82	30.90
520.1	33.73	35.18	36.29	24.15	27.27	29.95
580.1	32.66	34.17	35.71	23.04	26.48	29.56
640.1	32.30	33.68	34.86	22.22	24.91	27.90
700.1	32.04	33.75	35.00	22.34	24.73	26.89
740.1	31.62	33.34	34.48	22.40	24.77	26.47
800.1	31.12	32.86	34.19	23.15	25.73	27.20
840.1	30.61	32.19	33.39	23.43	26.36	27.83
900.1	30.29	31.80	33.02	22.99	27.74	29.74
940.1	29.85	31.66	33.29	22.20	27.16	29.87
1000.1	29.12	30.44	31.80	22.29	25.72	29.46
1040.1	29.06	30.38	32.05	22.80	25.28	28.75
1100.1	28.99	30.15	31.37	24.15	26.06	28.63
1140.1	29.04	30.41	31.55	25.15	26.59	28.40
1200.1	29.52	31.27	32.81	27.83	28.31	28.84
1240.1	30.17	32.20	34.13	30.35	29.65	28.77
1300.1	31.55	34.33	36.89	33.17	30.28	27.53
1340.1	32.84	36.29	37.42	30.84	28.29	25.04
1400.1	35.21	38.44	36.83	25.91	24.29	21.38
1440.1	37.58	38.85	36.77	23.12	21.72	19.46
1500.1	39.96	40.96	38.99	19.60	18.73	17.27
1540.1	39.62	41.43	39.83	17.54	16.94	15.82
1600.1	35.35	38.77	40.21	14.94	14.88	14.20
1640.1	33.55	36.66	38.48	13.32	13.38	12.87
1700.1	30.45	32.68	33.55	11.69	11.79	11.55
1740.1	29.33	30.93	31.16	10.90	11.01	10.70
1800.1	27.73	28.69	28.46	10.33	9.89	9.77
1840.1	26.97	27.35	26.97	9.92	9.25	9.13
1900.1	25.51	25.47	25.16	9.87	8.63	8.40
1940.1	24.41	24.15	23.60	9.34	8.22	7.77
2000.1	22.96	22.72	22.29	9.26	7.81	7.30
2040.1	21.97	21.72	21.36	8.78	7.56	7.04
2100.1	20.71	20.49	20.33	8.86	7.23	6.76
2140.1	19.56	19.42	19.44	8.07	6.84	6.50
2200.1	18.44	18.40	18.35	7.92	6.53	6.06

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
160.1	190.1	44.46	44.25	42.66
220.1	250.1	37.81	40.36	39.94
280.1	310.1	39.78	38.21	38.15
340.1	370.1	38.56	37.45	37.49
400.1	430.1	37.69	37.51	37.34
460.1	490.1	37.03	37.35	38.03
520.1	550.1	38.47	38.49	37.98
580.1	610.1	37.00	35.66	34.51
640.1	670.1	35.19	35.17	34.60
700.1	730.1	36.72	37.63	39.07
740.1	770.1	39.92	42.01	45.33
800.1	830.1	38.65	38.09	36.44
840.1	870.1	32.74	31.70	31.09
900.1	930.1	28.97	27.01	26.69
940.1	970.1	26.89	25.33	24.50
1000.1	1030.1	24.11	23.21	22.31
1040.1	1070.1	22.90	22.21	21.51
1100.1	1130.1	20.96	20.43	19.95
1140.1	1170.1	19.94	19.51	19.23
1200.1	1230.1	18.86	18.18	17.58
1240.1	1270.1	18.48	17.52	16.91
1300.1	1330.1	18.37	17.27	17.55
1340.1	1370.1	18.68	17.98	19.02
1400.1	1430.1	19.58	19.34	20.28
1440.1	1470.1	20.22	19.93	20.72
1500.1	1530.1	21.19	21.14	21.87
1540.1	1570.1	22.17	22.33	23.15
1600.1	1630.1	23.61	24.12	25.23
1640.1	1670.1	24.56	25.36	26.71
1700.1	1730.1	28.01	28.23	29.02
1740.1	1770.1	32.57	30.97	29.20
1800.1	1830.1	30.27	30.27	26.58
1840.1	1870.1	27.32	26.06	24.26
1900.1	1930.1	23.74	21.32	20.79
1940.1	1970.1	22.03	19.94	19.74
2000.1	2030.1	18.97	17.28	17.29
2040.1	2070.1	17.88	16.23	16.44
2100.1	2130.1	15.55	14.35	14.80
2140.1	2170.1	14.93	13.59	14.24
2200.1	2230.1	13.43	12.44	13.35

Frequency Mixer

ADE-10H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)		
		@LO (dBm)		
		+14	+17	+20
160.1	190.1	5.75	3.79	2.85
220.1	250.1	3.86	2.77	2.46
280.1	310.1	2.94	2.45	2.32
340.1	370.1	2.69	2.37	2.26
400.1	430.1	2.48	2.29	2.20
460.1	490.1	2.40	2.26	2.18
520.1	550.1	2.36	2.23	2.16
580.1	610.1	2.28	2.15	2.07
640.1	670.1	2.23	2.13	2.05
700.1	730.1	2.14	2.07	2.01
740.1	770.1	2.09	2.02	1.97
800.1	830.1	2.03	1.96	1.91
840.1	870.1	2.02	1.94	1.90
900.1	930.1	1.99	1.89	1.84
940.1	970.1	1.97	1.86	1.80
1000.1	1030.1	1.92	1.81	1.73
1040.1	1070.1	1.85	1.73	1.64
1100.1	1130.1	1.73	1.62	1.49
1140.1	1170.1	1.63	1.51	1.38
1200.1	1230.1	1.46	1.34	1.20
1240.1	1270.1	1.35	1.22	1.07
1300.1	1330.1	1.24	1.13	1.15
1340.1	1370.1	1.22	1.20	1.33
1400.1	1430.1	1.34	1.45	1.62
1440.1	1470.1	1.47	1.64	1.81
1500.1	1530.1	1.70	1.91	2.09
1540.1	1570.1	1.84	2.06	2.26
1600.1	1630.1	2.00	2.24	2.48
1640.1	1670.1	2.09	2.32	2.59
1700.1	1730.1	2.25	2.46	2.73
1740.1	1770.1	2.33	2.51	2.77
1800.1	1830.1	2.50	2.65	2.86
1840.1	1870.1	2.59	2.69	2.87
1900.1	1930.1	2.79	2.81	2.94
1940.1	1970.1	2.92	2.87	2.94
2000.1	2030.1	3.15	3.05	3.09
2040.1	2070.1	3.35	3.19	3.20
2100.1	2130.1	3.55	3.38	3.39
2140.1	2170.1	3.74	3.52	3.55
2200.1	2230.1	3.87	3.70	3.82

LO (MHz)	LO VSWR (:1)		
	@LO (dBm)		
	+14	+17	+20
160.1	52.65	42.38	16.72
220.1	30.49	11.53	6.30
280.1	16.41	6.37	4.57
340.1	7.05	3.90	3.84
400.1	4.00	3.08	3.48
460.1	3.02	2.69	3.30
520.1	2.35	2.53	3.33
580.1	2.02	2.38	3.23
640.1	1.85	2.36	3.27
700.1	1.74	2.40	3.35
740.1	1.68	2.39	3.35
800.1	1.64	2.42	3.42
840.1	1.63	2.41	3.40
900.1	1.70	2.50	3.50
940.1	1.76	2.57	3.56
1000.1	1.86	2.69	3.70
1040.1	1.92	2.76	3.78
1100.1	1.99	2.83	3.84
1140.1	2.05	2.89	3.92
1200.1	2.12	2.93	3.95
1240.1	2.18	2.99	4.00
1300.1	2.22	2.97	3.94
1340.1	2.27	2.99	3.95
1400.1	2.26	2.90	3.81
1440.1	2.28	2.92	3.85
1500.1	2.33	2.92	3.79
1540.1	2.46	3.03	3.88
1600.1	2.69	3.09	3.81
1640.1	2.88	3.20	3.86
1700.1	3.23	3.27	3.80
1740.1	3.44	3.38	3.83
1800.1	3.83	3.47	3.76
1840.1	3.90	3.53	3.76
1900.1	4.19	3.58	3.67
1940.1	4.15	3.58	3.62
2000.1	4.39	3.60	3.54
2040.1	4.28	3.61	3.52
2100.1	4.46	3.64	3.43
2140.1	4.24	3.58	3.38
2200.1	4.34	3.62	3.33

IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
	@LO (dBm)		
	+14	+17	+20
10.1	2.60	1.88	1.49
22.4	2.69	1.92	1.51
34.6	2.58	1.80	1.44
46.9	2.58	1.83	1.48
59.1	2.55	1.83	1.48
71.4	2.52	1.80	1.48
83.6	2.59	1.85	1.50
95.9	2.62	1.86	1.52
108.1	2.67	1.90	1.55
120.4	2.60	1.87	1.54
132.6	2.64	1.91	1.56
144.9	2.57	1.87	1.52
157.1	2.55	1.85	1.51
169.4	2.50	1.82	1.49
181.6	2.53	1.85	1.52
193.9	2.61	1.91	1.57
206.1	2.57	1.90	1.56
218.4	2.58	1.91	1.56
230.6	2.50	1.85	1.52
242.9	2.46	1.83	1.51
255.1	2.47	1.84	1.52
267.4	2.50	1.87	1.54
279.6	2.56	1.91	1.58
291.9	2.53	1.90	1.57
304.1	2.51	1.89	1.56
316.4	2.54	1.91	1.57
328.6	2.49	1.88	1.55
340.9	2.50	1.90	1.57
353.1	2.49	1.90	1.58
365.4	2.49	1.89	1.57
377.6	2.47	1.87	1.55
389.9	2.44	1.86	1.55
402.1	2.47	1.89	1.57
414.4	2.48	1.90	1.58
426.6	2.46	1.89	1.58
438.9	2.47	1.89	1.57
451.1	2.38	1.83	1.53
463.4	2.38	1.83	1.53
487.9	2.43	1.88	1.58
500.1	2.42	1.88	1.57

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	26	2	22	3	37	28	53	26	66
1	-	29	+0	42	14	26	38	40	32	59	42	56
2	93	56	39	62	42	56	39	55	41	57	53	71
3	>100	62	59	63	56	65	50	63	65	67	66	76
4	>100	86	74	86	74	88	69	80	71	79	71	80
5	>100	>92	>92	>92	88	>92	82	>92	82	89	87	>92
6	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
7	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
8	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
9	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
10	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 700.1 MHz; -1.00 dBm.
 LO IN: 730.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; -8.04 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	33	14	35	16	46	34	55	36	71
1	-	32	+0	37	14	29	37	39	42	63	58	64
2	72	46	31	54	31	51	30	47	32	68	52	68
3	>100	46	41	51	45	50	36	48	51	58	46	71
4	>100	68	57	62	49	80	51	58	49	60	53	64
5	>100	72	74	68	55	61	52	63	50	61	66	64
6	>100	82	67	87	70	73	60	76	56	67	57	66
7	>100	93	76	91	85	77	83	77	78	72	66	71
8	>100	98	83	88	89	86	71	83	68	82	71	73
9	>100	>102	>102	97	95	97	87	83	79	80	76	78
10	>100	>102	>102	>102	101	91	95	93	85	84	83	84
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 700.1 MHz; 9.00 dBm.
 LO IN: 730.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; 1.97 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 ADE-10H+
 100817
 Page 5 of 5




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see www.minicircuits.com

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. LO @ RF=700.1MHz




Conversion Loss vs. IF @ RF=700.1MHz




Conversion Loss vs. IF @ RF=400.1MHz




Conversion Loss vs. IF @ RF=1000.1MHz



IP3 Input




Compression @ RF IN=+14dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	26	2	22	3	37	28	53	26	66
1	-	29	+0	42	14	26	38	40	32	59	42	56
2	93	56	39	62	42	56	39	55	41	57	53	71
3	>100	62	59	63	56	65	50	63	65	67	66	76
4	>100	86	74	86	74	88	69	80	71	79	71	80
5	>100	>92	>92	>92	88	>92	82	>92	82	89	87	>92
6	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
7	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
8	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
9	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
10	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 700.1 MHz; -1.00 dBm.
 LO IN: 730.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; -8.04 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	33	14	35	16	46	34	55	36	71
1	-	32	+0	37	14	29	37	39	42	63	58	64
2	72	46	31	54	31	51	30	47	32	68	52	68
3	>100	46	41	51	45	50	36	48	51	58	46	71
4	>100	68	57	62	49	80	51	58	49	60	53	64
5	>100	72	74	68	55	61	52	63	50	61	66	64
6	>100	82	67	87	70	73	60	76	56	67	57	66
7	>100	93	76	91	85	77	83	77	78	72	66	71
8	>100	98	83	88	89	86	71	83	68	82	71	73
9	>100	>102	>102	97	95	97	87	83	79	80	76	78
10	>100	>102	>102	>102	101	91	95	93	85	84	83	84
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 700.1 MHz; 9.00 dBm.
 LO IN: 730.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; 1.97 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 ADE-10H+
 100817
 Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)

Case Style

CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits[®]

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
			100	
			200	
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	MMG	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR CD541/542/636/637 CASE STYLES,
"jv", "ju", "jw" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN MMG	07/17/02
TOLERANCES ON:	CHECKED WL	08/02/02
2 PL DECIMALS ±	APPROVED DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits[®] 13 Neptune Avenue
 Brooklyn NY 11235


PL, jv/ju/jw, CD541/542/636/637, ADE, TB-02

Mini-Circuits[®]
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-051	REV: A
FILE: 98PL051	SCALE: 8:1	SHEET: 1 OF 1	

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215