

Directional Coupler

ADC-ED10228/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD637


ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		5		1000	MHz
Coupling	Nominal		20.0 ± 1.0		dB
	Flatness		± 0.5		dB
Mainline Loss **	5-50 MHz		0.60		dB
	50-500 MHz		0.60		dB
	500-1000 MHz		0.70		dB
Directivity	5-50 MHz		28		dB
	50-500 MHz		18		dB
	500-1000 MHz		14		dB
VSWR	5-1000 MHz		1.1		(:1)
RF Power Input	5-1000 MHz			0.25	W

Note: ** Mainline loss includes theoretical coupled power loss of 0.044 dB at 20 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
INPUT	1
OUTPUT	6
COUPLED FORWARD	3
NOT USED	5
75Ω TERM. EXTERNAL	4
GROUND	2

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

Directional Coupler

ADC-ED10228/1





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
0.3	1.40	20.84	13.73	12.49	13.01	11.99
0.5	1.15	20.96	16.05	15.11	15.51	14.64
0.7	1.05	21.01	17.48	16.63	16.95	16.26
1.0	0.96	21.03	18.98	18.00	18.24	17.80
3.0	0.70	20.98	24.73	21.85	21.79	22.00
5.0	0.58	20.95	27.30	24.30	24.08	24.55
7.0	0.54	20.92	28.07	26.19	25.82	26.56
9.0	0.52	20.91	28.58	27.71	27.18	28.19
10.0	0.51	20.90	28.78	28.40	27.79	28.93
20.0	0.51	20.89	29.11	32.74	31.37	33.84
30.0	0.51	20.91	28.80	35.10	33.05	36.63
40.0	0.52	20.93	28.55	35.81	33.71	38.06
50.0	0.52	20.94	28.33	35.65	33.89	38.56
75.0	0.54	20.95	27.55	33.84	33.73	38.39
125.0	0.56	20.95	25.85	31.56	33.19	37.77
175.0	0.58	20.96	24.21	30.26	33.14	37.59
225.0	0.59	20.97	22.63	28.27	32.33	36.90
275.0	0.60	20.97	21.22	28.56	31.06	35.94
325.0	0.60	20.96	20.00	26.43	29.53	34.56
375.0	0.61	20.93	18.83	26.86	27.84	32.97
425.0	0.61	20.89	17.87	25.51	26.51	31.85
475.0	0.61	20.84	16.95	25.70	25.28	30.98
525.0	0.62	20.80	16.20	25.01	24.43	30.47
575.0	0.63	20.73	15.62	25.12	23.70	30.16
625.0	0.64	20.67	15.06	24.97	23.19	30.10
675.0	0.65	20.60	14.53	25.10	22.91	30.26
725.0	0.67	20.54	14.16	25.38	22.73	30.69
775.0	0.67	20.47	13.87	24.95	22.74	31.31
825.0	0.70	20.41	13.66	25.42	22.97	32.31
850.0	0.69	20.36	13.58	25.02	23.14	32.96
860.0	0.69	20.35	13.57	24.79	23.23	33.28
870.0	0.69	20.34	13.52	24.60	23.31	33.62
880.0	0.70	20.33	13.51	24.52	23.40	33.98
900.0	0.74	20.35	13.46	24.72	23.67	34.88
1000.0	0.78	20.24	13.31	23.46	25.36	42.49
1100.0	0.82	20.15	13.22	22.29	28.32	42.89
1200.0	0.86	20.12	12.94	21.08	33.62	32.74
1300.0	0.93	20.10	12.28	20.14	35.34	27.75
1400.0	1.00	20.13	11.32	19.51	28.79	24.39
1500.0	1.06	20.20	10.25	18.69	24.44	21.99

Directional Coupler

Typical Performance Curves

ADC-ED10228/1



CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F46



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
16	12	13	900

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	MMG	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL

Technical drawing of a 16-pin DIP package showing dimensions and features:

- PACKAGE OUTLINE**: Indicated by a dashed line.
- PIN 1**: Indicated by a dashed line.
- Dimensions**:
 - $.050$ TYP (Typical)
 - $.177, 2 \text{ PL.}$ (Pitch, 2 PL.)
 - $.025$ (Pitch)
 - $.025$ TYP (Typical)
 - $.064$ TRACE WIDTH, 3 PL. (SEE NOTE BELOW)
- Features**:
 - $7 \times \phi .020$ PTH FOR GROUND (7x $\phi .020$ PTH FOR GROUND)

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE _____

DIMENSIONS ARE IN INCHES

DRAWN

MMG

07/23/02

TOLERANCES ON:

QUESTIONS

LC

08 / 02 / 02

2 PL DECIMALS ±

CHECKED

00/02/02

S PL DECISION ANGLES +

APPROVE

DJ

08/05/02

FRACTIONS $\pm$

100

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

11



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, hz, CD542, ADC, TB-32

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-094


REV:	A
------	---

FILE: 98PL094


SCALE: 8:1

SHEET:	1 OF 1
--------	--------

Evaluation Board and Circuit



TB-32



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215