

Directional Coupler

ADC-ED12367/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.


CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50/75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		.3		1140	MHz
Coupling	Nominal		12.4±03		dB
	Flatness		±0.29		dB
Mainline Loss**	.3-3 MHz		0.86		dB
	3-570 MHz		0.72		dB
	570-1140 MHz		1.15		dB
Directivity	.3-3 MHz		13		dB
	3-570 MHz		12		dB
	570-1140 MHz		11		dB
VSWR	3-1140 MHz		1.18		(:1)
RF Power Input	3-1140 MHz			1.0	W

Note: ** Mainline loss includes theoretical coupled power loss of 0.257 dB at 12.4 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
INPUT (Impedance: 75Ω)	1
OUTPUT (Impedance: 75Ω)	6
COUPLED (Impedance: 50Ω)	3
GND	2
50Ω TERM EXTERNAL	4
ISOLATE (ISOLATE)	5



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

Directional Coupler

ADC-ED12367/1

Typical Performance Data





FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN (dB)	OUT (dB)	CPL
0.3	1.02	12.34	13.13	13.84	15.38	19.08
0.4	0.96	12.30	13.05	15.21	17.21	20.83
0.5	0.93	12.29	13.00	16.13	18.78	21.66
0.6	0.90	12.28	12.98	16.54	19.73	22.61
0.7	0.88	12.27	12.96	16.98	20.83	23.13
0.8	0.86	12.26	12.96	17.45	21.23	23.13
0.9	0.84	12.25	12.96	17.69	22.12	23.69
1.0	0.83	12.25	12.96	17.95	22.61	24.29
2.0	0.72	12.19	12.98	19.08	26.44	25.66
3.0	0.67	12.16	12.97	20.08	28.30	27.32
4.0	0.64	12.14	12.97	20.44	30.71	27.32
5.0	0.62	12.13	12.95	20.44	32.26	28.30
30.0	0.61	12.14	12.89	21.23	40.09	28.30
45.0	0.63	12.16	12.86	21.23	36.61	27.32
50.0	0.64	12.16	12.85	21.23	36.61	27.32
124.0	0.68	12.24	12.69	22.12	32.26	22.12
198.0	0.72	12.30	12.57	22.61	29.42	18.78
272.0	0.75	12.36	12.45	23.13	26.44	16.54
346.0	0.78	12.43	12.36	23.69	24.29	14.88
420.0	0.81	12.49	12.28	23.69	23.13	13.58
480.0	0.84	12.53	12.22	23.69	22.12	12.74
540.0	0.86	12.55	12.14	23.69	21.66	12.01
600.0	0.89	12.57	12.02	23.69	21.66	11.46
675.0	0.94	12.60	11.87	24.29	21.23	10.80
750.0	1.00	12.63	11.72	24.94	21.23	10.30
800.0	1.05	12.65	11.57	26.44	20.83	10.10
850.0	1.11	12.68	11.43	27.32	20.83	9.84
900.0	1.17	12.68	11.23	28.30	20.08	9.66
950.0	1.24	12.71	11.04	29.42	19.73	9.48
1045.0	1.39	12.71	10.60	27.32	18.49	9.26
1140.0	1.55	12.69	10.16	24.29	16.98	9.10
1226.0	1.73	12.67	9.76	21.66	15.75	9.00
1312.0	1.95	12.65	9.47	19.73	14.56	8.85
1398.0	2.20	12.66	9.32	18.22	13.71	8.75
1484.0	2.48	12.67	9.35	16.75	13.08	8.61
1570.0	2.77	12.65	9.69	15.56	12.63	8.39
1656.0	3.08	12.65	10.36	14.56	12.21	8.13
1742.0	3.45	12.69	11.50	13.32	11.82	7.78
1828.0	3.92	12.79	13.45	12.31	11.54	7.43
1914.0	4.56	13.08	16.67	11.46	11.29	7.04
2000.0	5.52	13.73	17.63	10.37	11.37	6.70



Directional Coupler

ADC-ED12367/1

Typical Performance Curves



Case Style

CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M100810	NEW RELEASE	02/13/06	MMG	DY

SUGGESTED MOUNTING CONFIGURATION FOR CD542 CASE STYLE, "kd" PIN CONNECTION



RESISTOR R1: 49.9 Ohm, 1206 SIZE.

- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK WITH BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN MMG	12/29/05
TOLERANCES ON:	CHECKED AV	02/13/06
2 PL DECIMALS ±	APPROVED DY	02/13/06
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, kd, 50/75, CD542, ADC, TB-358


Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.
 ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-215	OR
FILE:	98PL215	SCALE: 8:1	SHEET: 1 OF 1

Evaluation Board and Circuit




TB-358



Schematic Diagram

Notes:

1. BNC and SMA Female connectors
2. PCB Material: Rogers RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215