Engineering Development Model

Power Splitter/Combiner ADP-ED7900/2

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD636

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		**Min.**	**Typ.**	**Max.**	**Units**
Frequency		30.7		1250	MHz
Isolation	**30.7 - 307 MHz**		28		dB
	307 - 625 MHz		31		dB
	625 - 1250 MHz		25		dB
Insertion Loss Above 3.0 dB	**30.7 - 307 MHz**		0.38		dB
	307 - 625 MHz		0.48		dB
	625 - 1250 MHz		0.79		dB
Phase Unbalance	**30.7 - 307 MHz**		0.120		deg.
	307 - 625 MHz		0.368		deg.
	625 - 1250 MHz		0.285		deg.
Amplitude Unbalance	**30.7 - 307 MHz**		0.009		dB
	307 - 625 MHz		0.020		dB
	625 - 1250 MHz		0.059		dB
VSWR	**SUM Port**		1.06		(:1)
	OUT Ports		1.10		(:1)

Note: Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	4
GND EXT	2, 5, 6

Functional Diagram

2 Way-0° Power Splitter/Combiner ADP-ED7900/2

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS[1] (dB) S-1	TOTAL LOSS[1] (dB) S-2	AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (deg.)
30.7	3.38	3.39	0.00	23.52	0.05
37.1	3.37	3.38	0.01	24.68	0.04
43.6	3.37	3.37	0.00	25.65	0.07
50.0	3.36	3.37	0.01	26.48	0.05
127.8	3.36	3.37	0.01	31.40	0.12
205.6	3.37	3.38	0.01	32.53	0.22
283.3	3.39	3.41	0.02	32.73	0.29
361.1	3.42	3.43	0.01	32.47	0.30
438.9	3.45	3.47	0.02	31.82	0.34
516.7	3.49	3.51	0.02	30.87	0.48
594.4	3.52	3.55	0.03	29.60	0.35
672.2	3.54	3.59	0.05	28.19	0.37
750.0	3.59	3.64	0.04	26.82	0.36
777.8	3.62	3.65	0.04	26.37	0.37
805.6	3.64	3.68	0.04	25.94	0.35
833.3	3.65	3.70	0.06	25.50	0.30
861.1	3.67	3.72	0.05	25.10	0.27
888.9	3.70	3.75	0.05	24.76	0.34
916.7	3.71	3.76	0.06	24.39	0.23
944.4	3.74	3.81	0.06	24.11	0.23
972.2	3.76	3.83	0.07	23.86	0.14
1000.0	3.79	3.86	0.07	23.62	0.05
1062.5	3.87	3.93	0.06	23.21	0.01
1125.0	3.94	4.01	0.08	22.90	0.19
1187.5	4.03	4.11	0.08	22.45	0.38
1250.0	4.17	4.24	0.08	21.56	0.68

FREQ. (MHz)	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
30.7	1.13	1.24	1.23
37.1	1.12	1.20	1.20
43.6	1.11	1.18	1.17
50.0	1.10	1.16	1.15
127.8	1.07	1.06	1.06
205.6	1.07	1.05	1.04
283.3	1.07	1.05	1.04
361.1	1.07	1.06	1.05
438.9	1.07	1.07	1.06
516.7	1.06	1.08	1.06
594.4	1.05	1.09	1.07
672.2	1.03	1.09	1.07
750.0	1.03	1.09	1.07
777.8	1.02	1.09	1.07
805.6	1.03	1.09	1.08
833.3	1.04	1.09	1.08
861.1	1.03	1.09	1.08
888.9	1.02	1.09	1.08
916.7	1.04	1.09	1.08
944.4	1.06	1.09	1.09
972.2	1.05	1.09	1.09
1000.0	1.05	1.09	1.10
1062.5	1.06	1.09	1.10
1125.0	1.05	1.09	1.11
1187.5	1.02	1.09	1.10
1250.0	1.03	1.11	1.09

[1] Total Loss = Insertion Loss + 3dB Splitter Loss

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

2 Way-0° Power Splitter/Combiner ADP-ED7900/2

Typical Performance Curves

Total Loss



Isolation



Amplitude Unbalance



Phase Unbalance



VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style CD

CD541
CD542
CD636
CD637

Outline Dimensions





PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.082 (2.08)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.15
CD542					.112 (2.84)							.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:

1. Case material: Plastic.
2. Termination finish:
   For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F34

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.