

Engineering Development Model

Power Splitter/Combiner

ADP-ED7967/1

6 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CJ725

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		0.5		260	MHz
Isolation	0.5 - 5 MHz		36		dB
	5 - 130 MHz		39		dB
	130 - 260 MHz		35		dB
Insertion Loss Above 7.8 dB	0.5 - 5 MHz		0.34		dB
	5 - 130 MHz		0.27		dB
	130 - 260 MHz		0.66		dB
Phase Unbalance	0.5 - 5 MHz		0.164		deg.
	5 - 130 MHz		1.095		deg.
	130 - 260 MHz		4.601		deg.
Amplitude Unbalance	0.5 - 5 MHz		0.018		dB
	5 - 130 MHz		0.025		dB
	130 - 260 MHz		0.101		dB
VSWR	SUM Port		1.14		(:1)
	OUT Ports		1.31		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	8
PORT 2	7
PORT 3	6
PORT 4	5
PORT 5	4
PORT 6	3
GND EXT	2

Functional Diagram



6 Way-0° Power Splitter/Combiner

ADP-ED7967/1






Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)		PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-3	S-5		1-2	3-4			S	1	3
0.5	8.27	8.26	8.27	0.02	36.67	26.96	0.17	0.5	1.20	1.78	2.03
0.6	8.24	8.22	8.24	0.02	37.67	27.41	0.15	0.6	1.19	1.70	1.91
0.7	8.21	8.20	8.22	0.02	38.52	27.86	0.18	0.7	1.18	1.65	1.82
0.8	8.20	8.18	8.20	0.01	39.26	28.27	0.17	0.8	1.17	1.60	1.75
0.9	8.18	8.17	8.19	0.02	39.91	28.65	0.13	0.9	1.16	1.57	1.70
1.0	8.17	8.15	8.17	0.02	40.53	28.98	0.16	1.0	1.15	1.53	1.65
2.0	8.07	8.07	8.09	0.02	44.32	31.51	0.17	2.0	1.12	1.36	1.43
3.0	8.03	8.03	8.05	0.02	46.13	33.21	0.15	3.0	1.10	1.29	1.33
4.0	8.01	8.02	8.03	0.02	46.77	34.46	0.14	4.0	1.09	1.24	1.28
5.0	8.01	8.01	8.02	0.01	46.81	35.43	0.22	5.0	1.09	1.22	1.25
10.0	8.00	7.99	8.01	0.02	45.82	38.16	0.32	10.0	1.08	1.16	1.17
20.0	8.00	8.01	8.03	0.03	44.12	39.63	0.52	20.0	1.08	1.12	1.13
30.0	8.03	8.03	8.05	0.02	42.21	39.20	0.80	30.0	1.09	1.11	1.12
40.0	8.04	8.05	8.07	0.03	40.48	38.25	0.98	40.0	1.10	1.11	1.12
50.0	8.07	8.07	8.10	0.03	39.00	37.27	1.28	50.0	1.11	1.10	1.11
80.0	8.12	8.11	8.13	0.03	36.01	34.87	2.03	80.0	1.15	1.10	1.10
110.0	8.22	8.19	8.22	0.03	34.33	33.39	2.61	110.0	1.18	1.09	1.10
140.0	8.30	8.26	8.28	0.04	33.66	32.82	3.30	140.0	1.19	1.09	1.09
170.0	8.31	8.26	8.28	0.06	33.93	33.16	3.95	170.0	1.18	1.10	1.10
200.0	8.45	8.37	8.40	0.08	35.49	34.65	4.50	200.0	1.14	1.12	1.12
210.0	8.48	8.40	8.42	0.08	36.32	35.48	4.67	210.0	1.13	1.13	1.13
230.0	8.58	8.47	8.50	0.11	38.19	37.42	4.94	230.0	1.13	1.15	1.15
250.0	8.72	8.58	8.59	0.17	37.43	37.24	5.29	250.0	1.18	1.18	1.17
260.0	8.75	8.60	8.61	0.17	35.53	35.48	5.56	260.0	1.23	1.19	1.19

¹ Total Loss = Insertion Loss + 7.8dB Splitter Loss



Typical Performance Curves





Case Style

CJ

Outline Dimensions

CJ725



METALLIZATION

Weight: .40 gram

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.01; 3 Pl. ±.005 Inch

Notes:

1. Case material: Plastic.
2. Termination finish:
Tin plate over Nickel plate.

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit




TB-84



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215