

Surface Mount Power Splitter/Combiner

2 Way-90° 50Ω 104 to 340 MHz

ADQ-32W+



Generic photo used for illustration purposes only

CASE STYLE: CJ725

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

Maximum Ratings



Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

SUMPORT	1
PORT 1 (0°)	5
PORT 2 (+90°)	8
GROUND EXTERNAL	2,3,6,7
50 OHM TERM EXTERNAL	4


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	wt
.397	.032	.385	.435	.310	.215	.100	.015	.025	.035	.075	.120	.060	.420	grams
10.08	0.81	9.78	11.05	7.87	5.46	2.54	0.38	0.64	0.89	1.91	3.05	1.52	10.67	0.45

Demo Board MCL P/N: TB-83 Suggested PCB Layout (PL-063)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 104 to 340 MHz
- good isolation, 20 dB typ.
- good VSWR, 1.24 typ.
- small size surface mount

Applications

- point to point microwave link
- VHF/UHF receivers/transmitters




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) Avg. of Coupled Outputs ABOVE 3 dB		PHASE UNBALANCE (Degrees)		AMPLITUDE UNBALANCE (dB)		VSWR (:1)	
	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	S-Port Typ.	Output Typ.
f _L -f _U	20	16	0.6	0.9	3	8	0.8	1.8	1.22	1.25


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
104.00	2.65	3.99	1.34	22.56	90.93	1.20	1.22	1.22
106.00	2.70	3.93	1.23	22.43	90.97	1.20	1.22	1.22
110.00	2.80	3.82	1.02	22.15	91.02	1.20	1.22	1.22
120.00	3.03	3.58	0.55	21.58	91.15	1.20	1.22	1.23
140.00	3.40	3.26	0.14	20.67	91.41	1.21	1.23	1.23
160.00	3.67	3.07	0.60	20.12	91.68	1.21	1.24	1.24
180.00	3.84	2.98	0.87	19.90	91.94	1.20	1.25	1.25
200.00	3.92	2.95	0.98	19.96	92.15	1.19	1.25	1.25
240.00	3.86	3.04	0.82	21.04	92.47	1.17	1.24	1.24
280.00	3.59	3.32	0.27	24.27	92.65	1.12	1.20	1.22
300.00	3.39	3.53	0.14	27.41	92.73	1.08	1.16	1.19
320.00	3.18	3.81	0.63	30.93	92.86	1.05	1.12	1.17
325.00	3.12	3.89	0.77	31.02	92.91	1.05	1.11	1.17
329.00	3.08	3.96	0.88	30.66	92.95	1.05	1.10	1.17
340.00	2.95	4.16	1.21	28.27	93.11	1.07	1.08	1.17

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



2 Way-90° Power Splitter/Combiner

ADQ-32W+






Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	(dB)						S	1	2
	S-1	S-2							
104.0	2.65	3.99	1.34	22.56	90.93	104.0	1.20	1.22	1.22
106.0	2.70	3.93	1.23	22.43	90.97	106.0	1.20	1.22	1.22
108.0	2.75	3.87	1.12	22.29	90.99	108.0	1.20	1.22	1.22
110.0	2.80	3.82	1.02	22.15	91.02	110.0	1.20	1.22	1.22
115.0	2.92	3.69	0.77	21.86	91.09	115.0	1.20	1.22	1.22
120.0	3.03	3.58	0.55	21.58	91.15	120.0	1.20	1.22	1.23
140.0	3.40	3.26	0.14	20.67	91.41	140.0	1.21	1.23	1.23
160.0	3.67	3.07	0.60	20.12	91.68	160.0	1.21	1.24	1.24
180.0	3.84	2.98	0.87	19.90	91.94	180.0	1.20	1.25	1.25
200.0	3.92	2.95	0.98	19.96	92.15	200.0	1.19	1.25	1.25
220.0	3.93	2.97	0.95	20.34	92.31	220.0	1.18	1.25	1.25
240.0	3.86	3.04	0.82	21.04	92.47	240.0	1.17	1.24	1.24
260.0	3.75	3.16	0.59	22.28	92.56	260.0	1.15	1.22	1.23
280.0	3.59	3.32	0.27	24.27	92.65	280.0	1.12	1.20	1.22
300.0	3.39	3.53	0.14	27.41	92.73	300.0	1.08	1.16	1.19
320.0	3.18	3.81	0.63	30.93	92.86	320.0	1.05	1.12	1.17
321.0	3.17	3.83	0.66	30.99	92.87	321.0	1.05	1.12	1.17
323.0	3.14	3.86	0.71	31.06	92.88	323.0	1.05	1.12	1.17
325.0	3.12	3.89	0.77	31.02	92.91	325.0	1.05	1.11	1.17
327.0	3.10	3.92	0.82	30.90	92.93	327.0	1.05	1.11	1.17
329.0	3.08	3.96	0.88	30.66	92.95	329.0	1.05	1.10	1.17
340.0	2.95	4.16	1.21	28.27	93.11	340.0	1.07	1.08	1.17



¹Total Loss = Insertion Loss + 3dB Splitter Loss




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
CJ608	.397 (10.08)	.032 (.813)	.385 (9.78)	.435 (11.05)	.310 (7.87)	.175 (4.45)	.100 (2.54)	.015 (0.38)	.025 (0.64)	.035 (0.89)
CJ725						.215 (5.46)				

CASE #	L	M	N	P	WT. GRAM
CJ608	.075 (1.91)	.120 (3.05)	.060 (1.52)	.420 (10.67)	.40
CJ725					.45

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
Tin plate over Nickel plate.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100,200
		13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR CJ725 CASE STYLE, "ma", "nf" PIN CONNECTIONS



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	GF	07/18/02
CHECKED	HY	08/01/02
APPROVED	DJ	08/06/02

Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235


PL, ma/nf, CJ725, AD3PS/ADQ, TB-83

Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-063	A
FILE:	98PL063	SCALE:	6:1
SHEET:	1	OF	1

Evaluation Board and Circuit




TB-83



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215