

Engineering Development Model

Power Splitter/Combiner

2 Way-90°

ADQ-ED12533/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.


CASE STYLE : CJ725

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		100		300	MHz
Isolation	100 - 300 MHz		25		dB
Insertion Loss					
Average of Coupled Outputs above 3.0 dB	100 - 300 MHz		0.50		dB
Phase Unbalance	100 - 300 MHz		89.878		deg.
Amplitude Unbalance	100 - 300 MHz		0.976		dB
VSWR	SUM Port		1.15		(:1)
	OUT Ports		1.10		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	8
PORT 2	4
GND EXT	2,3,6,7
50Ω TERMINATION	5

Functional Diagram



2 Way-90° Power Splitter/Combiner

ADQ-ED12533/1






Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2	AVG.					S	1	2
60.0	0.85	8.16	4.51	7.31	36.09	89.57	60.0	1.03	1.04	1.03
70.0	1.08	7.14	4.11	6.07	34.55	89.58	70.0	1.03	1.04	1.03
80.0	1.31	6.33	3.82	5.01	33.43	89.60	80.0	1.04	1.04	1.03
100.0	1.79	5.12	3.46	3.34	31.65	89.61	100.0	1.04	1.05	1.04
110.0	2.02	4.68	3.35	2.66	30.89	89.62	110.0	1.05	1.05	1.04
120.0	2.25	4.32	3.29	2.07	30.14	89.63	120.0	1.05	1.05	1.05
125.0	2.35	4.16	3.26	1.81	29.79	89.65	125.0	1.05	1.05	1.05
130.0	2.45	4.02	3.24	1.57	29.50	89.64	130.0	1.05	1.05	1.05
135.0	2.55	3.89	3.22	1.34	29.23	89.65	135.0	1.06	1.06	1.06
139.0	2.63	3.80	3.22	1.17	29.05	89.65	139.0	1.06	1.06	1.06
140.0	2.65	3.78	3.22	1.13	29.01	89.66	140.0	1.06	1.06	1.06
142.0	2.68	3.73	3.21	1.05	28.90	89.66	142.0	1.06	1.06	1.06
144.0	2.72	3.69	3.21	0.97	28.82	89.66	144.0	1.06	1.06	1.06
146.0	2.75	3.65	3.20	0.90	28.73	89.67	146.0	1.07	1.06	1.06
148.0	2.79	3.61	3.20	0.83	28.63	89.67	148.0	1.07	1.06	1.06
150.0	2.82	3.58	3.20	0.76	28.53	89.67	150.0	1.07	1.06	1.07
154.0	2.88	3.51	3.20	0.62	28.33	89.68	154.0	1.07	1.06	1.07
158.0	2.94	3.45	3.20	0.50	28.15	89.69	158.0	1.07	1.06	1.07
160.0	2.97	3.42	3.20	0.44	28.04	89.70	160.0	1.07	1.06	1.07
170.0	3.10	3.29	3.20	0.19	27.59	89.73	170.0	1.08	1.07	1.08
180.0	3.21	3.20	3.21	0.01	27.17	89.75	180.0	1.09	1.07	1.09
190.0	3.29	3.14	3.22	0.15	26.81	89.78	190.0	1.09	1.07	1.09
200.0	3.35	3.10	3.23	0.24	26.46	89.80	200.0	1.10	1.08	1.10
210.0	3.37	3.10	3.24	0.27	26.13	89.83	210.0	1.11	1.08	1.10
220.0	3.38	3.13	3.26	0.25	25.77	89.87	220.0	1.11	1.08	1.11
230.0	3.34	3.18	3.26	0.16	25.41	89.92	230.0	1.12	1.08	1.12
240.0	3.28	3.27	3.28	0.01	25.06	89.98	240.0	1.12	1.09	1.12
250.0	3.18	3.40	3.29	0.22	24.73	90.06	250.0	1.12	1.09	1.12
260.0	3.06	3.59	3.33	0.52	24.40	90.13	260.0	1.13	1.09	1.12
262.0	3.04	3.63	3.34	0.60	24.35	90.14	262.0	1.13	1.09	1.12
264.0	3.01	3.68	3.35	0.67	24.29	90.16	264.0	1.13	1.09	1.12
266.0	2.97	3.72	3.35	0.75	24.23	90.18	266.0	1.13	1.09	1.12
268.0	2.94	3.77	3.36	0.83	24.17	90.20	268.0	1.13	1.08	1.12
269.0	2.92	3.80	3.36	0.88	24.14	90.21	269.0	1.13	1.08	1.12
270.0	2.91	3.83	3.37	0.92	24.12	90.22	270.0	1.13	1.08	1.12
280.0	2.71	4.13	3.42	1.42	23.84	90.31	280.0	1.12	1.08	1.12
290.0	2.48	4.54	3.51	2.06	23.66	90.41	290.0	1.11	1.07	1.11
300.0	2.22	5.08	3.65	2.86	23.56	90.53	300.0	1.10	1.06	1.10
310.0	1.94	5.82	3.88	3.88	23.64	90.68	310.0	1.08	1.04	1.08
320.0	1.64	6.83	4.24	5.19	23.97	90.92	320.0	1.06	1.02	1.06
330.0	1.34	8.28	4.81	6.94	24.68	91.32	330.0	1.02	1.01	1.03


¹ Total Loss = Insertion Loss + 3dB Splitter Loss



Typical Performance Curves



Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR CJ725 CASE STYLE, "ma", "nf" PIN CONNECTIONS



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	GF	07/18/02
CHECKED	HY	08/01/02
APPROVED	DJ	08/06/02


Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235

PL, ma/nf, CJ725, AD3PS/ADQ, TB-83


Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-063	A
FILE:	98PL063	SCALE:	6:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



TB-83



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215