



# 2 Way-0° Power Splitter/Combiner

# ADP-2-1W+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
1	3.29	3.28	0.01	0.01	24.75	1.09	1.32	1.32
10	3.17	3.16	0.01	0.01	41.91	1.10	1.14	1.14
25	3.16	3.15	0.01	0.00	48.07	1.10	1.13	1.13
50	3.19	3.17	0.02	0.07	39.92	1.11	1.13	1.13
75	3.21	3.20	0.01	0.07	35.98	1.12	1.13	1.13
100	3.23	3.22	0.01	0.09	33.63	1.13	1.13	1.13
125	3.25	3.24	0.01	0.14	31.60	1.13	1.13	1.13
150	3.28	3.26	0.02	0.13	30.11	1.14	1.13	1.13
175	3.30	3.27	0.03	0.13	28.90	1.15	1.13	1.13
200	3.31	3.29	0.02	0.17	27.81	1.16	1.13	1.13
225	3.34	3.31	0.03	0.20	26.97	1.16	1.13	1.12
250	3.34	3.31	0.03	0.21	26.19	1.17	1.13	1.12
275	3.37	3.33	0.04	0.23	25.55	1.18	1.12	1.12
300	3.38	3.34	0.04	0.26	24.95	1.18	1.12	1.12
325	3.40	3.35	0.05	0.26	24.40	1.19	1.12	1.12
350	3.41	3.36	0.05	0.28	23.96	1.19	1.12	1.11
375	3.43	3.38	0.05	0.29	23.60	1.20	1.12	1.11
400	3.44	3.39	0.05	0.30	23.26	1.20	1.11	1.11
425	3.46	3.40	0.06	0.29	23.00	1.20	1.11	1.10
450	3.48	3.41	0.07	0.33	22.80	1.20	1.11	1.10
475	3.49	3.42	0.07	0.32	22.63	1.21	1.10	1.09
500	3.51	3.43	0.08	0.32	22.50	1.20	1.10	1.09
525	3.53	3.44	0.09	0.32	22.44	1.20	1.09	1.08
550	3.55	3.45	0.10	0.30	22.42	1.20	1.09	1.08
575	3.57	3.46	0.11	0.30	22.45	1.19	1.09	1.07
600	3.59	3.48	0.11	0.28	22.54	1.19	1.09	1.07
625	3.61	3.49	0.12	0.26	22.68	1.18	1.09	1.06
650	3.64	3.50	0.14	0.24	22.93	1.17	1.09	1.06
675	3.67	3.52	0.15	0.23	23.21	1.16	1.09	1.06
700	3.69	3.54	0.15	0.21	23.58	1.15	1.10	1.06
750	3.75	3.57	0.18	0.15	24.44	1.14	1.12	1.08
800	3.83	3.63	0.20	0.12	25.48	1.14	1.15	1.11
850	3.94	3.71	0.23	0.09	25.77	1.19	1.19	1.15
900	4.09	3.83	0.26	0.01	24.38	1.27	1.25	1.21
950	4.31	4.01	0.30	0.06	21.55	1.41	1.32	1.28
1000	4.63	4.30	0.33	0.14	18.52	1.59	1.41	1.37

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2  
ADP-2-1W+  
100623  
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# 2 Way-0° Power Splitter/Combiner

# ADP-2-1W+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
1	3.25	3.24	0.01	0.01	19.98	1.12	1.46	1.46
10	3.12	3.12	0.01	0.00	33.10	1.10	1.15	1.15
25	3.12	3.11	0.01	0.01	39.48	1.10	1.11	1.11
50	3.14	3.13	0.01	0.09	38.66	1.11	1.11	1.10
75	3.16	3.16	0.00	0.11	34.92	1.14	1.11	1.11
100	3.18	3.17	0.01	0.15	32.81	1.15	1.12	1.12
125	3.19	3.18	0.01	0.19	31.56	1.15	1.12	1.12
150	3.21	3.19	0.02	0.21	30.44	1.14	1.11	1.11
175	3.22	3.21	0.01	0.23	28.88	1.16	1.11	1.11
200	3.24	3.23	0.01	0.27	27.34	1.19	1.12	1.12
225	3.26	3.24	0.02	0.32	26.43	1.20	1.13	1.13
250	3.26	3.24	0.02	0.34	25.90	1.19	1.12	1.12
275	3.27	3.25	0.02	0.38	25.47	1.19	1.11	1.11
300	3.28	3.26	0.02	0.44	24.83	1.20	1.11	1.11
325	3.30	3.27	0.03	0.45	24.19	1.22	1.11	1.12
350	3.31	3.27	0.04	0.49	23.75	1.22	1.11	1.12
375	3.32	3.28	0.04	0.51	23.52	1.21	1.11	1.11
400	3.33	3.29	0.04	0.53	23.36	1.21	1.10	1.09
425	3.35	3.29	0.06	0.55	23.08	1.22	1.10	1.10
450	3.36	3.30	0.06	0.60	22.82	1.22	1.10	1.10
475	3.37	3.30	0.07	0.61	22.69	1.22	1.10	1.09
500	3.39	3.31	0.08	0.68	22.71	1.21	1.09	1.08
525	3.41	3.33	0.08	0.77	22.83	1.21	1.09	1.07
550	3.41	3.33	0.08	0.65	22.67	1.21	1.09	1.07
575	3.43	3.34	0.09	0.67	22.68	1.20	1.09	1.07
600	3.44	3.35	0.09	0.66	22.72	1.19	1.09	1.07
625	3.46	3.35	0.11	0.66	22.90	1.18	1.08	1.06
650	3.48	3.36	0.12	0.65	23.09	1.17	1.08	1.05
675	3.50	3.38	0.12	0.64	23.38	1.16	1.08	1.05
700	3.52	3.38	0.14	0.63	23.74	1.15	1.09	1.05
750	3.57	3.41	0.16	0.61	24.42	1.14	1.11	1.07
800	3.64	3.46	0.18	0.64	25.25	1.15	1.14	1.10
850	3.76	3.54	0.22	0.69	25.41	1.18	1.19	1.15
900	3.88	3.64	0.24	0.62	23.89	1.27	1.23	1.20
950	4.07	3.81	0.26	0.64	21.22	1.40	1.31	1.28
1000	4.34	4.07	0.27	0.77	18.27	1.59	1.39	1.36

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2  
ADP-2-1W+  
100623  
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# 2 Way-0° Power Splitter/Combiner

# ADP-2-1W+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
1	3.35	3.34	0.01	0.00	25.91	1.07	1.33	1.33
10	3.19	3.18	0.01	0.01	42.83	1.10	1.16	1.16
25	3.19	3.18	0.01	0.02	45.55	1.10	1.15	1.15
50	3.22	3.21	0.01	0.10	37.46	1.11	1.16	1.15
75	3.25	3.23	0.02	0.11	35.54	1.10	1.16	1.15
100	3.27	3.25	0.02	0.16	34.54	1.10	1.15	1.15
125	3.29	3.28	0.01	0.23	32.24	1.11	1.14	1.14
150	3.32	3.30	0.02	0.24	30.00	1.14	1.15	1.15
175	3.34	3.32	0.02	0.27	28.68	1.14	1.15	1.15
200	3.36	3.33	0.03	0.31	28.00	1.14	1.15	1.15
225	3.38	3.35	0.03	0.36	27.57	1.13	1.14	1.14
250	3.39	3.36	0.03	0.39	26.78	1.14	1.14	1.13
275	3.42	3.38	0.04	0.42	25.83	1.16	1.14	1.13
300	3.43	3.40	0.03	0.47	25.03	1.17	1.14	1.14
325	3.45	3.41	0.04	0.49	24.54	1.17	1.14	1.13
350	3.46	3.42	0.04	0.52	24.22	1.17	1.13	1.12
375	3.48	3.43	0.05	0.57	23.90	1.17	1.12	1.11
400	3.50	3.45	0.05	0.57	23.49	1.18	1.12	1.11
425	3.53	3.46	0.07	0.61	23.12	1.19	1.12	1.11
450	3.54	3.48	0.06	0.65	22.87	1.19	1.12	1.11
475	3.56	3.48	0.08	0.66	22.75	1.19	1.11	1.10
500	3.58	3.50	0.08	0.69	22.66	1.18	1.10	1.09
525	3.61	3.52	0.09	0.71	22.61	1.18	1.10	1.08
550	3.63	3.54	0.09	0.72	22.50	1.19	1.10	1.08
575	3.66	3.55	0.11	0.74	22.46	1.19	1.10	1.08
600	3.69	3.57	0.12	0.75	22.55	1.18	1.10	1.07
625	3.72	3.61	0.11	0.81	22.89	1.17	1.10	1.06
650	3.73	3.63	0.10	0.83	23.09	1.17	1.10	1.06
675	3.75	3.63	0.12	0.69	23.21	1.16	1.10	1.07
700	3.78	3.64	0.14	0.67	23.50	1.15	1.10	1.07
750	3.86	3.68	0.18	0.65	24.39	1.13	1.12	1.08
800	3.95	3.74	0.21	0.68	25.59	1.14	1.14	1.11
850	4.06	3.82	0.24	0.75	26.18	1.17	1.18	1.15
900	4.22	3.95	0.27	0.70	25.12	1.25	1.24	1.20
950	4.45	4.14	0.31	0.68	22.20	1.37	1.31	1.27
1000	4.80	4.44	0.37	0.62	19.04	1.55	1.40	1.36

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2  
ADP-2-1W+  
100623  
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# 2 Way-0° Power Splitter/Combiner


# ADP-2-1W+

## Typical Performance Curves


### Total Loss




### Total Loss S-1 vs. TEMPERATURE




### Amplitude Unbalance vs. TEMPERATURE



### Phase Unbalance vs. TEMPERATURE



### Isolation 1-2 vs. TEMPERATURE



REV. X2  
ADP-2-1W+  
100623  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### VSWR



### VSWR SUM vs. TEMPERATURE



### VSWR OUT1 vs. TEMPERATURE





# Case Style


# CD

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

**Mini-Circuits**<sup>®</sup>

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M77049	NEW RELEASE	05/01	AV	CT
A	M82377	UPDATED DRAWING	07/31/02	AV	HY
B	M82846	UPDATED DRAWING	05/13/03	MMG	HY
C	M102713	ADDED BK292 CASE STYLE & "...WITH SMOBC"	01/17/08	MMG	IL

SUGGESTED MOUNTING CONFIGURATION  
FOR BK292/CD542/CD636 CASE STYLES,  
"hv" PIN CONNECTION



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



SOLID BLUE DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 HATCHED BLUE DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	AV	05/30/01
TOLERANCES ON:	DY	06/11/01
2 PL DECIMALS ±	CT	06/11/01
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		


 **Mini-Circuits®** 13 Neptune Avenue  
 Brooklyn NY 11235

PL, hv, BK292/CD542/CD636, ADP/JPS, TB-48


Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-035	C
FILE:	98PL035	SCALE: 10:1	SHEET: 1 OF 1

# Evaluation Board and Circuit




TB-48+



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215