

# Engineering Development Model

## Power Splitter/Combiner

## ADP-ED6714

### 2 Way-0°

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |               |      |       |      |       |
|---------------------------------------|---------------|------|-------|------|-------|
| Parameter                             |               | Min. | Typ.  | Max. | Units |
| Frequency                             |               | 250  |       | 600  | MHz   |
| Isolation                             | 250 - 600 MHz |      | 24    |      | dB    |
| Insertion Loss Above 3.0 dB           | 250 - 600 MHz |      | 0.39  |      | dB    |
| Phase Unbalance                       | 250 - 600 MHz |      | 0.447 |      | deg.  |
| Amplitude Unbalance                   | 250 - 600 MHz |      | 0.034 |      | dB    |
| VSWR                                  | SUM Port      |      | 1.32  |      | (:1)  |
|                                       | OUT Ports     |      | 1.19  |      | (:1)  |

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

| PIN CONNECTIONS |      |
|-----------------|------|
| SUM PORT        | 6    |
| PORT 1          | 3    |
| PORT 2          | 4    |
| GND EXT         | 1    |
| NOT USED        | 2, 5 |

#### Functional Diagram



# 2 Way-0° Power Splitter/Combiner

ADP-ED6714

## Typical Performance Data

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | ISOLATION<br>(dB)<br>1-2 | PHASE<br>UNBAL.<br>(deg.) | FREQ.<br>(MHz) | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|--------------------------|---------------------------|----------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                          |                           |                | S            | 1    | 2    |
| 250.0          | 3.19                            | 3.26 | 0.07                   | 27.05                    | 0.84                      | 250.0          | 1.30         | 1.19 | 1.23 |
| 300.0          | 3.37                            | 3.43 | 0.06                   | 25.63                    | 0.68                      | 300.0          | 1.29         | 1.16 | 1.19 |
| 325.0          | 3.27                            | 3.32 | 0.05                   | 24.96                    | 0.69                      | 325.0          | 1.29         | 1.15 | 1.18 |
| 350.0          | 3.24                            | 3.27 | 0.04                   | 24.46                    | 0.61                      | 350.0          | 1.29         | 1.15 | 1.17 |
| 360.0          | 3.23                            | 3.28 | 0.05                   | 24.31                    | 0.58                      | 360.0          | 1.29         | 1.15 | 1.17 |
| 370.0          | 3.31                            | 3.36 | 0.05                   | 24.22                    | 0.54                      | 370.0          | 1.29         | 1.15 | 1.17 |
| 380.0          | 3.40                            | 3.44 | 0.05                   | 24.12                    | 0.48                      | 380.0          | 1.29         | 1.15 | 1.17 |
| 390.0          | 3.40                            | 3.45 | 0.05                   | 24.00                    | 0.40                      | 390.0          | 1.29         | 1.15 | 1.16 |
| 400.0          | 3.36                            | 3.40 | 0.04                   | 23.87                    | 0.50                      | 400.0          | 1.29         | 1.15 | 1.17 |
| 410.0          | 3.33                            | 3.37 | 0.04                   | 23.77                    | 0.51                      | 410.0          | 1.29         | 1.16 | 1.17 |
| 420.0          | 3.31                            | 3.35 | 0.04                   | 23.69                    | 0.48                      | 420.0          | 1.29         | 1.16 | 1.17 |
| 430.0          | 3.30                            | 3.33 | 0.03                   | 23.64                    | 0.44                      | 430.0          | 1.30         | 1.16 | 1.17 |
| 440.0          | 3.31                            | 3.34 | 0.03                   | 23.64                    | 0.46                      | 440.0          | 1.30         | 1.17 | 1.17 |
| 450.0          | 3.33                            | 3.35 | 0.02                   | 23.66                    | 0.43                      | 450.0          | 1.30         | 1.17 | 1.17 |
| 460.0          | 3.39                            | 3.43 | 0.03                   | 23.68                    | 0.40                      | 460.0          | 1.30         | 1.18 | 1.18 |
| 470.0          | 3.46                            | 3.49 | 0.03                   | 23.70                    | 0.41                      | 470.0          | 1.31         | 1.18 | 1.18 |
| 480.0          | 3.43                            | 3.45 | 0.03                   | 23.69                    | 0.39                      | 480.0          | 1.31         | 1.19 | 1.19 |
| 490.0          | 3.37                            | 3.39 | 0.03                   | 23.73                    | 0.36                      | 490.0          | 1.32         | 1.20 | 1.19 |
| 500.0          | 3.36                            | 3.38 | 0.02                   | 23.80                    | 0.34                      | 500.0          | 1.32         | 1.20 | 1.20 |
| 510.0          | 3.39                            | 3.41 | 0.03                   | 23.89                    | 0.34                      | 510.0          | 1.33         | 1.21 | 1.21 |
| 520.0          | 3.43                            | 3.44 | 0.02                   | 23.97                    | 0.36                      | 520.0          | 1.34         | 1.22 | 1.21 |
| 530.0          | 3.44                            | 3.46 | 0.02                   | 24.06                    | 0.28                      | 530.0          | 1.34         | 1.23 | 1.22 |
| 540.0          | 3.46                            | 3.48 | 0.02                   | 24.16                    | 0.29                      | 540.0          | 1.35         | 1.24 | 1.23 |
| 550.0          | 3.51                            | 3.53 | 0.02                   | 24.24                    | 0.29                      | 550.0          | 1.36         | 1.24 | 1.24 |
| 575.0          | 3.50                            | 3.52 | 0.01                   | 24.39                    | 0.28                      | 575.0          | 1.40         | 1.27 | 1.26 |
| 600.0          | 3.55                            | 3.56 | 0.01                   | 24.42                    | 0.24                      | 600.0          | 1.44         | 1.30 | 1.28 |






<sup>1</sup> Total Loss = Insertion Loss + 3dB Splitter Loss



# 2 Way-0° Power Splitter/Combiner

# ADP-ED6714

## Typical Performance Curves



REV. X2  
ADP-ED6714  
100707  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



# Case Style

# CD

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE# | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | WT, GRAM |
|-------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| CD541 |                |                |                |                | .082<br>(2.08) |                |                |                |                |                |                | .15      |
| CD542 | .272<br>(6.91) | .310<br>(7.87) | .220<br>(5.58) | .100<br>(2.54) | .112<br>(2.84) | .055<br>(1.40) | .100<br>(2.54) | .030<br>(0.76) | .026<br>(0.66) | .065<br>(1.65) | .300<br>(7.62) | .20      |
| CD636 |                |                |                |                | .162<br>(4.11) |                |                |                |                |                |                | .25      |
| CD637 |                |                |                |                | .206<br>(5.23) |                |                |                |                |                |                | .40      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

**Mini-Circuits**<sup>®</sup>

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note          |      |
|----------------|-------------------------|-------------------|------------------------------------|------|
| 16             | 12                      | 7                 | Small quantity standard (see note) | 20   |
|                |                         |                   |                                    | 50   |
|                |                         |                   |                                    | 100  |
|                |                         |                   |                                    | 200  |
|                |                         | 13                | Standard                           | 500  |
|                |                         |                   |                                    | 1000 |

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION                              | DATE     | DR  | AUTH |
|-----|---------|--|----------|-----|------|
| OR  | M77049  | NEW RELEASE                              | 05/01    | AV  | CT   |
| A   | M82377  | UPDATED DRAWING                          | 07/31/02 | AV  | HY   |
| B   | M82846  | UPDATED DRAWING                          | 05/13/03 | MMG | HY   |
| C   | M102713 | ADDED BK292 CASE STYLE & "...WITH SMOBC" | 01/17/08 | MMG | IL   |


SUGGESTED MOUNTING CONFIGURATION  
FOR BK292/CD542/CD636 CASE STYLES,  
"hv" PIN CONNECTION



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ±  
 FRACTIONS ±

INITIALS

DATE

DRAWN

AV

05/30/01

CHECKED

DY

06/11/01

APPROVED

CT

06/11/01



Mini-Circuits®

13 Neptune Avenue  
 Brooklyn NY 11235

PL, hv, BK292/CD542/CD636, ADP/JPS, TB-48

SIZE  
 A

CODE IDENT  
 15542


DRAWING NO:  
 98-PL-035

REV:  
 C

FILE: 98PL035

SCALE: 10:1


SHEET: 1 OF 1




THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit




TB-48+



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition   | Reference/Spec   |
|--------------------------------|---|--|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment   | Individual Model Data Sheet  |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles   | MIL-STD-202, Method 107, Condition A-3, except +100°C  |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak  | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability                  | 10X Magnification   | J-STD-002, 95% Coverage  |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)   | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes   | MIL-STD-202, Method 213, Condition A   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215  |