

Surface Mount RF Transformer

ADT4-1WT+

50Ω 2 to 775 MHz

Maximum Ratings


| | |
|-----------------------|----------------|
| Operating Temperature | -20°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Power | 0.25W |
| DC Current | 30mA |

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

| | |
|---------------|---|
| PRIMARY DOT | 3 |
| PRIMARY | 1 |
| SECONDARY DOT | 4 |
| SECONDARY | 6 |
| SECONDARY CT | 5 |
| NOT USED | 2 |

Outline Drawing



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002


Outline Dimensions (inch)

| A | B | C | D | E | F | G |
|------|------|------|------|------|------|------|
| .272 | .310 | .220 | .100 | .112 | .055 | .100 |
| 6.91 | 7.87 | 5.59 | 2.54 | 2.84 | 1.40 | 2.54 |

| H | J | K | L | wt |
|------|------|------|------|-------|
| .030 | .026 | .065 | .300 | grams |
| 0.76 | 0.66 | 1.65 | 7.62 | 0.20 |

Demo Board MCL P/N: TB-430

Config. A



Features

- excellent return loss, 20 dB typ. in dB bandwidth
- excellent amplitude unbalance, 0.1 dB typ. and phase unbalance, 1 deg. typ. in 1 dB bandwidth
- aqueous washable
- protected under US patent 6,133,525

Applications

- impedance matching
- baluns



Generic photo used for illustration purposes only
CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

| Reel Size | Devices/Reel |
|-----------|------------------|
| 7" | 20, 50, 100, 200 |
| 13" | 500, 1000 |


Transformer Electrical Specifications

| Ω RATIO (Secondary/Primary) | FREQUENCY (MHz) | INSERTION LOSS* | | | PHASE UNBALANCE (Deg.) Typ. | | AMPLITUDE UNBALANCE (dB) Typ. | |
|-----------------------------------|--------------------|-----------------|-------------|-------------|--------------------------------------|-------------------|--|-------------------|
| | | 3 dB MHz | 2 dB MHz | 1 dB MHz | 1 dB bandwidth | 2 dB bandwidth | 1 dB bandwidth | 2 dB bandwidth |
| 4 | 2-775 | 2-775 | 3-600 | 6-250 | 1 | 3 | 0.1 | 0.3 |

* Insertion Loss is referenced to mid-band loss, 0.8 dB typ.

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | INPUT R. LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (Deg.) |
|--------------------|---------------------------|--------------------------|--------------------------------|------------------------------|
| 1.00 | 1.53 | 13.65 | 0.02 | 0.03 |
| 3.00 | 1.02 | 17.61 | 0.00 | 0.03 |
| 10.00 | 0.75 | 21.91 | 0.00 | 0.00 |
| 50.00 | 0.80 | 22.05 | 0.01 | 0.26 |
| 175.00 | 0.98 | 19.93 | 0.03 | 0.89 |
| 250.00 | 1.10 | 18.41 | 0.03 | 1.48 |
| 600.00 | 1.44 | 10.74 | 0.18 | 6.98 |
| 700.00 | 1.81 | 8.91 | 0.23 | 10.48 |
| 775.00 | 2.12 | 7.73 | 0.27 | 14.36 |
| 800.00 | 2.51 | 7.38 | 0.28 | 14.98 |



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. E
M158496
ADT4-1WT+
ED-6920/1
HY/ITD/CP/AM
200417

Typical Performance Data


| FREQUENCY (MHz) | AVERAGE INSERTION LOSS (dB) | INPUT RETURN LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (deg) |
|--------------------|--------------------------------------|---------------------------------|--------------------------------|-----------------------------|
| 1 | 1.53 | 13.65 | 0.02 | 0.03 |
| 3 | 1.02 | 17.61 | 0.00 | 0.03 |
| 10 | 0.75 | 21.91 | 0.00 | 0.00 |
| 50 | 0.80 | 22.05 | 0.01 | 0.26 |
| 175 | 0.98 | 19.93 | 0.03 | 0.89 |
| 250 | 1.10 | 18.41 | 0.03 | 1.48 |
| 600 | 1.44 | 10.74 | 0.18 | 6.98 |
| 700 | 1.81 | 8.91 | 0.23 | 10.48 |
| 775 | 2.12 | 7.73 | 0.27 | 14.36 |
| 800 | 2.51 | 7.38 | 0.28 | 14.98 |

Typical Performance Curves


Average Insertion Loss




Input Return Loss



Amplitude Unbalance



Phase Unbalance





Case Style


CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE# | A | B | C | D | E | F | G | H | J | K | L | WT, GRAM |
|-------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| CD541 | | | | | .082 (2.08) | | | | | | | .15 |
| CD542 | .272 (6.91) | .310 (7.87) | .220 (5.58) | .100 (2.54) | .112 (2.84) | .055 (1.40) | .100 (2.54) | .030 (0.76) | .026 (0.66) | .065 (1.65) | .300 (7.62) | .20 |
| CD636 | | | | | .162 (4.11) | | | | | | | .25 |
| CD637 | | | | | .206 (5.23) | | | | | | | .40 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note | |
|----------------|-------------------------|-------------------|------------------------------------|------|
| 16 | 12 | 7 | Small quantity standard (see note) | 20 |
| | | | | 50 |
| | | | 100 | |
| | | | 200 | |
| | | 13 | Standard | 500 |
| | | | | 1000 |

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.
3. Must use ENA/PNA type agilent's network analyzers with impedance conversion option to convert ports to appropriate impedances.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -20° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |