



Mini-Circuits

CERAMIC

Bandpass Filter & Balun **BBFCG2-3275+**

50Ω 2875 to 3675 MHz

THE BIG DEAL

- Tiny Size, (0805)
- Compact Design Includes Balun & Filter in One Package
- Low Cost
- Temperature Stable
- Hermetically Sealed



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-15

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Telecommunications
- 5G Sub 6 GHz

PRODUCT OVERVIEW

Mini-Circuits' BBFCG2-3275+ is a tiny ceramic RF balun filter with an impedance ratio of 1:2, covering a variety of wireless communications applications from 2875 to 3675 MHz. This model provides low insertion loss, low phase unbalance (relative to 180°), low amplitude unbalance. Fabricated using LTCC technology, the unit comes housed in a tiny, rugged ceramic package (0.079x0.049x0.037") suitable for harsh operating environments.

KEY FEATURES

Feature	Advantages
Compact Design	Integrates filter and balun in one tiny package.
Tiny Size, 0805	Accommodates tight space requirements for dense PCB layouts.
LTCC Construction	LTCC process enables tiny size and low cost, suitable for high-volume production. Rugged ceramic package provides excellent reliability in harsh operating environments.





Mini-Circuits

CERAMIC

Bandpass Filter & Balun **BBFCG2-3275+**

50Ω 2875 to 3675 MHz

ELECTRICAL SPECIFICATIONS AT +25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio			2			
Insertion Loss	F1-F2	2875-3675			3	dB
Return Loss	Unbalanced Port	F1-F2	2875-3675	8.5		dB
	Balanced Port	F1-F2	2875-3675	8.5		
Stopband Rejection	DC-F3	DC-1600	10			dB
	F4-F5	4285-6200	15			
		6200-9300	10			
		9300-10500	5			
Amplitude Unbalance ±	F1-F2	2875-3675	-1.5		1.5	dB
Phase Unbalance	F1-F2	2875-3675	-13		13	Degree

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
RF Power Input	0.5 W at +25°C

Permanent damage may occur if any of these limits are exceeded.


TYPICAL FREQUENCY RESPONSE



DC INTERFACE TABLE

Unbalance Port - GND	DC short
Unbalance Port - Balance Ports	DC open
Balance Port - GND	DC open
Balance Port - Balance Port	DC short

FUNCTIONAL SCHEMATIC





Bandpass Filter & Balun **BBFCG2-3275+**





Mini-Circuits




CERAMIC

Bandpass Filter & Balun BBFCG2-3275+

50Ω 2875 to 3675 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
10	65.73	0.10	2.69	33.47
100	56.34	0.12	0.65	0.57
1000	36.02	0.19	1.21	0.74
1400	32.67	0.25	3.76	4.00
2880	1.58	15.87	0.70	10.93
3680	1.93	11.64	0.46	0.35
4300	23.22	1.33	1.60	12.57
5000	55.34	0.43	4.23	172.84
6000	42.85	0.02	6.18	100.91
9000	56.50	0.53	1.18	177.51
10500	68.37	0.26	0.14	178.10
11000	64.19	0.23	0.10	177.12



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html






Ceramic Bandpass Filter & Balun BBFCG2-3275+

Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
10	65.73	0.10	2.69	33.47
100	56.34	0.12	0.65	0.57
500	42.50	0.17	0.11	0.07
800	38.20	0.18	0.52	0.38
1000	36.02	0.19	1.21	0.74
1400	32.67	0.25	3.76	4.00
1800	31.30	0.41	8.85	46.68
2000	33.18	0.57	4.29	91.52
2200	46.33	0.84	2.96	143.07
2400	32.44	1.60	0.19	6.81
2500	10.80	4.18	1.37	12.00
2600	3.56	11.54	1.26	13.18
2700	2.25	18.31	1.08	12.82
2800	1.72	21.37	0.87	11.89
2880	1.58	15.87	0.70	10.93
2940	1.51	14.23	0.57	10.21
2980	1.48	13.77	0.48	9.68
3040	1.41	13.72	0.36	8.91
3080	1.37	14.03	0.28	8.36
3140	1.30	15.03	0.16	7.57
3180	1.26	16.08	0.08	7.04
3240	1.21	18.44	0.03	6.27
3280	1.19	20.79	0.10	5.76
3340	1.19	27.04	0.19	5.00
3380	1.20	37.27	0.24	4.49
3440	1.26	26.78	0.31	3.71
3480	1.32	21.71	0.36	3.18
3540	1.45	17.22	0.40	2.37
3580	1.56	15.17	0.42	1.81
3640	1.77	12.85	0.45	0.95
3680	1.93	11.64	0.46	0.35
3700	2.02	11.12	0.46	0.06
3800	2.54	9.27	0.43	1.44
3900	3.21	8.74	0.29	3.03
4000	5.34	7.49	0.07	4.99
4100	15.13	2.86	1.03	10.96
4200	25.01	1.69	1.69	25.97
4300	23.22	1.33	1.60	12.57
4400	24.14	1.13	0.93	10.26
4500	26.37	0.96	0.28	8.76
4600	29.39	0.83	0.58	5.76
4700	33.14	0.71	2.03	1.01
4800	37.90	0.61	5.05	17.43
4900	44.54	0.51	11.79	83.03
5000	55.34	0.43	4.23	172.84
5200	45.79	0.28	2.33	121.33
5400	42.74	0.16	3.46	109.53
5600	42.10	0.07	4.31	107.50
5800	42.28	0.01	5.18	105.53
6000	42.85	0.02	6.18	100.91
6500	44.46	0.01	6.29	63.01
7000	46.32	0.21	6.34	8.79
7500	48.00	0.52	10.11	160.58
8000	49.97	0.80	3.98	172.00
8500	52.95	0.80	2.00	175.90
9000	56.50	0.53	1.18	177.51
9500	59.99	0.18	0.77	177.63
10000	62.39	0.10	0.46	176.83
10500	68.37	0.26	0.14	178.10
11000	64.19	0.23	0.10	177.12

Typical Performance Data



Outline Dimensions

Top View



CASE#	A	B	C	D	E	F	G	H	J	WT, GRAM
GE0805C-15	.079 (2.00)	.049 (1.25)	.037 (0.95)	.025 (0.63)	.026 (0.65)	.014 (0.35)	.110 (2.80)	.012 (0.30)	.010 (0.25)	.008

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01(.25)$; 3 Pl. $\pm .005(.100)$

Notes:

- Open style, ceramic base
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All model , (+) suffix.
For RoHS-5 Case Styles: Tin-lead plate over Nickel plate. All model ,no (+) suffix.
- Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004(0.1).
- Pin numbers do not appear on unit. For reference only.
- During the manufacturing process, the pad shape may not be rectangular and may take on a more semi-circle shape. However, the pad dimensions reflect this, with the pad shape being within the specified lengths. The metallization compensates accordingly and so performance will not be influenced by the pad shape





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-15 CASE STYLE



TOP VIEW TO LAYER 2

STACK-UP DIAGRAM



NOTES:

- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR FR4 NP-140TL WITH DIELECTRIC THICKNESS .006"±.0005"; COPPER: 1 OZ. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- COPPER LAYERS 3,4 OF THE PCB IS CONTINUOUS GROUND PLANES.

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

THIRD ANGLE PROJECTION			
			
OR	ECO-010908	NEW RELEASE	12/02/21 ITG IL
REV	ECN No.	DESCRIPTION	DATE DR AUTH
REVISIONS			

UNLESS OTHERWISE SPECIFIED			INITIALS	DATE
DIMENSIONS ARE IN INCHES			DRAWN	ITG
TOLERANCES ON:			CHECKED	GF
2 PL DECIMALS ±			APPROVED	IL
3 PL DECIMALS ±				12/02/21
ANGLES ±				
FRACTIONS ±				
 Mini-Circuits®				
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDOR AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.				
BSHETA1.DWG REV:A DATE:01/12/94				

 Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235			
PL, GE0805C-15, TB-1233+			
SIZE	CODE IDENT	DRAWING NO:	REV:
B	15542	98-PL-724	OR
FILE:	98PL724	SCALE: 15:1	SHEET: 1 OF 1



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A