



CERAMIC

Bandpass Filter & Balun **BBFCG2-232+**

50Ω 2150 to 2550 MHz

THE BIG DEAL

- Tiny size, (0805)
- Compact design includes Balun & Filter in one package
- Low cost
- Temperature stable
- Hermetically sealed



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-15

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Telecommunications
- 5G sub 6GHz
- ISM band

PRODUCT OVERVIEW

Mini-Circuits' BBFCG2-232+ is a tiny ceramic RF balun filter with an impedance ratio of 1:2, covering a variety of wireless communications applications from 2150 to 2550 MHz. This model provides low insertion loss, low phase unbalance (relative to 180°), low amplitude unbalance. Fabricated using LTCC technology, the unit comes housed in a tiny, rugged ceramic package (0.079" x 0.049" x 0.037") suitable for harsh operating environments.

KEY FEATURES

Feature	Advantages
Compact Design	Integrates filter and balun in one tiny package
Tiny size, 0805	Accommodates tight space requirements for dense PCB layouts.
LTCC construction	LTCC process enables tiny size and low cost, suitable for high-volume production. Rugged ceramic package provides excellent reliability in harsh operating environments.



CERAMIC

Bandpass Filter & Balun **BBFCG2-232+**

Mini-Circuits


ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio	—	—	2			
Insertion Loss	F1-F2	2150 - 2550	—	—	3	dB
Return Loss	Unbalanced Port	F1-F2	8.5	—	—	dB
	Balanced Port	F1-F2	8.5	—	—	
Stopband Rejection	F4-F5	3348 - 3748	27	—	—	dB
		8048 - 8448	27	—	—	
		9246 - 9646	27	—	—	
Amplitude Unbalance ±	F1-F2	2150 - 2550	-1.5	—	1.5	dB
Phase Unbalance	F1-F2	2150 - 2550	-13	—	13	Degree

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input	0.5W at 25°C


TYPICAL FREQUENCY RESPONSE



DC INTERFACE TABLE

Unbalance Port - GND	DC short
Unbalance Port - Balance Ports	DC open
Balance port - GND	DC open
Balance port-Balance Port	DC short

FUNCTIONAL SCHEMATIC





CERAMIC


Bandpass Filter & Balun **BBFCG2-232+**

PAD CONNECTIONS



UNBALANCED PORT	1
BALANCED PORT	4,6
GROUND	2,3,7,8
NOT CONNECT OR GND	5

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-BBFCG2-232+
SUGGESTED PCB LAYOUT (PL-724)




STACK-UP DIAGRAM



TOP VIEW TO LAYER 2

- NOTES:
- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
 - TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR FR4 NP-140TL WITH DIELECTRIC THICKNESS .006" ± .0005"; COPPER: 1 OZ. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - COPPER LAYERS 3,4 OF THE PCB IS CONTINUOUS GROUND PLANES.
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

OUTLINE DRAWING



*During the manufacturing process, the pad shape may not be rectangular and may take on a more semi-circle shape. However, the pad dimensions reflect this, with the pad shape being within the specified lengths. The metallization compensates accordingly and so performance will not be affected. In addition, solderability will not be influenced by the pad shape.

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F	G	H	J	wt
.079	.049	.037	.025	.026	.014	.110	.012	.010	grams
2.00	1.25	0.95	0.63	0.65	0.35	2.80	0.30	0.25	.008







CERAMIC

Bandpass Filter & Balun **BBFCG2-232+**

Mini-Circuits

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
10	87.73	0.04	0.99	154.18
100	56.45	0.13	0.63	14.11
1000	36.65	0.26	5.36	20.55
2150	1.26	32.55	0.92	7.24
2550	1.28	33.01	0.20	2.49
3300	31.70	1.43	0.91	7.05
3700	31.69	0.80	1.75	23.32
4400	36.58	0.66	8.45	43.00
5000	40.61	0.56	4.61	167.44
8000	54.83	1.70	0.43	178.61
8500	76.18	1.80	0.01	179.77
9646	53.66	1.45	0.29	174.06



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Ceramic Bandpass Filter & Balun BBFCG2-232+

Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
10	87.73	0.04	0.99	154.18
100	56.45	0.13	0.63	14.11
500	42.23	0.19	4.22	24.31
800	38.12	0.23	5.15	21.64
1000	36.65	0.26	5.36	20.55
1100	36.46	0.30	5.48	20.98
1200	37.05	0.34	5.87	22.29
1300	39.40	0.41	7.25	27.18
1400	48.39	0.52	25.65	128.06
1500	39.13	0.72	1.31	25.53
1600	31.42	1.19	0.29	4.80
1700	19.84	4.27	0.33	1.53
1800	4.98	7.09	0.54	0.95
1850	3.82	7.27	1.54	7.77
1900	3.04	9.34	0.46	22.23
1950	2.24	13.25	1.21	18.05
2000	1.74	19.01	1.40	12.80
2050	1.48	26.52	1.28	9.98
2100	1.34	32.06	1.10	8.36
2150	1.26	32.55	0.92	7.24
2200	1.21	34.87	0.76	6.41
2250	1.17	39.87	0.60	5.71
2300	1.16	37.47	0.44	5.08
2350	1.16	33.29	0.30	4.54
2400	1.17	31.90	0.16	4.02
2450	1.20	32.80	0.03	3.50
2500	1.23	36.42	0.09	2.98
2550	1.28	33.01	0.20	2.49
2600	1.35	26.17	0.31	1.99
2650	1.44	21.55	0.40	1.49
2700	1.57	18.28	0.48	0.97
2750	1.73	15.94	0.54	0.44
2800	1.93	14.34	0.59	0.07
2850	2.16	13.41	0.62	0.57
2900	2.43	13.20	0.64	1.05
2950	2.79	13.74	0.62	1.48
3000	3.36	14.54	0.58	1.85
3100	6.67	7.79	0.36	2.14
3200	16.72	2.63	0.19	1.01
3300	31.70	1.43	0.91	7.05
3400	38.87	1.08	4.09	2.25
3500	34.36	0.92	2.63	19.86
3600	32.33	0.85	2.03	22.26
3700	31.69	0.80	1.75	23.32
3800	31.77	0.77	1.55	23.12
3900	32.24	0.75	1.44	21.45
4000	32.94	0.73	1.14	16.78
4200	34.67	0.70	1.11	4.99
4400	36.58	0.66	8.45	43.00
4600	38.35	0.63	13.97	142.61
4800	39.80	0.60	7.88	177.05
5000	40.61	0.56	4.61	167.44
5500	46.40	0.51	10.71	118.94
6000	48.13	0.55	3.38	173.74
6500	49.04	0.68	2.27	176.32
7000	49.87	0.94	1.60	179.24
7500	51.07	1.32	1.02	178.97
8000	54.83	1.70	0.43	178.61
8500	76.18	1.80	0.01	179.77
9000	61.18	1.53	0.19	176.33
9500	54.40	1.40	0.19	174.26
9646	53.66	1.45	0.29	174.06

Typical Performance Data



Outline Dimensions

Top View



CASE#	A	B	C	D	E	F	G	H	J	WT, GRAM
GE0805C-15	.079 (2.00)	.049 (1.25)	.037 (0.95)	.025 (0.63)	.026 (0.65)	.014 (0.35)	.110 (2.80)	.012 (0.30)	.010 (0.25)	.008

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01(.25)$; 3 Pl. $\pm .005(.100)$

Notes:

- Open style, ceramic base
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All model, (+) suffix.
For RoHS-5 Case Styles: Tin-lead plate over Nickel plate. All model, no (+) suffix.
- Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004(0.1).
- Pin numbers do not appear on unit. For reference only.
- During the manufacturing process, the pad shape may not be rectangular and may take on a more semi-circle shape. However, the pad dimensions reflect this, with the pad shape being within the specified lengths. The metallization compensates accordingly and so performance will not be affected. In addition, solderability will not be influenced by the pad shape

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

**SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-15 CASE STYLE**




TOP VIEW TO LAYER 2

STACK-UP DIAGRAM



1. TOTAL FINISHED THICKNESS 0.057 ± 10%. ⊗
2. PTH HOLES PRESENT FROM COPPER LAYER 1 TO 4.

- NOTES:**
1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
 2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR FR4 NP-140TL WITH DIELECTRIC THICKNESS .006"±.0005"; COPPER: 1 OZ. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 3. COPPER LAYERS 3,4 OF THE PCB IS CONTINUOUS GROUND PLANES.
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.



OR	ECN	NO.	DESCRIPTION	DATE	DR	AUTH
ECO-010908			NEW RELEASE	12/02/21	ITG	IL
REV	ECN	No.	DESCRIPTION	DATE	DR	AUTH

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	ITG	12/02/21
TOLERANCES ON:	GF	12/02/21
2 PL DECIMALS ± .005	IL	12/02/21
3 PL DECIMALS ± .005		
ANGLES ± 1°		


		PL, GE0805C-15, TB-1233+
SIZE B	CODE IDENT 15542	DRAWING NO: 98-PL-724
FILE: 98PL724	SCALE: 15:1	SHEET: 1 OF 1

Mini-Circuits[®]
 13 Neptune Avenue
 Brooklyn NY 11235


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDORS AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Mini-Circuits[®]
 BSHEETA1.DWG REV:A DATE:01/12/94


Evaluation Board and Circuit



TB-1233+




Schematic Diagram



Stack-up Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: FR4 or equivalent, Dielectric Constant=4.5, Total finished Thickness = .057 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A