NON-CATALOG

Coaxial

Low Pass Filter

BBLP-300+
BBLP-300

50Ω Flat Time Delay DC to 180 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- flat group delay for low pulse distortion
- rugged shielded case
- other BBLP models available with wide selection of cut-off frequencies

Applications

- linear modulation techniques
- voice transmission applications
- digital communications

CASE STYLE: FF55

Connectors	Model	Price	Qty.
BNC	BBLP-300(+)	Contact Sales Dept.	

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz) (loss <1.2 dB) Min.	fco, MHz Nom. (loss 3 dB)	STOPBAND (MHz) (loss > 10 dB)	STOPBAND (MHz) (loss > 20 dB)	VSWR (:1) DC-0.2fco x̄	VSWR (:1) DC-0.6fco x̄	GROUP DELAY VARIATION (nsec) DC-fco x̄	GROUP DELAY VARIATION (nsec) DC-2fco x̄	GROUP DELAY VARIATION (nsec) DC-2.67fco x̄
DC-180	300	600-801	801	1.25:1	2.2:1	0.2	0.6	0.8

Outline Drawing



Outline Dimensions (inch / mm)

B	D	wt
.54	2.59	grams
13.72	65.79	40.0

TYPICAL GROUP DELAY



TYPICAL FREQUENCY RESPONSE INSERTION LOSS



Electrical Schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) x̄	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
10.0	0.16	0.2	30.7	10.0	1.563
67.0	0.27	0.2	16.4	39.0	1.282
95.0	0.37	0.1	13.4	67.0	1.509
124.0	0.53	0.1	11.1	95.0	1.368
152.0	0.73	0.1	9.4	124.0	1.468
180.0	0.99	0.1	7.9	125.0	1.487
200.0	1.24	0.1	7.1	180.0	1.297
267.0	2.35	0.2	4.9	200.0	1.351
300.0	3.06	0.2	4.1	234.0	1.343
400.0	5.85	0.2	2.5	267.0	1.534
458.0	7.82	0.2	1.8	300.0	1.427
515.0	9.91	0.3	1.3	400.0	1.383
543.0	11.02	0.4	1.1	429.0	1.448
572.0	12.18	0.4	0.9	458.0	0.984
600.0	13.35	0.5	0.8	486.0	1.599
700.0	17.70	0.5	0.5	515.0	1.173
729.0	18.96	0.6	0.5	543.0	1.140
758.0	20.25	0.6	0.5	572.0	1.134
773.0	20.92	0.6	0.5	600.0	0.869
787.0	21.51	0.6	0.5	700.0	0.878
801.0	22.10	0.6	0.5	715.0	0.983
900.0	26.28	0.7	0.6	729.0	0.767
950.0	28.25	0.7	0.7	744.0	1.244
1000.0	30.16	0.8	0.8	758.0	0.807
1050.0	32.02	0.9	0.8	773.0	1.089
1100.0	33.74	0.9	0.9	787.0	1.144
1125.0	34.62	1.1	0.9	801.0	0.587
1150.0	35.50	1.2	1.0	900.0	0.940
1175.0	36.29	1.2	1.0	925.0	0.980
1200.0	37.10	1.4	1.0	950.0	0.475

INSERTION LOSS



RETURN LOSS



GROUP DELAY



Coaxial Low Pass Filter (Flat Time Delay) BBLP-300

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.0	0.16	30.70
67.0	0.27	16.40
95.0	0.37	13.40
124.0	0.53	11.10
152.0	0.73	9.40
180.0	0.99	7.90
200.0	1.24	7.10
267.0	2.35	4.90
300.0	3.06	4.10
400.0	5.85	2.50
458.0	7.82	1.80
515.0	9.91	1.30
543.0	11.02	1.10
572.0	12.18	0.90
600.0	13.35	0.80
700.0	17.70	0.50
729.0	18.96	0.50
758.0	20.25	0.50
773.0	20.92	0.50
787.0	21.51	0.50
801.0	22.10	0.50
900.0	26.28	0.60
950.0	28.25	0.70
1000.0	30.16	0.80
1050.0	32.02	0.80
1100.0	33.74	0.90
1125.0	34.62	0.90
1150.0	35.50	1.00
1175.0	36.29	1.00
1200.0	37.10	1.00

FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	1.563
39.0	1.282
67.0	1.509
95.0	1.368
124.0	1.468
125.0	1.487
180.0	1.297
200.0	1.351
234.0	1.343
267.0	1.534
300.0	1.427
400.0	1.383
429.0	1.448
458.0	0.984
486.0	1.599
515.0	1.173
543.0	1.140
572.0	1.134
600.0	0.869
700.0	0.878
715.0	0.983
729.0	0.767
744.0	1.244
758.0	0.807
773.0	1.089
787.0	1.144
801.0	0.587
900.0	0.940
925.0	0.980
950.0	0.475

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Coaxial Low Pass Filter (Flat Time Delay) BBLP-300

Typical Performance Curves

Insertion Loss



Return Loss



Group Delay



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style FF

FF55

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	-- --	.57 (14.47)	-- --	2.59 (65.79)	-- --	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

1. Case material: Stainless steel.

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV28

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.