

Ceramic


Bandpass Filter

BFCN-7331+

50Ω 6850 to 7850 MHz

The Big Deal

- LTCC construction
- Temperature stable from -55 to +100°C
- Small size (0.126 x .063 X .037")



CASE STYLE: FV1206-4

Product Overview

The BFCN-7331+ LTCC bandpass filter covers the 6850 to 7850 MHz passband with 1.4 dB passband insertion loss, 23 dB lower stop band rejection, and 20 dB upper stopband rejection. This model handles up to 2.5W RF input power and provides a wide operating temperature range from -55 to +100°C. Utilizing LTCC multi-layer construction, the filter achieves excellent repeatability of performance and comes in a tiny 1206 ceramic package with wraparound terminations, minimizing performance variations due to parasitics and saving space in dense PCB layouts.

Key Features

Feature	Advantages
LTCC Construction	Provides a rugged package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.126 x .063 x .037")	Saves space in dense circuit boards and minimizes the effects of parasitics.
Wrap-around terminations	Provides excellent solderability and easy visual inspection
Wide operating temperature range, -55 to +100°C	Enables reliable performance in extreme environments




Ceramic

Bandpass Filter

50Ω 6850 to 7850 MHz

BFCN-7331+



Generic photo used for illustration purposes only

CASE STYLE: FV1206-4

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size 7" Devices/Reel 20, 50, 100, 200, 500, 1000, 3000


Features

- Small size(0.126 x .063 x .037)
- Temperature stable
- LTCC construction


Applications

- Harmonic rejection
- Transmitters / Receivers
- UWB impulse radar
- Emission masking


Specification Definition



Functional Schematic



Top View



Pad Connections

Input	1
Output	3
Ground	2,4

Electrical Specifications^{1,2} at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	7330	—	MHz
	Insertion Loss	F1 - F2	—	1.4	3.5	dB
	VSWR	F1 - F2	—	1.45	—	:1
Stop Band, Lower	Insertion Loss	DC - F3	10	23	—	dB
	VSWR	DC - F3	—	19	—	:1
Stop Band, Upper	Insertion Loss	F4 - F5	10	20	—	dB
	VSWR	F4 - F5	—	20	—	:1





1. Measured on Mini-Circuits Characterization Test Board TB-824+.

2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.

Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	2.5 W at 25°C

*Passband rating, derate linearly to 0.7 W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
ECO-011185
ED-15031105/3
BFCN-7331+
AVB/CP/AM
211221
Page 2 of 3

Bandpass Filter

BFCN-7331+

Full Band Performance

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Insertion Loss (dB)	Group Delay (nsec)
10	46.84	28.76	6850	1.84	0.34
50	46.46	58.17	6900	1.81	0.32
100	79.43	145.73	6950	1.79	0.32
500	56.33	103.82	7000	1.76	0.31
1000	45.00	82.08	7050	1.74	0.30
2000	33.01	73.35	7100	1.73	0.30
3000	25.04	77.98	7150	1.71	0.30
4000	21.00	77.98	7200	1.68	0.30
5800	26.32	21.94	7250	1.66	0.30
6850	1.84	1.80	7300	1.64	0.30
7350	1.61	1.72	7400	1.58	0.30
7850	1.60	1.23	7500	1.51	0.31
9300	20.59	11.64	7600	1.47	0.35
10500	26.05	37.56	7700	1.53	0.37
13300	30.42	21.10	7800	1.53	0.37
14000	19.49	13.58	7850	1.60	0.38



Pass Band Performance

Pad Connections


Input	1
Output	3
Ground	2,4

Product Marking: GS

Outline Drawing



Demo Board MCL P/N: TB-824+ Suggested PCB Layout (PL-454)



NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0066"±.0007". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J
.126	.063	.037	.026	.075	.012	.182	.104	.069
3.20	1.60	0.94	0.66	1.91	0.30	4.62	2.64	1.75
K	L	M	N	P	Q	R	wt	
.119	.041	.039	.013	.024	.020	.039	grams	
3.02	1.04	0.99	0.33	0.61	0.51	0.99	.020	

Additional Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (ns)
10	46.84	0.60	6850	0.34
50	46.46	0.30	6900	0.32
100	79.43	0.12	6950	0.32
200	70.30	0.13	7000	0.31
300	65.69	0.14	7050	0.30
400	60.54	0.16	7100	0.30
500	56.33	0.17	7150	0.30
600	53.62	0.18	7200	0.30
700	51.10	0.19	7250	0.30
800	48.71	0.20	7300	0.30
900	46.71	0.20	7350	0.30
1000	45.00	0.21	7400	0.30
1200	42.03	0.22	7450	0.31
1400	39.41	0.23	7500	0.31
1600	37.10	0.23	7550	0.32
1800	34.94	0.24	7600	0.33
2000	33.01	0.24	7650	0.34
2200	31.17	0.23	7700	0.35
2400	29.48	0.23	7750	0.35
2600	27.88	0.23	7800	0.37
2800	26.40	0.23	7850	0.38
3000	25.04	0.22		
3200	23.84	0.22		
3400	22.82	0.22		
3600	22.01	0.22		
3800	21.40	0.23		
4000	21.00	0.22		
4500	20.60	0.24		
5000	21.00	0.31		
5500	25.00	0.48		
6000	13.51	1.46		
6500	2.56	8.57		
6850	1.84	10.92		
6900	1.81	10.85		
6950	1.79	10.79		
7000	1.76	10.81		
7050	1.74	10.78		
7100	1.73	10.78		
7150	1.71	10.85		
7200	1.68	10.88		
7250	1.66	10.95		
7300	1.64	11.19		
7350	1.61	11.53		
7400	1.58	11.91		
7450	1.55	12.50		
7500	1.51	13.21		
7550	1.49	14.06		
7600	1.47	15.22		
7650	1.46	16.74		
7700	1.47	18.36		
7750	1.49	20.15		
7800	1.53	21.24		
7850	1.60	19.81		
8000	2.05	12.94		
8500	7.44	3.54		
9000	26.69	1.82		
9500	19.66	1.23		
10000	21.92	0.72		
10500	26.05	0.46		
11000	32.47	0.32		
11500	26.16	0.38		
12000	32.12	0.38		
12500	39.37	0.56		
13000	38.15	0.63		
13500	26.72	0.96		
14000	19.49	1.28		

Typical Performance Curves



DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152168	NEW RELEASE	07/31/15	ITG	AVB

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-4 CASE STYLE, "04FL01" PIN CODE

**NOTES:**

- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 04FL01, FV1206-4, TB-824+

SIZE
A

CODE IDENT
15542

DRAWING NO:

98-PL-454

REV:

OR

FILE: 98PL454


SCALE:

16:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-824+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A