



HIGH POWER

# Bi-Directional Coupler **BDCA1-6-22+**

Mini-Circuits

50Ω    6 dB    DC Pass    950 to 2200 MHz

## FEATURES

- Wideband, 950 to 2200 MHz
- Excellent VSWR, 1.15:1 Typ.
- Excellent Power Handling Capability, 44 W (1900 MHz)
- Hermetically Sealed
- Low Temperature Variation
- Protected by US Patent 7,049,905
- DC Current Through Input to Output, 0.25 A Max. at 1.0 Watt RF Input Power



Generic photo used for illustration purposes only

CASE STYLE: DZ944

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

## APPLICATIONS

- DCS, PCS
- Mobile Satellite

## ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		950		2200	MHz
Coupling	950-1400		6.9±1.0		dB
	1400-1900		6.0±0.5		
	1900-2200		6.5±0.7		
Coupling Flatness	950-1400			±1.0	dB
	1400-1900			±0.3	
	1900-2200			±0.7	
Mainline Loss <sup>1</sup>	950-1400		1.4	1.9	dB
	1400-1900		1.7	2.1	
	1900-2200		1.7	2.1	
Directivity	950-1400	14	15		dB
	1400-1900	17	19		
	1900-2200	17	24		
VSWR	950-1400		1.3		:1
	1400-1900		1.2		
	1900-2200		1.1		
Input Power <sup>2</sup>	950-1400			57	W
	1400-1900			44	
	1900-2200			37	

1. Includes theoretical coupled power loss of 1.25 dB at 6 dB coupling.


2. Derate linearly 1/3 at +100°C.

## ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
DC Current	0.25 A

Permanent damage may occur if any of these limits are exceeded.

## ELECTRICAL SCHEMATIC



\* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. H  
ECO028422  
BDCA1-6-22+  
MCL NY  
260206  
PAGE 1 OF 3



**HIGH POWER**

# Bi-Directional Coupler **BDCA1-6-22+**


Mini-Circuits

50Ω    6 dB    DC Pass    950 to 2200 MHz

## PIN CONNECTIONS


INPUT	1
OUTPUT	6
COUPLED (FORWARD)	10
COUPLED (REVERSE)	5
GROUND	2,3,4,7,8,9

## OUTLINE DRAWING



**PRODUCT MARKING:** LA5C19B

## DEMO BOARD MCL P/N: TB-BDCA1-6-22+ SUGGESTED PCB LAYOUT (PL-004)




NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

## OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F	G
.30	.250	.052	.266	.050	.050	.012
7.62	6.35	1.32	6.76	1.27	1.27	0.30
H	J	K	L	M	wt	
.029	.004	.085	.296	.030	grams	
0.74	0.10	2.16	7.52	0.76	0.25	

## TAPE & REEL INFORMATION: F34



HIGH POWER




# Bi-Directional Coupler **BDCA1-6-22+**

Mini-Circuits

50Ω    6 dB    DC Pass    950 to 2200 MHz

### TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
		In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd
900	1.22	7.5	7.54	15.23	15.8	18.64	18.67	17.72	17.69
1100	1.43	6.55	6.56	16.29	17.5	19.41	19.76	18.76	18.92
1200	1.52	6.2	6.2	17.12	18.5	20.21	20.71	19.46	19.66
1300	1.6	5.93	5.92	18.12	19.68	21.24	21.86	20.49	20.95
1400	1.66	5.72	5.7	19.24	20.86	22.49	23.23	21.6	22.31
1500	1.7	5.57	5.55	20.62	22.05	23.97	25.13	22.81	23.7
1600	1.73	5.48	5.45	22.24	24.18	25.83	27.52	24.95	25.98
1800	1.74	5.46	5.44	28.31	29.48	31.68	37.22	28.96	32.3
2000	1.68	5.68	5.65	63.76	43.54	33.63	34.59	31.77	39.12
2200	1.54	6.14	6.11	27.43	29.18	28.27	26.73	29.16	30.27



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# Bi-Directional Coupler

# BDCA1-6-22+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQ. (MHz)	INSERTION LOSS (dB)		COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
500	0.53	0.52	11.72	11.73	18.07	18.18	24.11	24.10	25.66	25.54
600	0.67	0.66	10.45	10.46	18.49	18.56	23.08	23.23	24.69	24.73
700	0.81	0.80	9.45	9.45	19.00	19.13	22.61	22.60	24.18	24.24
800	0.95	0.94	8.65	8.65	19.71	19.83	22.43	22.46	24.07	24.22
900	1.09	1.07	8.00	8.00	20.55	20.70	22.56	22.50	24.41	24.66
925	1.12	1.11	7.86	7.86	20.77	20.92	22.70	22.60	24.56	24.71
940	1.14	1.12	7.78	7.78	20.92	21.06	22.76	22.67	24.68	24.83
950	1.15	1.13	7.72	7.73	21.02	21.17	22.83	22.74	24.77	24.96
960	1.16	1.15	7.67	7.68	21.14	21.29	22.90	22.82	24.86	25.05
1000	1.21	1.20	7.48	7.48	21.61	21.81	23.17	23.12	25.24	25.34
1050	1.27	1.26	7.25	7.25	22.17	22.36	23.59	23.42	25.71	25.85
1100	1.33	1.32	7.05	7.06	22.79	23.02	24.01	23.85	26.41	26.56
1150	1.38	1.37	6.87	6.87	23.56	23.87	24.67	24.48	27.38	27.28
1200	1.43	1.42	6.71	6.72	24.38	24.66	25.63	25.32	28.37	27.96
1250	1.48	1.47	6.57	6.57	25.32	25.44	26.54	26.12	29.63	28.97
1300	1.52	1.51	6.45	6.45	26.35	26.47	27.67	27.08	31.45	30.16
1350	1.56	1.55	6.34	6.35	27.61	27.52	29.11	28.25	33.82	31.12
1400	1.59	1.58	6.25	6.26	28.95	28.62	31.32	29.83	37.08	31.96
1450	1.62	1.62	6.18	6.19	30.41	29.37	33.81	31.69	41.87	32.63
1500	1.65	1.65	6.13	6.13	31.72	29.90	37.00	33.40	50.98	32.34
1550	1.67	1.67	6.09	6.10	32.54	30.09	39.77	34.59	42.39	31.42
1600	1.69	1.69	6.06	6.07	32.38	29.56	38.12	34.26	36.68	30.33
1650	1.71	1.71	6.06	6.06	31.61	28.67	34.34	32.70	33.05	29.03
1700	1.72	1.72	6.06	6.07	30.06	27.52	31.46	30.84	30.44	27.55
1750	1.73	1.72	6.09	6.09	28.63	26.32	29.09	29.05	28.37	26.25
1800	1.73	1.73	6.12	6.13	27.05	25.01	27.18	27.35	26.62	25.09
1850	1.73	1.73	6.18	6.18	25.64	23.90	25.59	25.82	25.19	24.07
1900	1.72	1.72	6.24	6.25	24.33	22.87	24.20	24.54	24.02	23.11
1950	1.71	1.71	6.32	6.33	23.21	21.84	23.08	23.49	23.01	22.33
2000	1.70	1.70	6.42	6.42	22.22	20.92	22.14	22.55	22.13	21.55
2050	1.68	1.68	6.54	6.54	21.22	19.95	21.30	21.73	21.34	20.80
2100	1.66	1.66	6.66	6.66	20.24	19.17	20.50	20.87	20.62	20.14
2150	1.64	1.65	6.80	6.81	19.35	18.25	19.83	20.22	20.05	19.63
2190	1.63	1.63	6.93	6.93	18.65	17.57	19.47	19.84	19.68	19.13
2200	1.62	1.62	6.98	6.99	18.37	17.43	19.46	19.86	19.64	19.15
2210	1.60	1.61	7.00	7.01	18.41	17.39	19.31	19.68	19.46	19.00
2225	1.60	1.61	7.05	7.05	18.15	17.10	19.13	19.50	19.27	18.83
2250	1.58	1.58	7.14	7.15	17.82	16.79	18.95	19.24	19.08	18.57
2300	1.56	1.56	7.33	7.33	17.01	15.94	18.47	18.79	18.62	18.12
2400	1.48	1.48	7.76	7.77	15.63	14.76	17.98	18.19	18.00	17.45
2500	1.40	1.41	8.26	8.29	14.25	13.38	17.52	17.77	17.48	16.98
2600	1.32	1.33	8.89	8.94	12.79	11.98	17.38	17.70	17.32	16.73
2700	1.23	1.24	9.61	9.63	11.62	10.66	17.22	17.62	17.18	16.57
2800	1.16	1.17	10.58	10.58	9.88	8.96	17.41	17.87	17.36	16.63
2900	1.05	1.06	11.63	11.63	8.63	7.64	17.35	18.11	17.40	16.78
3000	0.98	1.00	13.05	12.96	6.88	5.86	17.52	18.42	17.41	16.78
3100	0.91	0.92	14.95	14.83	4.45	3.55	17.64	18.77	17.72	17.23
3200	0.85	0.87	17.36	17.17	1.76	0.95	17.48	18.55	17.59	17.29
3300	0.84	0.83	20.81	20.36	1.84	2.73	17.13	18.06	17.46	17.36
3400	0.87	0.86	26.31	25.19	7.15	8.48	16.75	17.04	16.89	17.13
3500	0.92	0.87	29.02	28.78	11.27	11.46	16.18	15.99	16.45	16.78
3750	1.10	1.04	17.55	18.32	1.87	0.45	14.38	13.51	14.73	15.10
4000	1.40	1.33	13.14	13.67	2.24	3.92	12.72	11.59	12.98	13.25

REV. X1

BDCA1-6-22+

081019

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Bi-Directional Coupler

# BDCA1-6-22+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -55°C

FREQ. (MHz)	INSERTION LOSS (dB)		COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
500	0.45	0.44	11.71	11.67	18.57	18.58	24.96	24.75	26.70	26.56
600	0.58	0.57	10.43	10.39	19.11	18.89	23.94	23.98	25.40	25.42
700	0.71	0.70	9.41	9.37	19.65	19.49	23.47	23.37	25.03	25.02
800	0.85	0.84	8.61	8.55	20.21	20.12	23.18	23.16	24.49	24.58
900	0.98	0.97	7.95	7.89	21.08	21.05	23.33	23.24	24.69	24.91
925	1.00	1.00	7.81	7.75	21.34	21.24	23.50	23.40	24.83	24.93
940	1.02	1.02	7.73	7.66	21.49	21.35	23.56	23.48	24.93	25.00
950	1.03	1.03	7.67	7.61	21.58	21.43	23.61	23.54	24.98	25.07
960	1.05	1.04	7.62	7.56	21.69	21.51	23.67	23.62	25.02	25.10
1000	1.09	1.09	7.42	7.36	22.12	21.94	23.86	23.89	25.23	25.17
1050	1.15	1.14	7.19	7.13	22.51	22.56	24.06	23.92	25.70	25.78
1100	1.20	1.20	6.99	6.92	23.11	23.29	24.33	24.19	26.52	26.71
1150	1.26	1.25	6.80	6.74	23.97	24.02	24.96	24.90	27.41	27.30
1200	1.30	1.30	6.64	6.57	24.83	24.64	25.79	25.75	28.25	27.76
1250	1.35	1.34	6.49	6.42	25.71	25.40	26.49	26.39	29.46	28.76
1300	1.39	1.38	6.37	6.30	26.35	26.67	27.14	26.73	31.63	30.63
1350	1.42	1.42	6.26	6.19	27.64	28.11	28.61	27.98	34.68	32.69
1400	1.46	1.45	6.17	6.09	29.69	29.25	31.04	30.80	37.53	34.53
1450	1.48	1.48	6.09	6.01	31.04	29.39	32.24	32.47	40.67	35.12
1500	1.51	1.51	6.03	5.95	32.07	29.32	35.07	33.80	59.92	33.01
1550	1.52	1.53	5.99	5.91	33.32	29.50	39.36	36.34	42.19	31.45
1600	1.54	1.55	5.96	5.87	33.66	28.97	38.11	37.54	37.15	30.53
1650	1.55	1.56	5.95	5.86	33.59	28.19	34.40	37.10	33.74	29.57
1700	1.56	1.57	5.95	5.86	31.79	27.67	32.90	34.46	31.88	28.85
1750	1.57	1.57	5.96	5.87	29.02	26.20	30.18	30.00	29.70	27.01
1800	1.57	1.58	6.00	5.90	27.03	24.55	27.77	28.04	26.81	25.11
1850	1.56	1.58	6.04	5.94	25.72	23.92	26.49	26.73	25.38	24.39
1900	1.55	1.56	6.11	6.01	24.23	22.86	24.86	24.98	24.17	23.17
1950	1.54	1.56	6.18	6.08	23.37	21.64	23.69	24.25	23.08	22.16
2000	1.52	1.54	6.26	6.16	23.02	20.91	22.94	23.72	22.60	21.70
2050	1.51	1.52	6.38	6.27	21.77	19.66	21.63	22.20	21.58	20.58
2100	1.49	1.50	6.49	6.39	20.42	18.80	20.55	20.99	20.72	19.93
2150	1.46	1.48	6.62	6.52	19.72	18.03	20.18	20.74	20.12	19.45
2190	1.45	1.47	6.75	6.63	19.26	17.38	19.97	20.60	19.63	18.78
2200	1.44	1.47	6.79	6.68	18.99	17.17	19.89	20.53	19.57	18.74
2210	1.43	1.45	6.83	6.72	18.87	17.12	19.82	20.46	19.51	18.78
2225	1.42	1.44	6.86	6.75	18.75	16.98	19.53	20.07	19.34	18.67
2250	1.40	1.42	6.96	6.84	18.29	16.71	19.11	19.48	19.29	18.60
2300	1.38	1.39	7.14	7.02	17.16	15.93	18.32	18.48	18.73	18.12
2400	1.29	1.31	7.56	7.43	15.98	14.80	18.02	18.31	18.00	17.43
2500	1.21	1.25	8.03	7.93	14.10	13.16	17.73	17.94	17.11	16.44
2600	1.13	1.14	8.63	8.52	13.14	12.11	17.32	17.76	17.55	17.02
2700	1.02	1.04	9.32	9.18	12.29	10.75	17.12	17.75	17.58	16.77
2800	0.94	0.97	10.24	10.07	10.53	9.14	17.17	17.71	17.25	16.24
2900	0.83	0.85	11.26	11.10	9.15	7.94	16.91	17.41	17.71	16.98
3000	0.75	0.78	12.62	12.37	7.52	6.22	17.15	17.93	17.28	16.56
3100	0.67	0.70	14.38	14.12	5.06	3.95	17.42	18.38	17.29	16.64
3200	0.62	0.64	16.69	16.34	2.52	1.38	16.95	17.56	17.40	16.91
3300	0.58	0.60	19.85	19.37	0.94	2.00	16.78	17.39	17.27	16.96
3400	0.59	0.60	24.84	23.82	5.84	7.11	16.72	17.02	16.94	16.98
3500	0.63	0.60	29.90	28.96	11.51	12.48	15.93	15.63	16.74	16.86
3750	0.79	0.76	18.06	18.64	2.31	1.24	14.55	13.63	14.89	15.02
4000	1.06	1.02	13.36	13.58	2.36	3.37	12.77	11.79	13.24	13.32

REV. X1

BDCA1-6-22+

081019

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Bi-Directional Coupler

# BDCA1-6-22+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +100°C

FREQ. (MHz)	INSERTION LOSS (dB)		COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
500	0.59	0.58	11.72	11.74	17.55	17.66	23.25	23.22	24.72	24.60
600	0.73	0.72	10.45	10.48	18.06	18.12	22.42	22.55	23.92	23.92
700	0.88	0.87	9.46	9.49	18.63	18.71	22.09	22.09	23.56	23.59
800	1.02	1.01	8.67	8.70	19.37	19.48	21.94	21.97	23.60	23.74
900	1.16	1.15	8.03	8.06	20.26	20.41	22.22	22.17	24.08	24.32
925	1.20	1.18	7.89	7.92	20.51	20.69	22.40	22.32	24.29	24.47
940	1.22	1.20	7.81	7.84	20.66	20.86	22.49	22.41	24.48	24.65
950	1.23	1.22	7.76	7.78	20.76	20.99	22.57	22.47	24.60	24.82
960	1.24	1.23	7.70	7.73	20.88	21.12	22.65	22.56	24.70	24.96
1000	1.29	1.28	7.51	7.54	21.38	21.66	22.97	22.89	25.15	25.29
1050	1.35	1.34	7.29	7.32	22.02	22.22	23.52	23.36	25.64	25.81
1100	1.41	1.40	7.09	7.12	22.74	22.95	24.12	24.00	26.43	26.59
1150	1.47	1.46	6.91	6.95	23.51	23.84	24.86	24.68	27.43	27.31
1200	1.52	1.51	6.76	6.79	24.41	24.68	25.95	25.68	28.43	27.94
1250	1.57	1.56	6.62	6.66	25.37	25.60	26.97	26.57	29.79	29.11
1300	1.61	1.61	6.51	6.55	26.47	26.82	28.16	27.56	31.76	30.39
1350	1.65	1.65	6.40	6.45	27.88	28.01	29.67	28.81	34.23	31.15
1400	1.69	1.68	6.32	6.37	29.24	29.26	31.85	30.08	37.71	31.78
1450	1.72	1.72	6.26	6.30	31.07	30.42	34.68	32.01	42.75	32.42
1500	1.75	1.75	6.20	6.25	33.04	31.49	37.34	34.16	48.44	32.55
1550	1.77	1.77	6.17	6.22	34.27	31.90	39.41	34.94	41.65	31.78
1600	1.79	1.80	6.15	6.20	34.57	31.30	37.88	34.49	35.98	30.48
1650	1.81	1.81	6.15	6.20	33.76	30.41	34.94	32.95	32.32	29.02
1700	1.82	1.82	6.16	6.21	31.46	29.14	31.91	30.67	29.96	27.57
1750	1.83	1.83	6.19	6.24	29.95	27.70	29.25	29.20	28.23	26.46
1800	1.83	1.84	6.23	6.28	28.63	26.20	27.58	28.01	26.87	25.43
1850	1.83	1.84	6.29	6.34	27.13	24.92	26.01	26.42	25.67	24.49
1900	1.83	1.83	6.36	6.42	25.68	23.80	24.76	25.27	24.58	23.66
1950	1.82	1.82	6.44	6.50	24.43	22.78	23.74	24.21	23.57	22.98
2000	1.81	1.81	6.55	6.61	23.07	21.80	22.80	23.18	22.60	22.15
2050	1.79	1.79	6.66	6.72	22.14	20.85	22.14	22.59	21.81	21.39
2100	1.77	1.78	6.78	6.86	21.16	19.93	21.39	21.85	21.15	20.79
2150	1.75	1.76	6.95	7.01	20.12	19.01	20.61	21.07	20.67	20.36
2190	1.73	1.73	7.09	7.15	19.43	18.46	20.16	20.56	20.30	19.92
2200	1.72	1.73	7.12	7.18	19.24	18.28	20.02	20.40	20.16	19.77
2210	1.72	1.73	7.15	7.22	19.01	18.05	19.92	20.33	20.06	19.70
2225	1.71	1.72	7.21	7.28	18.71	17.82	19.76	20.16	19.88	19.54
2250	1.69	1.70	7.29	7.36	18.45	17.47	19.52	19.84	19.59	19.15
2300	1.67	1.69	7.50	7.56	17.52	16.55	19.27	19.70	19.12	18.69
2400	1.59	1.60	7.95	8.02	16.24	15.28	18.69	19.10	18.38	17.89
2500	1.52	1.54	8.50	8.58	14.84	13.87	17.85	18.27	17.82	17.44
2600	1.44	1.46	9.18	9.26	12.93	12.35	17.52	17.80	17.37	16.87
2700	1.37	1.39	9.96	10.06	11.41	10.80	17.37	17.88	17.21	16.80
2800	1.28	1.30	10.96	11.03	9.82	9.14	17.31	18.00	17.42	16.86
2900	1.20	1.23	12.13	12.17	8.39	7.57	17.06	18.01	17.19	16.67
3000	1.17	1.18	13.59	13.62	6.40	5.62	16.93	17.80	17.20	16.71
3100	1.10	1.11	15.64	15.55	3.88	3.12	16.84	17.80	17.38	17.01
3200	1.06	1.08	18.18	18.00	1.01	0.31	16.73	17.58	17.04	16.89
3300	1.07	1.06	21.85	21.30	2.67	3.51	16.36	16.93	16.85	16.83
3400	1.11	1.12	27.59	26.67	8.68	9.66	16.21	16.11	16.28	16.65
3500	1.15	1.12	27.49	27.77	10.14	9.69	15.76	15.45	15.64	16.06
3750	1.35	1.31	17.19	17.98	1.37	0.25	14.19	13.22	13.97	14.57
4000	1.63	1.59	12.92	13.58	2.49	4.38	13.13	11.85	12.80	13.31

REV. X1

BDCA1-6-22+

081019

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661









The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Bi-Directional Coupler

# BDCA1-6-22+

## Typical Performance Curves



REV. X1  
BDCA1-6-22+  
081019  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# Bi-Directional Coupler


# BDCA1-6-22+

## Typical Performance Curves


Return Loss




Return Loss In vs. TEMPERATURE




Return Loss Out vs. TEMPERATURE



Return Loss Fwd vs. TEMPERATURE



Return Loss Rev vs. TEMPERATURE



REV. X1  
BDCA1-6-22+  
081019  
Page 2 of 2




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
DZ944	.30 (7.62)	.250 (6.35)	.052 (1.32)	.266 (6.76)	.050 (1.27)	.050 (1.27)	.012 (0.30)	.029 (0.74)	.004 (0.10)	.085 (2.16)	.296 (7.52)	.030 (0.76)	0.25

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

#### Notes:

- Case material: Ceramic.
- Termination finish:
  - For RoHS Case Styles: Tin plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M82377	UPDATED DRAWING	07/31/02	AV	DB
B	M101085	UPDATED DRAWING, ADDED DZ944 CASE STYLE & NOTE 2	10/06/05	MMG	HY
C	M102713	UPDATED NOTES	01/10/06	MMG	ABD

**SUGGESTED MOUNTING CONFIGURATION FOR  
SM1L/SM33/DZ944 CASE STYLES, "lf/nl" PIN CONNECTIONS**



- NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS  $.020 \pm .0015$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN <b>MMG</b>	04/12/00
TOLERANCES ON:	CHECKED <b>WP</b>	04/27/00
2 PL DECIMALS $\pm$	APPROVED <b>DB</b>	04/27/00
3 PL DECIMALS $\pm$ .005		
ANGLES $\pm$		
FRACTIONS $\pm$		

**Mini-Circuits**<sup>®</sup> 13 Neptune Avenue  
Brooklyn NY 11235


PL, lf/nl, SM1L/SM33/DZ944, BDCA/QBA, TB-115

SIZE <b>A</b>	CODE IDENT <b>15542</b>	DRAWING NO: <b>98-PL-004</b>	REV: <b>C</b>
FILE: <b>98PL004</b>	SCALE: <b>8:1</b>	SHEET: <b>1 OF 1</b>	


Mini-Circuits<sup>®</sup>  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


# Evaluation Board and Circuit



TB-115+



BDCA MODELS



QBA MODELS

## SCHEMATIC DIAGRAM

### Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215