

BFCQ-3852A+

Mini-Circuits

THE BIG DEAL

- Optimized for 5G N260 band (37 to 40 GHz)
- Low Insertion Loss Mid band 2.5dB typical
- Surface mountable pick and place standard case style
- Standard small 1008 (2.5mm x 2.0mm) case style
- High quality distributed filter topology
- Wide rejection band

APPLICATIONS

- Test and Measurement
- Ka-Band for SatCOM and Radar
- 5G N260 Telecom Band

PRODUCT OVERVIEW

The BFCQ-3852A+ LTCC (Low Temperature Co-Fired Ceramic) Bandpass Filter that covers the 5G N260 band from 37 to 40 GHz. It has a low insertion loss, 2.5dB (typ) and has upto 40dB stopband rejection. This model can handle upto 1W of RF input power and has an operating temperature from -55 to +125 °C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot-to-lot basis, up to mmWave frequencies.

KEY FEATURES

Feature	Advantages
5G n260 band compatible	Designed for 5G Telecommunications, n260 band, 37 – 40 GHz
Proprietary mmWave compatible LTCC material system	Low loss and repeatable performance on a lot-to-lot basis up to mmWave frequencies.
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (2.5mm x 2.0mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Surface Mountable	Suitable for very high volume automated assembly process.



Generic photo used for illustration purposes only

CASE STYLE: NL1008C-6

+RoHS Compliant The +Suffix identifies RoHS Compliance. ur website for methodologies and qualifica





Mini-Circuits

ELECTRICAL SPECIFICATIONS¹ AT 25°C

Para	ameter	F#	Frequency (GHz)	Min.	Тур.	Max.	Units
	Center Frequency	_	_	_	38.5	_	GHz
	Less Productions	F1 F2	37 - 38.6	_	2.9	_	dB
Passband	Insertion Loss	F1-F2	38.6 - 40	_	2.5	3.4	dB
	Return Loss (In)	E1 E2	37 - 40	_	10	—	dB
	Return Loss (Out)	F1-F2	37 - 40	_	10	—	dB
Stopband Lower	Insortion Loss		0.1 - 28	45	55	_	dB
Stopballu, Lowel	Insertion Loss	DC-F3	28 - 33.2	30	45	—	uв
			44.8 - 47	20	25	—	
Stopband, Upper	Insertion Loss	F4-F5	47 - 54	30	36	—	dB
			54 - 58	20	30		

1. Measured on Mini-Circuits Test Board TB-BFCQ-3852AC+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
RF Power Input	1 W at 25°C

Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



Mini-Circuits





Mini-Circuits

PAD CONNECTIONS

INPUT	1
OUTPUT	2
GROUND	3

OUTLINE DRAWING



DENOTES METALLIZATION

EVALUATION BOARD MCL P/N: TB-BFCQ-3852AC+ SUGGESTED PCB LAYOUT (PL-707)

PRODUCT MARKING: NS



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR MEGTRON-7 R5785(N); DIELECTRIC
- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR MEGTRON-YAVS(N); DIELECTRIC THICKNESS: 0.0049±.001; CLOTH STYLE: 2116; COPPER: HVLP/HVLP, FOR OTHER MATERIALS LINE WIDTH & GAP MAY NEED TO BE MODIFIED.
 SOLDER MASK OPENING FOR COMPONENT SOLDERING HAS BEEN INCREASED AGAINST PCB LAND PATTERN RECOMMENDATIONS PER NL1008C-6 AND CAN BE DEVIATED FROM THIS DRAWING TO COMPLY WITH CUSTOMERS' DESIGN RULES.
- 3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER). DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

OUTLINE DIMENSIONS (Inches)

		-								
wt	K	J	н	G	F	Е	D	С	В	Α
grams	.004	.004	.008	.012	.020	.024	.024	.028	.079	.098
.019	0.1	0.1	0.2	0.3	0.51	0.6	0.6	0.71	2.01	2.49

TAPE & REEL INFORMATION: F75

Mini-Circuits



Bandpass Filter

BFCQ-3852A+

Mini-Circuits

50Ω 37 to 40 GHz

TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	85.26	0.05
5000	70.51	0.38
10000	64.52	0.57
20000	73.53	0.88
25000	75.86	1.30
30000	60.17	1.15
34000	51.82	1.82
37000	2.10	13.39
38500	1.60	13.18
40000	1.61	14.39
45000	36.70	1.57
45000	36.70	1.57
50000	48.91	1.59
58000	36.29	2.03
60000	31.74	2.27







NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits

Ceramic Bandpass Filter Typical Performance Data

FREQUENCY	INSERTION LOSS	INPUT RETURN LOSS	OUTPUT RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
10	85.26	0.05	0.05
1700	75.50	0.54	0.56
3400	71.00	0.41	0.44
5100	69.27	0.38	0.36
6800	66.39	0.43	0.38
8500	65.21	0.47	0.46
10300	61 73	0.60	0.63
15400	65.47	0.83	0.84
17100	71.45	0.73	0.75
20600	72.32	0.97	0.91
24000	78.75	1.21	1.26
27400	71.31	1.24	1.27
30900	57.18	1.20	1.10
34300	47.08	1.43	2 17
36000	10.66	3.66	3.36
36200	5.86	7.46	6.11
36400	3.28	19.05	11.44
36500	2.89	15.69	11.63
36600	2.73	12.32	10.77
36800	2.47	10.95	10.78
37100	2.10 1.95	15.39	13.85
37200	1.86	17.99	21.62
37300	1.85	16.93	20.39
37400	1.91	14.32	16.23
37500	2.01	12.06	13.07
37600	2.13	10.52	11.08
37700	2.21	9.44	9.96
37800	2.28	8.85	9.37
38000	2.20	8.66	8.98
38100	2.15	8.84	9.30
38200	2.02	9.46	10.03
38300	1.87	10.46	11.31
38400	1.72	11.71	12.99
38500	1.60	13.18	15.49
38600	1.50	15.04	19.69
38700	1.44	15.13	29.53
38900	1.44	14 32	19.76
39000	1.55	12.90	15.89
39100	1.64	11.67	13.32
39200	1.72	10.80	12.04
39300	1.79	10.29	11.14
39400	1.84	9.94	10.41
39600	1.80	9.92 10.09	9.98
39700	1.80	10.69	10.27
39800	1.74	11.54	10.80
39900	1.66	12.84	11.32
40000	1.61	14.39	11.99
40500	1.56	21.36	15.30
41000	1.87 3.05	14.37	15.78
42000	8,28	3,67	4.34
42500	14.97	2.28	2.49
42700	17.43	2.06	2.19
43000	20.88	1.83	1.92
43100	21.94	1.78	1.85
43200	22.98	1.75	1.80
43300	23.93	1.70	1.73
43500	25.90	1.63	1.67
43600	26.75	1.63	1.62
43700	27.65	1.58	1.59
43800	28.56	1.54	1.55
43900	29.40	1.54	1.54
44000	30.14	1.55	1.50
40300 40800	42.03 49.12	1.72	1.00
51500	47.66	1.61	1.95
54900	43.43	1.61	1.84
56600	39.90	1.47	1.63



31.74

60000



2.43

REV. OR BFCQ-3852A+ 5/14/2021 Page 1 of 1

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site IF/RF MICROWAVE COMPONENTS

2.27

Ceramic Bandpass Filter

Typical Performance Curves







P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

IF/RF MICROWAVE COMPONENTS

REV. OR BFCQ-3852A+ 5/14/2021 Page 1 of 1

Case Style









.

C±.004[±0.100]

DENOTES METALLIZATION

Suggested Layout, Tolerance to be within $\pm .002$

CASE#	А	В	C	D	Е	F	G	Н	J	K	L	М	Ν
NI 1009C 6	.098	.079	.028	.024	.024	.020	.012	.008	.004	.004	.079	.098	.118
NL1008C-0	(2.50)	(2.00)	(.705)	(.60)	(.60)	(.51)	(.30)	(.20)	(.10)	(.10)	(2.0)	(2.5)	(3.0)
CASE #	Р	Q	R	S	Т	U	WT, GR	AM					
NI 1009C (.064	.013	.043	.024	.027	.046	010						
NL1008C-0	(1.63)	(.3)	(1.09)	(.60)	(.7)	(1.2)	.019						

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

Notes:

- 1. Open style, ceramic base.
- 2. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

- 3. Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.
- 4. Line width should be designed to match 50Ω characteristic depending on PCB material and thickness.





P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR MEGTRON-7 R5785(N); DIELECTRIC THICKNESS: .0049±.001; CLOTH STYLE: 2116; COPPER: HVLP/HVLP. FOR OTHER MATERIALS LINE WIDTH & GAP MAY NEED TO BE MODIFIED.
- 2. SOLDER MASK OPENING FOR COMPONENT SOLDERING HAS BEEN INCREASED AGAINST PCB LAND PATTERN RECOMMENDATIONS PER NL1008C-6 AND CAN BE DEVIATED FROM THIS DRAWING TO COMPLY WITH CUSTOMERS' DESIGN RULES.
- 3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED)	INITIALS	DATE					• A R			
DIMENSIONS ARE IN INCHES	DRAWN	ITG	05/12/21		Mini	I - CI	rcu	1ts 13 1	Neptu	ne Ave	nue
TOLERANCES ON:	CHECKED	GF	05/12/21					Broo)klyn	NY II	230
3 PL DECIMALS ± .005	APPROVED	IL	05/12/21	1							
FRACTIONS ±				1	PL. NL10	008C - 6	. TB-	-BFCQ-	XX	XX+	-
🥅 Mini	–Circuits ®				,		,				
THIS DOCUMENT AND ITS CONTENTS	ARE THE PROPER	TY OF MINI-CIRCUIT	S.		1						
EXCEPT FOR USE EXPRESSLY GRANTE	D, IN WRITING, T	O ITS VENDORS, VE		SIZE	CODE IDENT	DRAWING NO:	:			REV:	
DESIGN, USE , MANUFACTURING AND THESE CONTENTS SHALL NOT BE USI	REPRODUCTION R	IGHTS THERETO.	NY OUTSIDE	A	15542		98-	-PL-707	7		OR
PARTY, IN WHOLE OR IN PART, WITH	OUT WRITTEN PER	MISSION OF MINI-C	RCUITS.	FILE.		SCALE	1 = 1	SHEET	4		4
	ASHEETA1.D	WG REV:A DA	TE:01/12/95		984T101		19:1		1	OF.	T



Mini-Circuits	Environmental Specifications ENV06T8	
All Mini-Circuits products are manufacturec any or all of the following physical and envi	I under exacting quality assurance and control standards, and are capable of me ronmental test.	sting published specifications after being subjected to
Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Mechanical Shock	50g, 11ms half-sine, 18 shocks applied each to 3 axes	MIL-STD-202 Method 213, Condition A
Vibration	10-2000Hz sine, 20g, 12 cycles applied each to 3 axes	MIL-STD-202, Method 204, Condition D
Constant Acceleration	30Kg, Y1 Direction	MIL-STD-883, Method 2001, Condition E
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	
ENV06T8 Rev: OR 11/04/20 DC0 This document and its contents are the proper	D-0030 File: ENV06T8.pdf ty of Mini-Circuits.	Page: 1