


**THE BIG DEAL**

- SIW High-Performance Topology
- Low Insertion Loss, 0.8 dB Typ.
- Compact 1812 SMT package
- Ultra-High Stopband Rejection, up to 58 dB
- Scalable, Cost-Effective for Volume Production



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM**APPLICATIONS**

- SATCOM Ka-Band Downlink
- Satellite Communication Systems
- 5G / NTN Infrastructure
- Test and Measurement Equipment

PRODUCT OVERVIEW

Mini-Circuits' BFHK-1942+ is a high-performance bandpass filter designed for the SATCOM Ka-Band downlink, covering 17.7 to 21.2 GHz with exceptionally low insertion loss and high out-of-band rejection. This filter was designed with an advanced substrate integrated waveguide (SIW) topology to deliver waveguide-class selectivity and rejection in a compact, SMT LTCC package. This approach combines the low loss and high-Q performance of waveguide structures with the scalability and manufacturability of standard SMT components.

KEY FEATURES

Features	Advantages
Low Insertion Loss	Typical insertion loss of 0.8 dB
Cost Effective	Utilizes a scalable technology that is cost effective due to ease of production in high quantities.
Small Size (4.5 mm x 3.2 mm)	Allows for high layout density of circuit boards, while minimizing the effects of parasitics.
Surface Mountable	Suitable for very high-volume automated assembly process.



LTCC SURFACE MOUNT

Band Pass Filter

BFHK-1942+

50Ω 17.7 to 21.2 GHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C, $Z_0 = 50\Omega$

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency ⁴	—		—	19.45	—	GHz
	Insertion Loss	F4-F5	17.7-18	—	1.6	2	dB
		F5-F6	18-21.2	—	0.8	1.2	
	Return Loss	F4-F5	17.7-18	—	10.6	—	dB
		F5-F6	18-21.2	10.7	13.6	—	
Stopband, Lower	Rejection	DC-F1	DC-5	48	58	—	dB
		F1-F2	5-11.6	35	45	—	
		F2-F3	11.6-15	30	40	—	
Stopband, Upper	Rejection	F7-F8	24-25	20	27	—	dB
		F8-F9	25-27	35	47	—	
		F9-F10	27-31	48	58	—	
		F10-F11	31-35	40	52	—	

1. Tested in Evaluation Board P/N TB-BFHK-1942C+ with the connector and feedline effects de-embedded using the 2X Thru IEEE P370 method.

2. This filter is bi-directional. RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

4. Typical variation $\pm 1.5\%$.


ABSOLUTE MAXIMUM RATINGS⁵

Operating Temperature	-55 °C to +125 °C
Storage Temperature	-55 °C to +125 °C
Input Power ⁶	10 W

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25 °C operating temperature decreases linearly to 3.1 W at +125 °C.

TYPICAL FREQUENCY RESPONSE





LTCC SURFACE MOUNT





Band Pass Filter

BFHK-1942+

Mini-Circuits

50 Ω 17.7 to 21.2 GHz

TYPICAL PERFORMANCE GRAPHS





LTCC SURFACE MOUNT

Band Pass Filter

BFHK-1942+

Mini-Circuits

50Ω 17.7 to 21.2 GHz

FUNCTIONAL DIAGRAM





Figure 1. BFHK-1942+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-730)


CASE STYLE DRAWING




PRODUCT MARKING*: F632

*Marking may contain other features or characters for internal lot control.

SUGGESTED PCB LAYOUT: PL-730



STACK-UP DIAGRAM




NOTES:

- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.-PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

LAYER 2, B-VIA & PTH



LAYER 3 & PTH




Figure 2. Suggested PCB Layout



LTCC SURFACE MOUNT

Band Pass Filter

BFHK-1942+

Mini-Circuits

50Ω 17.7 to 21.2 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NM1812C-3 Finish: Tin over Nickel plating
RoHS/REACH Status	Compliant
Tape and Reel	F77
Suggested Layout for PCB Design	PL-730
Evaluation Board	TB-BFHK-1942C+ Gerber File
Environmental Rating	ENV164

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



LTCC Bandpass Filter

Typical Performance Data





BFHK-1942+


FREQUENCY (GHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
0.10	72.43	72.28	69.83	0.07	0.06	0.08
0.50	76.20	69.74	78.61	0.12	0.13	0.14
1.00	71.85	69.59	75.76	0.10	0.10	0.13
2.00	64.88	67.36	64.67	0.00	0.01	0.02
3.00	62.69	61.30	63.35	0.12	0.10	0.09
4.00	60.93	62.52	64.78	0.06	0.04	0.04
5.00	59.12	59.57	58.29	0.08	0.11	0.09
6.00	58.38	57.49	57.55	0.25	0.27	0.25
7.00	56.06	55.58	54.55	0.27	0.29	0.28
8.00	53.02	53.61	53.59	0.17	0.16	0.15
9.00	51.36	51.41	51.31	0.02	0.01	0.00
10.00	48.51	48.51	48.63	0.03	0.02	0.05
11.00	47.03	47.28	46.65	0.06	0.11	0.16
12.00	45.30	45.06	44.71	0.12	0.16	0.18
13.00	43.50	43.41	43.29	0.23	0.24	0.22
14.00	43.17	43.37	43.64	0.37	0.34	0.32
15.00	59.69	62.97	51.34	0.32	0.37	0.37
16.00	26.94	24.96	22.71	0.21	0.33	0.37
17.00	7.29	5.56	3.96	1.77	2.79	4.38
17.50	1.37	1.17	1.03	10.73	14.11	19.02
17.70	0.84	0.87	0.91	18.14	20.31	19.46
17.90	0.70	0.79	0.87	20.97	20.46	17.81
18.10	0.67	0.76	0.84	19.19	19.62	17.62
18.30	0.64	0.73	0.79	18.55	19.93	18.65
18.50	0.63	0.73	0.76	19.17	21.16	20.51
18.70	0.60	0.69	0.72	21.06	23.36	23.43
18.90	0.57	0.67	0.71	23.77	25.97	26.39
19.10	0.56	0.68	0.71	26.42	27.01	26.11
19.30	0.56	0.71	0.75	27.25	25.32	23.43
19.50	0.59	0.75	0.76	24.62	22.64	21.11
19.70	0.64	0.79	0.82	21.61	19.94	18.96
19.90	0.68	0.84	0.85	19.58	18.22	17.61
20.10	0.72	0.90	0.86	18.56	17.30	17.09
20.30	0.78	0.96	0.90	17.11	16.13	16.43
20.50	0.82	1.02	0.94	16.41	15.77	16.32
20.70	0.83	1.01	0.99	16.15	15.98	16.71
20.90	0.89	1.05	1.00	16.17	16.51	17.36
21.10	0.90	1.09	1.06	16.79	17.32	17.93
21.20	0.89	1.07	1.06	17.09	17.58	18.05
21.50	0.94	1.17	1.18	17.23	16.61	17.54
22.00	1.12	1.36	1.57	16.45	17.37	16.88
23.00	11.36	14.74	86.74	1.17	0.97	0.87
24.00	31.74	34.71	83.60	0.40	0.47	0.49
25.00	52.05	56.33	91.62	0.27	0.38	0.37
26.00	82.54	66.66	82.71	0.34	0.49	0.43
27.00	66.09	71.79	83.71	0.45	0.65	0.54
28.00	65.87	65.89	84.71	0.37	0.54	0.38
29.00	67.87	62.46	85.71	0.31	0.40	0.33
30.00	57.56	60.65	86.71	0.23	0.38	0.35
31.00	60.73	56.09	87.71	0.40	0.68	0.44
32.00	59.70	58.99	88.71	0.59	0.78	0.43
33.00	55.60	58.21	89.71	0.33	0.49	0.28
34.00	54.99	53.42	90.71	0.43	0.64	0.47
35.00	52.32	55.35	91.71	0.88	1.17	0.85

LTCC Band pass Filter

BFHK-1942+

Typical Performance Data





Weight: .126 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl.±.01; 3 Pl. ±.005 Inches

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles

GU1604, GU1804, GU2644,
TT1618-2

Applicable Case Styles

MZ4532C, NM1812C,
NM1812C-1, NM1812C-2,
NM1812C-3, NM1812C-5,
NM1812C-6, NM3237

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-013254	NEW RELEASE	05/16/22	ITG	IL
A	ECO-015587	UPDATED STACK-UP DIAGRAM	11/01/22	ITG	IL
B	ECO-020890	ADDED DIMENSIONS	02/16/24	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR NM1812C-3 CASE STYLE



STACK-UP DIAGRAM



1. TOTAL FINISHED THICKNESS $0.0228 \pm .004$.
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED PLUGGED PTH'S ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. LAYER 4 IS CONTINUOUS GROUND PLANE.

NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	ITG	05/16/22
	CHECKED	GF	05/16/22
	APPROVED	IL	05/16/22

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, NM1812C-3, TB-1239

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B
FILE:	98PL730	SCALE:	8:1
		SHEET:	1 OF 2

LAYER 2, B-VIA & PTH



LAYER 3 & PTH





THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA2.DWG REV:A DATE: 01/12/94


ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B
FILE:	98PL730	SCALE: 8:1	SHEET: 2 OF 2

Evaluation Board and Circuit



Schematic Diagram



STACK-UP DIAGRAM

Notes:

1. 2.92 mm Female End Launch Connector.
2. PCB Material: Megtron 6 R5775(N).
Dielectric Constant=3.6.
3. Total finished thickness .023".

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 500 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Humidity	50°C, 95% Relative Humidity, 240 Hours	MIL-STD-202, Method 103
Solderability	10X / 30X Magnification	J-STD-002 Method B, B1
Solder Reflow Heat	Pb-Free Process 245° - 250°C peak, 3X Reflow	J-STD-020
Bend Test	1mm, deflection for 5 seconds	