LTCC SURFACE MOUNT

Bandpass Filter

BFHKI-3142+

50Ω 28 to 36 GHz

THE BIG DEAL

- LTCC Band Pass Filter with Integrated Interposer Board
- Wide Stopband Rejection, Typ. 30 dB up to 67 GHz
- Small Size, 4.95 mm x 3.65 mm
- Shielded Construction
- Protected by US Patents 11,638,370 and 11,744,057




Generic photo used for illustration purposes only

APPLICATIONS

- Test & Measurement Equipment
- Aerospace and Defense Signal Conditioning

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

BFHKI-3142+ is a miniature low-temperature co-fired ceramic (LTCC) ultra-high stopband rejection band pass filter with a 28 to 36 GHz passband that supports a variety of applications. This model achieves 30 dB typical stopband rejection up to 67 GHz when mounted on coplanar waveguide layouts. Housed in a small 4.95 mm by 3.65 mm ceramic form factor, the filter is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The BFHKI family with integrated interposer board enables installation onto PCB layouts with automated manufacturing equipment. This model provides a 2.8 dB typical insertion loss over a wide band due to its rugged monolithic construction. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well-suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Surface Mountable due to Integrated Interposer Board	Enables installation with automated manufacturing equipment, making this suitable for high-volume processes.
Wide Rejection	Provides high stopband rejection of 30 dB typical up to 67 GHz.
Small Size (4.95 x 3.65mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Wide Operating and Storage Temperature (-55 to 125°C)	Enables use in high reliability and extreme environment conditions, such as in aerospace & defense applications.
Cost Effective	LTCC is a scalable technology that is cost-effective due to ease of production in high-volume.

REV. OR
ECO-020866
BFHKI-3142+
MCL NY
240220

Bandpass Filter

BFHKI-3142+

50Ω 28 to 36 GHz

ELECTRICAL SPECIFICATIONS[1,2,3] AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency[4]	—	—	—	32	—	GHz
	Insertion Loss	F2-F3	28 – 33	—	2.8	4.0	dB
			33 - 36	—	4.0	5.5	dB
	Return Loss	F2-F3	28 - 36	—	7.5	—	dB
Stopband, Lower	Rejection	DC-F1	0.1 – 20	40	50	—	dB
Stopband, Upper	Rejection	F4-F5	44 – 54	40	50	—	dB
			54 – 60	—	45	—	
			60 – 67	—	30	—	


1. Tested on Evaluation Board P/N TB-BFHKI-3142C+. Measured with the connector and feedline effects de-embedded using the 2XThru IEEE P370 method.
2. Bi-directional, RF1 and RF2 ports can be interchanged.
3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ±3%.

ABSOLUTE MAXIMUM RATINGS[5]

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power[6]	1 W

5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.5 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C





Bandpass Filter


BFHKI-3142+


50Ω 28 to 36 GHz

TYPICAL PERFORMANCE GRAPHS









Bandpass Filter

BFHKI-3142+

50Ω 28 to 36 GHz

FUNCTIONAL DIAGRAM





Figure 1. BFHKI-3142+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	1	Connects to RF Input Port
RF2[2]	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-767)

CASE STYLE DRAWING



Weight: .135 grams.
Dimensions are in inches [mm]. Tolerances: 2 Pl.±.01; 3 Pl. ±.005

SUGGESTED PCB LAYOUT (PL-767)




Figure 2. Suggested PCB Layout for BFHKI-3142+

PRODUCT MARKING*: F473

*Marking may contain other features or characters for internal lot control.

Bandpass Filter

BFHKI-3142+

50Ω 28 to 36 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD. CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NM3237 Finish: Gold over Nickel Plating
RoHS Status	Compliant
Tape and Reel	F77
Suggested Layout for PCB Design	PL-767
Evaluation Board	TB-BFHKI-3142C+ Gerber File
Environmental Rating	ENV06T12

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

LTCC Lowpass Filter BFHKI-3142+


Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
0.1	100.10	100.88	98.07	0.04	0.06	0.08
1.0	85.33	85.43	85.20	0.13	0.14	0.16
2.0	79.70	79.54	79.27	0.04	0.04	0.02
3.0	76.62	76.99	76.89	0.07	0.05	0.02
4.0	77.46	77.41	77.46	0.06	0.11	0.17
5.0	81.88	81.85	81.74	0.15	0.19	0.22
6.0	82.00	81.62	81.71	0.13	0.15	0.18
7.0	74.56	74.52	73.89	0.07	0.12	0.18
8.0	76.46	76.56	76.42	0.09	0.16	0.21
9.0	72.32	72.25	72.40	0.21	0.26	0.31
10.0	72.24	71.81	71.58	0.24	0.31	0.36
11.0	68.21	67.80	68.04	0.21	0.28	0.34
12.0	61.94	62.08	61.24	0.22	0.31	0.39
13.0	58.25	58.11	57.93	0.22	0.34	0.45
14.0	55.60	55.51	55.51	0.19	0.29	0.37
15.0	54.71	54.77	54.17	0.24	0.32	0.42
16.0	53.94	54.03	53.76	0.27	0.39	0.49
17.0	53.21	53.59	53.92	0.15	0.29	0.36
18.0	55.35	55.65	55.56	0.08	0.20	0.31
19.0	56.92	57.28	57.77	0.17	0.29	0.34
20.0	58.51	58.90	59.43	0.21	0.31	0.35
21.0	61.11	61.78	62.18	0.16	0.28	0.44
22.0	76.24	79.62	87.75	0.10	0.27	0.34
23.0	66.68	65.44	64.20	0.12	0.27	0.34
24.0	58.34	57.26	55.23	0.30	0.42	0.61
25.0	46.62	44.37	41.23	0.34	0.57	0.66
26.0	28.72	25.24	20.34	0.69	1.01	1.64
27.0	4.79	3.21	2.76	5.92	13.33	21.08
28.0	1.74	2.00	2.31	13.46	13.62	13.04
28.5	1.72	2.07	2.42	11.95	10.96	10.36
29.0	1.73	2.02	2.27	10.21	10.55	10.69
29.5	1.63	1.81	1.96	10.53	12.49	15.10
30.0	1.34	1.57	1.78	16.12	18.90	30.50
30.5	1.18	1.47	1.79	36.21	32.33	23.11
31.0	1.20	1.54	1.92	24.80	19.03	17.04
31.5	1.31	1.68	2.08	16.76	15.18	13.90
32.0	1.48	1.83	2.26	12.95	13.06	12.13
32.5	1.71	2.18	2.72	10.41	9.73	8.93
33.0	2.15	2.79	3.37	8.08	7.13	6.66
33.5	2.90	3.26	3.58	5.92	6.01	6.08
34.0	3.20	3.08	3.04	5.54	6.55	7.84
34.5	2.49	2.37	2.37	7.63	9.54	13.63
35.0	1.60	1.86	2.30	14.68	18.70	17.65
35.5	1.50	2.07	2.66	16.88	13.15	11.35
36.0	1.81	2.32	2.67	11.36	11.41	14.67
37.0	2.27	3.20	4.22	13.05	9.98	11.52
38.0	8.42	14.86	22.45	3.70	2.14	1.64
39.0	30.46	35.40	41.12	0.63	0.97	1.19
40.0	48.43	53.68	63.97	0.66	1.03	1.23
41.0	76.25	69.79	63.33	0.44	0.83	0.97
42.0	57.41	56.91	57.26	0.38	0.77	0.99
43.0	56.87	57.14	57.78	0.44	0.72	0.84
44.0	58.28	60.02	62.22	0.12	0.50	0.71
45.0	63.64	65.23	71.36	0.19	0.43	0.68
46.0	70.59	71.39	69.65	0.21	0.52	0.62
47.0	61.49	61.77	62.62	0.31	0.53	0.75
48.0	57.52	57.66	57.18	0.14	0.53	0.77
49.0	54.34	54.25	53.13	0.18	0.55	0.80
50.0	55.75	56.98	57.21	0.21	0.52	0.77
51.0	61.16	62.33	61.84	0.18	0.50	0.79
52.0	72.27	74.40	77.36	0.24	0.63	0.88
53.0	71.82	70.22	68.86	0.48	0.73	0.97
54.0	75.31	79.14	70.31	0.33	0.68	0.97
55.0	65.08	65.56	64.73	0.32	0.70	0.90
56.0	70.76	73.35	78.80	0.41	0.66	0.87
57.0	75.99	77.20	80.77	0.01	0.53	0.77
58.0	78.72	69.50	67.67	0.14	0.66	0.86
59.0	65.09	65.60	66.41	0.25	0.40	0.54
60.0	66.85	66.53	62.69	0.14	0.34	0.75
61.0	66.59	57.00	61.16	0.07	0.59	0.73
62.0	63.66	64.31	63.34	0.24	0.42	0.51
63.0	65.40	61.90	55.42	0.08	0.70	1.39
64.0	51.36	49.20	44.72	0.51	1.20	1.65
65.0	42.07	35.06	41.20	1.41	2.49	3.35


LTCC Lowpass Filter BFHKI-3142+

Typical Performance Data


INSERTION LOSS




RETURN LOSS



INSERTION LOSS (PASSBAND)




RETURN LOSS (PASSBAND)



Case Style NM

Outline Dimensions NM3237



Weight: .135 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005


Notes:

1. Case material: LTCC on printed circut board base.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
   For RoHS Case Styles: Gold Plate over Nickel plate. All models, (+) suffix.


Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles
GU1604, GU1804, GU2644, TT1618-2

Applicable Case Styles
MZ4532C, NM1812C, NM1812C-1, NM1812C-2, NM1812C-3, NM1812C-5, NM1812C-6, NM3237 NM1812C-9

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.


THIRD ANGLE PROJECTION



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-019771	NEW RELEASE	11/06/23	ITG	IL


SUGGESTED MOUNTING CONFIGURATION FOR NM3237 CASE STYLE

STACK-UP DIAGRAM



-COPPER LAYER 1(L1), .5 OZ.
-CORE 1, .0079 MEGTRON-7 R5785(N/GN)
-COPPER LAYER 2 (L2), .5 OZ.
-PREPREG, .0035 (89 um) MEGTRON-7 R5680(N/GN), CLOTH STYLE:1078
-PREPREG, .0035 (89 um) MEGTRON-7 R5680(N/GN), CLOTH STYLE:1078
-COPPER LAYER 3 (L3), .5 OZ.
-CORE 2, .0079 MEGTRON-7 R5785(N/GN)
-COPPER LAYER 4 (L4), .5 OZ.

1. TOTAL FINISHED THICKNESS 0.026 ± 10%.
2. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.



NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP ARE SHOWN FOR .0079 MEGTRON-7 R5785(N/GN), COPPER: 1/2 OZ. EACH LAYER. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
3. LAYERS L2, L3 & L4 OF PCB ARE CONTINUOUS GROUND PLANES.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	11/06/23
TOLERANCES ON:	CHECKED	GF	11/06/23
2 PL DECIMALS ±	APPROVED	IL	11/06/23
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL,NM3237, TB-BFHKI-XXXXC+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-767	OR

FILE:	SCALE:	SHEET:
98PL767	6:1	1 OF 1

Evaluation Board and Circuit



TB-BFHKI-3142C+



Schematic Diagram

1. 50 Ohm 1.85 mm Female end Launch connectors.
2. PCB Material: MEGTRON-7 R5785(N or GN) or equivalent, Dielectric Constant=3.37 Thickness=.0079 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV06T12

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--

This document and its contents are the property of Mini-Circuits.