


**THE BIG DEAL**


- Good Rejection, 25 dB Typ.
- 1206 Surface Mount Footprint
- Power Handling: 1.5 Watts



Generic photo used for illustration purposes only

APPLICATIONS

- Harmonic Rejection
- Transmitters / Receivers
- WiMAX

FUNCTIONAL DIAGRAM**PRODUCT OVERVIEW**

Mini-Circuits' BFCN-2700+ LTCC Band Pass Filter is constructed with multiple layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 200 MHz passband, these units offer low insertion loss and good rejection.

KEY FEATURES

Features	Advantages
Small Size, 1206	Allows for high layout density of circuit boards, while minimizing the effects of parasitics
Wrap around termination	Provides excellent solderability and easy visual inspection capability.
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.
Rugged Power handling	Handles up to 1.5 Watts in a small package.



LTCC SURFACE MOUNT

Bandpass Filter

BFCN-2700+

50Ω

2600 to 2800 MHz

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency ³	—	—	2700	—	MHz
	Insertion Loss	F1-F2	—	—	5	dB
	Return Loss	F1-F2	6.5	12.7	—	dB
Stop Band, Lower	Rejection	DC-F3	—	25	—	dB
		DC-F4	20	—	—	
Stop Band, Upper	Rejection	F5-F6	20	—	—	dB
		F6-F7	—	25	—	

1. Tested in Evaluation Board P/N TB-BFCN-2700+.

2. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.


3. Typical variation $\pm 5\%$ ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Input Power ⁵	1.5W @25°C

4. Permanent damage may occur if any of these limits are exceeded.

5. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.25W at +100°C.

TYPICAL FREQUENCY RESPONSE





LTCC SURFACE MOUNT

Bandpass Filter




BFCN-2700+

Mini-Circuits

50Ω

2600 to 2800 MHz

TYPICAL PERFORMANCE GRAPHS AT +25°C





FUNCTIONAL DIAGRAM





Figure 1. BFCN-2700+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	3	Connects to RF Output Port
GROUND	2,4	Connects to Ground on PCB, (See drawing PL-137)

SUGGESTED PCB LAYOUT (PL-137)




NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" $\pm$.0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Figure 2. Suggested PCB Layout PL-137

CASE STYLE DRAWING



Weight: .020 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm$.01; 3 Pl. $\pm$.005

PRODUCT MARKING*: N/A

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

LTCC SURFACE MOUNT

Bandpass Filter

BFCN-2700+

50Ω

2600 to 2800 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD.

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	FV1206 Lead Finish: Nickel Tin
RoHS Status	Compliant
Tape and Reel	TR-F71
Suggested Layout for PCB Design	PL-137
Evaluation Board	TB-BFCN-2700+ Gerber File
Environmental Rating	ENV06

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Ceramic Band Pass Filter

BFCN-2700+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
10	104.25	104.09	102.41	0.02	0.03	0.04	0.00	0.00	0.00
15	107.81	96.76	99.73	0.02	0.04	0.04	0.00	0.00	0.00
20	98.54	112.31	114.06	0.03	0.04	0.05	0.00	0.00	0.00
25	96.02	96.96	104.48	0.03	0.04	0.05	0.00	0.00	0.00
30	93.18	92.72	93.53	0.03	0.05	0.06	0.00	0.00	0.00
40	88.56	89.66	89.36	0.04	0.05	0.06	0.00	0.00	0.00
50	84.51	84.58	83.99	0.04	0.06	0.07	0.00	0.00	0.00
60	81.90	81.44	80.52	0.04	0.06	0.08	0.00	0.00	0.00
70	79.25	78.73	78.87	0.05	0.07	0.08	0.00	0.00	0.00
80	76.96	76.47	76.24	0.05	0.08	0.09	0.00	0.00	0.00
90	74.96	74.38	74.63	0.06	0.08	0.10	0.00	0.00	0.00
100	72.84	72.93	72.74	0.06	0.09	0.10	0.00	0.00	0.00
200	61.09	61.01	60.86	0.10	0.13	0.15	0.00	0.00	0.01
300	54.07	54.03	53.91	0.12	0.16	0.18	0.01	0.01	0.02
400	49.11	49.05	48.98	0.13	0.18	0.20	0.01	0.02	0.03
500	45.19	45.13	45.07	0.13	0.19	0.21	0.01	0.02	0.04
600	41.97	41.91	41.85	0.14	0.20	0.23	0.02	0.04	0.06
700	39.25	39.18	39.13	0.14	0.21	0.24	0.05	0.06	0.08
800	36.73	36.72	36.66	0.16	0.23	0.27	0.06	0.07	0.10
900	34.63	34.57	34.48	0.16	0.24	0.28	0.08	0.09	0.11
1000	32.67	32.60	32.54	0.17	0.25	0.29	0.10	0.11	0.13
1100	30.78	30.78	30.68	0.18	0.26	0.31	0.12	0.12	0.15
1200	29.05	29.06	28.96	0.19	0.27	0.32	0.14	0.14	0.18
1300	27.46	27.49	27.35	0.19	0.28	0.34	0.16	0.16	0.20
1400	26.03	26.04	25.92	0.20	0.30	0.37	0.18	0.19	0.22
1500	24.69	24.65	24.56	0.22	0.34	0.41	0.20	0.22	0.26
1600	23.29	23.28	23.17	0.25	0.38	0.46	0.23	0.25	0.29
1700	22.08	22.06	21.98	0.29	0.42	0.51	0.26	0.30	0.34
1800	20.98	20.97	20.92	0.35	0.49	0.59	0.31	0.36	0.42
1900	20.07	20.05	20.06	0.44	0.59	0.70	0.35	0.42	0.48
2000	19.56	19.58	19.72	0.57	0.74	0.87	0.39	0.49	0.55
2100	20.00	20.21	20.53	0.76	0.98	1.13	0.43	0.56	0.64
2200	23.48	24.40	25.19	1.05	1.33	1.54	0.54	0.72	0.83
2300	23.72	21.22	19.35	1.62	2.04	2.36	0.91	1.20	1.44
2400	9.63	8.86	8.24	3.26	3.97	4.60	2.42	3.06	3.68
2500	3.77	3.74	3.69	7.11	8.06	8.85	6.97	8.14	9.26
2600	2.15	2.34	2.49	10.47	11.18	11.52	12.49	13.48	14.15
2700	1.95	2.20	2.40	10.77	11.30	11.47	12.02	12.49	12.68
2800	2.01	2.32	2.59	10.98	11.94	12.19	12.72	14.52	15.57
2900	2.84	3.71	4.57	10.70	9.39	8.26	19.27	14.11	11.64
3000	9.47	11.77	13.71	2.83	2.69	2.60	3.32	3.01	2.77
3100	24.90	28.56	29.83	1.26	1.44	1.58	1.19	1.34	1.35
3200	26.12	24.96	24.51	0.98	1.17	1.32	0.79	0.95	0.99
3300	22.79	22.92	22.87	0.90	1.07	1.22	0.71	0.80	0.88
3400	23.14	23.41	23.64	0.84	1.03	1.16	0.60	0.76	0.84
3500	24.54	25.02	25.44	0.78	0.97	1.10	0.61	0.81	0.94
3600	27.63	28.52	29.42	0.73	0.90	1.01	0.93	1.35	1.71
3700	32.85	30.91	28.41	0.67	0.84	0.95	3.61	6.28	10.05
3800	23.79	24.14	24.60	0.64	0.83	0.91	6.27	4.46	3.56
3900	25.39	26.18	26.11	0.60	0.80	0.88	1.24	1.21	1.25
4000	27.82	28.84	29.52	0.56	0.76	0.82	0.58	0.63	0.76
4100	30.72	29.14	30.64	0.51	0.77	0.74	0.35	0.53	0.53
4150	28.98	29.15	29.33	0.50	0.69	0.76	0.31	0.46	0.55
4200	31.35	30.09	31.54	0.45	0.65	0.67	0.28	0.39	0.44
4300	32.78	31.15	33.26	0.36	0.58	0.62	0.21	0.33	0.41
4400	33.61	32.56	33.20	0.33	0.53	0.65	0.22	0.33	0.48
4500	30.72	33.08	30.84	0.39	0.53	0.66	0.29	0.34	0.48
4600	32.45	33.60	31.47	0.29	0.50	0.59	0.18	0.29	0.44
4700	30.76	32.96	31.40	0.31	0.50	0.55	0.17	0.28	0.37
4800	30.79	32.24	31.36	0.30	0.50	0.54	0.18	0.33	0.38
4900	33.77	28.48	35.29	0.28	0.53	0.52	0.19	0.42	0.32
5000	30.22	28.33	30.84	0.31	0.50	0.59	0.24	0.37	0.41
5100	30.26	28.58	29.76	0.27	0.51	0.58	0.29	0.38	0.48
5200	21.39	26.72	21.92	0.64	0.51	0.90	0.74	0.37	0.88
5300	22.94	26.12	22.86	0.18	0.40	0.52	0.29	0.39	0.55
5400	25.04	26.85	25.32	0.20	0.36	0.48	0.37	0.44	0.56
5500	26.37	24.91	25.88	0.13	0.50	0.44	0.24	0.69	0.47
5600	22.84	21.97	24.65	0.29	0.65	0.55	0.47	0.93	0.64



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




REV. X1
BFCN-2700+
090830
Page 1 of 1

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206	.126 (3.20)	.063 (1.60)	.037 (0.94)	.020 (0.51)	.032 (0.81)	.009 (0.23)	.169 (4.29)	.087 (2.21)	.024 (0.61)	.122 (3.10)	.024 (0.61)	.087 (2.21)	.012 (0.30)	.071 (1.80)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F71




ILLUSTRATION 1

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION




NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" $\pm$.0015".
 COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

GF

08/27/03

CHECKED

AV

08/28/03

APPROVED

ABD

08/28/03



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-137

REV:

A

FILE:


98PL137

SCALE:

10:1

SHEET:



1 OF 1



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A