

Coaxial

Bandpass Filter

NON-CATALOG

BIF-50+

50Ω Constant Impedance 41 to 58 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- low VSWR in pass & stopbands, 1.3:1 typ.
- rugged shielded case
- custom to models available

Applications

- harmonic rejection
- lab use




CASE STYLE: FF55

Connectors	Model	Price	Qty.
BNC	BIF-50+	Contact Sales Dept.	

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix has been added in order to identify RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Outline Drawing




Outline Dimensions (inch/mm)

B	D	wt
.54	2.59	grams
13.72	65.79	40.0


Bandpass Filter Electrical Specifications

MODEL NO.	CENTER FREQ. (MHz)	PASSBAND (MHz)	STOPBANDS		VSWR, 1.3:1 Typ. TOTAL BAND (MHz)
			(loss > 10 dB) at MHz	(loss > 20 dB) at MHz	
BIF-50+	50	41-58	11.5 & 200	3.1 & 350	DC-440

typical frequency response





Electrical Schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ			
1.0	33.62	0.2	56.3	3.1	1.540
1.4	30.60	0.2	53.5	3.2	2.572
1.8	28.39	0.2	51.1	5.9	3.434
2.3	26.60	0.2	49.3	8.7	3.800
2.7	25.16	0.2	47.6	11.4	3.893
3.1	23.91	0.2	46.4	11.6	3.910
4.0	21.72	0.3	43.9	18.2	4.448
9.0	14.63	0.2	35.6	24.4	5.257
11.5	12.44	0.2	33.2	31.1	6.290
20.0	7.25	0.2	28.5	32.2	6.428
23.7	5.61	0.2	27.1	41.0	7.293
27.3	4.18	0.2	26.3	41.7	7.342
31.0	2.95	0.2	26.2	43.9	7.325
41.0	0.70	0.1	29.3	46.2	7.197
45.5	0.28	0.1	30.2	48.7	6.905
50.0	0.21	0.1	30.0	51.3	6.571
53.0	0.34	0.1	29.3	53.1	6.309
77.0	3.12	0.1	23.2	55.9	5.874
80.0	3.52	0.1	23.1	57.9	5.441
120.0	7.84	0.1	25.4	58.9	5.242
160.0	10.99	0.2	27.0	77.6	2.769
200.0	13.61	0.2	27.5	117.5	1.114
250.0	16.51	0.2	28.8	119.5	1.093
316.7	20.38	0.4	29.6	160.3	0.679
350.0	22.46	0.4	29.7	200.7	0.525
390.0	25.29	0.6	29.5	246.9	0.414
402.5	26.25	0.7	29.5	251.2	0.408
415.0	27.29	0.8	29.3	298.5	0.306
427.5	28.35	0.9	29.2	342.8	0.185
440.0	29.49	1.0	28.9	348.7	0.163



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. B
M108294
BIF-50+
070509

Coaxial Band Pass Filter (Constant Impedance) BIF-50+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	33.62	56.30	3.1	1.540
1.4	30.60	53.50	3.2	2.572
1.8	28.39	51.10	5.9	3.434
2.3	26.60	49.30	8.7	3.800
2.7	25.16	47.60	11.4	3.893
3.1	23.91	46.40	11.6	3.910
4.0	21.72	43.90	18.2	4.448
9.0	14.63	35.60	24.4	5.257
11.5	12.44	33.20	31.1	6.290
20.0	7.25	28.50	32.2	6.428
23.7	5.61	27.10	41.0	7.293
27.3	4.18	26.30	41.7	7.342
31.0	2.95	26.20	43.9	7.325
41.0	0.70	29.30	46.2	7.197
45.5	0.28	30.20	48.7	6.905
50.0	0.21	30.00	51.3	6.571
53.0	0.34	29.30	53.1	6.309
77.0	3.12	23.20	55.9	5.874
80.0	3.52	23.10	57.9	5.441
120.0	7.84	25.40	58.9	5.242
160.0	10.99	27.00	77.6	2.769
200.0	13.61	27.50	117.5	1.114
250.0	16.51	28.80	119.5	1.093
316.7	20.38	29.60	160.3	0.679
350.0	22.46	29.70	200.7	0.525
390.0	25.29	29.50	246.9	0.414
402.5	26.25	29.50	251.2	0.408
415.0	27.29	29.30	298.5	0.306
427.5	28.35	29.20	342.8	0.185
440.0	29.49	28.90	348.7	0.163

REV. X1
BIF-50+
060724

Page 1 of 1






Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Coaxial Band Pass Filter (Constant Impedance) BIF-50+

Typical Performance Curves




REV. X1
BIF-50+
060724
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

1. Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I