



THE BIG DEAL

- Standard small 1008 (2.5mm x 2.0mm) case style
- Low Insertion Loss – Mid band 1.2 dB typical
- Wide rejection band
- Shielded construction preventing filter from de-tuning
- Reduced footprint area by employing LGA (land grid array)
- Surface mountable pick and place standard case style



Generic photo used for illustration purposes only

CASE STYLE: NL1008C-7

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Satellite Communications

PRODUCT OVERVIEW

The BFCQ-2872+ LTCC Band Pass Filter achieves a miniature size and high repeatability of performance by utilizing a proprietary LTCC material system and distributed filter topology. The typical passband loss at 27.5 –30.0 GHz is as low as 1.2 dB, with typical stopband rejections at 37 dB up to 55 GHz. This model handles up to 1W RF input power, and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot-to-lot basis.

KEY FEATURES

Feature	Advantages
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (2.5mm x 2.0mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Surface Mountable	Suitable for very high volume automated assembly process.



Mini-Circuits®

CERAMIC

Bandpass Filter

BFCQ-2872+

50Ω

27.5 to 30.0 GHz

ELECTRICAL SPECIFICATIONS¹ AT 25°C



Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	—	—	28.7	—	GHz
	Insertion Loss	F1-F2	—	1.2	3.0	dB
	Return Loss	F1-F2	—	12	—	dB
Stop Band, Lower	Insertion Loss	DC-F3	0.1 - 18	47	—	dB
		18 - 22.2	22	32	—	
Stop Band, Upper	Insertion Loss	F4-F5	35.3 - 38	28.4	—	dB
		38 - 55	27	37	—	

1. Measured on Mini-Circuits Test Board TB-BFCQ-2872C+ with connectors and feedline de-embedded with 2xThru.

MAXIMUM RATINGS

Parameter	Ratings
Operating temperature	-55°C to +125°C
Storage temperature	-55°C to +125°C
RF Power Input	1W

Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE**FUNCTIONAL SCHEMATIC**



Mini-Circuits®

CERAMIC

Bandpass Filter

BFCQ-2872+


50Ω

27.5 to 30.0 GHz

PAD CONNECTIONS

INPUT	1
OUTPUT	2
GROUND	3

PRODUCT MARKING: UC


DEMO BOARD MCL P/N: TB-BFCQ-2872C+
SUGGESTED PCB LAYOUT (PL-707)

NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR MEGTRON-7 R5785(N); DIELECTRIC THICKNESS: .0049±.001; CLOTH STYLE: 2116; COPPER: HVLP/HVLP. FOR OTHER MATERIALS LINE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. SOLDER MASK OPENING FOR COMPONENT SOLDERING HAS BEEN INCREASED AGAINST PCB LAND PATTERN RECOMMENDATIONS PER NL1008C-6 AND CAN BE DEVIATED FROM THIS DRAWING TO COMPLY WITH CUSTOMERS' DESIGN RULES.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

OUTLINE DRAWING

OUTLINE DIMENSIONS (Inches
mm)

A	B	C	D	E	F	G	H	J	K	wt
.098	.079	.028	.012	.024	.024	.008	.028	.043	.024	grams
2.49	2.01	0.71	0.30	0.61	0.61	0.20	0.71	1.09	0.61	.019



CERAMIC

Bandpass Filter

BFCQ-2872+




Mini-Circuits

50Ω

27.5 to 30.0 GHz

TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
100	97.10	0.07
3000	70.63	0.11
6000	66.55	0.01
9000	67.80	0.02
12000	75.89	0.05
15000	55.18	0.34
18000	46.72	0.12
22200	33.28	0.50
24000	23.39	1.08
27500	1.03	27.95
28700	1.03	21.91
30000	1.07	25.18
35300	31.23	0.17
38000	37.43	0.59
42000	52.13	0.32
45000	63.65	0.05
48000	54.31	0.53
51000	48.28	0.24
55000	41.74	0.08
60000	28.54	2.52



NOTES





- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	97.10	0.07
500	84.48	0.14
1000	79.18	0.21
2000	73.57	0.19
3000	70.63	0.11
4000	68.41	0.06
5000	67.12	0.03
6000	66.55	0.01
7000	65.79	0.04
8000	66.30	0.01
9000	67.80	0.02
10000	71.16	0.05
11000	79.55	0.04
12000	75.89	0.05
13000	65.24	0.12
14000	59.29	0.26
13000	65.24	0.12
14000	59.29	0.26
15000	55.18	0.34
16000	52.45	0.27
17000	49.79	0.14
18000	46.72	0.12
19000	43.20	0.17
20000	39.64	0.26
21000	36.63	0.38
22000	33.84	0.47
22200	33.28	0.50
23000	32.61	0.61
24000	23.39	1.08
25000	2.66	13.77
26000	1.26	18.05
27000	1.05	31.01
27500	1.03	27.95
28000	1.03	23.58
28500	1.03	21.97
29000	1.03	22.96
29500	1.03	25.96
30000	1.07	25.18
31000	1.35	21.29
32000	2.69	27.64
33000	28.71	1.11
34000	30.68	0.17
35000	31.09	0.10
35300	31.23	0.17
36000	31.52	0.49
37000	33.34	0.90
38000	37.43	0.59
39000	41.94	0.14
40000	45.51	0.01
41000	48.52	0.18
42000	52.13	0.32
43000	57.09	0.25
44000	62.10	0.03
45000	63.65	-0.05
46000	60.96	0.14
47000	56.35	0.43
48000	54.31	0.53
49000	52.15	0.39
50000	50.80	0.15
51000	48.28	0.24
52000	45.92	0.78
53000	45.26	1.01
54000	45.29	0.59
55000	41.74	-0.08
56000	35.63	-0.36
57000	33.11	-0.10
58000	30.66	0.92
59000	28.86	2.21
60000	28.54	2.52

Typical Performance Curves



Outline Dimensions

NL1008C-7



SUGGESTED LAYOUT FOR PCB LAND PATTERN
TOLERANCE TO BE WITHIN $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L
NL1008C-7	.098 (2.50)	.079 (2.00)	.028 (.70)	.012 (.30)	.024 (.61)	.024 (.61)	.008 (.20)	.028 (.70)	.043 (1.09)	.024 (.60)	.098 (2.50)

CASE#	M	N	P	Q	R	S	WT, GRAM
NL1008C-7	.118 (3.00)	.027 (.70)	.046 (1.20)	.013 (.30)	.079 (2.00)	.064 (1.63)	.019

Dimensions are in inches (mm). Tolerances: 2 PL. $\pm .01$; 3 PL. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

3. Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.
4. Line width should be designed to match 50 Ω characteristic depending on PCB material and thickness.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-007756	NEW RELEASE	05/12/21	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR NL1008C-6 CASE STYLE

SOLDER MASK BORDER
(SEE NOTE 2)

PACKAGE OUTLINE

COPLANAR WAVEGUIDE:
.0091±.001 TRACE WIDTH &
.0079±.001 GAP, 2 PL.




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR MEGTRON-7 R5785(N); DIELECTRIC THICKNESS: .0049±.001; CLOTH STYLE: 2116; COPPER: HVLP/HVLP. FOR OTHER MATERIALS LINE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. SOLDER MASK OPENING FOR COMPONENT SOLDERING HAS BEEN INCREASED AGAINST PCB LAND PATTERN RECOMMENDATIONS PER NL1008C-6 AND CAN BE DEVIATED FROM THIS DRAWING TO COMPLY WITH CUSTOMERS' DESIGN RULES.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG
TOLERANCES ON:	CHECKED	GF
2 PL DECIMALS ±	APPROVED	IL
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, NL1008C-6, TB-BFCQ-XXXX+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-707	OR
FILE:	98PL707	SCALE: 15:1	SHEET: 1 OF 1

Evaluation Board and Circuit



Schematic diagram



Notes:

1. 50 Ohm 1.85 Female connectors.
2. PCB Material: Megtron 7(N) or equivalent,
Dielectric Constant=3.4, Thickness=.005 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Mechanical Shock	50g, 11ms half-sine, 18 shocks applied each to 3 axes	MIL-STD-202 Method 213, Condition A
Vibration	10-2000Hz sine, 20g, 12 cycles applied each to 3 axes	MIL-STD-202, Method 204, Condition D
Constant Acceleration	30Kg, Y1 Direction	MIL-STD-883, Method 2001, Condition E
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	