

Ceramic

Bandpass Filter

50Ω 3400 to 3850 MHz

BFCV-3641+



Generic photo used for illustration purposes only

CASE STYLE: JV1210C-2

Features


- small size
- temperature stable
- hermetically sealed
- LTCC construction
- excellent stopband rejection (usable to 12 GHz, 20 dB typ.)

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Applications

- software defined radio
- WLAN
- cellular network


Functional Schematic




Typical Frequency Response



TOP VIEW



BOTTOM VIEW



Pad Connections

Input	1
Output	2
Ground	3

Electrical Specifications^(1,2) at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	3636	—	MHz	
	Insertion Loss	F3-F6	3400-3850	—	1.9	3.5	dB
		F4-F5	3600-3800	—	1.6	—	dB
Stop Band, Lower	VSWR	F3-F6	3400-3850	—	1.7	—	:1
	Insertion Loss	DC-F1	DC-2670	26	35	—	dB
		F2	2930	—	20	—	dB
Stop Band, Upper	VSWR	DC-F1	DC-2670	—	20	—	:1
	Insertion Loss	F7	4650	—	20	—	dB
		F8-F9	5350-9600	30	35	—	dB
		F8-F9	5350-9600	—	20	—	:1

(1) Measured on Mini-Circuits Characterization Test Board TB-980+

(2) This filter is not intended for use as a DC Blocking circuit element. In application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.



Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	0.5W max @

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C





Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
100	52.86	876.08
500	39.78	235.50
1000	38.14	74.48
2000	38.83	71.53
3400	1.74	1.44
3600	1.45	1.05
3800	1.57	1.23
3900	1.83	1.57
4600	17.86	19.72
5300	42.92	22.23
7000	41.47	45.89
9600	35.24	502.48
11000	25.28	93.97
12000	27.47	138.85
13000	13.31	14.68



Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
100	52.86	876.08
200	46.92	1074.59
300	43.57	564.53
400	41.36	384.59
500	39.78	235.50
600	38.68	162.13
700	37.99	122.93
800	37.67	97.57
1000	38.14	74.48
1200	40.48	67.51
1400	46.27	67.67
1600	61.67	71.57
1800	44.07	74.24
2000	38.83	71.53
2200	36.15	62.92
2400	35.37	51.16
2600	39.23	39.72
2670	39.23	39.72
2700	47.87	33.95
2800	31.69	27.49
2930	21.77	19.75
3000	13.37	10.68
3200	2.50	1.13
3400	1.74	1.44
3420	1.69	1.40
3440	1.64	1.35
3460	1.59	1.30
3480	1.56	1.26
3500	1.52	1.21
3520	1.50	1.17
3540	1.48	1.13
3560	1.47	1.09
3580	1.46	1.07
3600	1.45	1.05
3620	1.45	1.03
3640	1.45	1.02
3660	1.45	1.01
3680	1.46	1.02
3700	1.46	1.03
3720	1.48	1.06
3740	1.49	1.09
3760	1.51	1.13
3780	1.54	1.18
3800	1.57	1.23
3820	1.61	1.29
3840	1.65	1.35
3860	1.71	1.42
3880	1.77	1.49
3900	1.83	1.57
4000	2.20	1.86
4650	17.86	19.72
5000	30.61	27.97
5350	42.92	22.23
5500	53.98	18.04
6000	37.47	16.46
6500	37.68	26.52
7000	41.47	45.89
7500	51.17	67.14
8000	48.24	80.80
8500	40.31	120.90
9000	36.68	124.72
9500	35.26	233.79
9600	35.24	502.48
10000	34.84	165.77
10500	29.76	55.57
11000	25.28	93.97
11500	23.79	236.33
12000	27.47	138.85
12500	15.38	11.06
13000	13.31	14.68

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 • Fax (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

Outline Dimensions

JV1210C-2



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAM
JV1210C-2	.126 (3.2)	.098 (2.5)	.059 (1.5)	.012 (0.3)	.024 (0.6)	-- --	.205 (5.2)	.087 (2.2)	.079 (2.0)	.028 (0.70)	.047 (1.2)	-- --	.059 (1.5)	.026 (0.65)	.012 (0.3)	.045

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F74

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles

GE0805C-1
 GE0805C-1AP
 JV1210C-1
 GU2939




ILLUSTRATION 2

Applicable Case Styles

JV1210C
 JV1210C-2
 JV1210C-3
 JV1210C-4
 JV1210C-5
 JV1210C-6
 JV1210C-11




ILLUSTRATION 3

Applicable Case Styles

JC0603C-8
 JV1210C-7
 JV1210C-8
 JV1210C-9
 JV1210C-10
 JV1210C-13
 GE0805C-13

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000
				2000
			4000	

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M169330	NEW RELEASE	08/08/18	GF	BK

SUGGESTED MOUNTING CONFIGURATION
FOR JV1210C-2 CASE STYLE, "03FL01" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 (IT-180A) WITH DIELECTRIC THICKNESS $.010 \pm .001$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. UNIT LAND PATTERN WAS ADJUSTED FOR HIGH FREQUENCY PERFORMANCE AND DIFFERENT FROM SUGESTED LAYOUT AS PER JV1210C-2.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	08/02/18
TOLERANCES ON:	CHECKED IL	08/07/18
2 PL DECIMALS ±	APPROVED BK	08/08/18
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®



13 Neptune Avenue
 Brooklyn NY 11235

PL, 03FL01, JV1210C-2, TB-980+

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-542	REV: OR
FILE: 98PL542	SCALE: 15:1	SHEET: 1	OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: FR4 or equivalent,
Dielectric Constant=4.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A