

Low Pass Filter

50Ω DC to 32 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- rugged shielded case
- other standard and custom BLP models available with wide selection of fco

Applications

- test equipment
- lab use
- video equipment

BLP-30+



Generic photo used for illustration purposes only

CASE STYLE: FF55


Connectors Model

BNC BLP-30+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch/mm)

B	D	wt
.57	2.59	grams
14.47	65.79	40.0


Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-32	35	47-61 61-200	1.7 18

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
1.00	0.07	0.1	1.00	23.20
10.00	0.21	0.1	10.00	23.47
19.00	0.29	0.1	19.00	26.06
28.00	0.37	0.1	28.00	32.45
31.00	0.48	0.1	31.00	41.59
32.00	0.55	0.1	32.00	45.56
33.50	0.62	0.1	33.50	48.79
34.00	0.76	0.1	34.00	51.33
35.00	1.30	0.3	35.00	56.96
38.00	6.09	0.9	38.00	47.73
40.00	10.78	0.9	39.00	39.87
43.00	17.56	0.8	40.00	32.35
45.00	21.65	0.7	42.00	23.79
46.00	23.56	0.7	43.00	19.72
47.00	25.39	0.7	44.00	17.97
48.00	27.19	0.7	45.00	15.87
50.00	30.58	0.6	46.00	14.29
55.00	38.32	0.6	47.00	12.98
59.00	43.69	0.7	48.00	12.68
60.00	45.01	0.7	49.00	10.48
61.00	46.27	0.5	50.00	11.50
91.50	76.88	4.1	52.00	7.62
109.50	80.77	5.3	55.00	4.41
127.50	79.89	2.8	58.00	4.04
145.50	77.20	3.0	59.00	7.93
164.00	74.52	3.4	60.00	1.04
173.00	74.92	3.8	61.00	0.99
182.00	78.05	5.9	91.50	0.88
191.00	79.62	6.8	100.50	0.79
200.00	80.65	6.9	109.50	0.75



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	45.80	1.0	23.200
10.0	0.21	23.50	10.0	23.470
19.0	0.29	18.20	19.0	26.060
28.0	0.37	20.40	28.0	32.450
31.0	0.48	28.10	31.0	41.590
32.0	0.55	21.80	32.0	45.560
33.5	0.62	18.80	33.5	48.790
34.0	0.76	16.10	34.0	51.330
35.0	1.30	9.90	35.0	56.960
38.0	6.09	2.10	38.0	47.730
40.0	10.78	0.90	39.0	39.870
43.0	17.56	0.40	40.0	32.350
45.0	21.65	0.30	42.0	23.790
46.0	23.56	0.30	43.0	19.720
47.0	25.39	0.20	44.0	17.970
48.0	27.19	0.20	45.0	15.870
50.0	30.58	0.20	46.0	14.290
55.0	38.32	0.10	47.0	12.980
59.0	43.69	0.20	48.0	12.680
60.0	45.01	0.10	49.0	10.480
61.0	46.27	0.10	50.0	11.500
91.5	76.88	0.10	52.0	7.620
109.5	80.77	0.10	55.0	4.410
127.5	79.89	0.10	58.0	4.040
145.5	77.20	0.10	59.0	7.930
164.0	74.52	0.10	60.0	1.040
173.0	74.92	0.10	61.0	0.990
182.0	78.05	0.10	91.5	0.880
191.0	79.62	0.10	100.5	0.790
200.0	80.65	0.10	109.5	0.750

Coaxial Low Pass Filter

Typical Performance Curves

BLP-30+



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
BLP-30+
070603
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

1. Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I