

Low Pass Filter

BLP-850+

50Ω DC to 780 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- rugged shielded case
- other standard and custom BLP models available with wide selection of fco

Applications

- test equipment
- lab use
- video equipment



Generic photo used for illustration purposes only


CASE STYLE: FF55

Connectors	Model
BNC	BLP-850+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch/mm)

B	D	wt
.57	2.59	grams
14.47	65.79	40.0


Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB)	(loss > 40 dB)	Passband Typ.	Stopband Typ.
DC-780	850	1100-1400	1400-2000	1.7	18

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
10.00	0.02	0.1	10.0	1.00
175.00	0.38	0.1	92.5	1.05
342.50	0.44	0.1	175.0	0.94
507.50	0.18	0.1	257.5	0.95
672.50	0.57	0.1	342.5	0.97
755.00	0.43	0.1	425.0	1.22
780.00	0.40	0.1	507.5	1.35
820.00	1.33	0.6	590.0	1.40
850.00	3.00	0.9	672.5	1.38
1010.00	17.47	1.1	755.0	1.85
1030.00	19.18	1.1	780.0	2.23
1050.00	20.83	1.1	790.0	2.22
1060.00	21.63	1.1	820.0	2.55
1070.00	22.41	1.1	840.0	2.57
1100.00	24.70	1.1	850.0	2.36
1110.00	25.52	1.1	1010.0	0.99
1150.00	28.51	1.2	1020.0	0.92
1350.00	43.25	1.6	1030.0	0.88
1360.00	44.10	1.9	1050.0	0.78
1380.00	45.39	1.8	1060.0	0.75
1400.00	47.43	2.2	1070.0	0.80
1420.00	48.89	2.1	1100.0	0.84
1667.50	69.86	3.1	1110.0	0.70
1750.00	70.13	6.6	1120.0	0.70
1835.00	69.30	4.7	1150.0	0.69
1900.00	67.90	2.7	1300.0	0.45
1920.00	70.63	3.5	1350.0	0.02
1930.00	69.67	2.6	1360.0	0.24
1950.00	74.71	7.2	1380.0	0.48
2000.00	68.74	4.9	1400.0	0.05



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-023903
BLP-850+
MCL NY
241210

Coaxial Low Pass Filter

BLP-850+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.02	35.00	10.0	1.000
175.0	0.38	11.80	92.5	1.050
342.5	0.44	11.30	175.0	0.940
507.5	0.18	37.10	257.5	0.950
672.5	0.57	11.80	342.5	0.970
755.0	0.43	20.20	425.0	1.220
780.0	0.40	21.90	507.5	1.350
820.0	1.33	9.10	590.0	1.400
850.0	3.00	4.40	672.5	1.380
1010.0	17.47	0.30	755.0	1.850
1030.0	19.18	0.20	780.0	2.230
1050.0	20.83	0.20	790.0	2.220
1060.0	21.63	0.20	820.0	2.550
1070.0	22.41	0.20	840.0	2.570
1100.0	24.70	0.20	850.0	2.360
1110.0	25.52	0.20	1010.0	0.990
1150.0	28.51	0.20	1020.0	0.920
1350.0	43.25	0.10	1030.0	0.880
1360.0	44.10	0.10	1050.0	0.780
1380.0	45.39	0.10	1060.0	0.750
1400.0	47.43	0.10	1070.0	0.800
1420.0	48.89	0.10	1100.0	0.840
1667.5	69.86	0.10	1110.0	0.700
1750.0	70.13	0.10	1120.0	0.700
1835.0	69.30	0.10	1150.0	0.690
1900.0	67.90	0.10	1300.0	0.450
1920.0	70.63	0.10	1350.0	0.020
1930.0	69.67	0.10	1360.0	0.240
1950.0	74.71	0.10	1380.0	0.480
2000.0	68.74	0.10	1400.0	0.050


REV. X1
BLP-850+
060724
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Typical Performance Curves



REV. X1
BLP-850+
060724
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

- Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I