

Band Pass Filter

BPF-EDU1915

Surface Mount

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



99-01-OPU518


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter	Min.	Typ.	Max.	Units
Passband (Loss - 6 dB Typ)	89		95	MHz
Centre frequency		92		MHz
Low Band (Loss > 20 dB)	DC	82		MHz
High Band (Loss > 20 dB)		102	2000	MHz
Passband VSWR		2		(:1)
Stopband VSWR		20		(:1)

Functional Schematic

MAXIMUM RATINGS

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.1 W



PIN CONNECTIONS

Input	1
Output	6
Ground	1,2,3,4,5,7,8,9,10

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	83.73	0.05	89.0	110.13
60	52.22	0.09	89.4	104.72
82	51.11	1.25	89.8	100.27
84	32.62	2.88	90.2	96.72
85	21.84	5.23	90.6	93.86
86	13.44	10.39	91.0	91.57
87	8.37	14.88	91.4	89.72
89	5.01	15.09	91.8	88.29
90	4.56	14.35	92.2	87.37
90	4.56	14.35	92.4	87.13
91	4.42	12.93	92.6	87.05
92	4.49	11.21	92.8	87.19
93	4.67	10.47	93.0	87.55
95	5.27	16.20	93.2	88.14
96	6.27	20.36	93.4	88.99
98	14.43	5.26	93.6	90.09
99	22.65	2.77	93.8	91.51
100	32.15	1.72	94.0	93.15
120	59.27	0.14	94.2	95.13
500	63.87	0.05	94.4	97.35
1000	50.62	0.01	94.6	99.89
1500	41.12	0.04	94.8	102.67
1750	37.13	0.09	95.0	105.73
2000	32.58	0.16	95.2	109

Typical Performance Curves

