COAXIAL

Precision Fixed Attenuator BW-N5W5+

50Ω 5 W 5 dB DC to 18 GHz N-Type Female to N-Type Male

FEATURES

- DC to 18 GHz
- Precision Attenuation
- Excellent VSWR, 1.20 Typ.
- Stainless Steel N-Type Male and Female Connectors



Generic photo used for illustration purposes only

Model No.	BW-N5W5+
Case Style	DC736
Connectors	N-Type Female to N-Type Male

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Impedance Matching
- Instrumentation
- Test Setups

ELECTRICAL SPECIFICATIONS AT +25 °C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range		DC		18	GHz
Attenuation, Nominal	–	–	5	–	dB
Attenuation, Accuracy[1]	DC–18	–	±0.40	–	dB
VSWR[2]	DC–4	–	–	1.20	:1
	4–8	–	–	1.25	
	8–12.4	–	–	1.30	
Input Power[3]	–	–	–	5.0	W

1. At +25 °C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: 0.0004 dB/dB/°C typ.
2. VSWR from 12.4 to 18 GHz, 1.6:1 typ.
3. Average power at +25 °C ambient, derate linearly to 2 W at +100 °C. Peak Power 125 W max. 5 µsec. pulse width, 100 Hz PRF.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55 °C to +100 °C
Storage Temperature[4]	-55 °C to +100 °C

4. With mated connectors. Unmated, +85 °C max.
Permanent damage may occur if any of these limits are exceeded.


REV. E
ECO-024310
BW-N5W5+
MCL NY
260811

COAXIAL

Precision Fixed Attenuator BW-N5W5+

50Ω 5 W 5 dB DC to 18 GHz N-Type Female to N-Type Male

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch / mm)

B	D	E	wt
.61	1.90	.812	grams
15.49	48.26	20.62	49.7


COAXIAL


Precision Fixed Attenuator BW-N5W5+

50Ω 5 W 5 dB DC to 18 GHz N-Type Female to N-Type Male

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
100	5.02	1.00
2000	5.04	1.02
4000	5.05	1.04
6000	5.03	1.02
8000	5.00	1.06
10000	4.97	1.12
11000	4.95	1.13
13000	4.91	1.12
15000	4.86	1.17
18000	4.90	1.26





NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Fixed Attenuator BW-N5W5+


Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	RETURN LOSS (dB)
100.00	5.02	46.06
2000.00	5.04	40.09
4000.00	5.05	34.15
6000.00	5.03	40.09
8000.00	5.00	30.71
10000.00	4.97	24.94
11000.00	4.95	24.29
13000.00	4.91	24.94
15000.00	4.86	22.12
18000.00	4.90	18.78


Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

Attenuation



Return Loss




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style DC

Outline Dimensions

DC736



CASE#	A	B	C	D	E	WT. GRAMS
DC736	-- --	.61 (15.49)	-- --	1.90 (48.26)	.812 (20.62)	49.7

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .03; 3 Pl. ± .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish: Black anodize.

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV28

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.