

Low Pass Filter


50Ω DC to 81 MHz
Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing

Outline Dimensions (inch/mm)

B	D	wt
.57	2.59	grams
14.47	65.79	40.0

Features

- rugged shielded case
- other standard and custom BLP models available with wide selection of fco

Applications

- test equipment
- lab use
- video equipment



Generic photo used for illustration purposes only

CASE STYLE: FF55

Connectors Model



BNC BLP-90+

+RoHS Compliant




The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB)	(loss > 40 dB)	Passband Typ.	Stopband Typ.
DC-81	90	121-157	157-400	1.7	18

typical frequency response

electrical schematic

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
1.00	0.05	0.1	1.00	9.672
12.50	0.14	0.1	12.50	9.503
24.00	0.18	0.1	24.00	9.491
35.50	0.31	0.1	35.50	9.776
46.50	0.42	0.1	46.50	10.240
58.00	0.43	0.1	58.00	11.244
81.00	0.69	0.1	81.00	15.573
87.00	1.28	0.4	84.00	17.894
90.00	2.01	0.5	87.00	19.997
93.00	6.43	0.9	90.00	24.263
97.00	8.74	1.0	93.00	21.734
104.01	12.94	1.1	97.00	17.532
111.00	16.72	1.2	104.00	15.893
115.52	21.91	1.2	111.00	12.218
121.03	26.16	1.2	115.50	5.804
130.03	32.40	1.3	121.00	5.229
140.04	38.50	1.4	130.00	3.892
145.04	41.31	1.4	135.00	2.740
150.04	43.98	1.5	140.00	0.487
155.05	46.76	1.7	145.00	0.841
157.05	47.69	1.8	150.00	2.060
184.06	60.11	2.9	155.00	7.687
206.57	66.87	1.4	157.00	5.680
229.58	75.03	5.6	184.00	5.380
252.57	74.83	7.6	195.50	5.060
298.08	76.96	7.1	206.50	4.740
321.08	75.07	4.9	218.00	4.320
355.57	73.10	4.4	229.50	4.010
378.08	75.50	4.8	241.00	3.760
400.07	74.56	6.3	252.50	3.450


Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

BLP-90+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.05	42.00	1.0	9.672
12.5	0.14	37.50	12.5	9.503
24.0	0.18	27.70	24.0	9.491
35.5	0.31	18.70	35.5	9.776
46.5	0.42	14.90	46.5	10.240
58.0	0.43	16.10	58.0	11.244
81.0	0.69	17.00	81.0	15.573
87.0	1.28	9.70	84.0	17.894
90.0	2.01	7.60	87.0	19.997
93.0	6.43	3.80	90.0	24.263
97.0	8.74	1.70	93.0	21.734
104.0	12.94	0.80	97.0	17.532
111.0	16.72	0.50	104.0	15.893
115.5	21.91	0.10	111.0	12.218
121.0	26.16	0.20	115.5	5.804
130.0	32.40	0.30	121.0	5.229
140.0	38.50	0.30	130.0	3.892
145.0	41.31	0.30	135.0	2.740
150.0	43.98	0.30	140.0	0.487
155.1	46.76	0.30	145.0	0.841
157.1	47.69	0.30	150.0	2.060
184.1	60.11	0.30	155.0	7.687
206.6	66.87	0.30	157.0	5.680
229.6	75.03	0.20	184.0	5.380
252.6	74.83	0.20	195.5	5.060
298.1	76.96	0.10	206.5	4.740
321.1	75.07	0.10	218.0	4.320
355.6	73.10	0.10	229.5	4.010
378.1	75.50	0.10	241.0	3.760
400.1	74.56	0.10	252.5	3.450

REV. X1
BLP-90+
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
BLP-90+
060724
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

- Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I