Surface Mount

Bandpass Filter

BPF-C141+

50Ω 110 to 180 MHz

Generic photo used for illustration purposes only

CASE STYLE: HU1186

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.2W Max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	2
OUTPUT	9
NOT CONNECTED	6,13
GROUND	1, 3, 4, 5, 7,8,10,11,12,14

Features

- Good VSWR, 1.3:1 Typ @ Passband
- Flat Group Delay
- Shielded case
- Aqueous washable

Applications

- Military communications
- Receivers / Transmitters
- Harmonic rejection

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	G	H	J	K	M	N	wt
.870	.800	.25	.100	.097	.060	.040	.105	.910	.060	.060	grams
22.10	20.32	6.35	2.54	2.46	1.52	1.02	2.67	23.11	1.52	1.52	2.85

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-500+
Suggested PCB Layout (PL-294)



NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030"± .002"; COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Bandpass Filter Electrical Specifications (T_{AMB}= 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 2dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss 40dB Typ.		Passband		Stopband
Fc	F1 - F2	F3	F4	F5	F6	Typ.	Max.	Typ.
141	110 - 180	92	213	90	217 - 2500	1.3	1.7	18

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB) $\bar{x}$	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
0.5	72.15	0.59	0.01	108.0	25.97
90.0	44.81	2.20	1.10	110.0	22.54
92.0	37.23	1.95	1.28	113.6	18.47
96.0	17.01	1.27	1.96	116.0	16.79
98.4	9.41	0.97	3.33	120.8	14.45
100.8	4.46	0.58	6.68	126.4	12.72
103.2	2.27	0.22	12.23	132.0	11.63
110.0	1.07	0.03	31.61	137.6	10.90
120.8	0.74	0.01	25.27	141.0	10.62
141.0	0.75	0.03	15.86	148.8	10.31
160.0	0.79	0.03	17.53	153.6	10.37
180.0	1.12	0.03	14.39	154.4	10.38
199.2	3.19	0.28	13.24	160.0	10.70
204.0	8.23	0.82	5.73	165.6	11.09
208.8	18.43	1.13	2.45	171.2	11.67
213.0	30.56	1.54	1.30	176.8	12.52
217.0	42.20	1.22	1.00	180.0	13.48
2500.0	45.14	1.32	0.24	188.0	16.72

BPF-C141+
INSERTION LOSS



BPF-C141+
RETURN LOSS



BPF-C141+
GROUP DELAY



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Surface Mount Band Pass Filter BPF-C141+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	71.96	72.74	72.28	0.00	0.00	0.00	0.01	0.01	0.00
10	46.28	46.28	46.28	0.00	0.00	0.00	0.01	0.02	0.03
20	41.64	41.61	41.59	0.00	0.01	0.01	0.05	0.08	0.10
30	40.79	40.82	40.82	0.01	0.02	0.02	0.13	0.18	0.21
40	43.61	43.75	43.87	0.03	0.04	0.04	0.25	0.31	0.34
50	61.75	62.15	62.99	0.05	0.06	0.07	0.38	0.44	0.47
60	43.38	43.39	43.32	0.09	0.11	0.12	0.48	0.55	0.59
70	38.78	38.80	38.77	0.16	0.19	0.21	0.54	0.64	0.71
80	45.33	45.73	46.02	0.29	0.34	0.38	0.61	0.75	0.84
90	47.46	47.65	47.50	0.62	0.72	0.80	0.80	0.98	1.10
92	39.47	37.88	36.77	0.75	0.88	0.98	0.89	1.08	1.21
96	18.89	18.37	17.96	1.32	1.56	1.74	1.28	1.56	1.73
100	6.70	6.58	6.47	4.05	4.70	5.19	3.55	4.13	4.53
110	1.03	1.19	1.30	21.14	20.92	20.79	19.64	19.49	19.35
120	0.73	0.86	0.95	24.10	24.43	24.47	22.00	21.81	21.57
130	0.70	0.82	0.89	18.06	18.23	18.35	18.30	18.27	18.18
140	0.72	0.84	0.92	15.83	15.83	15.79	16.22	16.11	15.92
141	0.72	0.84	0.92	15.80	15.80	15.75	16.16	16.05	15.86
150	0.72	0.84	0.93	16.83	16.87	16.79	16.76	16.66	16.38
160	0.74	0.88	0.97	20.23	20.19	19.92	18.70	18.40	17.93
170	0.85	1.00	1.10	18.41	18.80	18.96	17.18	17.31	17.28
180	1.05	1.23	1.33	16.05	16.92	17.72	16.01	16.83	17.62
190	1.33	1.59	1.76	21.71	23.44	25.39	22.45	24.32	26.63
200	3.12	3.80	4.32	11.46	10.79	10.23	13.34	12.85	12.33
204	7.38	8.50	9.38	4.22	4.18	4.12	5.35	5.36	5.25
210	20.96	22.29	23.35	1.32	1.50	1.61	1.81	2.01	2.09
213	30.27	31.75	32.93	0.98	1.15	1.26	1.34	1.51	1.59
215	38.46	39.85	40.79	0.86	1.01	1.11	1.14	1.30	1.38
217	45.22	44.19	43.49	0.77	0.91	1.01	0.99	1.14	1.22
250	53.64	53.73	53.82	0.40	0.47	0.52	0.34	0.43	0.46
300	64.65	63.99	63.44	0.38	0.44	0.47	0.16	0.26	0.30
400	49.40	49.32	49.31	0.31	0.39	0.45	0.06	0.16	0.20
500	53.46	53.60	53.56	0.23	0.34	0.40	0.02	0.13	0.18
600	59.97	60.16	60.28	0.21	0.33	0.40	0.00	0.13	0.18
700	74.85	74.54	75.25	0.22	0.36	0.43	0.00	0.14	0.20
800	49.01	49.95	50.82	0.25	0.41	0.49	0.02	0.18	0.24
900	58.96	59.11	59.05	0.29	0.47	0.56	0.00	0.18	0.25
950	52.75	52.52	52.33	0.36	0.55	0.66	0.02	0.19	0.26
1000	47.14	48.39	49.54	0.54	0.71	0.79	0.01	0.20	0.27
1100	61.28	62.23	62.24	0.36	0.56	0.66	0.03	0.22	0.30
1200	62.94	63.46	64.04	0.38	0.58	0.69	0.03	0.24	0.32
1300	68.40	71.90	71.05	0.39	0.59	0.70	0.25	0.40	0.45
1400	68.07	69.15	69.45	0.38	0.58	0.70	0.05	0.28	0.36
1500	70.57	74.52	71.91	0.36	0.57	0.69	0.06	0.30	0.40
1600	62.67	64.22	64.56	0.35	0.56	0.68	0.08	0.32	0.43
1700	62.38	60.08	64.08	0.34	0.53	0.66	0.08	0.34	0.46
1800	67.41	71.01	66.48	0.31	0.52	0.62	0.08	0.34	0.49
1900	66.44	60.39	65.65	0.30	0.50	0.60	0.08	0.36	0.52
2000	62.61	60.63	59.68	0.30	0.49	0.61	0.09	0.37	0.54
2100	61.67	62.41	60.16	0.31	0.51	0.61	0.09	0.39	0.56
2200	58.79	55.22	58.96	0.46	0.60	0.70	0.09	0.39	0.57
2300	57.04	58.00	56.71	0.33	0.49	0.61	0.08	0.41	0.58
2400	51.29	54.49	50.55	0.37	0.52	0.65	0.07	0.41	0.59
2500	58.11	49.13	60.01	0.44	0.61	0.73	0.05	0.43	0.57

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
108.0	26.87	26.74	26.10
108.5	26.15	25.52	25.23
109.0	25.37	24.83	24.54
109.5	24.18	23.82	23.40
110.0	23.33	22.66	22.46
110.5	22.56	22.25	22.09
111.0	21.83	21.47	21.34
111.5	21.40	21.33	20.90
112.0	20.72	20.40	20.18
112.5	20.49	20.08	19.92
113.0	19.57	19.50	19.15
113.5	19.33	18.86	19.05
114.0	18.85	19.07	18.67
114.5	18.34	18.13	18.19
115.0	18.14	18.06	17.91
117.5	16.62	16.49	16.41
120.0	15.39	15.29	15.22
122.5	14.38	14.27	14.25
125.0	13.59	13.58	13.49
127.5	12.85	12.87	12.80
130.0	12.26	12.24	12.22
132.5	11.81	11.79	11.84
135.0	11.43	11.42	11.42
137.5	11.09	11.07	11.03
140.0	10.88	10.89	10.84
141.0	10.84	10.88	10.84
142.0	10.81	10.78	10.80
143.0	10.71	10.76	10.72
144.0	10.67	10.68	10.73
145.0	10.71	10.62	10.57
147.5	10.57	10.57	10.57
150.0	10.59	10.55	10.60
152.5	10.57	10.55	10.51
155.0	10.68	10.66	10.65
157.5	10.73	10.75	10.69
160.0	10.86	10.92	10.88
162.5	10.92	10.97	10.91
165.0	11.17	11.19	11.19
167.5	11.55	11.51	11.57
170.0	11.73	11.72	11.79
175.0	12.36	12.43	12.58
176.0	12.60	12.69	12.73
177.0	12.74	12.83	12.96
178.0	12.95	13.25	13.20
179.0	13.29	13.52	13.52
180.0	13.42	13.65	13.81
181.0	13.84	13.90	14.25
182.0	14.06	14.21	14.35
183.0	14.76	14.93	15.11
184.0	14.90	15.24	15.28
185.0	15.27	15.51	15.90
186.0	16.08	16.21	16.50
187.0	16.66	16.78	17.03
188.0	17.15	17.32	17.60

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Surface Mount Band Pass Filter BPF-C141+

Typical Performance Curves

INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style HU

Outline Dimensions

HU1186



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	- -	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	- -	.060 (1.52)	.060 (1.52)	- -	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
   For RoHS Case Styles: 2-5 µ inch (.05-.13 microns) Gold over 120-240 µ inch (3.05-6.10 microns) Nickel plate.
   For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F21

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119979	NEW RELEASE (FROM RAVON)	11/08	DK	HH
OR	R74463	NEW RELEASE (FROM RAVON)	11/08	DK	HH

SUGGESTED MOUNTING CONFIGURATION FOR HU1186 CASE STYLE, "14FL03" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030" ± .002"; COPPER: 1/2 OZ ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DK (RAVON)	02 NOV 08
TOLERANCES ON:	CHECKED	DH (RAVON)	02 NOV 08
2 PL DECIMALS ±	APPROVED	HH (RAVON)	02 NOV 08
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 14FL03, HU1186, BPF-C
TB-500+ (50 OHM)

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-294	OR

FILE:	SCALE:	SHEET:
98PL294	3:1	1 OF 1

Evaluation Board and Circuit



TB-500+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent.
   Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV12

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D

This document and its contents are the property of Mini-Circuits.