

Surface Mount Bandpass Filter

CBP-1555C+

50Ω 1525 to 1585 MHz



Generic photo used for illustration purposes only
CASE STYLE: MP1766

The Big Deal

- Narrow bandwidth
- Excellent Rejection
- High power handling
- Miniature shielded package

Product Overview

CBP-1555C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aeronautical and satellite applications

Key Features

Feature	Advantages
High Selectivity	The CBP-1555C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1555C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Bandpass Filter

50Ω 1525 to 1585 MHz

CBP-1555C+



Generic photo used for illustration purposes only

CASE STYLE: MP1766

Features

- Narrow bandwidth
- Excellent rejection
- High selectivity
- High power handling
- Miniature shielded package

Applications

- Aviation / Aeronautical
- Mobile satellite
- Differential GPS
- Maritime

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	1555	—	MHz
	Insertion Loss	F1-F2	—	1.10	2.50	dB
	VSWR	F1-F2	—	1.43	2.32	:1
Stop Band, Lower	Insertion Loss	DC-F3	20	29	—	dB
	VSWR	DC-F3	—	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	20	27	—	dB
	VSWR	F4-F5	—	20	—	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10W

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	99.52	289.53	1525	6.79
550	90.84	347.44	1528	6.68
1150	69.10	108.58	1530	6.62
1415	29.55	36.97	1532	6.56
1437	20.92	26.33	1534	6.52
1456	12.06	13.29	1536	6.47
1468	6.18	5.65	1538	6.43
1475	3.48	3.03	1540	6.40
1525	0.98	1.19	1542	6.38
1555	0.93	1.17	1544	6.36
1585	0.96	1.03	1550	6.34
1600	1.33	1.46	1553	6.36
1615	3.57	3.73	1555	6.37
1625	6.55	7.73	1558	6.40
1640	11.70	18.90	1560	6.42
1670	20.64	46.96	1565	6.48
1700	27.54	66.82	1570	6.58
1715	30.46	75.53	1575	6.71
2000	78.98	91.43	1580	6.90
3600	40.03	57.91	1585	7.18

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13

Demo Board MCL P/N: TB-684+
Suggested PCB Layout (PL-373)




- NOTES:
1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



PCB Land Pattern



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z	wt.	
.790	.541	.790	.499	.384	.203	.080	.069	.630	.630	.145		grams
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68		4.6

Note: Please refer to case style drawing for details.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	105.12	99.52	99.03	0.06	0.06	0.06	0.05	0.05	0.05
230	110.70	104.49	97.28	0.01	0.03	0.03	0.01	0.03	0.04
350	100.56	115.14	96.19	0.01	0.03	0.04	0.01	0.04	0.05
530	91.15	91.63	89.49	0.01	0.05	0.06	0.02	0.05	0.06
810	80.67	80.16	80.67	0.02	0.08	0.10	0.05	0.10	0.12
1070	70.11	69.73	69.56	0.08	0.14	0.17	0.10	0.17	0.19
1150	69.27	69.10	68.89	0.10	0.16	0.20	0.13	0.19	0.22
1250	73.40	72.58	72.15	0.13	0.20	0.23	0.17	0.24	0.26
1277	86.97	85.56	86.71	0.14	0.22	0.24	0.18	0.26	0.29
1319	60.49	60.09	60.53	0.17	0.25	0.29	0.21	0.29	0.31
1350	50.55	50.28	50.36	0.20	0.29	0.33	0.24	0.32	0.36
1382	40.87	40.50	40.50	0.25	0.35	0.40	0.28	0.38	0.42
1400	35.14	34.74	34.70	0.28	0.40	0.46	0.32	0.43	0.48
1410	31.77	31.33	31.28	0.31	0.44	0.50	0.35	0.47	0.53
1413	30.71	30.27	30.22	0.32	0.45	0.51	0.36	0.49	0.55
1414	30.36	29.91	29.86	0.33	0.46	0.52	0.37	0.49	0.55
1415	30.00	29.55	29.49	0.33	0.47	0.52	0.37	0.50	0.56
1420	28.18	27.72	27.66	0.35	0.50	0.56	0.40	0.53	0.60
1439	20.58	20.05	20.00	0.51	0.70	0.79	0.55	0.74	0.84
1444	18.35	17.82	17.77	0.58	0.80	0.91	0.63	0.84	0.96
1445	17.90	17.37	17.32	0.61	0.83	0.94	0.65	0.87	0.99
1457	12.07	11.56	11.57	1.05	1.39	1.55	1.10	1.46	1.62
1461	10.02	9.56	9.60	1.36	1.79	1.97	1.44	1.88	2.06
1476	3.19	3.19	3.40	5.51	6.54	6.64	5.76	6.87	7.01
1480	2.13	2.27	2.49	8.28	9.47	9.38	8.71	10.02	9.95
1495	0.93	1.19	1.34	23.39	25.12	25.27	26.36	26.53	25.89
1503	0.85	1.09	1.22	22.75	26.26	29.45	22.09	23.46	24.43
1513	0.77	1.01	1.14	26.35	29.18	28.35	23.70	24.02	23.67
1525	0.75	0.98	1.10	21.51	21.28	21.28	20.95	20.55	20.59
1550	0.74	0.94	1.04	18.05	20.10	22.67	18.27	20.38	23.09
1555	0.72	0.93	1.03	19.36	22.16	25.73	19.65	22.61	26.61
1570	0.68	0.91	1.04	29.55	33.38	27.75	31.16	37.65	28.53
1579	0.69	0.94	1.08	39.35	31.01	26.35	47.50	31.72	26.63
1585	0.71	0.96	1.11	47.14	37.15	32.09	42.93	38.39	32.76
1587	0.72	0.98	1.12	44.90	41.01	36.75	39.84	43.67	39.43
1612	2.11	2.88	3.44	6.98	6.03	5.41	7.01	6.08	5.47
1623	4.78	5.90	6.69	2.89	2.61	2.40	2.92	2.65	2.44
1639	10.20	11.36	12.20	0.90	0.97	0.98	0.93	1.00	1.02
1668	19.21	20.12	20.81	0.25	0.38	0.43	0.29	0.42	0.47
1671	20.02	20.90	21.57	0.23	0.36	0.41	0.28	0.40	0.45
1694	25.56	26.29	26.87	0.15	0.27	0.32	0.19	0.31	0.36
1700	26.84	27.54	28.10	0.14	0.26	0.31	0.18	0.30	0.34
1710	28.86	29.51	30.04	0.13	0.24	0.29	0.17	0.28	0.32
1720	30.75	31.37	31.87	0.12	0.23	0.27	0.16	0.27	0.31
1730	32.53	33.12	33.60	0.11	0.22	0.26	0.16	0.26	0.30
1780	40.20	40.68	41.09	0.10	0.19	0.23	0.15	0.24	0.27
1860	50.19	50.56	50.91	0.09	0.18	0.21	0.15	0.23	0.26
1940	60.59	61.35	62.20	0.10	0.18	0.21	0.15	0.22	0.26
2000	77.09	78.98	83.83	0.11	0.19	0.22	0.15	0.22	0.25
2070	64.69	64.20	64.00	0.11	0.19	0.22	0.15	0.22	0.25
2200	60.18	59.79	58.94	0.11	0.19	0.21	0.15	0.22	0.25
2440	50.63	50.38	49.37	0.10	0.19	0.21	0.12	0.21	0.23
2500	48.67	48.55	48.05	0.09	0.19	0.21	0.11	0.20	0.22
2600	50.42	50.32	49.64	0.09	0.19	0.21	0.12	0.20	0.24
2700	47.51	47.24	47.05	0.11	0.20	0.26	0.11	0.21	0.26
2900	46.95	46.77	46.15	0.06	0.18	0.21	0.11	0.21	0.27
3060	45.00	44.94	44.53	0.09	0.20	0.27	0.12	0.23	0.32
3200	41.19	41.48	41.36	0.07	0.21	0.26	0.13	0.26	0.36
3500	40.54	41.07	40.43	0.12	0.27	0.34	0.21	0.35	0.46
3600	39.84	40.03	40.20	0.15	0.30	0.41	0.20	0.37	0.45







Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1525	6.85	6.79	6.80
1526	6.81	6.75	6.77
1527	6.77	6.72	6.73
1528	6.73	6.68	6.70
1529	6.70	6.65	6.66
1530	6.66	6.62	6.64
1531	6.63	6.59	6.62
1532	6.59	6.56	6.59
1533	6.57	6.54	6.57
1534	6.54	6.52	6.55
1535	6.51	6.49	6.53
1536	6.49	6.47	6.51
1537	6.46	6.45	6.49
1538	6.43	6.43	6.48
1539	6.41	6.42	6.46
1540	6.39	6.40	6.45
1541	6.38	6.39	6.44
1542	6.36	6.38	6.44
1543	6.34	6.37	6.42
1544	6.33	6.36	6.42
1545	6.33	6.35	6.41
1546	6.32	6.35	6.41
1547	6.31	6.34	6.41
1548	6.30	6.34	6.41
1549	6.30	6.34	6.41
1550	6.30	6.34	6.41
1551	6.30	6.34	6.41
1552	6.31	6.35	6.42
1553	6.31	6.36	6.42
1554	6.31	6.36	6.43
1555	6.32	6.37	6.43
1556	6.33	6.38	6.45
1557	6.34	6.38	6.45
1558	6.35	6.40	6.46
1559	6.35	6.41	6.47
1560	6.37	6.42	6.48
1561	6.38	6.43	6.49
1562	6.39	6.44	6.51
1563	6.40	6.45	6.52
1564	6.42	6.47	6.53
1565	6.43	6.48	6.54
1566	6.45	6.50	6.57
1568	6.49	6.54	6.60
1569	6.50	6.56	6.62
1570	6.52	6.58	6.64
1571	6.54	6.60	6.67
1572	6.57	6.62	6.70
1573	6.58	6.64	6.72
1574	6.61	6.68	6.76
1575	6.64	6.71	6.79
1576	6.66	6.74	6.83
1577	6.70	6.77	6.87
1578	6.73	6.81	6.91
1579	6.75	6.85	6.96
1580	6.79	6.90	7.01
1581	6.83	6.94	7.07
1582	6.87	7.00	7.13
1583	6.92	7.05	7.20
1584	6.97	7.12	7.26
1585	7.02	7.18	7.34

Band Pass Filter

CBP-1555C+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS




REV. OR
CBP-1555C+
140203
Page 1 of 2

Band Pass Filter


CBP-1555C+

Typical Performance Curves




Outline Dimensions

MP1766



PCB Land Pattern



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111



Applicable Case styles:

Applicable Case styles: RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M137721	NEW RELEASE	JUN 12	DDR	KG

SUGGESTED MOUNTING CONFIGURATION FOR MP1766 CASE STYLE "13FL01" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS $.022 \pm .0015$ ". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS $\pm$
3 PL DECIMALS $\pm$.005"
ANGLES $\pm$
FRACTIONS $\pm$

DRAWN

DDR

22 JUN 12

CHECKED

MD

22 JUN 12

APPROVED

GM

22 JUN 12

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 13FL01, MP1766, BPF,
TB-684+, 50 Ohm

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-373



REV:
OR

FILE: 98PL373

SCALE: 4:1

SHEET: 1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant= $2.50 \pm .04$, Thickness=.022 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A