

Surface Mount Bandpass Filter

50Ω 329 to 335 MHz

BPHI-332+



CASE STYLE: HQ1157

Features

- Very sharp rejection
- Low passband IL
- Shielded case

Applications

- Aviation/Aeronautical
- Radio communications
- Defense systems

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	332	—	MHz
	Insertion Loss	F1-F2	—	4.5	5.0	dB
	VSWR	F1-F2	—	1.5	2.0	:1
Stop Band, Lower	Insertion Loss	DC-F3	40	50	—	dB
	VSWR	F3-F4	20	30	—	dB
		DC-F3	—	20	—	:1
Stop Band, Upper	Insertion Loss	F5-F6	20	25	—	dB
	VSWR	F6-F7	40	50	—	dB
		F5-F7	—	20	—	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1.5 W

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1.0	94.42	347.44	329.0	54.85
100.0	110.76	1737.18	329.5	54.39
300.0	47.38	157.93	330.0	54.11
313.0	30.84	44.55	330.5	53.97
318.0	20.79	17.22	331.0	53.98
322.0	10.17	4.10	331.5	54.15
325.0	4.82	1.17	332.0	54.53
329.0	3.64	1.43	332.5	55.10
332.0	3.69	1.45	333.0	55.91
335.0	4.32	1.34	333.5	56.96
338.0	6.77	2.40	334.0	58.19
340.0	11.19	3.27	334.5	59.57
341.5	19.33	6.58	335.0	61.07
342.0	22.68	8.31		
343.0	29.53	12.18		
343.5	32.62	14.26		
370.0	51.01	173.72		
500.0	74.83	434.30		
1500.0	61.17	217.15		
2600.0	52.47	23.81		

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 35166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



REV. OR
M162235
BPHI-332+
EDU2540/1
URJ
171025
Page 1 of 2

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

[illegible]

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-



A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Notes:

- A.** Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B.** Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C.** The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MC/Store/terms.jsp



Typical Performance Data

FREQUENCY (MHz)	Insertion Loss (dB)	Input Return Loss (dB)	Output Return Loss (dB)
1.0	94.42	0.04	0.05
10.0	101.55	0.03	0.03
20.0	101.48	0.02	0.03
50.0	116.02	0.01	0.01
100.0	110.76	0.01	0.01
150.0	102.17	0.01	0.01
200.0	93.73	0.01	0.01
250.0	75.88	0.02	0.01
270.0	68.02	0.04	0.03
280.0	62.52	0.05	0.04
290.0	55.78	0.07	0.06
296.0	51.05	0.10	0.09
300.0	47.38	0.12	0.11
304.0	43.18	0.16	0.15
310.0	35.55	0.26	0.27
312.0	32.49	0.32	0.34
313.0	30.84	0.37	0.39
315.0	27.21	0.48	0.54
320.0	15.69	1.45	1.84
322.0	10.17	3.12	4.32
326.0	4.30	10.96	15.59
328.0	3.79	14.53	13.68
329.0	3.64	19.37	15.08
330.0	3.58	26.37	16.06
331.0	3.61	20.67	15.49
332.0	3.69	17.04	14.67
333.0	3.82	16.24	14.86
334.0	4.00	17.24	16.35
335.0	4.32	17.12	16.79
336.0	4.86	13.33	13.19
338.0	6.77	8.34	7.72
340.0	11.19	7.18	5.48
341.0	16.19	4.41	3.43
341.5	19.33	3.36	2.66
342.0	22.68	2.61	2.10
343.0	29.53	1.72	1.43
343.5	32.62	1.45	1.22
344.0	34.96	1.25	1.06
345.0	36.67	0.96	0.83
350.0	38.15	0.42	0.37
355.0	41.77	0.25	0.23
360.0	45.25	0.18	0.16
370.0	51.01	0.11	0.10
376.0	53.83	0.10	0.08
380.0	55.48	0.09	0.07
390.0	59.14	0.08	0.06
400.0	62.04	0.07	0.05
500.0	74.83	0.08	0.04
750.0	81.62	0.12	0.06
800.0	83.03	0.12	0.06
1000.0	64.02	0.13	0.06
1200.0	68.11	0.13	0.05
1400.0	66.68	0.13	0.06
1500.0	61.17	0.14	0.08
1600.0	60.78	0.15	0.10
1750.0	58.39	0.21	0.16
2000.0	56.27	0.43	0.34
2250.0	54.65	0.69	0.57
2500.0	53.08	0.84	0.72
2600.0	52.47	0.83	0.73


Typical Performance Data

FREQ. (MHz)	GROUP DELAY (ns)
329.0	54.85
329.5	54.39
330.0	54.11
330.5	53.97
331.0	53.98
331.5	54.15
332.0	54.53
332.5	55.10
333.0	55.91
333.5	56.96
334.0	58.19
334.5	59.57
335.0	61.07

Typical Performance Curves




Typical Performance Curves



Outline Dimensions

HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F83

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR HQ1157 CASE STYLE, rf PIN CONNECTION




NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS $.025" \pm .002"$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, rf, HQ1157, TB-363+, 50 OHM

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-227	C
FILE:	98PL227	SCALE:	2:1
SHEET:	1	OF	1

Evaluation Board and Circuit



TB-363+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215