

Ceramic

Directional Coupler

DCW-9-432+

50Ω 2300 to 4300 MHz 9dB Coupling

The Big Deal

- High Power handling
- Industry leading combination of size/ bandwidth



CASE STYLE: JC0603C

Product Overview

Mini-Circuits new directional coupler DCW-9-432+ offers an industry leading combination of operating bandwidth and size. The low insertion loss makes this component a versatile building block for use in a variety of systems and sub-system designs.

Key Features

Feature	Advantages
Small Size	Offered in the JC0603C package size, the DCW-9-432+ offers an industry leading combination of size, bandwidth and frequency. The small footprint allows for reduced parasitics in systems with improved performance and simplified layout.
High Power handling	Capable of operating up to 2W, the LTCC construction of the DCW-9-432+ makes this directional coupler a robust, rugged product that can be used effectively in either the transmit or receive paths.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Directional Coupler

50Ω 2300 to 4300 MHz 9dB Coupling

DCW-9-432+



Generic photo used for illustration purposes only

CASE STYLE: JC0603C

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 4000

Maximum Ratings

Operating Temperature -55°C to 125°C


Storage Temperature* -55°C to 125°C

*Refer to product storage temperature after installation.
Suggestion for T&R unused product storage condition: +5--+35°C, Humidity 45-75%RH, 12 Month max.
Permanent damage may occur if any of these limits are exceeded.

Pad Connections

Input	1
GND	2
Coupled	3
Termination	4
GND	5
Output	6


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	wt
.063	.031	.024	.012	.008	.006	.020	grams
1.60	0.79	0.61	0.30	0.20	0.15	0.51	0.005

Evaluation Board MCL P/N: TB-DCW-9-432+ Suggested PCB Layout (PL-572)



- NOTES:**
- TRACE WIDTH & GAP ARE SHOWN FOR FR4, GRADE IT-180TC (ITEQ CORP.) WITH DIELECTRIC THICKNESS .016±.0015. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - REFER TO MODEL DATASHEET FOR PIN OUTS.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- miniature size 0603
- low cost
- aqueous washable

Applications

- ISM Band
- Cellular
- Bluetooth
- Zigbee




Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		2300		4300	MHz
Mainline Loss	2300 - 4300	—	1.3	1.7	dB
Coupling	2300 - 4300	—	9±2	—	dB
Directivity	2300 - 4300	14	17	—	dB
Return Loss (Input)	2300 - 4300	11	—	—	dB
Return Loss (Output)	2300 - 4300	11	—	—	dB
Input Power¹	2300 - 4300	—	—	2	W


1. Derate linearly to 0.5W at 125°C.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
2300	0.66	10.87	19.07	16.71	16.60	20.55
2500	0.73	10.30	20.50	17.04	16.86	21.05
2800	0.85	9.54	23.10	17.89	17.86	21.97
3200	1.00	8.71	25.24	20.17	20.36	22.84
3400	1.07	8.38	24.57	21.56	22.26	22.22
3600	1.15	8.09	23.05	22.83	24.74	21.37
3800	1.23	7.86	21.52	23.30	27.32	20.35
4000	1.30	7.68	20.18	22.89	28.06	19.55
4200	1.37	7.54	19.18	21.85	26.04	18.87
4300	1.41	7.48	18.77	21.24	24.83	18.57



Electrical Schematic



* ELECTRICAL SCHEMATIC FOR DIRECTIONAL COUPLERS REQUIRING EXTERNAL TERMINATION THAT IS DESIGNED WITHOUT INTERNAL TRANSFORMERS.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-005075
DCW-9-432+
SL/CP/AM
201202
Page 2 of 2





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
2000	0.54	11.87	17.23	16.67	16.62	20.18
2050	0.56	11.69	17.51	16.65	16.54	20.23
2100	0.58	11.51	17.86	16.65	16.53	20.35
2150	0.60	11.34	18.12	16.63	16.53	20.39
2200	0.62	11.18	18.40	16.65	16.54	20.37
2250	0.64	11.03	18.73	16.68	16.58	20.40
2300	0.66	10.87	19.07	16.71	16.60	20.55
2350	0.68	10.72	19.39	16.78	16.62	20.71
2400	0.69	10.58	19.81	16.83	16.72	20.77
2450	0.71	10.43	20.17	16.93	16.79	20.87
2500	0.73	10.30	20.50	17.04	16.86	21.05
2550	0.75	10.16	20.92	17.14	16.99	21.20
2600	0.77	10.03	21.38	17.28	17.13	21.34
2650	0.79	9.90	21.76	17.40	17.28	21.44
2700	0.81	9.78	22.18	17.54	17.43	21.60
2750	0.83	9.66	22.63	17.71	17.62	21.79
2800	0.85	9.54	23.10	17.89	17.86	21.97
2850	0.87	9.42	23.52	18.13	18.07	22.15
2900	0.88	9.31	23.89	18.35	18.32	22.29
2950	0.90	9.20	24.28	18.61	18.59	22.50
3000	0.92	9.10	24.60	18.86	18.91	22.62
3050	0.94	9.00	24.85	19.18	19.26	22.69
3100	0.96	8.90	25.07	19.49	19.61	22.72
3150	0.98	8.81	25.21	19.80	19.95	22.76
3200	1.00	8.71	25.24	20.17	20.36	22.84
3250	1.01	8.62	25.22	20.53	20.78	22.70
3300	1.03	8.54	25.10	20.86	21.25	22.44
3350	1.05	8.46	24.92	21.17	21.73	22.27
3400	1.07	8.38	24.57	21.56	22.26	22.22
3450	1.09	8.30	24.27	21.92	22.81	22.01
3500	1.11	8.23	23.84	22.24	23.44	21.70
3550	1.13	8.16	23.48	22.52	24.06	21.50
3600	1.15	8.09	23.05	22.83	24.74	21.37
3650	1.17	8.03	22.71	23.02	25.37	21.09
3700	1.19	7.97	22.29	23.17	26.06	20.74
3750	1.21	7.91	21.91	23.26	26.71	20.51
3800	1.23	7.86	21.52	23.30	27.32	20.35
3850	1.24	7.81	21.15	23.30	27.76	20.15
3900	1.26	7.76	20.83	23.19	28.05	19.89
3950	1.28	7.72	20.52	23.06	28.13	19.70
4000	1.30	7.68	20.18	22.89	28.06	19.55
4050	1.32	7.64	19.93	22.66	27.69	19.37
4100	1.34	7.60	19.66	22.40	27.22	19.17
4150	1.36	7.57	19.40	22.13	26.65	19.01
4200	1.37	7.54	19.18	21.85	26.04	18.87
4250	1.39	7.51	18.94	21.54	25.43	18.73
4300	1.41	7.48	18.77	21.24	24.83	18.57
4350	1.43	7.46	18.58	20.95	24.26	18.48
4400	1.44	7.44	18.40	20.67	23.78	18.41
4450	1.46	7.42	18.23	20.37	23.27	18.32
4500	1.47	7.41	18.08	20.11	22.81	18.27

Directional Coupler

Typical Performance Curves

DCW-9-432+



Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M168200	NEW RELEASE	05/31/18	NP	SL

SUGGESTED MOUNTING CONFIGURATION
FOR JC0603C CASE STYLE, "06DC12" PIN CODE




NOTES:


1. TRACE WIDTH IS SHOWN FOR FR4, GRADE IT-180TC (ITEQ CORP.) WITH DIELECTRIC THICKNESS $.016 \pm .0015$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DRAWN	NP	05/30/18
CHECKED	GF	05/30/18
APPROVED	SL	05/31/18



 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

PL, 06DC12, JC0603C, TB-1031+

 Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.
 ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-572	OR
FILE:	98PL572	SCALE: 10:1	SHEET: 1 OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: FR4 or equivalent,
Dielectric Constant=4.5, Thickness=.016 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A