

Engineering Development Model

Directional Coupler

DCX-ED13056/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-998


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.3		1000 MHz
Coupling	Nominal		11 ± 1	dB
	Flatness		± 0.6	dB
Mainline Loss *	0.3-3 MHz		0.95	dB
	3-500 MHz		0.85	dB
	500-1000 MHz		1.00	dB
Directivity	0.3-3 MHz		32	dB
	3-500 MHz		41	dB
	500-1000 MHz		22	dB
VSWR	0.3-1000 MHz		1.22	(:1)
Power Input	.3-1000 MHz			1 W

Note: * Mainline loss includes theoretical coupled power loss of 0.359 dB at 11 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
INPUT	1
OUTPUT	6
COUPLED	3
50Ω TERM. EXTERNAL	4
GROUND	2,5

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.



P.O. Box 350188, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4651 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X1
DCX-ED13056/1
3/11/2009
Page 1 of 1

Directional Coupler

DCX-ED13056/1





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
0.3	1.10	10.71	28.20	15.62	17.27	13.93
0.5	1.03	10.68	30.34	17.90	20.66	15.69
0.7	0.97	10.65	31.44	19.12	22.72	16.63
0.9	0.93	10.62	32.50	19.94	24.19	17.29
1.0	0.91	10.61	33.17	20.27	24.80	17.56
4.0	0.77	10.49	42.04	23.19	31.33	20.12
7.0	0.74	10.48	46.17	23.60	32.37	20.53
10.0	0.74	10.47	48.56	23.77	32.60	20.69
25.0	0.74	10.49	52.49	23.96	32.63	20.85
40.0	0.76	10.51	51.75	23.98	32.66	20.80
60.0	0.77	10.53	51.82	24.11	32.23	20.64
80.0	0.78	10.55	50.49	24.06	31.88	20.42
100.0	0.79	10.57	48.91	24.04	31.45	20.15
120.0	0.80	10.59	47.15	24.01	30.90	19.81
140.0	0.80	10.61	45.75	23.89	30.42	19.44
160.0	0.81	10.63	44.48	23.80	30.05	19.05
180.0	0.82	10.65	42.73	23.68	29.62	18.65
200.0	0.82	10.67	41.23	23.50	29.17	18.26
220.0	0.83	10.70	39.79	23.35	28.75	17.86
240.0	0.83	10.72	38.89	23.16	28.43	17.46
260.0	0.84	10.75	37.69	22.99	28.08	17.07
280.0	0.84	10.77	36.55	22.79	27.72	16.69
300.0	0.85	10.79	35.45	22.62	27.38	16.33
330.0	0.85	10.84	34.26	22.40	26.97	15.82
360.0	0.86	10.88	32.84	22.14	26.52	15.32
390.0	0.87	10.92	31.38	21.88	26.04	14.84
420.0	0.88	10.97	30.24	21.62	25.67	14.38
450.0	0.89	11.01	29.15	21.39	25.33	13.97
500.0	0.90	11.09	27.33	21.03	24.73	13.32
550.0	0.91	11.18	25.76	20.74	24.24	12.71
600.0	0.93	11.26	24.33	20.51	23.73	12.17
650.0	0.95	11.36	23.03	20.24	23.24	11.67
700.0	0.96	11.45	21.80	20.02	22.80	11.23
750.0	0.98	11.55	20.63	19.83	22.31	10.81
800.0	1.01	11.65	19.50	19.62	21.82	10.43
1000.0	1.10	12.06	15.69	19.05	20.14	9.24
1200.0	1.25	12.48	12.56	18.39	18.70	8.44
1400.0	1.49	12.90	9.92	17.24	17.72	7.95
1600.0	1.89	13.43	7.65	15.20	17.34	7.73
1800.0	2.56	14.40	5.73	12.53	18.13	7.61
2000.0	3.38	16.07	3.97	9.98	19.02	7.65

Directional Coupler

Typical Performance Curves

DCX-ED13056/1





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215