

Engineering Development Model

Dual Low Pass Filter

Surface Mount

DLPF-EDU1162

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.




Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE: HU1186

Electrical Specifications 50Ω @ +25°C				
Parameter	Min	Typ	Max	Units
Passband (Loss < 1 dB)	DC	-	20	MHz
Stopband (Loss > 20 dB)	36	-	80	MHz
Stopband (Loss > 40 dB)	80	-	1700	MHz
Passband VSWR		1.1	1.35	:1
Group Delay variation b/w 2 filters @ 12 MHz		1		nS

Functional Schematic

MAXIMUM RATINGS	
Operating Temperature	-40°C to +60°C
Storage Temperature	-55°C to +85°C
RF Power Input	0.5 W



PIN CONNECTIONS	
RF IN 1	2 (filter1)
RF OUT 1	13 (filter1)
RF IN 2	6 (filter2)
RF OUT 2	9 (filter2)
GROUND	1,3,4,5,7,8,10,11,12,14



Dual Low Pass Filter

DLPF-EDU1162

Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	0.18	32.91	0.5	17.60
1.0	0.19	30.79	1.0	19.98
2.0	0.20	27.39	2.0	21.17
2.5	0.20	26.17	2.5	21.29
3.0	0.21	24.90	3.0	21.30
5.0	0.23	21.98	5.0	21.59
10.0	0.26	22.36	6.0	21.79
11.0	0.27	23.89	7.0	22.09
12.0	0.27	26.16	7.4	22.18
13.0	0.28	29.67	8.0	22.40
14.0	0.29	36.00	9.0	22.74
15.0	0.31	43.32	9.8	23.16
19.0	0.37	33.89	10.0	23.24
20.0	0.42	24.93	11.0	23.75
22.0	0.76	12.83	12.0	24.40
23.0	1.26	8.84	12.3	24.53
24.0	2.17	5.86	13.0	25.07
25.0	3.55	3.79	14.0	25.83
26.0	5.36	2.46	15.0	26.75
27.0	7.48	1.65	16.0	27.83
28.0	9.76	1.17	18.0	30.95
29.0	12.11	0.89	19.0	33.36
30.0	14.48	0.72	20.0	36.54
35.0	26.25	0.41		
36.0	28.69	0.39		
40.0	40.14	0.31		
42.0	49.46	0.29		
43.0	59.27	0.27		
50.0	45.04	0.21		
60.0	44.50	0.16		
70.0	46.59	0.13		
80.0	49.11	0.10		
90.0	51.59	0.09		
100.0	53.96	0.08		
150.0	63.64	0.05		
200.0	70.57	0.05		
300.0	78.75	0.05		
400.0	86.61	0.07		
500.0	85.10	0.08		
700.0	80.15	0.12		
1000.0	81.45	0.18		
1200.0	73.80	0.25		
1300.0	72.41	0.67		
1500.0	62.43	0.30		
1700.0	54.61	0.40		
2000.0	50.83	1.29		
2200.0	50.82	0.47		
2300.0	48.46	0.44		
2500.0	43.87	0.44		
2700.0	40.24	0.48		
3000.0	35.64	0.58		
3200.0	30.59	0.73		
3300.0	26.87	0.92		
3500.0	18.57	2.58		

Typical Performance Curves




Outline Dimensions

HU1186



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	- -	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	- -	.060 (1.52)	.060 (1.52)	- -	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified