Surface Mount

Diplexer

DPLB-2025A0+

75Ω DC to 1220 MHz (DC-204, 258-1220 MHz)

CASE STYLE: NU1620

The Big Deal

- Low insertion loss, 1dB Typ.
- High rejection
- High crossover isolation
- Excellent return loss, 24dB Typ.
- 75Ω Impedance
- Used in DOCSIS 3.1 standard

Product Overview

DPLB-2025A0+ is a Low cost high performance diplexer with the lowpass port at DC-204 MHz and high-pass port at 258-1220 MHz. Excellent return loss combined with high out of channel rejection makes it a ideal component in cable TV and multiband radio systems.

Key Features

Feature	Advantages
Low passband insertion loss	Passband insertion loss 1dB ensures low signal loss through both the channels.
Excellent Stopband rejection	Co-channel rejection of 50dB ensures unwanted spurious are eliminated.
Excellent return loss at DC-204 and 258-1220 MHz	This makes signal transmission with very less reflection and well-matched with the adjacent component used in the system.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Surface Mount

Diplexer

DPLB-2025A0+

75Ω DC to 1220 MHz (DC-204, 258-1220 MHz)

CASE STYLE: NU1620

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-40° to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	27dBm Max.

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

Pin Connections

HIGH PASS PORT	7
LOW PASS PORT	9
COMMON PORT	18
GROUND	1-6,8,10-17,19,20

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C		D	E	F	G	H	J	K
-	-	Max	Min	-	-	-	-	-	-	-
1.181	1.181	.280	.205	.197	.394	.591	.787	.984	.066	.089
30.00	30.00	7.11	5.21	5.00	10.00	15.00	20.00	25.00	1.68	2.26

L	M	N	P	Q	R	S	T	Wt. grams
-	-	-	-	-	-	-	-	
.111	.079	.071	1.221	1.221	.079	.091	.280	3.6
2.82	2.01	1.80	31.01	31.01	2.01	2.31	7.11	

Demo Board MCL P/N: TB-786+
Suggested PCB Layout (PL-435)



Features

- Low insertion loss
- Excellent return loss
- High rejection
- High crossover isolation
- 75Ω Impedance

Applications

- Cable TV systems (DOCSIS 3.1 standard)
- Multiband radio systems

CAUTION NOTE: *Open units are not recommended for use with Aqueous wash systems. Please evaluate your wash process before use.*

Electrical Specifications at 25°C

Parameter		Port	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	Low Pass	DC-204	-	1	1.5	dB
		High Pass	258-1220	-	1	1.5	
	Return Loss	Low Pass	DC-204	20	24	-	dB
		High Pass	258-1000	18	24	-	
			1000-1220	17	20	-	
		Common	DC-204	20	24		
			258-1000	18	24	-	
			1000-1220	17	20	-	
Stop Band Isolation		Low Pass	258-1220	44	50	-	dB
		High Pass	DC-204	48	55	-	
Cross Over Isolation		LP-HP	204-258	35	40	-	

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)		RETURN LOSS (dB)		
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
1.0	0.00	88.86	50.81	51.27	0.00
5.0	0.06	82.40	41.58	41.60	0.05
10.0	0.09	77.89	36.58	36.90	0.06
45.0	0.17	67.33	25.74	26.76	0.09
60.0	0.20	68.18	24.29	25.21	0.10
85.0	0.24	71.36	24.18	24.34	0.13
100.0	0.26	73.36	25.78	24.97	0.17
200.0	0.84	87.09	30.46	28.27	0.70
204.0	0.95	60.60	30.15	38.25	0.73
214.0	2.28	45.89	9.44	9.22	0.84
216.0	3.21	43.41	6.91	6.54	0.87
221.0	7.53	30.88	3.13	2.59	0.95
226.0	14.16	20.82	1.93	1.26	1.12
230.0	20.47	14.67	1.84	0.92	1.41
235.0	29.89	8.52	2.62	0.74	2.37
241.0	43.78	3.75	5.72	0.65	5.54
245.0	47.24	2.19	9.40	0.61	9.23
258.0	54.91	0.94	28.30	0.53	27.96
300.0	63.81	0.57	25.98	0.40	25.01
750.0	54.50	0.40	31.86	0.07	32.33
1000.0	52.90	0.51	25.52	0.17	24.17
1220.0	52.16	0.53	20.67	0.41	23.89

Functional Schematic



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

DPLB-2025A0+ LOW PASS PORT
INSERTION LOSS (P_{in}=0dBm)



DPLB-2025A0+ HIGH PASS PORT
INSERTION LOSS (P_{in}=0dBm)



DPLB-2025A0+ LOW PASS PORT
RETURN LOSS (P_{in}=0dBm)



DPLB-2025A0+ HIGH PASS PORT
RETURN LOSS (P_{in}=0dBm)



DPLB-2025A0+ COMMON PORT
RETURN LOSS (P_{in}=0dBm)



DPLB-2025A0+ CROSS OVER
ISOLATION (P_{in}=0dBm)



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Surface Mount Diplexer DPLB-2025A0+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		Cross over isolation (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Lowpass port	Highpass port		Common port	Lowpass port	Highpass port
1.0	0.00	88.86	87.12	50.81	51.27	0.00
3.0	0.05	86.60	89.33	44.71	44.92	0.03
5.0	0.06	82.40	91.40	41.58	41.60	0.05
10.0	0.09	77.89	76.61	36.58	36.90	0.06
13.0	0.10	74.16	75.74	34.64	35.09	0.06
20.0	0.12	72.52	73.76	31.39	32.13	0.07
28.0	0.14	70.12	70.16	28.93	29.79	0.08
45.0	0.17	67.33	68.07	25.74	26.76	0.09
56.0	0.19	67.69	68.77	24.60	25.54	0.10
60.0	0.20	68.18	68.34	24.29	25.21	0.10
74.0	0.22	68.90	68.96	23.87	24.46	0.12
83.0	0.23	71.71	71.05	24.07	24.32	0.13
85.0	0.24	71.36	71.61	24.18	24.34	0.13
100.0	0.26	73.36	73.47	25.78	24.97	0.17
103.0	0.27	73.69	72.69	26.29	25.22	0.18
118.0	0.29	73.62	73.37	30.55	27.43	0.23
135.0	0.34	71.85	69.96	42.26	32.64	0.29
148.0	0.38	66.57	66.73	39.53	38.12	0.35
158.0	0.42	63.99	64.35	37.11	39.50	0.40
167.0	0.47	62.04	62.53	39.47	43.15	0.46
171.0	0.49	61.72	61.98	42.74	49.33	0.48
174.0	0.51	62.17	61.84	45.17	48.85	0.50
178.0	0.54	61.83	61.95	41.98	39.39	0.53
182.0	0.58	62.39	61.75	36.60	33.93	0.55
191.0	0.68	64.42	63.91	29.90	27.43	0.62
196.0	0.76	69.90	68.23	28.97	26.45	0.66
200.0	0.84	87.09	72.56	30.46	28.27	0.70
203.0	0.92	63.57	62.87	31.48	34.59	0.72
204.0	0.95	60.60	60.46	30.15	38.25	0.73
214.0	2.28	45.89	44.09	9.44	9.22	0.84
216.0	3.21	43.41	42.22	6.91	6.54	0.87
221.0	7.53	30.88	39.94	3.13	2.59	0.95
226.0	14.16	20.82	39.81	1.93	1.26	1.12
230.0	20.47	14.67	40.19	1.84	0.92	1.41
235.0	29.89	8.52	40.93	2.62	0.74	2.37
241.0	43.78	3.75	42.83	5.72	0.65	5.54
245.0	47.24	2.19	45.19	9.40	0.61	9.23
258.0	54.91	0.94	53.94	28.30	0.53	27.96
260.0	56.00	0.90	54.95	31.81	0.52	30.76
266.0	58.42	0.80	57.68	30.98	0.49	29.22
284.0	63.85	0.64	62.23	25.91	0.44	24.78
300.0	63.81	0.57	62.70	25.98	0.40	25.01
328.0	59.36	0.49	59.43	29.16	0.35	28.60
341.0	59.40	0.47	58.97	31.54	0.34	31.46
346.0	58.64	0.46	58.82	32.37	0.33	32.83
365.0	58.99	0.43	58.68	33.36	0.31	37.21
385.0	59.21	0.42	59.06	31.07	0.29	34.64
400.0	59.62	0.41	58.50	29.38	0.27	31.72
445.0	59.19	0.40	58.93	26.82	0.22	27.52
575.0	56.25	0.39	56.92	29.56	0.11	29.43
595.0	56.05	0.39	56.41	30.44	0.10	30.82
630.0	55.83	0.39	55.72	33.38	0.09	34.50
665.0	55.31	0.39	55.36	35.00	0.08	39.32
750.0	54.50	0.40	54.23	31.86	0.07	32.33
875.0	54.02	0.44	53.29	27.29	0.09	25.39
930.0	53.58	0.46	52.66	26.24	0.13	24.36
970.0	53.20	0.48	52.47	25.99	0.16	24.19
995.0	52.36	0.52	53.59	25.32	0.17	24.47
1000.0	52.90	0.51	53.65	25.52	0.17	24.17
1220.0	52.16	0.53	51.09	20.67	0.41	23.89

Typical Performance Curves

LOWPASS INSERTION LOSS
INPUT POWER = 0 dBm



LOWPASS RETURN LOSS
INPUT POWER = 0 dBm



HIGHPASS INSERTION LOSS
INPUT POWER = 0 dBm



HIGHPASS RETURN LOSS
INPUT POWER = 0 dBm



CROSS OVER ISOLATION
INPUT POWER = 0 dBm



COMMON PORT RETURN LOSS
INPUT POWER = 0 dBm



Case Style NU

Outline Dimensions

NU1620





PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE#	A	B	C		D	E	F	G	H	J	K	L	M
			Max	Min									
NU1620	1.181 (30.00)	1.181 (30.00)	.280 (7.11)	.205 (5.21)	.197 (5.00)	.394 (10.00)	.591 (15.00)	.787 (20.00)	.984 (25.00)	.066 (1.68)	.089 (2.26)	.111 (2.82)	.079 (2.01)

CASE#	N	P	Q	R	S	T	WT.GRAMS
NU1620	.071 (1.80)	1.221 (31.01)	1.221 (31.01)	.079 (2.01)	.091 (2.31)	.280 (7.11)	3.6

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

1. Base: Printed wiring laminate.
2. Termination finish:
   For RoHS Case Styles: 3-5 µ inch Gold over 120-240 µ inch Nickel plate.
   For RoHS-5 Case Styles: Tin-Lead plate.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F80

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	40	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M147697	NEW RELEASE	SEP 14	DDR	MD

SUGGESTED MOUNTING CONFIGURATION FOR NU1620, NV1998, NZ2001, PA2002 CASE STYLE "20DP01" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR OAK-602 WITH DIELECTRIC THICKNESS .031"±.002". COPPER: 1/2 OZ. EACH SIDE.
   FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DDR	09 SEP 14
TOLERANCES ON:	CHECKED	MD	09 SEP 14
2 PL DECIMALS ±	APPROVED	KR	09 SEP 14
3 PL DECIMALS ± .005"			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits ®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 20DP01, NU1620, NV1998, NZ2001, PA2002, TB-786+, 75 OHM

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-435	OR
FILE: 98PL435		SCALE: 3:1	SHEET: 1 OF 1

Evaluation Board and Circuit





Schematic Diagram

Notes:
1. 75 Ohm N Female connectors.
2. PCB Material: OAK-602 OR Equivalent
   Dielectric Constant=2.50±.04, Thickness=.031 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV03

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.