

COAXIAL MILLIMETER WAVE

Precision Fixed Attenuator **BW-V1-1W54+**

Mini-Circuits 50

50 Ω 1 W 1 dB DC to 50 GHz 2.4 mm Female to 2.4 mm Male

THE BIG DEAL

- DC to 50 GHz
- Precise Attenuation
- Excellent VSWR, 1.15 Typ.
- Passivated Stainless Steel Connectors



Generic photo used for illustration purposes only

Model No.	BW-V1-1W54+			
Case Style	DJ2264			
Connectors	2.4 mm Female -2.4 mm Male			

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Matching
- Instrumentation
- Test Setups

PRODUCT OVERVIEW

The BW-VX-1W54+ Series of precision fixed attenuators achieves extremely wide frequency range with excellent VSWR. Available in a variety of attenuation values for different requirements, these units support a broad range of system and testing applications. Precise performance, excellent VSWR and wide band features make these models ideal solutions for systems requiring precise attenuation across very wide frequency range.

KEY FEATURES

Feature	Advantages
Extremely Wideband, DC to 50 GHz	Ideal for an exceptionally wide variety of applications.
Excellent VSWR, 1.15 Typ.	Efficient power utilization with low power reflected back to source.
Passivated Stainless Steel Connectors	Rugged construction withstands harsh environmental conditions for high reliability and long life of use.

PAGE 1 OF 2

COAXIAL MILLIMETER WAVE

Precision Fixed Attenuator **BW-V1-1W54+**

Mini-Circuits

 50Ω $\,$ 1 W $\,$ 1 dB $\,$ DC to 50 GHz $\,$ 2.4 mm Female to 2.4 mm Male $\,$

ABSOLUTE MAXIMUM RATINGS

Operating Temperature	-55°C to +100°C	
Storage Temperature	-55°C to +100°C	

Permanent damage may occur if any of these limits are exceeded.

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch)

А	В	С	D	Е	wt
0.360	0.312	0.281	0.871		grams
9.14	7.93	7.14	22.12		5.44

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		DC		50	GHz
Attenuation	DC - 26.5	0.5	1.0	1.5	
	26.5 - 40	0.05	1.2	1.95	dB
	40 - 50		1.4	2.5	
	DC - 26.5		1.06	1.35	
VSWR	26.5 - 40		1.2	1.6	:1

ELECTRICAL SPECIFICATIONS AT +25°C

 Input Power¹
 DC - 50

 1. Max. power at 25°C ambient, derate linearly to 0.1 W at 100°C

40 - 50

TYPICAL PERFORMANCE DATA

1.75

1

W

1.13

Frequency (GHz)	Attenuation (dB)	VSWR (:1)
0.01	0.78	1.03
1.00	0.83	1.05
5.00	0.88	1.06
10.00	0.92	1.04
15.00	0.96	1.06
20.00	1.02	1.08
26.50	1.09	1.07
30.00	1.18	1.21
35.00	1.27	1.26
40.00	1.30	1.14
45.00	1.37	1.12
50.00	1.48	1.08



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits

Fixed Attenuator

Typical Performance Data

FREQUENCY	ATTENUATION	VSWR
(GHz)	(dB)	(:1)
0.01	0.78	1.03
0.2	0.79	1.04
0.3	0.80	1.04
0.4	0.80	1.04
0.5	0.81	1.04
0.6	0.81	1.04
0.7	0.82	1.04
0.8	0.82	1.04
0.9	0.83	1.05
1.0	0.83	1.05
3.0	0.87	1.06
5.0	0.88	1.06
7.0	0.90	1.04
9.0	0.91	1.03
11.0	0.93	1.06
13.0	0.95	1.08
15.0	0.96	1.06
17.0	0.98	1.05
19.0	1.00	1.08
21.0	1.02	1.10
23.0	1.05	1.08
25.0	1.07	1.05
26.5	1.09	1.07
28.0	1.12	1.12
30.0	1.18	1.21
32.0	1.23	1.25
34.0	1.26	1.27
36.0	1.28	1.23
38.0	1.30	1.19
40.0	1.30	1.14
43.0	1.24	1.18
44.0	1.33	1.14
46.0	1.41	1.10
48.0	1.45	1.08
50.0	1.48	1.08

CONTROL PROVIDE A STATE AND A STATE A

Fixed Attenuator

Typical Performance Curves





REV. OR BW-V1-1W54+ 1/24/2022 Page 1 of 1

Case Style

Outline Dimensions



CASE #	А	В	С	D	Е	WT. GRAM
DI2264	.36	.312	.281	.871		5 44
DJ2204	(9.14)	(7.93)	(7.14)	(22.10)		5.77

Dimensions are in inches (mm). Tolerances: 2 Pl. \pm .030; 3Pl. \pm .015

Notes:

- 1. Case material:Stainless Steel.
- 2. Finish: Passivation.





DJ2264

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



DJ2264 Rev.: BA (04/10/25) ECO-025172 File: DJ2264.docx

Mini-Circuits Environmental Specifications ENV28

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

ENV28 Rev: B 09/26/13 M143494 File: ENV28.pdf

This document and its contents are the property of Mini-Circuits.