
MMIC SURFACE MOUNT

Power Splitter/Combiner EP4RKU+

4 Way-0° 50Ω DC to 18 GHz

THE BIG DEAL

- Wide bandwidth, DC to 18 GHz
- Excellent isolation, 20 dB typ. at 9 GHz
- Excellent amplitude unbalance, 0.3 dB typ. at 9 GHz
- Good phase unbalance, 2 deg typ. at 9 GHz
- Small size, 5x5 mm
- Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: DG1677-2

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- WIMAX
- ISM
- Instrumentation
- Radar
- WLAN
- Satellite communications
- LTE

PRODUCT OVERVIEW

Mini-Circuits' EP4RKU+ is a MMIC 4-way 0° splitter/combiner designed for wideband operation from 10.7 to 31 GHz supporting many applications requiring high performance across a wide frequency range including LTE bands through phased array radars, 5G, as well as instrumentation and more. This model provides good isolation, and low phase and amplitude unbalance in a small 5 x 5mm QFN package. Manufactured using GaAs IPD technology, the EP4RKU+ not only provides a repeatable performance, but also a high level of ESD protection.

KEY FEATURES

Feature	Advantages
Wideband, DC to 18 GHz	One power splitter can be used in a HF thru, LTE bands, WiMax and WiFi, saving component count. Also ideal for wideband applications such as military and instrumentation.
Excellent Amplitude unbalance, 0.3 dB typ. at 9 GHz Excellent phase unbalance, 2° typ. at 9 GHz	Ideal for Applications such as MIMO & phased array radars
Small size, 5 x 5mm QFN package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.

Power Splitter/Combiner EP4RKU+

ELECTRICAL SPECIFICATIONS[1] AT +25°C

Parameter		Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range			DC		18	GHz
Insertion Loss above 6.0 dB		DC - 4	—	4.2	5.2	dB
		4 - 18	—	3.4	4.9	
Isolation		DC - 4	9	12.1	—	dB
		4 - 18	11	18.8	—	
Phase Unbalance		DC - 4	—	0.3	4	Degree
		4 - 18	—	1.9	19	
Amplitude Unbalance		DC - 4	—	0.1	0.6	dB
		4 - 18	—	0.2	1.2	
VSWR (Port S)		DC - 4	—	1.8	—	:1
		4 - 18	—	1.4	—	
VSWR (Port 1-4)		DC - 4	—	1.6	—	:1
		4 - 18	—	1.5	—	
Power Handling[2]	As a splitter	DC - 18	—	—	3.1	W
	Per Port as a combiner	DC - 18	—	—	1.5	

1. Tested on Mini-Circuits Test Board TB-EP4RKUC+
2. Measurements performed with one port energized and other ports terminated.

ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-55°C to +105°C
Storage temperature	-65°C to +150°C

Permanent damage may occur if any of these limits are exceeded.

PAD CONNECTIONS

Function	Pad Number
SUM PORT	21
PORT 1	14
PORT 2	10
PORT 3	31
PORT 4	27
GROUND	9,11,13,15,20,22,26,28,30,32 and Paddle
NOT USED, GROUND EXTERNALLY	1-8, 12, 16-19, 23-25, 29

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

SIMPLIFIED ELECTRICAL SCHEMATIC



Power Splitter/Combiner EP4RKU+


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data and Graphs	Data Table Swept Graphs S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1677-2 Plastic package, exposed paddle; lead finish: Matte Tin
Tape & Reel **Standard quantities available on reel**	F68 7" reels with 20, 50, 100, 200, 500 & 1000 devices
Suggested Layout for PCB Design	PL-649
Evaluation Board	TB-EP4RKU+ (Without connectors) TB-EP4RKUC+ (With connectors)
Environmental Ratings	ENV08T1

ESD RATING

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL TEST FLOW CHART



NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

4 Way-0° Power Splitter/Combiner

EP4RKU+

Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS[1] (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
100	10.09	10.07	10.09	10.10	0.03	0.13	13.17	12.39	13.18	1.84	1.10	1.10	1.10	1.10
200	10.08	10.05	10.08	10.09	0.04	0.13	13.22	12.36	13.22	1.83	1.11	1.11	1.11	1.11
300	10.09	10.04	10.08	10.10	0.06	0.20	13.28	12.29	13.29	1.82	1.13	1.13	1.13	1.13
400	10.07	10.03	10.07	10.08	0.06	0.26	13.40	12.23	13.42	1.79	1.16	1.17	1.16	1.16
500	10.08	10.03	10.08	10.10	0.07	0.28	13.51	12.15	13.52	1.79	1.19	1.19	1.19	1.19
600	10.10	10.04	10.10	10.12	0.08	0.29	13.65	12.07	13.66	1.79	1.22	1.22	1.22	1.22
700	10.12	10.05	10.11	10.13	0.09	0.39	13.82	11.99	13.83	1.79	1.25	1.26	1.25	1.25
800	10.13	10.06	10.12	10.15	0.09	0.45	14.01	11.91	14.02	1.78	1.29	1.29	1.28	1.28
900	10.16	10.07	10.14	10.17	0.10	0.45	14.22	11.82	14.23	1.77	1.32	1.32	1.31	1.32
1000	10.18	10.08	10.16	10.19	0.11	0.47	14.46	11.75	14.47	1.77	1.36	1.37	1.35	1.36
1500	10.29	10.18	10.29	10.31	0.13	0.65	15.86	11.44	15.89	1.78	1.56	1.55	1.56	1.56
2000	10.35	10.28	10.35	10.36	0.08	0.85	17.39	11.44	17.43	1.80	1.70	1.71	1.70	1.71
2500	10.36	10.27	10.38	10.37	0.12	1.02	18.60	11.73	18.65	1.81	1.77	1.81	1.77	1.77
3000	10.30	10.17	10.36	10.31	0.19	1.41	19.48	12.21	19.54	1.80	1.76	1.82	1.78	1.76
3500	10.15	10.05	10.21	10.16	0.17	1.94	20.25	12.81	20.29	1.78	1.70	1.77	1.72	1.69
4000	9.98	9.92	10.04	9.98	0.11	2.40	21.11	13.55	21.15	1.76	1.64	1.71	1.66	1.62
4500	9.85	9.76	9.89	9.86	0.13	2.92	22.07	14.40	22.10	1.75	1.57	1.62	1.60	1.57
5000	9.75	9.56	9.74	9.76	0.20	3.29	23.00	15.29	23.06	1.70	1.53	1.56	1.54	1.53
5500	9.67	9.41	9.61	9.67	0.27	3.41	23.92	16.25	23.98	1.65	1.51	1.53	1.50	1.52
6000	9.56	9.29	9.49	9.57	0.28	3.40	24.82	17.19	24.87	1.58	1.50	1.48	1.47	1.51
6500	9.45	9.20	9.39	9.47	0.27	3.53	25.85	17.98	25.94	1.49	1.48	1.46	1.45	1.51
7000	9.42	9.15	9.36	9.44	0.29	3.69	27.08	18.57	27.19	1.44	1.47	1.47	1.45	1.51
7500	9.44	9.15	9.39	9.47	0.32	3.91	28.24	19.19	28.34	1.38	1.48	1.48	1.47	1.52
8000	9.45	9.18	9.40	9.47	0.29	4.19	29.23	19.79	29.29	1.27	1.49	1.48	1.46	1.50
8500	9.47	9.21	9.42	9.47	0.27	4.38	30.08	20.19	30.18	1.12	1.51	1.48	1.43	1.47
9000	9.53	9.23	9.47	9.51	0.30	4.50	31.44	20.33	31.52	1.09	1.50	1.48	1.45	1.46
9500	9.56	9.23	9.51	9.53	0.33	4.75	33.70	20.46	33.84	1.17	1.46	1.43	1.42	1.43
10000	9.50	9.17	9.45	9.48	0.33	5.06	36.12	20.99	36.19	1.18	1.37	1.35	1.33	1.33
10500	9.40	9.09	9.36	9.38	0.31	5.32	35.30	21.86	35.43	1.12	1.25	1.24	1.25	1.24
11000	9.32	8.99	9.26	9.29	0.33	5.62	32.68	22.42	32.80	1.12	1.16	1.12	1.18	1.17
11500	9.31	8.95	9.23	9.28	0.36	5.85	31.45	22.48	31.57	1.27	1.15	1.09	1.11	1.13
12000	9.38	9.00	9.29	9.35	0.38	6.04	31.55	22.87	31.62	1.45	1.23	1.18	1.15	1.19
12500	9.44	9.08	9.36	9.41	0.36	6.23	31.86	24.37	31.92	1.54	1.30	1.28	1.23	1.26
13000	9.39	9.04	9.31	9.36	0.35	6.45	29.98	26.17	30.09	1.34	1.32	1.30	1.23	1.27
13500	9.36	9.02	9.29	9.34	0.34	6.71	27.35	25.72	27.46	1.09	1.31	1.26	1.21	1.26
14000	9.41	9.08	9.34	9.41	0.33	7.05	25.57	24.32	25.63	1.15	1.31	1.24	1.18	1.25
14500	9.42	9.10	9.34	9.46	0.36	7.35	24.76	23.67	24.84	1.19	1.26	1.22	1.15	1.22
15000	9.40	9.07	9.31	9.46	0.38	7.53	24.82	23.06	24.90	1.22	1.24	1.24	1.17	1.23
15500	9.36	9.08	9.27	9.44	0.36	7.75	25.21	21.08	25.29	1.28	1.26	1.26	1.20	1.24
16000	9.31	9.07	9.21	9.39	0.32	7.99	24.91	18.73	24.98	1.24	1.16	1.19	1.12	1.14
16500	9.46	9.14	9.33	9.53	0.38	8.20	24.11	17.32	24.16	1.29	1.08	1.15	1.08	1.10
17000	9.69	9.32	9.52	9.76	0.44	8.15	23.69	16.96	23.75	1.41	1.25	1.28	1.21	1.23
17500	9.72	9.41	9.58	9.82	0.41	8.44	23.99	17.29	24.07	1.28	1.37	1.39	1.31	1.33
18000	9.74	9.47	9.67	9.84	0.37	8.81	25.09	17.45	25.16	1.13	1.43	1.41	1.36	1.38

[1] Total Loss = Insertion Loss + 6dB Splitter Loss

Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = -55°C

FREQ. (MHz)	TOTAL LOSS[1] (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
100	10.03	10.02	10.02	10.04	0.02	0.08	13.10	12.40	13.06	1.84	1.10	1.10	1.10	1.10
200	10.02	10.00	10.00	10.03	0.03	0.08	13.14	12.35	13.11	1.83	1.11	1.11	1.12	1.11
300	10.02	9.99	10.00	10.03	0.04	0.14	13.19	12.25	13.16	1.83	1.13	1.14	1.14	1.13
400	10.00	9.96	9.97	10.00	0.04	0.24	13.30	12.20	13.29	1.81	1.17	1.17	1.16	1.17
500	10.01	9.95	9.98	10.02	0.06	0.24	13.41	12.10	13.38	1.81	1.20	1.19	1.20	1.20
600	10.02	9.95	9.99	10.03	0.07	0.23	13.53	12.01	13.51	1.82	1.23	1.23	1.23	1.23
700	10.02	9.95	9.99	10.03	0.08	0.34	13.70	11.91	13.67	1.81	1.26	1.27	1.25	1.26
800	10.03	9.96	10.00	10.04	0.07	0.38	13.88	11.82	13.87	1.81	1.29	1.30	1.28	1.29
900	10.05	9.97	10.01	10.05	0.08	0.37	14.08	11.72	14.06	1.80	1.33	1.33	1.32	1.33
1000	10.06	9.98	10.01	10.06	0.09	0.41	14.32	11.63	14.29	1.81	1.37	1.37	1.37	1.37
1500	10.12	10.04	10.09	10.13	0.09	0.67	15.70	11.29	15.67	1.81	1.56	1.57	1.57	1.57
2000	10.17	10.10	10.12	10.18	0.07	0.71	17.23	11.27	17.19	1.84	1.71	1.74	1.72	1.72
2500	10.17	10.08	10.15	10.18	0.10	0.88	18.45	11.52	18.42	1.87	1.78	1.83	1.81	1.79
3000	10.09	9.98	10.10	10.09	0.11	1.20	19.30	11.98	19.30	1.86	1.78	1.85	1.82	1.78
3500	9.91	9.83	9.92	9.91	0.09	1.58	20.04	12.55	20.02	1.83	1.71	1.80	1.75	1.70
4000	9.73	9.67	9.73	9.72	0.06	1.65	20.87	13.27	20.82	1.81	1.65	1.73	1.69	1.63
4500	9.57	9.50	9.56	9.57	0.07	1.97	21.86	14.08	21.81	1.80	1.58	1.65	1.63	1.58
5000	9.46	9.29	9.38	9.45	0.17	2.25	22.79	14.95	22.76	1.78	1.55	1.59	1.57	1.55
5500	9.36	9.11	9.24	9.35	0.25	2.23	23.65	15.91	23.60	1.73	1.53	1.56	1.53	1.54
6000	9.23	8.98	9.09	9.22	0.25	2.47	24.50	16.86	24.43	1.63	1.52	1.52	1.50	1.53
6500	9.08	8.86	8.95	9.08	0.23	2.81	25.47	17.65	25.41	1.52	1.48	1.48	1.47	1.51
7000	9.02	8.78	8.89	9.03	0.25	3.01	26.75	18.19	26.71	1.48	1.47	1.48	1.46	1.51
7500	9.03	8.76	8.91	9.04	0.28	3.52	27.96	18.78	27.93	1.42	1.48	1.49	1.48	1.52
8000	9.03	8.77	8.90	9.03	0.26	4.08	28.87	19.40	28.83	1.31	1.50	1.50	1.47	1.50
8500	9.03	8.78	8.89	9.00	0.24	4.34	29.62	19.84	29.55	1.13	1.52	1.51	1.46	1.48
9000	9.06	8.80	8.93	9.03	0.25	4.41	30.92	19.92	30.82	1.09	1.52	1.51	1.48	1.48
9500	9.08	8.80	8.96	9.04	0.28	4.71	33.24	19.99	33.08	1.19	1.48	1.47	1.46	1.45
10000	9.01	8.72	8.88	8.97	0.29	5.11	35.91	20.50	35.97	1.21	1.39	1.37	1.37	1.36
10500	8.89	8.62	8.76	8.85	0.27	5.44	35.15	21.36	35.33	1.15	1.27	1.26	1.28	1.26
11000	8.78	8.50	8.64	8.73	0.28	5.62	32.52	21.94	32.58	1.12	1.16	1.13	1.19	1.18
11500	8.74	8.43	8.58	8.68	0.31	5.91	31.15	21.98	31.11	1.26	1.14	1.09	1.10	1.11
12000	8.79	8.47	8.63	8.74	0.32	6.27	31.18	22.25	31.13	1.49	1.23	1.18	1.16	1.19
12500	8.85	8.53	8.68	8.80	0.32	6.67	31.64	23.69	31.62	1.62	1.32	1.29	1.25	1.28
13000	8.79	8.48	8.61	8.73	0.31	6.96	29.85	25.63	29.89	1.44	1.35	1.32	1.26	1.29
13500	8.73	8.43	8.57	8.69	0.29	7.14	27.13	25.39	27.11	1.12	1.34	1.28	1.24	1.28
14000	8.77	8.48	8.60	8.74	0.29	7.40	25.18	23.89	25.10	1.16	1.33	1.26	1.20	1.27
14500	8.76	8.49	8.59	8.76	0.28	7.68	24.25	23.16	24.15	1.22	1.28	1.24	1.16	1.24
15000	8.72	8.44	8.53	8.74	0.30	8.18	24.27	22.73	24.16	1.24	1.26	1.26	1.17	1.24
15500	8.66	8.43	8.47	8.70	0.27	8.81	24.73	20.83	24.60	1.32	1.28	1.30	1.21	1.27
16000	8.58	8.40	8.38	8.62	0.24	8.75	24.45	18.34	24.31	1.27	1.20	1.23	1.16	1.17
16500	8.69	8.45	8.48	8.73	0.28	8.60	23.58	16.78	23.43	1.30	1.10	1.16	1.08	1.10
17000	8.93	8.61	8.67	8.99	0.38	9.40	23.06	16.29	22.90	1.47	1.25	1.30	1.24	1.24
17500	8.95	8.70	8.70	9.03	0.33	10.31	23.28	16.57	23.11	1.35	1.39	1.42	1.34	1.34
18000	8.92	8.71	8.73	8.99	0.28	10.81	24.27	16.71	24.05	1.14	1.46	1.44	1.38	1.39


[1] Total Loss = Insertion Loss + 6dB Splitter Loss


TEST CONDITIONS: Input Power = -10dBm @Temperature = +105°C


FREQ. (MHz)	TOTAL LOSS[1] (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
100	10.09	10.08	10.08	10.09	0.02	0.07	13.17	12.37	13.18	1.84	1.10	1.10	1.10	1.10
200	10.07	10.04	10.08	10.07	0.03	0.13	13.24	12.33	13.23	1.83	1.11	1.11	1.11	1.11
300	10.07	10.03	10.08	10.08	0.05	0.17	13.29	12.27	13.29	1.82	1.13	1.13	1.13	1.13
400	10.05	10.01	10.07	10.06	0.05	0.21	13.41	12.22	13.41	1.80	1.16	1.16	1.16	1.16
500	10.06	10.02	10.09	10.08	0.06	0.20	13.51	12.13	13.51	1.79	1.18	1.19	1.18	1.18
600	10.07	10.03	10.10	10.09	0.07	0.25	13.65	12.06	13.66	1.79	1.22	1.22	1.21	1.22
700	10.09	10.04	10.11	10.10	0.07	0.33	13.81	11.98	13.82	1.79	1.25	1.26	1.24	1.24
800	10.11	10.05	10.13	10.12	0.08	0.40	14.01	11.89	14.01	1.78	1.28	1.29	1.27	1.28
900	10.14	10.06	10.15	10.15	0.09	0.44	14.22	11.81	14.22	1.77	1.32	1.32	1.31	1.32
1000	10.16	10.07	10.17	10.17	0.10	0.46	14.46	11.74	14.46	1.78	1.36	1.36	1.35	1.36
1500	10.28	10.19	10.31	10.29	0.11	0.64	15.88	11.44	15.89	1.78	1.56	1.55	1.56	1.56
2000	10.33	10.30	10.37	10.35	0.07	0.82	17.40	11.44	17.43	1.81	1.70	1.71	1.70	1.71
2500	10.34	10.29	10.41	10.35	0.13	1.09	18.60	11.73	18.63	1.81	1.76	1.81	1.77	1.77
3000	10.29	10.19	10.39	10.30	0.20	1.51	19.48	12.22	19.50	1.80	1.75	1.83	1.78	1.76
3500	10.15	10.08	10.26	10.15	0.18	2.06	20.27	12.82	20.29	1.78	1.70	1.77	1.71	1.69
4000	9.97	9.97	10.09	9.97	0.12	2.59	21.13	13.57	21.14	1.77	1.63	1.72	1.65	1.62
4500	9.85	9.80	9.95	9.84	0.14	3.20	22.06	14.42	22.08	1.75	1.56	1.63	1.60	1.57
5000	9.75	9.60	9.80	9.75	0.20	3.62	23.00	15.32	23.01	1.70	1.53	1.57	1.53	1.53
5500	9.66	9.46	9.67	9.66	0.22	3.79	23.95	16.28	23.97	1.65	1.51	1.53	1.49	1.51
6000	9.56	9.36	9.56	9.56	0.20	3.87	24.89	17.24	24.89	1.58	1.49	1.48	1.46	1.51
6500	9.46	9.27	9.46	9.47	0.21	4.02	25.90	18.04	25.96	1.50	1.48	1.46	1.45	1.51
7000	9.44	9.23	9.45	9.46	0.23	4.20	27.14	18.63	27.18	1.45	1.47	1.47	1.44	1.51
7500	9.46	9.24	9.49	9.47	0.25	4.50	28.31	19.24	28.35	1.38	1.48	1.49	1.47	1.52
8000	9.47	9.27	9.50	9.48	0.23	4.81	29.32	19.84	29.36	1.26	1.49	1.49	1.45	1.50
8500	9.50	9.31	9.53	9.49	0.22	5.07	30.21	20.24	30.25	1.11	1.51	1.49	1.43	1.47
9000	9.55	9.33	9.58	9.53	0.25	5.26	31.57	20.40	31.65	1.09	1.49	1.48	1.44	1.46
9500	9.58	9.33	9.62	9.55	0.30	5.52	33.84	20.55	33.87	1.17	1.45	1.43	1.41	1.43
10000	9.52	9.29	9.57	9.49	0.29	5.90	36.07	21.10	36.20	1.18	1.36	1.34	1.32	1.33
10500	9.42	9.21	9.48	9.40	0.27	6.30	35.09	21.94	35.13	1.11	1.25	1.24	1.24	1.23
11000	9.34	9.11	9.40	9.31	0.29	6.65	32.66	22.49	32.66	1.13	1.16	1.12	1.17	1.17
11500	9.34	9.08	9.37	9.30	0.29	7.00	31.49	22.57	31.52	1.28	1.16	1.10	1.11	1.13
12000	9.41	9.14	9.44	9.38	0.30	7.21	31.64	22.99	31.65	1.47	1.24	1.18	1.15	1.19
12500	9.48	9.23	9.51	9.44	0.28	7.52	31.82	24.52	31.80	1.53	1.30	1.28	1.23	1.26
13000	9.43	9.19	9.46	9.39	0.27	7.86	29.94	26.29	29.92	1.32	1.32	1.30	1.23	1.27
13500	9.41	9.18	9.46	9.39	0.28	8.22	27.40	25.79	27.37	1.09	1.31	1.26	1.20	1.26
14000	9.46	9.24	9.50	9.46	0.26	8.57	25.64	24.43	25.66	1.16	1.30	1.24	1.18	1.25
14500	9.48	9.27	9.52	9.50	0.25	8.93	24.87	23.80	24.94	1.19	1.25	1.22	1.15	1.22
15000	9.46	9.25	9.50	9.50	0.25	9.23	24.96	23.13	25.04	1.22	1.24	1.24	1.17	1.24
15500	9.43	9.26	9.46	9.49	0.23	9.60	25.30	21.12	25.35	1.29	1.25	1.26	1.19	1.24
16000	9.40	9.26	9.42	9.46	0.20	9.99	24.97	18.81	24.99	1.24	1.15	1.18	1.12	1.13
16500	9.55	9.35	9.54	9.61	0.26	10.25	24.21	17.45	24.21	1.30	1.09	1.16	1.08	1.11
17000	9.77	9.53	9.72	9.84	0.31	10.26	23.83	17.14	23.86	1.41	1.26	1.29	1.20	1.24
17500	9.81	9.61	9.79	9.90	0.29	10.07	24.17	17.45	24.23	1.26	1.38	1.38	1.30	1.33
18000	9.85	9.71	9.90	9.94	0.24	10.14	25.33	17.60	25.39	1.14	1.43	1.41	1.35	1.38


[1] Total Loss = Insertion Loss + 6dB Splitter Loss


Typical Performance Curves

















Typical Performance Curves









DG1677-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C MAX	C MIN	D	E	F	G	H	J
DG1677-2	.197 (5.00)	.197 (5.00)	.039 (1.00)	.031 (0.80)	.008 (0.20)	.142 (3.60)	.142 (3.60)	.009 (0.23)	- -	.016 (0.40)

CASE #	K	L	M	N	P	Q	R	S	WT. GRAM
DG1677-2	.020 (0.50)	.193 (4.90)	.193 (4.90)	.110 (2.79)	.012 (0.30)	.035 (0.89)	.110 (2.79)	.008 (0.20)	.05

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:


1. Case material: Plastic.
4. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier transitioning to Matte-Tin. All models, (+) suffix. See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf


Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M175739	NEW RELEASE	09/10/19	ITG	CM

SUGGESTED MOUNTING CONFIGURATION FOR DG1677-2 CASE STYLE



NOTES:

1. TRACE WIDTH & GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	08/28/19
TOLERANCES ON:	CHECKED	GF	09/03/19
2 PL DECIMALS ±	APPROVED	CM	09/10/19
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235


PL, DG1677-2, TB-EP4RKU+/EP4KA+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-649	OR

FILE:	SCALE:	SHEET:
98PL649	10:1	1 OF 1

Evaluation Board and Circuit





SCHEMATIC DIAGRAM
(SCALE 5:1)


Notes:


1. PCB Material: Roger RO4350B or equivalent, Dielectric constant=3.5, Thickness=0.010 inch

Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Evaluation Board and Circuit





DETAIL "A"
(SCALE 5:1)



SCHEMATIC DIAGRAM
(SCALE 5:1)

Notes:

1. 2.92mm Female Connectors.
2. PCB Material: Roger RO4350B or equivalent, Dielectric constant=3.5, Thickness=0.010 inch

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications **ENV08T1**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.