

2 Way-90° 50Ω

5 to 11 GHz

## The Big Deal

- Wideband (5-11 GHz)
- Good Isolation and Return Loss
- Highly repeatable performance (GaAs based design)
- No external termination required
- High power handling (>30dBm)
- Small Size MCLP 4x4mm



CASE STYLE: DG1847

## Product Overview

Mini-Circuits' EPQ-113+ is a wideband 5-11 GHz, 90° hybrid. It splits an input signal into two output signals with quadrature phase shift between them. It provides low loss, wideband in a small layout size and handles high power with good VSWR.

## Key Features

Feature	Advantages
Small Size	The EPQ-113+ offers an industry leading combination of size, bandwidth and frequency. The small footprint (4mm x 4 mm) allows for reduced parasitics in systems with improved performance and simplified layout.
Low Phase and Amplitude Unbalance	3.7 deg. and 0.8 dB unbalance make this 90° hybrid applicable for use in higher level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers.
High Power Handling	Capable of operating up to 32 dBm, MMIC structure of EPQ-113+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths.

MMIC Surface Mount

# Power Splitter/Combiner

EPQ-113+

2 Way-90° 50Ω

5 to 11 GHz

## Features

- Low insertion loss, 0.6 dB typ. at 7-9 GHz
- Good isolation, 19 dB typ. at 7-9 GHz
- Miniature size, 4x4 mm
- High power handling (>30 dBm)



Generic photo used for illustration purposes only

CASE STYLE: DG1847

## Applications

- Balanced amplifiers
- Modulators
- Attenuator
- Point to Point
- Military

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5000		11000	MHz
Insertion Loss, (Avg. of Mainline & Coupled) above 3dB	5000 - 6000	—	0.5	1.1	dB
	6000 - 7000	—	0.6	1.2	
	7000 - 9000	—	0.6	1.4	
	9000 - 10000	—	0.7	1.5	
	10000 - 11000	—	0.8	1.8	
Isolation	5000 - 6000	16	19	—	dB
	6000 - 7000	16	19	—	
	7000 - 9000	16	19	—	
	9000 - 10000	16	19	—	
	10000 - 11000	14	18	—	
Amplitude Unbalance	5000 - 6000	—	0.4	1.4	dB
	6000 - 7000	—	0.4	1.2	
	7000 - 9000	—	0.8	1.5	
	9000 - 10000	—	0.7	1.4	
	10000 - 11000	—	0.2	1.1	
Phase Unbalance (Deviation from 90°)	5000 - 6000	—	1.9	6.6	Degree
	6000 - 7000	—	2.4	7.6	
	7000 - 9000	—	3.7	8.8	
	9000 - 10000	—	4.1	9.7	
	10000 - 11000	—	4.2	—	
Input VSWR	5000 - 6000	—	1.2	—	:1
	6000 - 7000	—	1.2	—	
	7000 - 9000	—	1.2	—	
	9000 - 10000	—	1.2	—	
	10000 - 11000	—	1.3	—	
Output VSWR (0°&90°)	5000 - 6000	—	1.2	—	:1
	6000 - 7000	—	1.2	—	
	7000 - 9000	—	1.1	—	
	9000 - 10000	—	1.1	—	
	10000 - 11000	—	1.2	—	

## Maximum Ratings


Parameter	Ratings
Operating Temperature	-45°C to 85°C
Storage Temperature	-65°C to 150°C
Power Input (as a splitter)	32 dBm (5 minute max.) 30 dBm (continuous)
Internal Dissipation	30 dBm

Permanent damage may occur if any of these limits are exceeded.

## Pad Connections

Function	Pad Number
SUM PORT	1
PORT 1 (0°)	9
PORT 2 (+90°)	22
NC	2-8, 10-21,23,24

## Simplified Electrical Schematic





\* ESD rating

Human body model (HBM): Class 1A(250 to <500 V) in accordance with ANSI/ESD 5.1-2007

 **Mini-Circuits®**

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


**Outline Drawing****PCB Land Pattern****Product Marking**

Suggested Layout,  
Tolerance to be within  $\pm .002$

**Outline Dimensions (inch mm)**

A	B	C	D	E	F	G	H	J
.157	.157	.039	.008	.104	.104	.009	--	.016
4.0	4.0	1.0	0.20	2.64	2.64	0.23	--	0.41
K	L	M	N	P	Q	R	wt	
.020	.166	.166	.102	.012	.020	.102	grams	
0.50	4.22	4.22	2.59	0.30	0.51	2.59		0.04


**Demo Board MCL P/N: TB-961-113+**  
**Suggested PCB Layout (PL-520)**

**NOTES:**

- TRACE WIDTH AND GAP PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ±.001; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

**Tape and Reel (F68)**

DEVICE ORIENTATION IN T&R







Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
			20	50
12	8	7	Small quantity standard	100
			200	500
		7	Standard	1000
		13	Standard	2000
			3000	4000

## Typical Performance Data

Frequency (MHz)	Total Loss <sup>1</sup> (dB)	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
S-1	S-2						
5000	3.07	3.84	0.8	20.45	90.1	1.20	1.11
5500	3.33	3.62	0.3	19.82	90.0	1.23	1.13
6000	3.54	3.45	0.1	19.28	90.2	1.25	1.15
6500	3.71	3.33	0.4	18.89	90.4	1.23	1.15
7000	3.84	3.25	0.6	18.61	90.7	1.22	1.16
7500	3.96	3.19	0.8	18.57	91.1	1.21	1.14
8000	4.02	3.15	0.9	18.75	91.5	1.18	1.12
8500	4.05	3.13	0.9	18.98	91.8	1.17	1.08
9000	4.04	3.14	0.9	19.29	92.2	1.17	1.04
9500	3.98	3.21	0.8	19.40	92.2	1.14	1.03
10000	3.91	3.33	0.6	19.05	92.1	1.18	1.05
11000	3.65	3.91	0.3	17.60	91.8	1.25	1.16

1. Total Loss = Insertion Loss + 3dB splitter loss.



## Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# 2 Way-90° Power Splitter

EPQ-113+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10 dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS <sup>(1)</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
5000	3.10	3.85	0.75	88.72	19.87	1.22	1.11	1.27
5200	3.20	3.73	0.54	88.64	19.71	1.22	1.13	1.26
5400	3.30	3.66	0.36	88.69	19.64	1.23	1.13	1.26
5600	3.40	3.58	0.18	88.57	19.23	1.26	1.15	1.29
5800	3.47	3.51	0.04	88.69	19.30	1.24	1.15	1.26
6000	3.56	3.47	0.10	88.72	19.10	1.25	1.17	1.23
6200	3.66	3.42	0.24	88.78	19.11	1.25	1.16	1.22
6400	3.74	3.39	0.35	88.91	19.22	1.24	1.15	1.18
6600	3.78	3.34	0.45	88.81	19.31	1.23	1.16	1.21
6800	3.81	3.28	0.53	89.15	19.38	1.20	1.13	1.16
7000	3.86	3.25	0.62	89.13	19.23	1.22	1.15	1.15
7200	3.89	3.21	0.69	89.29	19.23	1.19	1.12	1.13
7400	3.93	3.19	0.74	89.35	19.33	1.18	1.11	1.11
7600	3.97	3.17	0.80	89.44	19.15	1.19	1.11	1.08
7800	3.99	3.15	0.84	89.50	19.24	1.16	1.06	1.09
8000	4.02	3.16	0.86	89.64	19.08	1.19	1.11	1.02
8200	4.07	3.17	0.90	89.60	19.01	1.20	1.06	1.11
8400	4.05	3.18	0.87	89.63	18.84	1.18	1.07	1.07
8600	4.06	3.19	0.87	89.69	18.74	1.18	1.06	1.07
8800	4.04	3.19	0.85	89.74	18.96	1.13	1.02	1.03
9000	4.06	3.24	0.82	89.80	18.52	1.20	1.06	1.07
9200	4.03	3.25	0.78	89.78	18.65	1.15	1.01	1.05
9400	4.03	3.29	0.74	89.90	18.49	1.18	1.01	1.09
9600	3.99	3.34	0.66	89.76	18.39	1.18	1.04	1.09
9800	3.96	3.39	0.57	89.66	18.31	1.17	1.03	1.13
10000	3.90	3.44	0.46	89.89	18.19	1.18	1.05	1.05
10200	3.88	3.50	0.38	89.80	18.23	1.19	1.06	1.13
10400	3.83	3.59	0.23	89.55	18.03	1.21	1.06	1.15
10600	3.75	3.70	0.04	89.63	17.86	1.21	1.10	1.13
10800	3.70	3.78	0.07	89.86	17.80	1.22	1.10	1.11
11000	3.65	3.92	0.27	89.55	17.71	1.23	1.14	1.15

<sup>(1)</sup>Total Loss = Insertion Loss + 3dB Splitter Loss



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR  
EPQ-113+  
10/11/2017  
Page 1 of 3

# 2 Way-90° Power Splitter

EPQ-113+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10 dBm @Temperature = -45 °C

FREQ. (MHz)	TOTAL LOSS <sup>(1)</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
5000	2.74	3.53	0.79	91.68	19.03	1.25	1.19	1.29
5200	2.82	3.38	0.56	91.75	19.57	1.20	1.18	1.23
5400	2.92	3.33	0.41	91.91	19.16	1.29	1.23	1.23
5600	3.00	3.23	0.23	91.88	18.88	1.31	1.22	1.27
5800	3.03	3.13	0.09	92.28	19.75	1.22	1.20	1.21
6000	3.12	3.06	0.06	92.46	19.57	1.27	1.17	1.20
6200	3.17	2.97	0.19	92.69	19.96	1.22	1.09	1.23
6400	3.24	2.92	0.32	92.83	20.06	1.21	1.11	1.21
6600	3.31	2.89	0.42	93.21	19.98	1.28	1.05	1.25
6800	3.36	2.82	0.54	93.41	20.15	1.19	1.05	1.23
7000	3.43	2.80	0.63	93.48	19.31	1.28	1.02	1.26
7200	3.45	2.74	0.71	93.75	19.34	1.24	1.06	1.25
7400	3.49	2.71	0.77	93.74	18.40	1.24	1.11	1.24
7600	3.54	2.72	0.81	93.79	17.73	1.33	1.10	1.22
7800	3.53	2.69	0.84	94.06	18.24	1.21	1.23	1.22
8000	3.59	2.73	0.86	94.27	16.96	1.37	1.22	1.12
8200	3.61	2.75	0.86	94.65	17.02	1.38	1.30	1.10
8400	3.61	2.76	0.84	94.90	16.96	1.38	1.29	1.05
8600	3.58	2.73	0.85	95.15	17.48	1.31	1.23	1.02
8800	3.59	2.73	0.85	95.75	17.94	1.28	1.26	1.09
9000	3.63	2.78	0.85	95.61	17.15	1.42	1.22	1.10
9200	3.55	2.67	0.88	96.26	18.74	1.15	1.20	1.09
9400	3.49	2.66	0.83	95.73	19.22	1.13	1.09	1.08
9600	3.47	2.72	0.75	95.72	18.33	1.23	1.05	1.10
9800	3.39	2.69	0.70	95.91	20.65	1.05	1.18	1.03
10000	3.35	2.72	0.63	95.83	20.60	1.01	1.18	1.11
10200	3.31	2.78	0.53	95.69	19.25	1.20	1.16	1.21
10400	3.22	2.85	0.37	95.56	19.04	1.12	1.18	1.23
10600	3.20	2.96	0.24	95.37	18.89	1.14	1.20	1.27
10800	3.14	3.08	0.06	95.62	17.45	1.31	1.14	1.21
11000	3.10	3.29	0.19	95.09	16.84	1.33	1.30	1.49

(1)Total Loss = Insertion Loss + 3dB Splitter Loss



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR  
EPQ-113+  
10/11/2017  
Page 2 of 3

# 2 Way-90° Power Splitter

EPQ-113+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @Temperature = +85 °C

FREQ. (MHz)	TOTAL LOSS <sup>(1)</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
5000	3.37	4.08	0.71	84.71	20.13	1.23	1.09	1.24
5200	3.48	3.98	0.50	84.50	19.96	1.22	1.11	1.27
5400	3.58	3.89	0.31	84.36	19.90	1.22	1.07	1.26
5600	3.69	3.82	0.13	84.17	19.60	1.25	1.13	1.27
5800	3.78	3.76	0.02	84.01	19.57	1.22	1.13	1.28
6000	3.88	3.71	0.17	83.90	19.09	1.24	1.14	1.24
6200	3.98	3.68	0.29	83.78	19.18	1.24	1.21	1.21
6400	4.03	3.64	0.39	83.75	19.07	1.22	1.15	1.19
6600	4.12	3.61	0.51	83.56	18.95	1.23	1.19	1.18
6800	4.16	3.60	0.56	83.54	19.25	1.20	1.24	1.13
7000	4.23	3.57	0.66	83.58	19.18	1.20	1.18	1.10
7200	4.28	3.55	0.73	83.57	19.31	1.19	1.20	1.07
7400	4.33	3.56	0.77	83.43	19.81	1.16	1.19	1.06
7600	4.37	3.51	0.86	83.48	19.78	1.14	1.09	1.02
7800	4.42	3.52	0.90	83.22	20.31	1.11	1.16	1.01
8000	4.45	3.52	0.93	83.36	20.22	1.12	1.07	1.06
8200	4.50	3.50	1.00	82.86	20.38	1.13	1.13	1.13
8400	4.49	3.55	0.94	82.73	20.70	1.13	1.13	1.09
8600	4.51	3.54	0.97	82.47	19.61	1.14	1.09	1.11
8800	4.50	3.57	0.93	82.18	19.88	1.17	1.18	1.14
9000	4.49	3.62	0.87	82.21	19.70	1.14	1.03	1.14
9200	4.49	3.64	0.86	81.25	18.88	1.16	1.20	1.14
9400	4.46	3.74	0.72	82.00	18.41	1.23	1.05	1.14
9600	4.44	3.78	0.65	81.45	18.59	1.17	1.15	1.14
9800	4.40	3.87	0.53	81.28	17.67	1.26	1.05	1.13
10000	4.36	3.98	0.39	81.57	17.30	1.29	1.20	1.12
10200	4.37	4.05	0.32	81.21	17.41	1.32	1.20	1.12
10400	4.33	4.16	0.17	81.40	17.10	1.36	1.15	1.06
10600	4.26	4.30	0.04	80.97	17.08	1.35	1.28	1.10
10800	4.24	4.38	0.14	81.47	17.21	1.36	1.11	1.14
11000	4.25	4.57	0.33	81.41	16.83	1.49	1.24	1.12

(1)Total Loss = Insertion Loss + 3dB Splitter Loss



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS







REV. OR  
EPQ-113+  
10/11/2017  
Page 3 of 3

# 2 Way-90° Power Splitter

EPQ-113+


## Typical Performance Curves




# 2 Way-90° Power Splitter

EPQ-113+

## Typical Performance Curves



## Outline Dimensions



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm .002$

**Weight: .04 Grams**

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin.  
All models, (+) suffix. See model Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

ALL NEW  
[minicircuits.com](http://minicircuits.com)

# Tape & Reel Packaging TR-F68

## DEVICE ORIENTATION IN T&R



## DIRECTION OF FEED



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20 50 100 200
			500	500
			Standard	1000
			Standard	2000
		13	Standard	3000
			Standard	4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M162448	NEW RELEASE	07/19/17	CA	RS

SUGGESTED MOUNTING CONFIGURATION FOR  
DG1847 CASE STYLE, "24SP06" PIN CONNECTION

NOTES:

1. TRACE WIDTH AND GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ±001; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN CA 07/07/17

CHECKED GF 07/12/17

APPROVED RS 07/19/17



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235



PL, 24SP06, DG1847, TB-961-133+

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
 EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
 AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
 DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
 THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
 PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEET1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-520	OR
FILE: 98PL520	SCALE: 8:1	SHEET: 1 OF 1	

# Evaluation Board and Circuit



PINS 2-8,10-21,23,24 – NOT CONNECTED INTERNALLY  
(GROUNDED ON PCB)

## Schematic Diagram

### Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®



## Environmental Specifications

## ENV08T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C or -40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	