

MMIC

# Power Splitter/Combiner Die

EPQ-133-D+

2 Way-90° 50Ω 6 to 14 GHz

## The Big Deal

- Wideband, 6 to 14 GHz
- Good Isolation and Return Loss
- Highly repeatable performance (GaAs based design)
- No external termination required
- High Power handling (>30 dBm)



## Product Overview

Mini-Circuits' EPQ-133-D+ is a wideband 6-14 GHz , 90° hybrid die . It splits an input signal into two output signals with quadrature phase shift between them. It provides low loss, wideband in a small layout size and handles high power with good VSWR.

## Key Features

Feature	Advantages
Low Phase and Amplitude Unbalance	3.4 deg. and 0.5 dB unbalance make this 90° hybrid applicable for use in higher level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers.
High Power Handling	Capable of operating up to 32 dBm, MMIC structure of EPQ-133-D+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths.
Unpackaged Die	Enables user to integrate it directly into hybrids.



MMIC

# Power Splitter/Combiner Die

## EPQ-133-D+

2 Way-90° 50Ω 6 to 14 GHz

### Features

- Low insertion loss, 0.6 dB typ. at 8-10 GHz
- Good isolation, 20 dB typ. at 8-10 GHz
- High Power

### Applications

- Balanced amplifiers
- Modulators
- Electronic variable attenuator
- Phase shifter




**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

**Ordering Information: Refer to Last Page**

### General Description

Mini-Circuits' EPQ-133-D+ is a wideband 6-14 GHz , 90° hybrid die . It splits an input signal into two output signals with quadrature phase shift between them. It provides low loss, wideband in a small layout size and handles high power with good VSWR.

### Simplified Schematic and Pad Description



Pad#	Function
1	Sum Port
2	Port 1 (0°)
3	Port 2 (+90°)

Note: 1. Bond Pad material - Gold  
 2. Bottom of Die - Gold plated

### Bonding Pad Position



Dimensions in  $\mu\text{m}$ , Typical

L1	L2	L3	H1	H2	H3	H4	Thickness	Bond Pad Size
84	2566	2650	42	948	1078	1120	100	80 x 175



**Electrical Specifications<sup>1</sup> at 25°C, 50Ω**

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		6000		14000	MHz
Insertion Loss, (Avg. of Mainline & Coupled) above 3dB	6000 - 8000		0.6		dB
	8000 - 10000		0.6		
	10000 - 12000		0.8		
	12000 - 14000		1.0		
Isolation	6000 - 8000		20		dB
	8000 - 10000		20		
	10000 - 12000		18		
	12000 - 14000		16		
Amplitude Unbalance	6000 - 8000		0.5		dB
	8000 - 10000		0.5		
	10000 - 12000		0.6		
	12000 - 14000		0.4		
Phase Unbalance (Deviation from 90°)	6000 - 8000		2.9		Degree
	8000 - 10000		3.4		
	10000 - 12000		4.1		
	12000 - 14000		4.4		
Input VSWR	6000 - 8000		1.2		:1
	8000 - 10000		1.2		
	10000 - 12000		1.4		
	12000 - 14000		1.6		
Output VSWR (0°&90°)	6000 - 8000		1.2		:1
	8000 - 10000		1.1		
	10000 - 12000		1.3		
	12000 - 14000		1.5		


1. Measured on Mini-Circuits Die Characterization Test Board. Die packaged in 4x4 mm, 24-lead MCLP package and soldered in TB-961-133+.

**Maximum Ratings**

Parameter	Ratings
Operating Temperature	-45°C to 85°C
Power Input (as a splitter) <sup>1</sup>	32 dBm
Internal Dissipation <sup>1</sup>	30 dBm

Permanent damage may occur if any of these limits are exceeded.

## Assembly Diagram



## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The Die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total Die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic Die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the Die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

<b>Additional Detailed Technical Information</b> <i>additional information is available on our dash board.</i>		
<b>Performance Data</b>	Data Table	
	Swept Graphs	
	S-Parameter (S3P Files) Data Set with and without port extension(.zip file)	
<b>Case Style</b>	Die	
<b>Die Ordering and packaging information (Note 5)</b>	Quantity, Package Small, Gel - Pak: 5,10, 50, KGD* Medium†, Partial wafer: 350 Max. Large†, Full wafer	Model No. EPQ-133-DG+ EPQ-133-DP+ EPQ-133-DF+
	†Available upon request contact sales representative Refer to <a href="#">AN-60-067</a>	
<b>Environmental Ratings</b>	ENV-80	

\*Known Good Dice ("KGD") means that the dice are taken from PCM good wafer and are visually inspected. While this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits."

## ESD Rating\*\*

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard, 4x4mm, 24-lead MCLP package.

### Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, Die preparation, Die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



# 2 Way-90° Power Splitter/Combiner Die EPQ-133-D+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10 dBm @Temperature = +25°C

FREQ. (GHz)	TOTAL LOSS <sup>(1)</sup> (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
3.0	1.25	7.30	6.05	90.51	25.98	1.09	1.08	1.02
3.5	1.54	6.37	4.83	90.61	24.21	1.10	1.06	1.04
4.0	1.84	5.65	3.80	90.69	22.53	1.13	1.02	1.09
4.5	2.14	5.08	2.93	90.73	21.57	1.16	1.05	1.13
5.0	2.43	4.64	2.21	90.72	20.92	1.20	1.09	1.16
5.5	2.71	4.29	1.59	90.80	20.18	1.24	1.10	1.19
6.0	2.96	4.01	1.05	90.86	19.89	1.26	1.16	1.20
6.5	3.18	3.81	0.63	90.91	19.90	1.27	1.18	1.21
7.0	3.38	3.63	0.25	90.99	19.62	1.27	1.17	1.23
7.5	3.53	3.50	0.04	91.08	19.75	1.24	1.19	1.24
8.0	3.64	3.38	0.26	91.35	20.31	1.17	1.17	1.22
8.5	3.73	3.29	0.44	91.67	20.32	1.13	1.16	1.20
9.0	3.81	3.23	0.58	91.98	20.02	1.13	1.16	1.16
9.5	3.86	3.17	0.70	92.43	19.91	1.12	1.12	1.10
10.0	3.92	3.15	0.77	92.54	19.17	1.18	1.12	1.02
10.5	4.00	3.17	0.83	92.57	17.85	1.31	1.11	1.09
11.0	4.10	3.33	0.78	92.80	16.48	1.46	1.19	1.19
11.5	4.17	3.49	0.68	92.61	15.80	1.58	1.29	1.23
12.0	4.24	3.72	0.52	92.45	15.04	1.72	1.40	1.24
12.5	4.26	4.00	0.26	92.30	14.45	1.86	1.58	1.18
13.0	4.08	4.15	0.06	92.48	14.41	1.81	1.56	1.08
13.5	3.75	4.19	0.44	92.68	15.86	1.52	1.53	1.17
14.0	3.54	4.45	0.91	93.75	16.08	1.49	1.46	1.31
14.5	3.32	4.66	1.34	94.49	17.23	1.35	1.39	1.47
15.0	3.12	5.01	1.88	95.38	17.68	1.30	1.29	1.55
15.5	2.95	5.38	2.43	96.32	18.54	1.22	1.26	1.57
16.0	2.76	5.80	3.04	96.73	18.98	1.17	1.19	1.50

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss

Note: Data tested in industry standard, 4x4mm, 24-lead MCLP package



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site








The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
EPQ-133-D+  
2/28/2018  
Page 1 of 1

## Typical Performance Curves



Note: Data tested in industry standard, 4x4mm, 24-lead MCLP package



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment	20° to 35° C and 40 to 60% humidity (In Factory Shipped Package)	Individual Model Data Sheet