



Mini-Circuits®



Test Cable

CBL-6FT-SMNM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male

FEATURES

- Wideband coverage, DC to 18 GHz
- Extra rugged construction with strain relief for longer life
- Stainless steel connectors for long mating-cycle life
- Useful over temperature range, -55°C to +105°C
- Triple shield cable for excellent shielding effectiveness
- Flexible for easy connection & bend radius
- Superior stability of insertion loss, VSWR & phase vs. flexing
- 6 month guarantee*

*Generic photo used for illustration purposes only*

Model No.	CBL-6FT-SMNM+
Case Style	GM1105-6
Connectors	SMA-Male to N-Male

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- High volume production test stations
- Research & development labs
- Environmental & temperature test chambers
- Replacement for OEM test port cables
- Field RF testing
- Cellular infrastructure site testing

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency range		DC		18	GHz
Length ¹		6			FT
Insertion Loss	DC - 2.5	—	1.2	1.4	dB
	2.5 - 6	—	2.0	2.35	
	6 - 12	—	3.0	3.55	
	12 - 18	—	3.8	4.44	
Return Loss	DC - 2.5	23	30	—	dB
	2.5 - 6	20	30	—	
	6 - 12	17	27	—	
	12 - 18	17	22	—	

1. Custom sizes available, consult factory.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
Shielding Effectiveness	>100 dB
Power Handling at 25°C	891W Max. at 0.4 GHz
	539W Max. at 1 GHz
	363W Max. at 2 GHz
	180W Max. at 6 GHz
	117W Max. at 12 GHz
	88W Max. at 18 GHz

Product Guarantee*

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.





Mini-Circuits




Test Cable


CBL-6FT-SMNM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male

CABLE CONSTRUCTION



OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch mm)

A		B	C	D	E	T		wt
Feet	Meters					Feet	Meters	grams
6	1.83	0.42	0.312	0.88	.750	0.18	0.05	173
		10.67	7.92	22.35	19.05			





Mini-Circuits





Test Cable

CBL-6FT-SMNM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		SMA-Male	SMA-Male
50.00	0.16	64.77	47.86
100.00	0.22	49.15	51.38
1000.00	0.72	31.81	31.75
2000.00	1.03	28.95	28.91
2500.00	1.18	36.62	36.19
4000.00	1.54	38.15	35.38
5000.00	1.74	38.97	36.05
6000.00	1.94	40.85	28.69
7000.00	2.09	28.84	32.34
8000.00	2.26	28.21	35.97
9000.00	2.43	24.28	29.74
12000.00	2.88	25.22	26.87
14000.00	3.24	26.88	30.04
15000.00	3.35	28.22	30.07
18000.00	3.67	23.02	28.77





Test Cable, SMA-Male/N-Male

CBL-6FT-SMNM+


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
50	0.16	64.77	47.86
100	0.22	49.15	51.38
300	0.39	37.24	39.99
500	0.51	44.92	45.64
700	0.60	34.45	34.91
900	0.68	35.44	35.00
1000	0.72	31.81	31.75
1300	0.85	30.25	30.02
1500	0.89	40.94	39.35
1700	0.97	31.19	30.78
1900	1.02	30.78	29.98
2000	1.03	28.95	28.91
2300	1.12	29.11	28.41
2500	1.18	36.62	36.19
2700	1.18	31.34	31.13
2900	1.26	33.07	29.76
3000	1.32	30.16	27.58
3500	1.45	33.77	38.70
4000	1.54	38.15	35.38
4500	1.62	34.12	44.95
5000	1.74	38.97	36.05
5500	1.85	38.22	48.23
6000	1.94	40.85	28.69
6500	2.02	37.84	29.71
7000	2.09	28.84	32.34
7500	2.16	32.58	26.91
8000	2.26	28.21	35.97
8500	2.35	27.88	29.70
9000	2.43	24.28	29.74
9500	2.54	28.33	32.58
10000	2.68	25.39	23.31
11000	2.82	33.76	29.13
12000	2.88	25.22	26.87
13000	3.00	25.43	26.03
14000	3.24	26.88	30.04
15000	3.35	28.22	30.07
16000	3.49	24.74	21.87
17000	3.58	21.21	27.60
18000	3.67	23.02	28.77

Typical Performance Curves



Outline Dimensions



GM1105 SERIES
SMA MALE (CONN-1)
N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
GM1105-1	1.00	.30	0.42 (10.67)	0.312 (7.92)	0.88 (22.35)	0.750 (19.05)	.06	.02	76
GM1105-1.15	1.15	.35					.06	.02	79
GM1105-1.25	1.25	.38					.06	.02	81
GM1105-1.5	1.50	.46					.06	.02	86
GM1105-1.64	1.64	.50					.06	.02	88
GM1105-2	2.00	.61					.06	.02	95
GM1105-3	3.00	.91					.09	.03	115
GM1105-3.28	3.28	1.00					.10	.03	120
GM1105-4	4.00	1.22					.12	.04	134
GM1105-4.92	4.92	1.50					.15	.05	152
GM1105-5	5.00	1.52					.15	.05	154
GM1105-6	6.00	1.83					.18	.05	173
GM1105-6.56	6.56	2.00					.20	.06	184
GM1105-7	7.00	2.13					.21	.06	193
GM1105-8	8.00	2.44					.24	.07	212
GM1105-9	9.00	2.74					.27	.08	232
GM1105-9.84	9.84	3.00					.30	.09	248
GM1105-10	10.00	3.05					.30	.09	251
GM1105-11	11.00	3.35					.33	.10	271

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

1. Flexible Coaxial Cable.
2. $+ .51$ [13.00], -0 [0]

Case Style

GM

GM1105 SERIES

SMA MALE (CONN-1)

N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
GM1105-12	12.00	3.66	0.42 (10.67)	0.312 (7.92)	0.88 (22.35)	0.750 (19.05)	.36	.11	290
GM1105-13.1	13.12	4.00					.39	.12	312
GM1105-14	14.00	4.27					.42	.13	329
GM1105-15	15.00	4.57					.45	.14	349
GM1105-16	16.00	4.88					.48	.15	368
GM1105-21	21.00	6.40					.63	.19	466
GM1105-22	22.00	6.71					.66	.20	485
GM1105-25	25.00	7.62					.75	.23	544
GM1105-35	35.00	10.67					1.05	.32	739
GM1105-39.4	39.37	12.00					1.18	.36	824
GM1105-40	40.00	12.19					1.20	.37	836

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 105°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -105°C
Mechanical Flexing	20,000 cycles During each cycle, cable flexed from 90° through 0° to -90° and back with a Radii of 3 inches	- - -