



Mini-Circuits

COAXIAL

Phase-Stable Flex Cables

CBN-xx-NMNM+

50Ω DC to 18 GHz N-Male to N-Male

KEY FEATURES

- Exceptional Phase & Amplitude Stability
- Extremely Flexible
- Low Loss Dielectric
- Broadband

APPLICATIONS

- Test & Measurement
- High-Speed Data Systems
- Instrumentation
- Precision Measurement
- High-Volume Production Test
- R&D Labs & Device Characterization
- Circuit Level Breadboarding
- Equipment Rack & Stack Interconnects
- Tight & Limited Spacing Applications



Generic photo used for illustration purposes only

PRODUCT OVERVIEW

The CBN series is designed to achieve extreme flexibility while carrying on the Mini-Circuits commitment to quality, consistency, performance, and value. By largely eliminating flex resistance as well as spring-back, the CBN design has greatly simplified difficult routing challenges and still maintains improved attenuation and unparalleled RF insertion phase stability.

Whether your application is packaged device characterization on the bench, circuit-level breadboarding, the interconnection of RF equipment in a lab or production environment, or deliverable products where space limitations exist, CBN is the correct choice when extreme flexibility and RF stability is of primary concern.

The CBN-XX-NMNM+ N-Male to N-Male cable family is ideal for interconnecting coaxial components and subassemblies in a wide range of systems, including test and measurement, instrumentation, and more. The CBN cable provides excellent phase and amplitude stability as well as flexibility. These cables are presently available at 1-6 feet long; for custom lengths, please contact the Mini-Circuits Sales Department.



COAXIAL

Phase-Stable Flex Cables

CBN-xx-NMNM+

50Ω DC to 18 GHz N-Male to N-Male

ELECTRICAL SPECIFICATIONS¹

Operation Frequency (GHz)	18
Impedance (Ω)	50
Velocity of Propagation (%)	74
Shielding Effectiveness (dB)	90
Voltage Withstand Min. (V.DC)	500
Bending Phase ² Max. (deg.)	±6 ° @ 18 GHz
Return Loss Typ. [VSWR]	33.3 dB [1.05:1]
Return Loss Max. [VSWR]	17.5 dB [1.30:1]


1. Permanent damage may occur if any of these limits are exceeded

2. Phase & Amplitude stability specs guaranteed from 18-inch cable lengths. For cables shorter than 18 inches, no degradation in performance is expected.

MECHANICAL & ENVIRONMENTAL SPECIFICATIONS¹

Operating Case Temperature ³	-40 °C to +85 °C
Storage Temperature	-40 °C to +85 °C
Bend Radius: Installation (mm) [in]	16 [0.64]
Bend Radius: Repeated (mm) [in]	50 [1.97]
Weight (g/m) [lbs/1000ft] @ A < 0.61 M	(50 + 88)*A ± 15 [(33.57 + 59.1)*A ± 10.1]
Weight (g/m) [lbs/1000ft] @ A < 0.61 M	(50 + 90)*A ± 15 [(33.57 + 60.5)*A ± 10.1]

3. Occasional use only.



Attenuation (Typical @ 25 °C & VSWR = 1.0) dB

Frequency (MHz)	1000	2000	3000	4000	6000	8000	10000	12000	14000	18000
dB / 100 m	38.51	55.94	69.90	82.07	103.30	121.99	139.06	154.98	170.03	198.17
dB / 100 ft	11.75	17.07	21.33	25.04	31.52	37.22	42.43	47.29	51.88	60.46

$$\text{Calculate Attenuation} = K1 * \sqrt{FMHz} + K2 * FMHz + 0.02 * \sqrt{FGHz} \text{ dB}$$

dB / 100 m	K1 =	1.1370000	K2 =	0.0025300
dB / 100 ft	K1 =	0.3465576	K2 =	0.0007711

Power (VSWR = 1.0; @ 40 °C; Sea Level) W

Frequency (MHz)	1000	2000	3000	4000	6000	8000	10000	12000	14000	18000	20000
Avg. Power (kW)	0.473	0.362	0.261	0.222	0.176	0.149	0.131	0.118	0.107	0.092	0.086





Mini-Circuits

COAXIAL

Phase-Stable Flex Cables


CBN-xx-NMNM+

50Ω DC to 18 GHz N-Male to N-Male


COAXIAL CONNECTIONS

Description	Connector 1	Connector 2
Connector Type	N-Type Male	N-Type Male
Orientation	Straight	Straight

CABLE CONSTRUCTION



CASE STYLE DRAWING



Unless Otherwise Specified dimensions are in inches [mm],
 Tolerances: 2 Pl.±0.03; 3 Pl.±0.015 inches

A		B	C1	C2	D	E1	E2	F	T		Wt. grams
Feet	Meters								Feet	Meters	
1.00	0.30	.88 (22.35)	.748 (19.00)	-	.88 (22.35)	.748 (19.00)	-	.205 (5.20)	+.04/-0	+.01/-0	103.0
3.00	0.91								+.06/-0	+.02/-0	135.5
6.00	1.83								+.12/-0	+.04/-0	181.5
15.00	4.57								+.30/-0	+.09/-0	318.5

PRODUCT MARKING*: CBN-XX-NMNM+

*Marking may contain other features or characters for internal lot control.





Mini-Circuits

COAXIAL

Phase-Stable Flex Cables

CBN-xx-NMNM+

50Ω DC to 18 GHz N-Male to N-Male

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	GM3735
RoHS Status	Compliant
Environmental Ratings	ENV149

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html





Phase-Stable Flexible Cable N-Type Male to N-Type Male

CBN-1FT-NMNM+

Typical Performance Data

FREQ.	INSERTION LOSS	N-TYPE MALE RETURN LOSS IN	N-TYPE MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.02	45.51	43.18
1	0.13	43.98	50.90
2	0.19	33.07	33.19
3	0.22	44.38	41.87
4	0.25	39.39	37.46
5	0.30	31.28	28.87
6	0.31	32.57	38.01
7	0.33	30.13	30.76
8	0.31	28.40	27.31
9	0.31	29.06	28.58
10	0.29	34.74	31.45
11	0.29	35.80	37.91
12	0.31	30.65	28.53
13	0.33	31.42	30.86
14	0.29	36.86	25.73
15	0.31	27.05	25.55
16	0.38	21.26	22.47
17	0.30	30.47	31.03
18	0.30	34.25	33.43

Typical Performance Curves




Case Style

GM

Outline Dimensions

GM3735



CASE#	A		B	C1	C2	D	E1	E2	F	T		WEIGHT (GRAMS)
	FEET	METERS								FEET	METERS	
GM3735-1	1.00	0.30	.88 (22.35)	.748 (19.00)	-	.88 (22.35)	.748 (19.00)	-	.205 (5.20)	+.04/-0	+.01/-0	103.0
GM3735-3	3.00	0.91								+.06/-0	+.02/-0	135.5
GM3735-6	6.00	1.83								+.12/-0	+.04/-0	181.5
GM3735-15	15.00	4.57								+.30/-0	+.09/-0	318.5

Unless Otherwise Specified dimensions are in inches [mm],
Tolerances: 2 Pl.±0.03; 3 Pl. ±0.015 inches

- Notes:
- "A" Represents Length of Cable.
 - * Overall Connector Dimension
[Connector Shape May Vary]

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-45° to 85°C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-45° to 85°C, 100 cycles	MIL-STD-202; Method 107G
Mechanical Flexing	1000 cycles During each cycle, cable flexed in U-shape up to 90 degrees	----
Connector Durability	500 mating cycles	MIL-PRF-39012E, PARAGRAPH 4.6.12
Connector Retention	Force: 60 lb. Min.; Torque: Cable connector turned while held 6 inches from end; Stop at 9 in-lb. or 90-degree twist.	---
Heat-Aging Stability	There are no cracks, defects, or other damage to the surface material of the sample.	MIL-C-17G Para. 4.8.18
Cold Bend	There are no cracks, defects, or other damage to the surface material of the sample.	MIL-C-17G Para. 4.8.19